



LUNKENHEIMER FIGURE 605 COMBINATION VALVE

DN 80 - 600 (NPS 3 - 24) ASME CLASS 150

The F605 combination valve is a three way diverting valve specifically designed for severe service in alumina applications where scale and erosion are present.



GENERAL APPLICATION

Designed and engineered specifically for use in the alumina industry for bypass applications. Services include all slurry and liquor applications.

TECHNICAL DATA

Size range: DN 80 - 600 (NPS 3 - 24)
Temperature rating: Up to 345°C (650°F)
Pressure rating: ASME Class 150

FEATURES

- Valves can be reground in-line.
- Designed to ASME B16.34
- Heavy duty wall and flange thickness well in excess of ASME B16.34 and ASME B16.5
- Pads for fitting drain ports.
- Tested to API 598.
- Large stem diameters for strength and stiffness.
- Stellite 6 hardfacing as standard on disc and seat surfaces.
- Hard facing available on stem.
- Roller or plain bearings fitted to yoke bush - depending upon size.
- Manufactured under quality system ISO 9001:2008, Certificate No. MEL 0929678/A
- Documentation to EN 10424 1999 Type 3.1B (DIN 50409).
Material certification for pressure containing components.

Options

- Range of internal linings available to combat the effects of erosion or corrosion.
- High performance erosion resistant discs and seats.
- Custom face to face dimensions.
- Custom designs for specific applications.


Actuation options

- Spur gear operation standard on larger sizes.
- Bevel gear operators.
- Patented stem clutch design for easy grind set-up.
- Customized actuation design.
- Range of actuation available including:
 - Electric
 - Pneumatic
 - Hydraulic
 - All with regrounding where required.



LUNKENHEIMER FIGURE 605 COMBINATION VALVE

DN 80 - 350 (NPS 3 - 14) ASME CLASS 150



PARTS LIST


No.	Description	Material standards
010	Body	ASTM A216 - WCB
030	Yoke	ASTM A216 - WCB
050	Seat	ASTM A29 - 1020, 1518 or ASTM A105 - Stellite coated
060	Disc	ASTM A29 - 1020, 1518 or ASTM A105 - Stellite coated
080	Stem	ASTM A29 - 4140
090	Yoke bush	ASTM A29 - 1020
100	Yoke bush locknut	ASTM A29 - 1020
110	Yoke bush handle	ASTM A29 - 1020 or ASTM A216 WCB
120	Bearing - yoke bush	Bronze
130	Retaining cap	ASTM A29 - 1020
220	Gland follower	ASTM A29 - 1020 or ASTM A216 WCB
230	Stem jam nut	ASTM A29 - 1020 or ASTM A216 WCB
240	Stem handle	ASTM A29 - 1020 or ASTM A216 WCB
260	Torque reactor hub	ASTM A29 - 1020
270	Torque reactor pin	ASTM A29 - 1020

NOTE

No bolts, washers or gaskets included in parts list.

LUNKENHEIMER FIGURE 605 COMBINATION VALVE

DN 150 - 600 (NPS 6 - 24) ASME CLASS 150



PARTS LIST

No.	Description	Material standards
010	Body	ASTM A216 - WCB
030	Yoke	ASTM A216 - WCB
050	Seat	ASTM A29 - 1020, 1518 or ASTM A105 - Stellite coated
060	Disc	ASTM A29 - 1020, 1518 or ASTM A105 - Stellite coated
080	Stem	ASTM A29 - 4140
090	Yoke bush	ASTM A29 - 1020
100	Yoke bush locknut	ASTM A29 - 1020
120	Bearing - yoke bush	Steel Roller
130	Retaining cap	ASTM A29 - 1020
140	Bearing - retaining cap	Bronze
160	Gear	ASTM A29 - 1020
170	Pinion gear	ASTM A29 - 1020
180	Pinion shaft	ASTM A29 - 4140
220	Gland follower	ASTM A29 - 1020 or ASTM A216 WCB
230	Stem jam nut	ASTM A29 - 1020 or ASTM A216 WCB
260	Torque reactor hub	ASTM A29 - 1020
270	Torque reactor pin	ASTM A29 - 1020


NOTES

No bolts, washers or gaskets included in parts list.

Bevel gear operation option available.

LUNKENHEIMER FIGURE 605 COMBINATION VALVE

DN 80 - 350 (NPS 3 - 14) ASME CLASS 150



DIMENSIONS mm (inches)


Valve size											
DN (NPS)	$\varnothing A$ bore	$\varnothing B$	C open	C1 closed	D	E	$\varnothing F$	H	$\varnothing M$	$\varnothing P$	N
80 (3)	76 (3.00)	191 (7.50)	429 (16.89)	375 (14.76)	137 (5.39)	140 (5.51)	203 (7.99)	79 (3.11)	51 (2.01)	191 (7.52)	38 (1.50)
100 (4)	102 (4.00)	229 (9.00)	632 (24.88)	530 (20.87)	222 (8.74)	165 (6.50)	305 (12.01)	122 (4.80)	76 (2.99)	229 (9.02)	46 (1.81)
150 (6)	152 (6.00)	279 (11.00)	810 (31.89)	683 (26.89)	289 (11.38)	203 (7.99)	406 (15.98)	154 (6.06)	121 (4.76)	279 (10.98)	52 (2.05)
200 (8)	203 (8.00)	343 (13.50)	892 (35.12)	740 (29.13)	359 (14.13)	248 (9.76)	406 (15.98)	191 (7.52)	171 (6.73)	343 (13.50)	52 (2.05)
250 (10)	254 (10.00)	406 (16.00)	1156 (45.51)	953 (37.52)	452 (17.80)	292 (11.50)	508 (20.00)	240 (9.45)	216 (8.50)	406 (15.98)	57 (2.24)
300 (12)	305 (12.00)	483 (19.00)	1251 (49.25)	1010 (39.76)	522 (20.55)	349 (13.74)	508 (20.00)	276 (10.87)	267 (10.51)	483 (19.02)	64 (2.52)
350 (14)	337 (13.25)	533 (21.00)	1510 (59.45)	1230 (48.43)	576 (22.68)	368 (14.49)	610 (24.02)	305 (12.01)	298 (11.73)	533 (20.98)	70 (2.76)

NOTE

Dimension E is from the valve center to the flange raised face.

LUNKENHEIMER FIGURE 605 COMBINATION VALVE

DN 150 - 600 (NPS 6 - 24) ASME CLASS 150



DIMENSIONS mm (inches)

Valve size													
DN (NPS)	ØA bore	ØB	C open	C1 closed	D	E	F	F1	H	J (A/F)	ØM bore	ØP	N
150 (6)	152 (6.00)	279 (11.00)	810 (31.89)	683 (26.89)	289 (11.38)	203 (7.99)	285 (11.22)	185 (7.28)	154 (6.06)	60 (2.36)	121 (4.76)	279 (10.98)	52 (2.05)
200 (8)	203 (8.00)	343 (13.50)	892 (35.12)	740 (29.13)	359 (14.13)	248 (9.76)	285 (11.22)	185 (7.28)	191 (7.52)	60 (2.36)	171 (6.73)	343 (13.50)	52 (2.05)
250 (10)	254 (10.00)	406 (16.00)	1156 (45.51)	953 (37.52)	452 (17.80)	292 (11.50)	285 (11.22)	185 (7.28)	240 (9.45)	60 (2.36)	216 (8.50)	406 (15.98)	57 (2.24)
300 (12)	305 (12.00)	483 (19.00)	1251 (49.25)	1010 (39.76)	522 (20.55)	349 (13.74)	345 (13.58)	225 (8.86)	276 (10.87)	60 (2.36)	267 (10.51)	483 (19.02)	64 (2.52)
350 (14)	337 (13.25)	533 (21.00)	1510 (59.45)	1230 (48.43)	576 (22.68)	368 (14.49)	345 (13.58)	225 (8.86)	305 (12.01)	60 (2.36)	298 (11.73)	533 (20.98)	70 (2.76)
400 (16)	387 (15.25)	597 (23.50)	1648 (64.88)	1356 (53.39)	638 (25.12)	381 (15.00)	345 (13.58)	225 (8.86)	340 (13.39)	60 (2.36)	343 (13.50)	597 (23.50)	73 (2.87)
450 (18)	438 (17.25)	635 (25.00)	1661 (65.39)	1368 (53.86)	667 (26.26)	406 (15.98)	345 (13.58)	225 (8.86)	356 (14.02)	60 (2.36)	387 (15.24)	635 (25.00)	83 (3.27)
500 (20)	489 (19.25)	699 (27.50)	1835 (72.24)	1518 (59.76)	740 (29.13)	457 (17.99)	415 (16.34)	315 (12.40)	394 (15.51)	60 (2.36)	425 (16.73)	699 (27.52)	86 (3.39)
600 (24)	591 (23.25)	813 (32.00)	2000 (78.74)	1626 (64.02)	864 (34.02)	508 (20.00)	415 (16.34)	315 (12.40)	451 (17.76)	60 (2.36)	521 (20.51)	813 (32.01)	95 (3.74)


NOTE

Dimension E is from the valve center to the flange raised face.

LUNKENHEIMER FIGURE 605 COMBINATION VALVE

DN 80 - 600 (NPS 3 - 24) ASME CLASS 150

PRESSURE/TEMPERATURE GRAPH



PRESSURE/TEMPERATURE RATINGS

NOTES

1. The pressure temperature ratings displayed are for carbon steel ASTM A 216 Gr WCB according to ASME B16.5 Table 2.
2. Upper temperature is set by standard gland packing.
3. Customer requested changes to gland packing may affect the temperature ratings of the valve.

- PTFE braided packing
- Reinforced graphite packing

TYPICAL SPECIFYING SEQUENCE

100 (4)	F605	3	3	C	3	3	3	3	3	/	00
Valve size	Figure no.	Flange rating	Flange rating	Body material	Seat trim	Disc trim	Stem trim	Certification code	Valve variant	Standard option	

Size range: DN 80 - 600 (NPS 3 - 24)

Figure no: F605 - Combination valve ASME Class 150

Trim code	Flange rating	Flange rating	Body material	Seat trim	Disc trim	Stem trim
11C334	Class 150	Class 150	A 216 Gr WCB	Steel - stellite	Steel - stellite	Grade ASTM A29 - 4140 - Stellite coated
11C353	Class 150	Class 150	A 216 Gr WCB	Steel - stellite	Steel	Grade ASTM A29 - 4140
33C333	Class 300	Class 300	A 216 Gr WCB	Steel - stellite	Steel - stellite	Grade ASTM A29 - 4140
66C334	Class 600	Class 600	A 216 Gr WCB	Steel - stellite	Steel - stellite	Grade ASTM A29 - 4140 - Stellite coated