




ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES

Weight or spring loaded valves capable of providing pressure and vacuum relief that vent to atmosphere. Designed and tested to reduce costs and emissions with higher flow capacities and industry leading conformity to API 2000.



FEATURES

- Increased flow capacities reduce the required valve size and the corresponding connections and piping costs.
- Fully open at 10% overpressure, enabling setting close to MAWP/MAWW and minimizing tank emissions.
- Large body for increased capacity providing high flow performance for full conformance to API2000/ISO28300.
- Leakage rate of 0.5 scfh (0.015 Nm³ /hr) or less at 90% of setpoint.
- Weight or spring loaded models available.
- Choice of body materials.
- Modular design enables all components to be removed and replaced in-situ for quicker, simpler maintenance.
- Optional 'all-weather' coating prevents frozen condensate build-up and sticking of vital components in cold weather applications.

GENERAL APPLICATION

Type 4020 valves allow tanks to work closer to their MAWP thus increasing productivity, reducing emissions and product evaporation. Increased flow capacities reduce the valve's size, corresponding connections and piping costs in applications for storage tank farms, oil and gas production, the petroleum, pharmaceutical and chemical sectors.

TECHNICAL DATA

Materials:	Aluminum, carbon steel, stainless steel
Sizes:	NPS 2 to 12 (DN 50 to 300)
Pressure settings	
Weight loaded:	up to 1.5 psig (100 mbarg)
Spring loaded:	up to 15 psig (1 barg)
Vacuum settings	
Weight loaded:	up to -1.5 psig (-100 mbarg)
Spring loaded:	up to -15 psig (-1 barg)
Certification:	ATEX 94/9 EC

ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES

MODELS OVERVIEW

Type 4020 valves are high capacity, full lift pressure and vacuum relief valves designed for use on atmospheric and low pressure storage tanks. Their primary function is to protect the tank from physical damage or permanent deformation caused by increases in internal pressure or vacuum encountered in normal operations. On smaller tanks, the valves may also provide sufficient flow capacity for emergency venting.

The valves are fully open at 10% overpressure allowing the user to have a quicker acting valve that can be set closer to the tank's maximum allowable working pressure, reducing emission losses. There are four vent-to-atmosphere model variants:

Model 4020H offers weight-loaded pressure and vacuum relief.

Model 4020HP spring-loaded pressure and weight-loaded vacuum relief.

Model 4020HC spring-loaded pressure and vacuum relief.

Model 4020HV weight-loaded pressure and spring-loaded vacuum relief.

APPLICATION

By controlling tank venting, Type 4020 pressure/vacuum valves not only minimize emissions to the environment but also the loss of product to evaporation. Their 'air-cushion' seating design keeps the valve sealed tightly until the pressure inside the tank approaches the valve setting. The larger body allows for greater vacuum capacity in accordance with the most recent versions of tank vents sizing standards (API 2000/ISO 28300).

They offer the option of a non-frosting and icing-resistant coating on the pallet perimeter, stem, guide posts and seats which, along with the flexible PTFE seat insert, provides additional protection against pallets freezing closed.

TESTING

Each valve is tested for proper setting, for a leakage rate of less than 0.5 SCFH (0.015 Nm³/hr) of air at 90% of the set point and for leak tightness at 75% of set point as required in API standard 2000.

SPECIFICATIONS

Available materials

- Aluminum with aluminum or stainless steel trim
- Carbon steel with stainless steel trim
- Stainless steel with stainless steel trim
- Special materials on application

Sizes

- NPS 2 (DN 50)
- NPS 3 (DN 80)
- NPS 4 (DN 100)
- NPS 6 (DN 150)
- NPS 8 (DN 200)
- NPS 10 (DN 250)
- NPS 12 (DN 300)

Flanged connections –standard flange drilling

Aluminum body

- Drilled to ANSI Class 150 dimensions (flat face)
- Drilled to DIN 2633 [PN 16] dimensions (flat face)


CS and SS body

- Drilled to ANSI Class 150 dimensions (raised or flat face)
- Drilled to Imperial DIN 2633 [PN 16] dimensions (raised or flat face)


Options

- PTFE coated trim to minimize ice buildup
- Stainless steel weights
- Steam jackets
- Proximity sensors to monitor valve opening and closing

Weight loaded




Model 4020H




Model 4020HP

Spring loaded



Model 4020HC




Mode 4020 HV

ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES

DIMENSIONS (mm)

MODEL 4020H


Size		A	B	C	D
NPS	DN				
2	50	344	160	99	381
3	80	431	200	130	458
4	100	509	235	157	511
6	150	708	320	227	689
8	200	913	405	302	869
10	250	1123	500	375	1018
12	300	1325	590	447	1164



Model 4020H

MODEL 4020HP


Size		A	B	C	D
NPS	DN				
2	50	344	160	99	502
3	80	431	200	130	579
4	100	509	235	157	646
6	150	708	320	227	916
8	200	913	405	302	1174
10	250	1123	500	375	1428
12	300	1325	590	447	1665



Model 4020HP

MODEL 4020HC


Size		A	B	C	D
NPS	DN				
2	50	344	160	99	502
3	80	431	200	130	579
4	100	509	235	157	646
6	150	708	320	227	916
8	200	913	405	302	1174
10	250	1123	500	375	1428
12	300	1325	590	447	1665



Model 4020HC

MODEL 4020HV

Size		A	B	C	D
NPS	DN				
2	50	344	160	99	502
3	80	431	200	130	579
4	100	509	235	157	646
6	150	708	320	227	916
8	200	913	405	302	1174
10	250	1123	500	375	1428
12	300	1325	590	447	1665



Model 4020HV

ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES

SIZING

API 2000 - valve sizing (air)

Once the required air venting rates have been determined using data from the following pages or supplied by the customer, a calculation should be conducted to determine the required valve discharge area using the formula below. Once this area has been determined, select the first standard valve flow area above this.

Metric units:

$$A = \frac{R F_o}{12515 \times (P_{10} + At) \times K_{d_o} \times F_o} \sqrt{\frac{K}{M \times T \times Z \times (K-1)} \left[\left(\frac{P_2 + At}{P_{10} + At} \right)^{\frac{2}{K}} - \left(\frac{P_2 + At}{P_{10} + At} \right)^{\frac{K+1}{K}} \right]}$$

Where:

VR	=	Air venting requirements	Nm ³ /h Air
A	=	Required flow area of valve	cm ²
Kd	=	Coefficient of discharge (see page 9)	
P ₁	=	Inlet flowing pressure (Set + over pressure – inlet pressure loss)*	Barg
P ₂	=	Outlet pressure (Back pressure)	Barg
K	=	Ratio of specific heats	Air = 1.4
T	=	Temperature at valve inlet	273 deg K
M	=	Molecular weight	Air = 28.97
Z	=	Compressibility factor	Air = 1.0
At	=	Atmospheric pressure	1.013 bar
F	=	Over pressure factor (Use 1 for Type 4020 valves)	

* The inlet pressure loss is due to factors such as difficult inlet piping, flame arresters, etc. and must be less than overpressure.

ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES

SIZING

TABLE OF FLOW COEFFICIENTS (Kd) - MODEL 4020H

Size		Flow area (cm ²)	API connection		Conical reducer	
NPS	DN		Pressure	Vacuum	Pressure	Vacuum
2	50	21.239	0.857	0.593	1.000	0.813
3	80	46.568	0.857	0.593	1.000	0.800
4	100	83.322	0.857	0.593	1.000	0.765
6	150	186.264	0.857	0.593	1.000	0.724
8	200	326.851	0.826	0.523	1.000	0.680
10	200	510.702	0.710	0.515	1.000	0.675
12	300	730.747	0.737	0.502	0.914	0.649

MINIMUM SET PRESSURES – WEIGHT LOADED

Size		Aluminum			Stainless steel		
NPS	DN	V mbarg	L mbarg	H mbarg	V mbarg	L mbarg	H mbarg
2	50	1.04	2.42	4.87	2.38	5.91	9.70
3	80	0.84	1.74	4.36	1.84	3.98	8.46
4	100	0.90	1.64	4.48	1.93	3.63	8.90
6	150	0.96	1.60	6.33	1.92	3.90	13.37
8	200	1.10	1.30	13.00	2.50	3.80	20.00
10	250	1.10	1.20	14.00	2.50	3.50	22.00
12	300	1.10	1.20	14.00	2.50	3.20	24.00

NOTE

V = very low pressure pallet

L = low pressure pallet

H = high pressure pallet

MINIMUM SET PRESSURES – SPRING LOADED

Size		Aluminum				Stainless steel			
NPS	DN	V mbarg	L mbarg	H mbarg	Spring mbarg	V mbarg	L mbarg	H mbarg	Spring mbarg
2	50	1.04	2.42	4.87	N/A	2.38	5.91	9.70	70
3	80	0.84	1.74	4.36	N/A	1.84	3.98	8.46	70
4	100	0.90	1.64	4.48	N/A	1.93	3.63	8.90	70
6	150	0.96	1.60	6.33	N/A	1.92	3.90	13.37	70
8	200	1.10	1.30	13.00	N/A	2.50	3.80	20.00	70
10	250	1.10	1.20	14.00	N/A	2.50	3.50	22.00	70
12	300	1.10	1.20	14.00	N/A	2.50	3.20	24.00	70

NOTE

V = very low pressure pallet

L = low pressure pallet


H = high pressure pallet

ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES

FLOW CAPACITIES


API 2000 connection

API connection testing requires a square-edge flange connection for capacity publishing. This setup mimics a typical tank connection with its inherent pressure drop/capacity.




PRESSURE PERFORMANCE

Model 4020H/4020HV
(ISO/API connection)



Model 4020HP/4020HC
(ISO/API connection)



ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES



FLOW CAPACITIES

API 2000 connection


API connection testing requires a square-edge flange connection for capacity publishing. This setup mimics a typical tank connection with its inherent pressure drop/capacity.

VACUUM PERFORMANCE

Model 4020H/4020HP
(ISO/API connection)



Model 4020HC/4020HV
(ISO/API connection)




ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES

FLOW CAPACITIES


Conical reducer

A conical reducer reduces the flow losses associated with the tank connection, providing the more accurate representation of pure valve performance. With this capacity, users can calculate their own tank connection losses and apply it to the valve flow.




PRESSURE PERFORMANCE

Model 4020H/4020HV
(Conical reducer)



Model 4020HP/4020HC
(Conical reducer)



ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES



FLOW CAPACITIES

Conical reducer


A conical reducer reduces the flow losses associated with the tank connection, providing the more accurate representation of pure valve performance. With this capacity, users can calculate their own tank connection losses and apply it to the valve flow.

VACUUM PERFORMANCE

Model 4020H/4020HP
(Conical reducer)



Model 4020HC/4020HV
(Conical reducer)



ANDERSON GREENWOOD TYPE 4020 ATMOSPHERIC PRESSURE AND VACUUM RELIEF VALVES

SELECTION GUIDE

Example:	4020H	04	H	H	1	1	S	T	F	F	B	N
Model												
4020H												
4020HP												
4020HC												
4020HV												
Tank connection												
02 2"	04 4"	08 8"	12 12"									
03 3"	06 6"	10 10"										
Pressure load												
V Weight loaded – very low pressure pallet												
L Weight loaded – low pressure pallet												
H Weight loaded – high pressure pallet												
X Spring loaded												
O Not applicable												
Vacuum load												
V Weight loaded – very low pressure pallet												
L Weight loaded – low pressure pallet												
H Weight loaded – high pressure pallet												
X Spring loaded												
O Not applicable												
Body material												
1 Aluminum												
3 Carbon steel												
5 316 Stainless steel (CF8M)												
7 316L Stainless steel (CF3M)												
Trim (pallet/seat)												
1 AL pallets/AL seat												
2 316SS pallets/316SS seat												
3 316LSS pallets/316LSS seat												
4 316SS press pallet, coated AL vac pallet, SS seat												
All-weather code												
S Standard, no coating												
W Polytetrafluoroethylene (PTFE) coated winterization												
Insert												
T Carbon impregnated PTFE (standard for HP pallet)												
B PFA (standard for VLP and LP pallet)												
V Fluorocarbon (FKM)												
Flange drilling												
F ANSI 150 for imperial studs												
O DIN PN10 for metric studs												
6 DIN PN16 for metric studs												
Flange face												
F Flat face												
R Raised face (not available for aluminum bodies)												
Soft Goods												
B Nitrile (NBR) (standard)												
T PTFE												
V FKM												
Options												
N None (standard)	S Stainless steel weights	B Proximity switch (Press side)										
A Proximity switch (Vac side)	H Purge holes	J Steam jackets										

VCTDS-03735-EN © 2017, 2023 Emerson Electric Co. All rights reserved 12/23. Anderson Greenwood is a mark owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Electric Co. does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Emerson Electric Co. product remains solely with the purchaser.

Emerson.com