# VALVE JTOMATION

# ASCO™ Direct Mount Inline Spool Valves

Pilot Operated | Direct NAMUR Mount | 1/4" - 1/2" NPT

### **Features**

- Compact spool valve convertible from 3/2 to 5/2 with a single flow plate design (551 Series only)
- NAMUR mount construction
- Standard manual operator
- DIN, Watertight and Explosionproof solenoids available
- Single and dual solenoid constructions
- Mountable in any position
- Vents air from spring side of actuator to prevent corrosion of actuator

### Construction

Valve Parts in Contact with Fluids					
Body	Black Anodized Aluminum				
Spring	Phosphate treated black steel				
Shading Coil	Copper				
Seals	NBR + PUR				
Core and Core Tube	Stainless Steel / Brass				
End Covers and Plate	6/6 glass filled PA/FV				
Spool	Aluminum				
Internal Parts	Zamak, Steel, CA				

# **Electrical**

Standard Coil and		W		g and Pov Imption	Spare Coil Part Number		
Class of Insulation	Enclosure Type	DC Watts	AC Watts	VA Holding	VA Inrush	AC	DC
F	SC	3	2.5	3.5	6	400127	400127
F	SC	6.9	5	7	15	400727	400727
F	EF	6.9	6.3	7	10.1	266762	270007
F	WT	6.9	6.3	7	10.1	266763	270008

Standard Voltages: SC: 24, 120, 240 Volts AC, 50-60 Hz; 12, 24, 120 Volts DC. WT and EF: 24/50-60HZ, (120/60, 110-120/50) ①, (240/60, 220-240/50) ② Volts AC; 6, 12, 24, 120 Volts DC.

① Order as 120/60, 110/50 ② Order as 240/60, 220/50

### **Solenoid Enclosures**

Standard: - Prefix

**SC** = IP65 type DIN (open frame) per 46244

WT = Combination General Purpose and Watertight Types 1, 2, 3, 3S, 4, and 4X


**EF** = Combination Explosionproof and Watertight Types 3, 3S, 4, 4X, 6, 5P, 7, 9 Class I, Div. 1 (Groups A - D) and Class II, Div. 1 Type 9 (Groups E-G)











# **Nominal Ambient Temp. Ranges**

**SC:** AC/DC:  $5^{\circ}F$  to  $+140^{\circ}F$  ( $-15^{\circ}C$  to  $60^{\circ}C$ )

**EF:** AC: 5°F to +104°F (-15°C to 40°C)

DC:  $5^{\circ}F$  to  $+125^{\circ}F$  ( $-15^{\circ}C$  to  $52^{\circ}C$ )

**WT:** AC: 5°F to +140°F (-15°C to 60°C)

DC:  $5^{\circ}F$  to  $+125^{\circ}F$  ( $-15^{\circ}C$  to  $52^{\circ}C$ )

**Note:** For temperatures below 32°F (0°C) moisture-free air must be used.

Refer to Engineering Section for details.

# **Approvals**

**SC:** (2.5W and 3W only) UL recognized component, CSA certified. (551Series only)

WT: UL listed, CSA certified. (551 Series only)

**EF:** UL and CSA listed solenoid. Meets applicable CE directives.

SIL 3 capable per IEC 61508 on normally closed single solenoid. Third party certification provided by EXIDA.

Refer to Engineering Section for details.

# Pilot Operated | Direct NAMUR Mount | 1/4" - 1/2" NPT

# **Specifications English units (Metric)**

Pipe	Orifice	Flow Factor	Diffe	j Pressure rential (bar)		l Temperatu le and dual :		Single Solenoid PFD <sub>AVG</sub> = 3.3 x 10 <sup>-3</sup>	Dual Solenoid		Class	Rating/ of Coil lation
Size (in)	Size in (mm)	Cv (m <sup>3</sup> /h)	Min.	Max.	Min.	Max. AC	Max. DC	Catalog Number	Catalog Number	Const. Ref.	AC	DC
, ,	OPEN FRAME DIN COIL											
1/4 ①	1/4 (6.4)	.86 (.7)	30 (2)	150 (10)	5 (-15)	140 (60)	140 (60)	SC8551A001MS	SC8551A002MS	1	2.5	3
1/2	1/2 (13)	3.7 (3.15)	30 (2)	150 (10)	-15 (-25)	140 (60)	140 (60)	SC8553A001MS	SC8553A002MS	2	5	6.9
WATERTIG	WATERTIGHT ENCLOSURE											
1/4 ①	1/4 (6.4)	.86 (.7)	30 (2)	150 (10)	5 (-15)	140 (60)	125 (52)	WT8551A001MS	WT8551A002MS	1	6.3	6.9
1/2	1/2 (13)	3.7 (3.15)	30 (2)	150 (10)	-15 (-25)	140 (60)	125 (52)	WT8553A001MS	WT8553A002MS	2	6.3	6.9
EXPLOSIONPROOF ENCLOSURE												
1/4 ①	1/4 (6.4)	.86 (.7)	30 (2)	150 (10)	5 (-15)	104 (40)	125 (52)	EF8551A001MS	EF8551A002MS	1	6.3	6.9
1/2	1/2 (13)	3.7 (3.15)	30 (2)	150 (10)	-15 (-25)	104 (40)	125 (52)	EF8553A001MS	EF8553A002MS	2	6.3	6.9
① 1/8 inch	① 1/8 inch NPT exhausts.											

# **Dimensions** inches (mm)


Series	551
NPT	1/4
L1	5.47 (139)
L2	7.56 (192)
H1	1.30 (33)
W	1.77 (45)

**NOTE:** Valve shown with CM22 DIN terminal coil and connector. Connector sold separately.

# 1/8 NPT 1/4 NPT

Const. Ref. 1

## **551 NAMUR Footprint**



# VALVE AUTOMATION

# ASCO™ Direct Mount Inline Spool Valves


Pilot Operated | Direct NAMUR Mount | 1/4" - 1/2" NPT

# Dimensions inches (mm)

Series	553
NPT	1/2
L1	7.76 (197)
L2	10.25 (260)
H1	1.94 (49)
W	2.85 (72)

**NOTE:** Valve shown with CM22 DIN terminal coil and connector. Connector sold separately.

Const. Ref. 2



## **553 NAMUR Footprint**

