


ECONOMIZER REGULATORS

ECONOMIZER REGULATORS IN CRYOGENIC SYSTEMS TO EXPAND LINES IN TANKS



FR (Bronze, stainless steel)

- **Body Size:** 1/2 to 2 in. / 15 to 50 mm
- **Pressure Range:** 0 to 600 psig / 0 to 41.4 barg
- **Maximum Capacity:** 4100 SCFM / 162 GPM
- **Temperature:** -320 to 150°F / -195 to 65.5°C



FRM/FRM2 (Bronze, stainless steel)

- **Body Size:** 1/4 to 1/2 in. / 8 to 15 mm
- **Pressure Range:** 0 to 600 psig / 0 to 41.4 barg
- **Maximum Capacity:** 60 SCFM / 10 GPM
- **Temperature:** -320 to 150°F / -195 to 65.5°C