

PRESSURE BUILD / ECONOMIZERS

COMBINATION OF PRESSURE REGULATOR AND ECONOMIZER REGULATOR AS A SINGLE DEVICE




PBE-1A (Brass)

- **Body Size:** 1/4 in. / 8 mm
- **Outlet Pressure Range:** 15 to 600 psig / 1 to 41.4 barg
- **Maximum Inlet Pressure:** 600 psig / 41.4 barg
- **Maximum Capacity:** 96.0 SCFM
- **Temperature:** -320 to 150°F / -195 to 65.5°C



PBE-2 (Bronze)

- **Body Size:** 1/2 in. / 15 mm
- **Outlet Pressure Range:** 10 to 400 psi / 0.70 to 27.5 barg
- **Maximum Inlet Pressure:** 400 psig / 27.5 barg
- **Maximum Capacity:** 197 SCFM
- **Temperature:** -320 to 150°F / -195 to 65.5°C



PBE-5 (Brass)

- **Body Size:** 1/2 in. / 15 mm
- **Outlet Pressure Range:** 0 to 600 psig / 0 to 41.4 barg
- **Maximum Inlet Pressure:** 650 psig / 45.7 barg
- **Maximum Capacity:** 298.9 SCFM
- **Temperature:** -320 to 150°F / -195 to 65.5°C