





Transmitter

Technical data


	FLUXUS G800SR-A1	FLUXUS G801SR-A1
		
design	explosion proof field device zone 1 SIL2	explosion proof offshore device zone 1 SIL2
supported transducer frequencies	F, G, H, K, M on request: P, Q	
measurement		
measurement principle	transit time difference correlation principle	
flow velocity	m/s	0.01...35, depending on pipe diameter
repeatability	0.15 % of reading \pm 0.01 m/s	
fluid	all acoustically conductive gases, e.g. nitrogen, air, oxygen, hydrogen, argon, helium, ethylene, propane	
temperature compensation	corresponding to the recommendations in ANSI/ASME MFC-5.1-2011	
measurement uncertainty		
volumetric flow rate	\pm 1...3 % of reading \pm 0.01 m/s depending on application \pm 0.5 % of reading \pm 0.01 m/s with field calibration	
transmitter		
power supply	<ul style="list-style-type: none"> • 100...230 V/50...60 Hz or • 20...32 V DC 	
power consumption	W	<10
number of measuring channels	1, optional: 2	
damping	s	0...100 (adjustable)
measuring cycle	Hz	100...1000 (1 channel)
response time	s	1 (1 channel), option: 0.07
housing material	cast aluminum, powder coated	stainless steel 316/316L (1.4401, 1.4404, 1.4432)
degree of protection	IP66	
dimensions	mm	see dimensional drawing
weight	kg	6
fixation	wall mounting, 2" pipe mounting	
ambient temperature	$^{\circ}$ C	-20...+60
display	2 x 16 characters, dot matrix, backlight	
menu language	English, German, French, Dutch, Spanish	
explosion protection		
• ATEX/IECEx		
marking	CE 0637  II2G Ex db eb IIC T6 Gb T _a -20...+60 $^{\circ}$ C	CE 0637  II2G II2D Ex db eb IIC T6 Gb Ex tb IIIC T100 $^{\circ}$ C Db T _a -20...+60 $^{\circ}$ C
certification ATEX	IBExU01ATEX1064	IBExU05ATEX1078
certification IECEx	-	IECEx IBE 12.0020

¹ connection of the interface RS232 outside of explosive atmosphere (housing cover open)

		FLUXUS G800SR-A1	FLUXUS G801SR-A1
measuring functions			
physical quantities		operating volumetric flow rate, standard volumetric flow rate, mass flow rate, flow velocity	
totalizer		volume, mass	
calculation functions		average, difference, sum (2 measuring channels necessary)	
diagnostic functions		sound speed, signal amplitude, SNR, SCNR, standard deviation of amplitudes and transit times	
communication interfaces			
service interfaces		<ul style="list-style-type: none"> • RS232¹ • USB (with adapter)¹ 	
accessories			
serial data kit		<ul style="list-style-type: none"> • cable • adapter 	
		RS232 RS232 - USB	
software		<ul style="list-style-type: none"> • FluxDiagReader: download of measured values and parameters, graphical presentation • FluxDiag (optional): download of measurement data, graphical presentation, report generation • FluxSubstanceLoader: upload of fluid data sets 	
data logger			
loggable values		all physical quantities, totalized values and diagnostic values	
capacity		> 100 000 measured values	
outputs			
		The outputs are galvanically isolated from the transmitter.	
• current output			
number		2 (1 (SIL2), 1 (diagnosis))	
range	mA	0/4...20	
accuracy		0.1 % of reading ±15 µA	
active output		R _{ext} < 500 Ω	
• binary output			
number		0...2 (diagnosis)	
open collector		24 V/4 mA	
binary output as alarm output			
• functions		limit, change of flow direction or error	
binary output as pulse output			
• functions		mainly for totalizing	
• pulse value	units	0.01...1000	
• pulse width	ms	1...1000	



¹ connection of the interface RS232 outside of explosive atmosphere (housing cover open)

Dimensions





Wall and 2" pipe mounting kit

G800



*801



Terminal assignment

G800

***801**

power supply ¹			
AC		DC	
terminal	connection	terminal	connection
L1	phase	L+	+
N	neutral	L-	-
PE	earth	PE	earth

transducers, extension cable				transducer
measuring channel A		measuring channel B		
terminal	connection	terminal	connection	
AV	signal	BV	signal	↑
AVS	internal shield	BVS	internal shield	
ARS	internal shield	BRS	internal shield	⌋
AR	signal	BR	signal	
cable gland	external shield	cable gland	external shield	↑ ⌋

outputs ¹	
terminal	connection
1(-), 2(+)	active current output I1
3(-), 4(+)	active current output I2
5(-), 6(+)	binary output B1 (open collector)
7(-), 8(+)	binary output B2 (open collector)

¹ cable (by customer): e.g. flexible leads, with insulated wire end ferrules, lead cross sectional area: 0.25...2.5 mm²