

ROSEMOUNT™ DIGITAL 396A ANTI-COATING pH/ORP SENSORS

Advanced Sensor Solutions for Your Engineering Needs

Precision, Performance, and Reliability

These sensors can be used in an extensive variety of industries, including wastewater treatment, chemical processing, power generation, and more.

Experience the ease of installation with the plug-and-play digital connection and factory calibration embedded into the sensor memory.

Designed with an innovative throughwall junction with a larger surface area, these sensors effectively minimize coating effects, ensuring reliable and accurate measurements every time.

Easy Installation

- Plug-and-play M12, 5-pin connection eliminates the need for wiring diagrams.

Advanced Diagnostics

- Predictive health indicators and built-in troubleshooting tips.

Exceptional Reliability

- Digital cable and connection eliminates errors from ground loops, vibration, or EMI interference.

Flexible Calibration

- Bench calibrate with data stored in the sensor for easy field deployment.

Detailed Failure Analysis

- Access detailed event logs for comprehensive failure analysis.

Water and Dust Protection

- IP67/IP68 rating for durability in harsh environments.

For more information, visit [Emerson.com](https://www.emerson.com)



Rosemount 396A Digital pH Sensor

- Range: 0 - 14 pH
- Max Temperature: 100 °C
- Max Pressure: 150 psig
- Digital 102C cable available up to 200 ft (61 m).
- 3/4 inch and 1 inch NPT front-facing connections
- IP67/IP68 rating

The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners.
©2025 Emerson Electric Co. All rights reserved.

MS-00807-0100-3396 A

ROSEMOUNT™


EMERSON™