

Fisher™ Baumann™ 24000CVF Carbon and 24000SVF Stainless Steel

Flanged Control Valves



General Application

The Fisher Baumann 24000CVF and 24000SVF control valves can be utilized for the control of pressure, temperature, level and flow. These valves are available with ASME CL150 RF, CL300 RF or PN 10 to 40 flanged end connections. The high performance 24000CVF and SVF designs feature low deadband and hysteresis, high flow capacity, superb control characteristics, tight shutoff and advanced packing systems to meet demanding service conditions. Compact and light weight make them ideal for installation in high density piping systems where space is a premium.

Features

- Compact and light weight design reduces installed piping costs
- ASME and EN end connection options to meet your piping standards
- Full lift post-guided contoured plug allows flushing of debris through valve body
- S31600 austenitic stainless steel trim material is standard; S41600 stainless steel trim is available
- Multiple trim options are available to meet changing process requirements
- Fisher FIELDVUE™ digital valve controller available for remote calibration and diagnostics
- Fisher enhanced ENVIRO-SEAL™ packing available for increased packing life and integrity
- NOLEEK bellows bonnet suitable for a wide range of operating temperatures
- Extension bonnets in multiple lengths available for elevated temperature and cryogenic application service




W9745-1

**FISHER BAUMANN 24000CVF CONTROL VALVE WITH
FISHER FIELDVUE DVC6200 DIGITAL VALVE CONTROLLER**



W9746

**FISHER BAUMANN 24000SVF CONTROL VALVE WITH
FISHER FIELDVUE DVC2000 DIGITAL VALVE CONTROLLER**

Figure 1. 24000CVF / SVF Control Valve Sub-assembly


E1245

Table 1. Materials of Construction

Key No.	Description	Material
1	Valve body, Carbon steel	Cast Carbon Steel (ASME SA216 WCC and EN10213 1.0619 Dual certified)
	Valve body, Stainless steel	ASME SA351 CF3M
2	Seat ring (For low flow trim, refer to Tables 2 and 3)	Standard ASTM A276 S31600 / S31603 Dual certified / Optional ASTM A582 S41600 Condition T
4	Plug (Metal Seat) $C_v < 3.3$	ASME SA479 S21800 (standard) / ASTM A582 S41600 Condition T (optional)
	Plug (Metal Seat) $C_v > 3.7$	ASTM A276 S31600 / S31603 (standard) / ASTM A582 S41600 Condition T (optional)
	Plug (Soft seat)	ASTM A276 S31600 / S31603 with PTFE (Polytetrafluoroethylene) insert
5	Stem	ASTM A276 S31600
8	Bonnet, Carbon steel (Std)	Cast Carbon Steel (ASME SA216 WCC and EN10213 1.0619 Dual Certified)
	Bonnet, Stainless steel (Std)	ASME SA351 CF3M
	Bonnet (Extended) ⁽¹⁾	ASME SA351 CF3M
	Bonnet (NOLEEK) ⁽¹⁾	ASME SA351 CF3M and ASTM A479 S31600/S31603, Annealed
8a	Bonnet bushing ⁽²⁾	ASTM A276 S44004, HT 56-60 HRC
9	Drive nut (Yoke)	S30400
10	Packing follower	ASTM A276 S31600 / S31603 Dual Certified
11	Stud	ASME SA193 Grade B8, Class 1
12	Nut	ASME SA194 Grade 8
14	V-ring packing (standard)	Refer to Figure 4, Table 4
	Packing (optional)	Refer to Figures 5 and 6, Tables 5 and 6
27	Locknuts	Stainless steel (18-8 SST)
49	Body gasket	Graphite grade GHR with S31600 insert
58	Travel indicator	ASME SA240 S30400


1. Extension bonnets and NOLEEK bellows bonnets are available with 24000SVF stainless steel valves only.
2. Guide bushing is applicable to 24000CVF carbon steel valve assembly only

Figure 2. Optional 151 Low Flow Trim Assembly



E1246

Figure 3. Optional 177 Low Flow Trim Assembly



E1247

151 Low Flow Trim Assembly

The PTFE seat surrounds the valve plug (key 4) to eliminate clearance flow typical of lapped-in metal-to-metal close clearance micro trims. Flow is directed over the valve plug and forced through a single V-notch path as the plug moves above the PTFE seat providing precise and predictable control over its entire travel range. When the V-notch moves below the PTFE seat, CL VI primary shutoff is achieved.


A live-loaded metal collar fully retains the PTFE seat. The valve plug (key 4) seats against the metal collar providing CL IV secondary shutoff. In addition, the fluid process pressure combines with the actuator seating force to form a hydraulic seal within the fully retained PTFE seat. Therefore, the higher the process pressure the tighter the shutoff.

Table 2. 151 Low Flow Trim

Key No.	Description	Material
2 ⁽¹⁾	Seat ring	ASTM A276 S31600 / S31603
4 ⁽¹⁾	Plug	ASME SA479 S21800
Seat Sub-assembly		
51 ⁽¹⁾	Cage	ASTM A276 S31600 / S31603
	Seat	PTFE
	Collar	ASTM A276 S31600 / S31603
	Washer	ASTM A276 S31600 Cond B
	Insert	ASTM A276 S31600 / S31603
1. For optional trim materials, consult your Emerson sales office for price and delivery.		

Table 3. 177 Low Flow Trim


Key No.	Description	Material
2 ⁽¹⁾	Seat ring	ASTM A276 S31600 / S31603
Seat Sub-assembly		
2a ⁽¹⁾	23 Gland	ASTM A276 S31600 / S31603
	24 Retainer nut	ASTM A276 S31600 / S31603
	25 Insert	Reinforced PTFE
	26 Housing	ASTM A276 S31600 / S31603
4 ⁽¹⁾	--- Plug	ASME SA479 S21800
1. For optional trim materials, consult your Emerson sales office for price and delivery. Fisher Baumann 32 actuator requires dual-stops with 177 trim Series.		

Figure 4. Standard Spring-Loaded PTFE V-ring Packing Kit

E1240

Table 4. Standard Spring-Loaded PTFE V-ring Packing Kit


Key No.	Description	Material
6	Spring	ASTM A313 S30200
14	Packing set	PTFE (Polytetrafluoroethylene) / PTFE, 25% Carbon-filled
16	Washer	ASME SA240 S31600
20	Spacer	J-2000 (filled-Polytetrafluoroethylene)

Figure 5. Molded Graphite (Flexible Graphite) Packing Kit (Optional)

E1241

Table 5. Molded Graphite (Flexible Graphite) Packing Kit (Optional)

Key No.	Description	Material
13	Bushings	Carbon - Graphite
14A	Packing rings	Graphite
14B	Packing ring	Graphite

Figure 6. Fisher enhanced ENVIRO-SEAL Packing Kit (Optional)

E1248

Table 6. Fisher enhanced ENVIRO-SEAL Packing Kit (Optional)

Key No.	Description	Material
13	Bushings	Carbon Graphite
14	Packing set	PTFE (Polytetrafluoroethylene) / PTFE, 25% Carbon-filled
17	Belleville spring	ASTM B637 N07718, 40 HRC max
18	Bushing	PEEK (Polyetheretherketone)
19	Washer	Modified PTFE

Special Fisher enhanced ENVIRO-SEAL Packing Note

The Fisher enhanced ENVIRO-SEAL PTFE packing system is suitable for 100 ppm environmental applications on services up to 51.7 barg / 750 psig and process temperatures ranging from -46 to +232°C / -50 to +450°F.

For non-environmental applications, this packing system offers excellent performance at the same temperature range up to the maximum valve working pressure.

Temperature limits apply to packing arrangements only. Complete valve assembly temperature limits may differ. Refer to appropriate pressure/ temperature ratings.

Reference Fisher Packing Selection Guidelines for Sliding-Stem Valves, Bulletin 59.1:062 ([D101986X012](#)).


⚠ WARNING

The NOLEEK valve bonnet assembly is not intended for use in lethal service applications.

The NOLEEK Bellows Bonnet Assembly is reliable and user-friendly. Typical service life is in excess of 250,000 full cycles under 100 psi pressure. The bonnet adds only approximately 5 inches to the height of a standard valve. Operating temperature range is -195 to +399°C / -320 to +750°F.

ONLY AVAILABLE WITH 24000SVF STAINLESS STEEL VALVES.

Figure 7. NOLEEK Bellow Bonnet Assembly



E1249

Table 7. NOLEEK Bellow Bonnet Assembly

Key Number	Description	Material
4	Plug	Refer to Table 1
8	Bellows Bonnet Sub-assembly	Housing
		S31600/S31603
		Bellows
		S31603/1.4571 SST
		Bonnet
		CF3M
21	Plug Retaining Pin	S30300
22	Hex Socket Pipe Plug, 1/8 NPT	S30400

Figure 8. Bellows Pressure / Temperature Curve




Table 8. C_V Values at 100% Plug Opening ($K_V = 0.86 \times C_V$)⁽¹⁾

VALVE SIZE	ORIFICE DIAMETER	PLUG TRAVEL	PLUG SERIES						
			102	151	177	577	548 / 588	677	648 / 688
NPS	in.	in.	C_V	C_V	C_V	C_V	C_V	C_V	C_V
1/2	0.156	0.50	---	0.00013, 0.00025, 0.0005, 0.001, 0.002, 0.004, 0.008, 0.015, 0.03, 0.06, 0.10, 0.20, 0.45	---	---	---	---	---
	0.25	0.50	0.02, 0.05, 0.10, 0.20	---	---	---	0.22, 0.61, 1.0	---	0.5, 1.0
	0.3125	0.50	---	---	0.0005, 0.001, 0.002, 0.005, 0.01, 0.02, 0.05	---	---	---	---
	0.375	0.50	---	---	---	1.0, 1.6, 2.7	1.6, 2.9	0.10, 0.20, 0.50, 1.0, 2.8	1.6, 2.9
	0.8125	0.50	---	---	---	3.9, 6.1	3.9, 6.1	3.4	3.7, 6.1
3/4	0.156	0.50	---	0.00013, 0.00025, 0.0005, 0.001, 0.002, 0.004, 0.008, 0.015, 0.03, 0.06, 0.10, 0.20, 0.45	---	---	---	---	---
	0.25	0.50	0.02, 0.05, 0.10, 0.20	---	---	---	0.22, 0.61, 1.0	---	0.5, 1.0
	0.3125	0.50	---	---	0.0005, 0.001, 0.002, 0.005, 0.01, 0.02, 0.05	---	---	---	---
	0.375	0.50	---	---	---	1.0, 1.6, 2.7	1.6, 2.9	0.10, 0.20, 0.50, 1.0, 2.8	1.6, 2.9
	0.8125	0.50	---	---	---	3.9, 9.5	3.9, 9.8	3.4	3.7, 9.8
1	0.156	0.50	---	0.00013, 0.00025, 0.0005, 0.001, 0.002, 0.004, 0.008, 0.015, 0.03, 0.06, 0.10, 0.20, 0.45	---	---	---	---	---
	0.25	0.50	0.02, 0.05, 0.10, 0.20	---	---	---	0.22, 0.61, 1.0	---	0.5, 1.4
	0.3125	0.50	---	---	0.0005, 0.001, 0.002, 0.005, 0.01, 0.02, 0.05	---	---	---	---
	0.375	0.50	---	---	---	1.1, 1.6, 3.2	1.7, 3.3	0.10, 0.20, 0.50, 1.0, 3.3	1.7, 3.3
	0.8125	0.50	---	---	---	5, 11	4.4, 11	5.1	4.6, 11
	1.0625	0.50	---	---	---	13	15.5	---	13
1-1/2	1.25	0.75	---	---	---	26	10, 27	26	11, 26
	1.5	0.75	---	---	---	13, 20, 33	11, 19, 31	14, 23	12, 22, 31
2	1.5	0.75	---	---	---	13, 20, 38	11, 18, 35	14, 23	12, 22, 35
	2.0	0.75	---	---	---	33	55	37, 56	33, 55

1. See Fisher Catalog 12 for a full range of flow and sizing information.

Figure 9. 24000CVF / SVF Trims





Table 9. Technical Specifications

VALVE TYPE	EN	ASME
NOMINAL PIPE SIZE	DN 15, 20, 25, 40 and 50	NPS 1/2, 3/4, 1, 1-1/2 and 2
END CONNECTIONS	PN 10 to 40 Flanges per EN 1092-1	CL150 RF or CL300 RF Flanges per ASME B16.5
PRESSURE RATING	PN 40 per EN 1092-1	CL150 or CL300 per ASME B16.34
FACE-TO-FACE DIMENSIONS	Consistent with EN 558-1	Consistent with EN 588-2 (ISA S75.03)


Table 10. Temperature Ratings for Packing and Seat Material⁽¹⁾

SEATING MATERIAL	PTFE Soft Seat	151 Trim	-29 to +177°C / -20 to +350°F
		577 and 677 Trim	-73 to +232°C / -100 to +450°F
	Reinforced PTFE	177 Trim	-73 to +232°C / -100 to +450°F
	Metal Seat	102, 588 and 688 Trim	-195 to +537°C / -320 to +1000°F
		548 and 648 Trim	-29 to +537°C / -20 to +1000°F
PACKING AND BONNET COMBINATIONS	BONNET STYLE	PACKING	TEMPERATURE LIMIT
	Standard Bonnet	Spring Loaded PTFE	-73 to +232°C / -100 to +450°F
		Fisher enhanced ENVIRO-SEAL	-46 to +232°C / -50 to +450°F
		Graphite	-73 to +232°C / -100 to +450°F
	Single Extension Bonnet ^(2,3)	Spring Loaded PTFE	-73 to +343°C / -100 to +650°F
		Fisher enhanced ENVIRO-SEAL	-46 to +343°C / -50 to +650°F
		Graphite	-73 to +427°C / -100 to +800°F
	Double Extension Bonnet ^(2,3)	Spring Loaded PTFE	-101 to +427°C / -150 to +800°F
		Fisher enhanced ENVIRO-SEAL	-101 to +427°C / -150 to +800°F
		Graphite	-101 to +537°C / -150 to +1000°F
	Triple Extension Bonnet ^(2,3)	Spring Loaded PTFE	-195 to +427°C / -320 to +800°F
		Fisher enhanced ENVIRO-SEAL	-195 to +427°C / -320 to +800°F
		Graphite	-195 to +537°C / -320 to +1000°F
	Bellows ⁽²⁾	NOLEEK Bellows	-195 to +399°C / -320 to +750°F
CHARACTERISTIC	Equal Percentage or Linear		
1. Temperature limits apply to seating or packing arrangements only. Complete valve assembly temperature limits may differ, refer to appropriate pressure/temperature ratings. For more information on packing selection, reference Fisher Packing Selection Guidelines for Sliding-Stem Valves Bulletin 59.1:062 (D101986X012).			
2. Extension bonnets and NOLEEK bellows bonnets are applicable for the 24000SVF stainless steel body assembly ONLY.			
3. PTFE packing can be used in cryogenic service but becomes stiff.			

Figure 10. 24000CVF Carbon Steel Flanges, Pressure-Temperature Ratings




E1251-1




E1252-1

Figure 11. 24000SVF Stainless Steel Flanges, Pressure-Temperature Ratings




E1254-1




E1255-1

Figure 12. 24000CVF and 24000SVF Pressure-Temperature Ratings for EN 1092-1




24000CVF



24000SVF

Figure 13. 24000SVF Stainless Steel Control Valves with Extension Bonnets Dimensional Drawing



E1258

Table 11. Dimensions^(1, 2)

VALVE SIZE		A - FACE-TO-FACE								B - BONNET							
EN	ASME	CL150		CL300		EN 10-40		Standard		Extension ⁽³⁾						NOLEEK Bellows ⁽³⁾	
										Single		Double		Triple			
DN	NPS	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
15	1/2	184	7.25	190	7.5	130	5.11	79	3.1	216	8.5	352	13.9	488	19.2	226	8.9
20	3/4	184	7.25	194	7.62	150	5.90	79	3.1	216	8.5	352	13.9	488	19.2	226	8.9
25	1	184	7.25	197	7.75	160	6.30	84	3.3	221	8.7	356	14.0	493	19.4	229	9.0
40	1-1/2	222	8.75	235	9.25	200	7.87	96	3.8	234	9.2	370	14.6	505	19.9	229	9.0
50	2	254	10.0	267	10.5	230	9.06	107	4.2	244	9.6	381	15.0	516	20.3	234	9.2

1. Actuator requires 115 mm / 4.5 in. vertical clearance.


2. Face-to-face dimension per EN 558-1 and ISA S75.03.

3. Extension and NOLEEK bellows bonnets are available with 24000SVF stainless steel body ONLY.

Table 12. Valve Assembly Weights

VALVE SIZE		24000CVF WEIGHTS						24000SVF WEIGHTS					
EN	ASME	CL150		CL300		EN 10-40		CL150		CL300		EN 10-40	
DN	NPS	kg	lb	kg	lb	kg	lb	kg	lb	kg	lb	kg	lb
15	1/2	3.1	6.8	3.3	8.3	3.8	7.7	3.7	7.2	3.5	8.2	3.5	7.8
20	3/4	3.3	7.3	3.4	10	4.5	9.2	4.7	7.4	4.2	10.3	4.3	9.4
25	1	4.8	10.6	5.1	13.8	6.3	12.6	6.4	11.2	5.7	14	5.9	13
40	1-1/2	8.3	18.2	8.3	24.8	11.3	21.2	11.4	18.3	9.6	25.2	9.8	21.7
50	2	14.1	31	13.8	35.3	16	33.4	16.1	30.4	15.2	35.4	15.2	33.4

Figure 14. Dimensional Drawings



24000CVF/SVF FLANGED WITH
32 ATO ACTUATOR WITH HANDWHEEL

E1257

MM / IN.

NOTE: ACTUATOR REMOVAL REQUIRES 115 MM / 4.5 IN. VERTICAL CLEARANCE.

Table 13. Model Numbering System

24	Plug Series	Characteristic	Seat Leakage	S		Bonnet Style	
Valve Body				Valve Body Material			
	102	Linear / Metal Seat	IV	CVF	Carbon	Omit	Standard
	151	Modified Equal % / PTFE Seat	VI	SVF	Stainless steel	E	Extension
	177	Modified Equal % / Reinforced PTFE	VI			EE	Double Extension
	548	Equal % / Metal Seat (S41600)	IV			ET	Triple Extension
	577	Equal % / PTFE Seat	VI			EB	NOLEEK
	588	Equal % / Metal Seat (S31600)	IV				
	648	Linear / Metal Seat (S41600)	IV				
	677	Linear / PTFE Seat	VI				
	688	Linear / Metal Seat (S31600)	IV				

 [LinkedIn.com/groups/3941826](https://www.linkedin.com/groups/3941826)
 [Fisher.com](https://www.fisher.com)

 [Facebook.com/FisherValves](https://www.facebook.com/FisherValves)
 [X.com/FisherValves](https://www.x.com/FisherValves)

D103333X012 © 2009, 2026 Emerson. All rights reserved. The Emerson logo is a trademark and service mark of Emerson Electric Co. Baumann, Fisher, FIELDVUE, PlantWeb, and ENVIRO-SEAL are marks of an entity in the Emerson family of businesses. All other marks are the property of their respective owners.

Neither Emerson nor any of its affiliated entities assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson
Marshalltown, Iowa 50158 USA
Sorocaba, 18087 Brazil
Cernay 68700 France
Dubai, United Arab Emirates
Singapore 128461 Singapore

www.fisher.com

FISHER™

