Fieldbus Electronics

G3 | Communication Node and I/O 580 | Communication Node






Table of Contents

G3 Electronics

	Features and Benefits	
	G3 Platform Distribution Options	
	CANopen [®]	
	CC-Link IE Field™	
	DeviceNet™	
	EtherCAT [®]	
	EtherNet/IP™ DLR	10
	Ethernet POWERLINK®	
	Modbus® TCP/IP	
	PROFIBUS™ DP	13
	PROFINET™	14
	I/O Modules	15
	Input Modules - RTD & NAMUR IS	18
	Sub-bus Modules	19
	Miscellaneous Modules & Accessories	21
	G3 Dimensions	23
	G3 How To Order	26
	501 Series	30
	502 Series	33
	503 Series	36
	2002 R2 & 02 Series	
	2005 Series	41
	2012 Series	43
	2035 Series	45 45
	ISO 15407-2 18mm Series	47
	ISO 15407-2 26mm Series	49
	ISO 5599/2 Series	48 51
	Power Cables & Connectors	
	CANopen® and DeviceNet™ Cables & Connectors	53
	CC-Link IE Field™ Cables & Connectors	56
	EtherCAT® Cables & Connectors	57
		58
	EtherNet/IP™, EtherNet/IP™ DLR and Modbus® TCP/IP Cables & Connectors	59
	Ethernet POWERLINK® Cables & Connectors	60
	PROFIBUS™ DP Cables & Connectors	61
	PROFINET™ Cables & Connectors	62
	I/O Cables & Connectors	63
	M23 19 Pin Cables & Connectors	66
	Sub-bus Cables & Connectors	67
580	Series	
	Features and Benefits	69
	CANopen [®]	70
	DeviceNet™	71
	EtherCAT®	72
	EtherNet/IP™ DLR	 73
	Ethernet POWERLINK®	
	IO-Link [®]	 75
	PROFIBUS™ DP	 76
	PROFINET™	77
	580 CHARM Node	78
	CHARM Communication & Power Connection	79
	580 Dimensions	80
	580 How to Order	81
	Power and Communication Cables & Connectors	82



G3 Fieldbus - Electronics Made Easy!

Innovative Graphic Display is used for easy commissioning, visual status & diagnostics.

Commissioning Capabilities

- · Set network address (including IP & Subnet mask for Ethernet)
- · Set baud rate
- Set auto or manual I/O sizes
- Set fault/idle output states
- Set brightness
- · Set factory defaults
- · Visual diagnostics

- Shorted and open load detection
- · Shorted sensor/cable detection
- Low & missing power detection
- · Missing module detection
- · Self-test activation
- Log of network errors
- Distribution errors



Graphic Display for

Configuration & Diagnostics





Auto Recovery Module



Easy, Robust Connections

G3 Fieldbus Communications Electronics

Why use AVENTICS Fieldbus communication electronics? Modular Reality...

No internal wiring simplifies assembly

- SPEEDCON® M12 connector technology allows for fast and efficient ½ turn I/O connector attachment
- Power connector allows output power to be removed while inputs and communication are left active
- IP65 protection
- Up to 1,200 Input/1,200 Output capability with one communication node!
- Up to 128 valve solenoids per manifold, up to 17 manifolds per communication node!
- One node supports 16 I/O modules Analog I/O, Digital I/O (NPN & PNP) and Specialty
- Integrated web server with EtherCAT®, EtherNet/IP™ DLR, Ethernet POWERLINK®, Modbus® TCP/IP, and PROFINETTM
- Innovative clip design allows easy module removal/ replacement without dismantling manifold
- Auto Recovery Module (ARM) protects configuration information during a critical failure. Allows configuration information to be saved and reloaded to replacement module automatically

*AVENTICS I/O with

• 1/2 turn for faster I/O connections

SPEEDCON® Technology

- · Backwards compatible with standard M12 cables/connectors
- Meets the same IP/NEMA standards as M12/Micro cables/connectors
- Same cost as standard M12/Micro cables/connectors
- See the I/O Cables and Connectors section for cables with SPEEDCON® connector technology

Supported Protocols

- CANopen®
- CC-Link IE Field™
- DeviceNet™
- DeviceNetTM w/ QuickConnect™
- EtherCAT®
- EtherNet/IP™ DLR w/ QuickConnect™
- Ethernet POWERLINK®
- Modbus® TCP/IP
- PROFIBUS™ DP
- PROFINET™



EtherNet/IP, DeviceNet and QuickConnect are trademarks of ODVA. EtherCAT is a registered trademark of the EtherCAT Technology Group. CANopen is a registered Community trademark of CAN in Automation e.V. PROFIBUS and PROFINET are trademarks of Profibus Nutzerorganisation e.V.


Ethernet POWERLINK is a registered trademark of Bernecker + Rainer Industrie - Elektronik Ges.m.b.H. CC-Link is a registered trademark and CC-Link IE Field is a trademark of the CC-Link Partner Association.

G3 Electronics Modularity

Discrete I/O

The G3 Series product line is a completely modular system. All of the G3 electronic modules plug together, via mechanical clips, allowing easy assembly and field changes. This makes the system highly distributable. Additional flexibility is incorporated because the same modules can be used in either centralized or distributed applications.


The G3 electronics interfaces with the highly modular AVENTICS 500 Series, Generation 2000 Series, ISO 5599/2 and ISO 15407-2 Series valve lines to further enhance the modularity and flexibility of the entire system. 500 Series valves allow up to 128 valve solenoids per manifold when properly configured. An external air pilot supply may be required with more than 32 valve solenoids on a manifold.





G3 Platform Distribution Options

Easy, Cost Effective Solutions for Digital I/O and Valve Automation using G3 Electronics.



- Unique distribution system allows system efficiency by allowing the same modules to be used in either centralized or distributed applications
- Distribution options include:

Inputs OR Outputs

Inputs AND Outputs

Valves with Inputs AND Outputs

Valves with Inputs OR Outputs

Valves Only

Maximum Sub-bus length not to exceed 30 meters. Maximum Sub-bus cable current not to exceed 4 amps or
excessive cable voltage drops per segment. Auxiliary power connections available for currents above 4 amps.
Consult factory for possible deviations.




G3 Platform Distribution Options

The G3 platform is flexible to the point that there are a virtually infinite number of I/O distribution options using the few basic G3 modules. The following basic rules should be followed in the configuration of your control architecture.

Typical Main Fieldbus Manifold


Valve Side

 Up to a total of 128 valve solenoids can be driven in a manifold assembly integrated into the main fieldbus manifold. This can be any number of single or double solenoid valves with a total number of solenoids not to exceed 128




I/O Side Distribution

- A total of 16 modules can be integrated into the network and controlled by the main fieldbus communication module (node)
- Modules include analog and digital I/O modules providing addressing capacity for up to 1200 Inputs/1200 Outputs per node
- Unique distribution system allows system efficiency by allowing the same modules to be used in either centralized or distributed applications
- Distribution options include Inputs only, Outputs only, I/O only, valves with Inputs, valves with Outputs and valves with I/O
- Configuration can include up to 16 of the following modules:
 - Digital I/O modules
 - Sub-bus valve modules
 - Analog I/O modules



16 Modules can be supported on this side of the comm. module





CANopen®

CANopen[®] is an open protocol based on Controller Area Network (CAN). It was designed for motion-oriented machine control networks but has migrated to various industrial applications. CAN in Automation (CIA) is the international users' and manufacturers' organization that develops and supports CAN-based protocols. AVENTICS' G3 nodes for CANopen[®] have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

More information regarding this organization can be found at: www.can-cia.org.



Description	Replacement Part Number
CANopen® Communications Module (node)	240-291

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.0404 Amps
Bus Power	11 – 25 VDC	0.025 Amps
Valves & Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 4 Pin 7/8" MINI type (male)	
Communication Connector	Single key 5 Pin 7/8" MINI type (male)	
LEDs	Module Status and Network Status	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65 (with appropriate assembly and termination)

Configuration Data		
Graphic Display	Display used for setting Node Address, Baud Rate, Fault/Idle Actions, and all other system settings	
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure	
Maximum Valve-Solenoid Outputs	32	
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs	

Network Data		
Supported Baud Rates	125K Baud, 250K Baud, 500K Baud, 1M Baud	
Bus Connector	Single key 5 Pin 7/8" MINI type (male)	
Diagnostics	Power, short, open load conditions and module health are monitored and fail-safe device settings	

	Weight
CANopen® Communications Module	252g/8.9 oz



CC-Link IE Field[™]

CC-Link IE Field™ is an open standard 1 Gbps Ethernet Manufacturing network that enables seamless data communication from the plant-level enterprise network to the production floor network. The CC-Link Partner Association (CLPA) oversees and manages CC-Link® specifications.

AVENTICS' G3 nodes for CC-Link IE Field™ have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

CC-Link IE Field™ is based on 1 Gbps Ethernet standards and complements them with specific protocols and mechanisms to achieve real time performance.

More information regarding CC-Link IE Field™ can be obtained from the following website: www.CCLinkAmerica.org



Description	Replacement Part Number	
CC-Link IE Field™ Communications Module (node)	240-362	

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.0495 Amps
Valves & Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 5 Pin 7/8" MINI type (male)	
Communication Connector	Two X-coded 8 Pin M12 type (female)	
LEDs	Run, ERR, Link, D Link, L.ERR, L.ER	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65 (with appropriate assembly and termination)

Configuration Data		
Graphic Display	Display used for setting Node Number, Network Number, Fault/Idle Actions, and all other system settings	
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure	
Maximum Valve-Solenoid Outputs	128 for 501, 80 for 502/503 and 32 for all other series	
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs	

Network Data	
Supported Baud Rates	1 Gbps
Bus Connector	Two D-coded 8 Pin M12 type (2-Female)
Diagnostics	Power, short, open load conditions and module health and configuration are monitored
Special Features	Integrated 2 port switch, fail-safe device settings

	Weight
CC-Link IE Field™ Communications Module	269g/9.5 oz





DeviceNet™

DeviceNet™ is an open bus fieldbus communication system developed by Allen-Bradley based on Controller Area Network (CAN) technology. The governing body for DeviceNet™ is the Open DeviceNet™ Vendors Association (ODVA). The ODVA controls the DeviceNet™ specification and oversees product conformance testing.

AVENTICS' G3 nodes for DeviceNet[™] have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

They have been tested and approved for conformance by the ODVA.

More information about DeviceNet[™] and the ODVA can be obtained from the following website: www.odva.org.



Description	Replacement Part Number
DeviceNet™ Communications Module (node)	240-180

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.0404 Amps
Bus Power	11 – 25 VDC	0.025 Amps
Valves & Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 4 Pin 7/8" MINI type (male)	
Communication Connector	Single key 5 Pin 7/8" MINI type (male)	
LEDs	Module Status and Network Status	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65 (with appropriate assembly and termination)

Configuration Data	
Graphic Display	Display used for setting Node Address, Baud Rate, Fault/Idle Actions, DeviceNet™ w/ QuickConnect™ and all other system settings
ARM (Auto Recovery Module) Optional module that contains automatic recovery of system setting in the even total or partial system failure	
Maximum Valve-Solenoid Outputs	32
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs

Network Data	
Supported Baud Rates	125K Baud, 250K Baud, 500K Baud, with Auto-Baud detection
Supported Connection Type Polled, Cyclic, Change of State (COS) and combination Message Capability	
Bus Connector Single key 5 Pin 7/8" MINI type (male)	
Diagnostics Power, short, open load conditions and module health are monitored	
Special Features	Supports Auto-Device Replacement (ADR) and fail-safe device settings, and QuickConnect™ capability

	Weight
DeviceNet™ Communications Module	252g/8.9 oz



EtherCAT®

EtherCAT® is an open ethernet-based fieldbus protocol developed by Beckhoff. EtherCAT® sets new standards for real-time performance and topology flexibility with short data update/cycle times and low communication jitter.

AVENTICS' G3 EtherCAT® node has an integrated graphic display for simplified commissioning and diagnostics. It is capable of addressing combinations of up to 1200 outputs and 1200 inputs.

The G3 nodes for EtherCAT® have been designed and tested to conform with EtherCAT® specifications set forth by the ETG.

More information regarding EtherCAT® can be obtained from the following website: www.ethercat.org.



Description	Replacement Part Number
EtherCAT® Communications Module (node)	240-310

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.073 Amps
Valves and Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 5 Pin 7/8" MINI type (male)	
Communication Connector	Two D-coded 4 Pin M12 type (female)	
LEDs	Module Status, Network Status and Activity /Link	

Operating Data	
Temperature Range	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC 60068-2-6
Moisture	IP65 (with appropriate assembly and termination)

Configuration Data	
Graphic Display	Display used for setting IP address, Subnet Mask, Fault/Idle Actions, and all other system settings
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system settings in the event of total or partial system failure
Maximum Valve Solenoid Outputs	128 for 501, 80 for 502/503 and 32 for all other series
Maximum Sub-bus I/O Points	Various combinations of 1200 outputs and 1200 inputs

Network Data	
Supported Baud Rates	10 Mbit/100 Mbit
Bus Connector	Two D-coded 4 Pin M12 type (female)
Diagnostics	Power, short, open load conditions and module health and configuration are monitored
Special Features	Integrated web server, fail-safe device settings

	Weight
EtherCAT® Communications Module	227g /8 oz






EtherNet/IP™ DLR

EtherNet/IPTM used throughout the world to network millions of PCs has now evolved into a viable industrial network. EtherNet/IPTM is an open architecture high-level communication network that meets the demands of today's industrial applications requiring high-speed (10/100 Mbit/s), high-throughput and flexibility. Additionally, EtherNet/IPTM technology can integrate an on-board web server, which can make the node readily accessible to any standard web browser for configuration, testing and even retrieval of technical documentation.

AVENTICS' G3 EtherNet/IP™ DLR (Device Level Ring) node with integrated display has an embedded switch which allows the unit to be used in simplified networks with linear topology configurations (daisy chain). This technology alleviates the need for an external Ethernet switch device in a single subnet configuration. Additionally, the DLR compatibility allows the node to be used in a fault tolerant "ring" network, when using appropriate EtherNet/IP™

DLR scanners. DLR configuration allows communication recovery from a single point failure on the network ring (e.g. failed network connection or cable).

AVENTICS G3 EtherNet/IP™ nodes are capable of addressing combinations of up to 1200 outputs and 1200 inputs.



The G3 EtherNet/IP™ nodes have been tested and approved for conformance by the ODVA.

More information about EtherNet/IP™ and the ODVA can be obtained from the following website: www.odva.org.

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.0953 Amps
Valves and Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 4 Pin 7/8" MINI type (male)	
Communication Connector	Two D-coded 4 Pin M12 type (female)	
LEDs	Module Status, Network Status and Activity/Link	

Operating Data	
Temperature Range	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC 60068-2-6
Moisture	IP65 (with appropriate assembly and termination)

Configuration Data	
Graphic Display	Display used for setting IP address, Subnet Mask, Fault/Idle Actions, and all other system settings
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system settings in the event of total or partial system failure
Maximum Valve Solenoid Outputs	128 for 501, 80 for 502/503 and 32 for all other series
Maximum Sub-bus I/O Points	Various combinations of 1200 outputs and 1200 inputs

Network Data	
Supported Baud Rates	10 Mbit/100 Mbit
Bus Connector	Two D-coded 4 Pin M12 type (female)
Diagnostics	Power, short, open load conditions and module health and configuration are monitored
Special Features	Embedded two port switch, Device Level Ring (DLR) compatibility, Linear network topology, QuickConnect™ capability, fail-safe device settings, integrated web server, HTTP, TFTP, UNICAST

	Weight
EtherNet/IP™ DLR Communications Module	227g/8 oz



Ethernet POWERLINK®

Ethernet POWERLINK® is an open fieldbus protocol designed by B&R for communication between automation control systems and distributed I/O at the device level.

AVENTICS' G3 Ethernet POWERLINK® nodes have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

The G3 Ethernet POWERLINK[®] nodes have been designed and tested to conform to the Ethernet POWERLINK[®] specifications available at EPSG group (Ethernet Powerlink[®] Standardization Group). The certification process ensures interoperability for all Ethernet POWERLINK[®] devices and compatibility with B&R systems

More information regarding Ethernet POWERLINK® can be obtained from the following website: www.ethernet-powerlink.org.

POWERL	INK [®]
d I/O at the	
an integrated binations of	
esigned and ecifications lardization bility for all ith B&R systems.	

Description	Replacement Part Number
POWERLINK® Communications Module (node)	240-309

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.0955 Amps
Valves & Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 5 Pin 7/8" MINI type (male)	
Communication Connector	Two D-coded 4 Pin M12 type (female)	
LEDs	Module Status, Network Status and Activity/Link	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65 (with appropriate assembly and termination)

Configuration Data	
Graphic Display	Display used for setting IP Address, Subnet Mask, Fault/Idle Actions, and all other system settings
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure
Maximum Valve-Solenoid Outputs	128 for 501, 80 for 502/503 and 32 for all other series
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs

Network Data	
Supported Baud Rates	10 Mbit/100 Mbit
Bus Connector	Two D-coded 4 Pin M12 type (2-Female)
Diagnostics	Power, short, open load conditions and module health and configuration are monitored
Special Features	Integrated web server, Integrated 2 port switch and fail-safe device settings

Weight	
POWERLINK® Communications Module	227g/8 oz





Modbus® TCP/IP

Ethernet used throughout the world to network millions of PCs has now evolved into a viable industrial network. Ethernet is an open architecture high-level communication network that meets the demands of today's industrial applications requiring high-speed (10/100 Mbit/s), high-throughput and flexibility. Additionally, Ethernet technology can integrate an on-board web server, which can make the node readily accessible to any standard web browser for configuration, testing and even retrieval of technical documentation.

AVENTICS' G3 nodes for Modbus® TCP/IP have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.



Description	Replacement Part Number
Modbus® TCP/IP Communications Module (node)	240-292

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.0657 Amps
Valves & Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 4 Pin 7/8" MINI type (male)	
Communication Connector	D-coded 4 Pin M12 type (female)	
LEDs	Module Status, Network Status and Activity/Link	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65 (with appropriate assembly and termination)

Configuration Data	
Graphic Display	Display used for setting IP Address, Subnet mask, Fault/Idle Actions, DHCP/BootP and all other system settings
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure
Maximum Valve-Solenoid Outputs	128 for 501, 80 for 502/503 and 32 for all other series
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs

Network Data	
Supported Baud Rates	10 Mbit/100 Mbit
Bus Connector	D-coded 5 Pin M12 type (female)
Diagnostics	Power, short, open load conditions and module health are monitored
Special Features	Integrated web server, fail-safe device settings, HTTP, FTP, and UNICAST (for EtherNet/IP™)

Weight	
Modbus® TCP/IP Communications Module	255g/9 oz



PROFIBUS™ DP

PROFIBUS™ DP is a vendor-independent, open fieldbus protocol designed for communication between automation control systems and distributed I/O at the device level.

AVENTICS' G3 nodes for PROFIBUS™ DP have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

The G3 nodes for PROFIBUS™ DP have been designed and tested to conform to the PROFIBUS™ standard EN50170. Certification has been done by the PROFIBUS™ Interface Center (PIC) according to the guidelines determined by the PROFIBUS™ Trade Organization (PTO). The certification process ensures interoperability for all PROFIBUS™ devices.

More information regarding PROFIBUS $^{\text{TM}}$ can be obtained from the following website: www.profibus.com.



Description	Replacement Part Number
PROFIBUS TM DP Communications Module (node)	240-239

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.0623 Amps
Valves & Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 5 Pin 7/8" MINI type (male)	
Communication Connector	Single reverse key (B-Coded) 5 Pin M12 type (1 male and 1 f	emale)
LEDs	Module Status and Network Status	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65 (with appropriate assembly and termination)

Configuration Data	
Graphic Display	Display used for setting Node Address, Baud Rate, Fault/Idle Actions, and all other system settings
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure
Maximum Valve-Solenoid Outputs	128 for 501, 80 for 502/503 and 32 for all other series
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs

Network Data		
Supported Baud Rates	125K Baud, 250K Baud, 500K Baud, with Auto-Baud detection	
Bus Connector	Single key 5 Pin 7/8" MINI type (male)	
Diagnostics	Power, short, open load conditions and module health are monitored	
Special Features	Supports Auto-Device Replacement (ADR) and fail-safe device settings	

	Weight
PROFIBUS TM DP Communications Module	227g/8 oz





PROFINET™

PROFINET™ is the innovative open standard for Industrial Ethernet, developed by Siemens and the PROFIBUS® User Organization (PNO). PROFINET™ complies to IEC 61158 and IEC 61784 standards. PROFINET™ products are certified by the PNO user organization, guaranteeing worldwide compatibility.

AVENTICS' G3 nodes for PROFINET™ IO (PROFINET™ RT) have an integrated graphic display and are capable of addressing combinations of up to 1200 outputs and 1200 inputs.

PROFINET™ is based on Ethernet and uses TCP/IP and IT standards and complements them with specific protocols and mechanisms to achieve Real Time performance.

More information regarding PROFINET $^{\text{TM}}$ can be obtained from the following website: www.profibus.com.



Description	Replacement Part Number
PROFINET TM Communications Module (node)	240-240

Electrical Data	Voltage	Current
Node Power at Max. Brightness	24 VDC +/- 10%	0.0903 Amps
Valves & Discrete I/O	24 VDC +/- 10%	8 Amps Maximum
Power Connector	Single key 5 Pin 7/8" MINI type (male)	
Communication Connector	Two D-coded 4 Pin M12 type (female)	
LEDs	Module Status, Network Status and Activity/Link	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65 (with appropriate assembly and termination)

Configuration Data		
Graphic Display	Display used for setting IP Address, Subnet Mask, Fault/Idle Actions, and all other system settings	
ARM	(Auto Recovery Module) Optional module that contains automatic recovery of system setting in the event of total or partial system failure	
Maximum Valve-Solenoid Outputs	128 for 501, 80 for 502/503 and 32 for all other series	
Maximum Addressable I/O Points	Various combinations of 1200 outputs and 1200 inputs	

Network Data		
Supported Baud Rates	10 Mbit/100 Mbit	
Bus Connector	Two D-coded 4 Pin M12 type (2-Female)	
Diagnostics	Power, short, open load conditions and module health and configuration are monitored	
Special Features	Integrated web server, Integrated 2 port switch, fail-safe device settings, and FSU	

Weight		
PROFINET TM Communications Module	227g/8 oz	



I/O Modules

Digital I/O - Terminal Strip Modules

Description	Part Number
16 PNP Inputs	240-203
16 NPN Inputs	240-204
8 PNP Inputs	240-316
16 PNP Outputs	240-330



Operating Data		
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)	
Humidity	95% relative humidity, non-condensing	
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6	
Wire Range	12 to 24 AWG	
Strip Length	7mm	
Tightening Torque	0.5 Nm	
Ingress Protection	IP20	


Spare Parts		
Replacement Terminal Strip (I/O 0-7)	140-1073	
Replacement Terminal Strip (I/O 8-15)	140-1074	
Keying Element for terminal strip	140-1076	
Keying Element for Module	140-1077	

Weight	
Input Module	292g/10.3 oz

I/O Modules

Digital I/O 5 Pin M12 Modules

Description	Part Number
Inputs	
8 PNP Inputs	240-206
8 NPN Inputs	240-210
16 PNP Inputs	240-205
16 PNP Inputs 19 Pin M23 (Fig. B Only)	240-323
16 NPN Inputs	240-209
Outputs	
8 PNP Outputs	240-208
8 PNP High Current Outputs (Fig. A Only)	240-300
16 PNP Outputs	240-207
Inputs and Outputs	
8 PNP Inputs and 8 PNP Outputs	240-211



Analog I/O with settable high and low alarms 5 Pin M12 Modules

Description	Signal Type	Part Number	
Inj	Inputs		
4 Analog Inputs	0 – 10 VDC	240-212	
4 Analog Inputs	4 – 20 mA	240-214	
Inputs and Outputs			
2 Analog Inputs & 2 Analog Outputs	0 – 10 VDC	240-213	
2 Analog Inputs & 2 Analog Outputs	4 – 20 mA	240-215	
2 Analog Inputs & 2 Analog Outputs High Current (Figure A Only)	0 – 10 VDC	240-307	
4 Analog Inputs & 4 Analog Outputs High Current (Figure A Only)	4 – 20 mA	240-363	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Ingress Protection	IP65 (with appropriate assembly and termination)
Connector-Analog & Digital	M12 4 Pin Female, SPEEDCON [®] (Compatible with 5 Pin)
Connector-Figure A	M12 4 Pin Male
Connector-Figure B	M23 19 Pin Female
Resolution	16 bit






Dust Cover -M12 Male 230-647

Weight	
I/O Module-Analog	244g/8.6 oz
I/O Module-Digital	274g/9.7 oz
I/O Module-Figure A	264g/9.3 oz
I/O Module-Figure B	343g/12.1 oz

I/O Modules

Digital I/O 3 Pin M8 Sub-bus Module

Description	Part Number	
Inputs		
8 PNP Inputs	240-379	



Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Ingress Protection	IP67 (with appropriate assembly and termination)
Connector	M8 3 Pin Female
Special Features	Linear topology and internally powered through Sub-bus connection
M12 Terminating Resistor (required on last M8 Module)	TA05TR0000000000



Weight	
Sub-bus Module	204g /7.2 oz



G3 RTD Temperature Module 240-311

The RTD module is for use with RTD (Resistive Temperature Detectors), supporting up to four RTD devices simultaneously. The module supports various RTD types including: Pt100, Pt200, Pt500, Pt1000, Ni100 and Ni1000.

Technical Data

Electrical Data		
Voltage	24 VDC Module Supply (Via G3 System Aux. Power Connection)	
Input Type	RTD (Resistive Temperature Detector), 4 per Module	
Supported Sensor Type	Pt100, Pt200, Pt500, Pt1000, Ni100, Ni1000	
Supported Temperature Coefficients	.00385; .00392;Ω/Ω/°C	
Resolution	15 bits plus sign	
Data Format	Signed Integer	
Calibration	Factory Calibrated Field Calibration w/ high tolerance (\pm .005%) 100 ohm and 350 ohm resistors.	
Input Update (filter) Rate	Adjustable (5 – 20ms), factory default: 5ms	
Accuracy	0.1% of full scale @ 25 °C	

Mechanical Data	
I/O Connector	M12 4 Pin Female. SPEEDCON [®] (Compatible with 5 Pin)
Mass	247g/8.7 oz

Operating Data	
Temperature Range Ambient	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity: non-condensing
Ingress Protection	IP65 (with appropriate assembly and terminations)

G3 [Ex ia] NAMUR Input Modules 240-320 and 240-322

The [Ex ia] modules are for use with NAMUR certified intrinsically safe (IS) sensors.

Electrical Data	
Voltage	24 VDC Module Supply
Voltage	Sensor Supply = 8.2 VDC Nominal
Input Type	NAMUR
	Signal Current (0) ≥ 2.1 mA
NC (Normally Closed)	Signal Current (1) ≤ 1.2 mA
	Short Circuit Monitoring < 100 Ω
	Open/Broken Wire Detection < 0.05 mA
	Uo ≤ 9.6 V
Safety Parameter Output Maximums	lo ≤ 13 mA
	Po ≤ 31 mW
Diagnostics	Open (broken wire) and Short Circuit

Certification	
Wodale Warking (WEX)	c size (1)GD [Ex ia Ga] C

Mechanical Data			
Connector-Figure A M12 4 Pin Female SPEEDCON® (Compatible with 5 Pin)			
Connector-Figure B Terminal Strip			
Mass-Figure A	284g/10.0 oz		
Mass-Figure B	303g/10.7 oz		

Operating Data			
Temperature Range Ambient -23 °C to 50 °C (-10 °F to 122 °F)			
Humidity 95% relative humidity: non-condensing			
Ingress Protection-Figure A	IP65 (with appropriate assembly and termination)		
Ingress Protection-Figure B	IP20		





Figure A




Figure B

Sub-bus Modules

Sub-bus Valve Module

Provides Sub-bus In and Aux. Power In connections to a distributed valve manifold.

Description	Part Number	Weight
Sub-bus Valve Module w/ I/O	240-241	235g/8.3 oz
Sub-bus Valve Module w/o I/O*	P580AEDS4010A00	320g/11.3 oz
Sub-bus Valve Module w/o I/O, w/ DIN Rail Clips*	P580AEDS4010DRM	332g/11.7 oz

^{*500} Series only



Provides Sub-bus Out and Aux. Power Out connections for I/O distribution.

Description	Part Number	Weight
Sub-bus Out Module w/ DIN Rail Clips	240-244	141g/5.0 oz
Sub-bus Out Module	240-183	130g/4.6 oz
Sub-bus Out Module for Intrinsically Safe	240-318	150g/5.3 oz

Sub-bus In Module

Provides Sub-bus In and Aux. Power In connections for I/O distribution.

Description	Part Number	Weight
Sub-bus In Module w/ DIN Rail Clips	240-246	141g/5.0 oz
Sub-bus In Module	240-185	130g/4.6 oz
Sub-bus In Module for Intrinsically Safe	240-318	150g/5.3 oz











G3 4 Branch Sub-bus HUB Module 240-326

The G3 HUB module allows for branch distribution from the I/O side of the G3 System and can be integrated into the existing G3 Series Sub-bus configuration. Auto Addressing allows for trouble free set up and configuration. Input, output, as well as Valve manifolds can be attached to the available four Branches on a HUB module. Each G3 System can support up to two HUB modules, allowing for maximum flexibility. The HUB module is transparent to the I/O side of the G3 and does not reserve one of the potential sixteen positions.

As with all other G3 I/O modules, standard G3 display and ARM functionality (storing of all parameters) is supported.



Electrical Data		
Voltage	24 VDC Module Supply	
No. of HUB Branches	4 Per HUB Module, 2 HUB Modules per G3 System (A HUB module cannot be connected to the Branch of another HUB module)	
HUB Branch Length	30 Meters Per Branch	
Addressing	Auto Addressing on Power Up (Branch I/O reserve capability)	
Display/Diagnostics	Onboard LCD Multi Function Display	
G3 System Integration	Integrated into existing G3 I/O Side	
Topology	Star, Tree and Hybrid	

Mechanical Data		
Branch Connector	M12 5 Pin Female	
Mass	255g/9.0 oz	

Operating Data		
Temperature Range -23 °C to 50 °C (-10 °F to 122 °F)		
Humidity 95% relative humidity: non-condensing		
Ingress Protection IP65 (with appropriate assembly and terminations)		

Miscellaneous Modules

Auto Recovery Module (ARM)


Protects configuration information during a critical failure. Allows configuration information to be saved and reloaded to replacement module automatically.

New ARM and Wireless ARM Modules are drop in products into existing G3 Electronics platform and are backwards compatible to legacy ARM Module.

New ARM and Wireless ARM Modules fit in the space of a standard Jumper Clip.

Description	Part Number	Figure	Weight
ARM Module (legacy)	240-182	1	127g/4.5 oz
ARM Module (New)	240-383	2	131g/4.6 oz
Wireless ARM Module	240-382	3	131g/4.6 oz








Provides termination for the Sub-bus. Must be installed after the last I/O module or after the communications module if there are no I/O modules installed.


Description	Part Number	Weight
Terminator Module w/ DIN Rail Clips	240-245	102g/3.6 oz
Terminator Module	240-184	91g/3.2 oz



Provides electrical connections between modules.

Description	Part Number	Weight
Jumper Clip	240-179	45g/1.6 oz
Jumper Clip for Intrinsically Safe	240-317	65g/2.3 oz








Miscellaneous Modules

Valve Driver Module

Provides connections between the communication module or Sub-bus valve module and the valve manifold.

Generation 2000, ISO 5599/2 and ISO 15407-2 Series

Description	Part Number	Weight
Valve Driver Module w/ DIN Rail Clips	219-858	147g/5.2 oz
Valve Driver Module	219-828	136g/4.8 oz



501, 502 and 503 Series Valves


Description	Part Number	Weight
Valve Driver Module	P599AE508827001	234g/8.3 oz
Valve Driver Module w/ DIN Rail Clips	P599AE508827002	246g/8.7 oz

Right Hand Mounting Cover

Used when a communications module is used without local valves installed.

Description	Part Number	Weight
Right Hand Mounting Cover w/ DIN Rail Clips*	240-289	82g/2.9 oz
Right Hand Mounting Cover*	240-255	71g/2.5 oz
Right Hand Mounting Cover Assembly Kit for ARM	245-189	371g/13.1 oz

^{*} Not for use in combination with ARM Module




Accessories

For use with Murrplastik[©] Type 20 Software.

Labels - 122-1251


Technical Data									
Material	Polycarbonate (PC)								
Color	White								
Temperature Range	-40 °C to 140 °C (-40 °F to 284 °F)								
Label Dimensions	0.19" x 0.39"								
Label - Printable Area	0.19" x 0.39"								



Dimensions: mm (inches)

G3 Fieldbus Manifold Assembly

503 Series Valve Manifold Assembly with G3 Electronics and Sub-bus Output



Α	В	С	D	E	F	G	Н	J	K	L	М	N	Р
105.5 (4.154)	6.3 (0.248)	38 (1.5)	52.8 (2.08)	33.8 (1.33)	7 (0.28)	57.5 (2.264)	67.5 (2.66)	71.7 (2.82)	-	39.1 (1.54)	75.8 (2.984)	68.1 (2.68)	56.3 (2.217)
Q	R	S	Т	U	V	W	Х	Υ	Z	AA	AB	AC	AD

)	R	S	Т	U	V	W	X	Υ	Z	AA	AB	AC	AD
5 (2.		24.8 (0.98)	67.5 (2.66)	36.9 (1.45)	221.3 (8.713)	368.6 (14.51)	12.5 (0.49)	24.8 (0.976)	53 (2.087)	_	55.1 (2.17)	101.1 (3.98)	112.9 (4.445)	207 (8.2)


NOTE: For valve manifold dimensions refer to valve series product catalogs.





Dimensions: mm (inches)

G3 Fieldbus I/O Assembly

I/O Assembly with G3 Electronics and Sub-bus Input








Α	В	С	D	E	F	G	Н	J	K	L	М	N	Р	R	S	Т	U
46.35	67.50	57.50	6.90	105.50	38.00	33.75	6.25	185.25	13.50	67.25	36.75	54.00	12.50	62.50	5.05	59.00	118.00
(1.82)	(2.66)	(2.26)	(0.27)	(4.15)	(1.50)	(1.33)	(0.25)	(7.29)	(0.53)	(2.65)	(1.45)	(2.13)	(0.49)	(2.46)	(0.20)	(2.32)	(4.65)

Dimensions: mm (inches)

G3 Sub-bus I/O Assembly


3 Pin M8 Sub-bus Module



Α	В
33	171.75
(1.299)	(6.762)



How To Order: 500 Series Manifold Assembly




 $^{^{\}rm 1}$ Port Type 8 & G only available in Port Size 3/8 for 502 & 503 and 1/8 for 501


 $^{^2}$ 501 not available with 2 stations, 502 and 503 only available with an even number of stations and with up to 80 valve solenoids

 $^{^{\}rm 3}$ With 502 11mm (501) valve available, with 503 18mm (502) valve available

 $^{^4}$ 501 Port Sizes 1/8, 1/4, 5/16, 8mm, 502 and 530 Port Sizes 3/8, 1/2, 10 and 12mm

How to Order: Sub-bus Valve Manifold without I/O or Additional Distribution





Shaded components are described by the manifold assembly number. The communications module is described by the electronic interface model number designation.

Each valve station is listed in sequential order from left to right when facing the port side of the manifold as shown.


NOTE:

Up to 128 solenoid outputs are available. Either 128 single solenoid valves or 64 double solenoid valves or any combination of singles and doubles not to exceed 128 outputs can be specified.

Example Order	- 503 Shown
Assembly Kit	8503AV8H300VMUF
Valve Station #1	R503A2B40MA00F1
Valve Station #2	R503A2B40MA00F1
Mounting #1	8503AMM22MA0010
Valve Station #3	R503A2B40MA00F1
Valve Station #4	R503A2B40MA00F1
Mounting #2	8503AMM22MA0010
Valve Station #5	R503A2B40MA00F1
Valve Station #6	R503A2B40MA00F1
Mounting #3	8503AMM22MA0010
Valve Station #7	R503A2B40MA00F1
Valve Station #8	R503A2B40MA00F1
Mounting #4	8503AMM22MA0010
Electronics	P580AEDS4010A00
	Assembled




How To Order: 2000 and ISO Series Manifold Assembly



^{*}For manifold assembly with multiple valve series - consult factory


How To Order

G3 Electronics



How to Order: Valve Manifold Assemblies w/ G3 Electronics & Discrete I/O

For valve series 2002, 2005, 2012, 2035, ISO 15407-2 & ISO 5599/2 (2005 shown)



Shaded components are described by the assembly kit (AK) model number (see previous page). The communications module and number of I/O modules are described by the electronic interface (G3) model number designation (see previous page).

Each valve station is listed in sequential order from left to right when facing the port side of the manifold as shown.


Each discrete I/O module is listed in sequential order from RIGHT to LEFT starting from the communication module as shown.

NOTE:

- 1. A total of 32 solenoid outputs are available. Either 32 single solenoid valves or 16 double solenoid valves or any combination of singles and doubles not to exceed 32 outputs can be specified.
- 2. For manifold assemblies that exceed 16 solenoids, the assembly MUST be configured so that an even number of solenoids are utilized prior to the station using the ribbon cable feature. The 16th and the 17th solenoids cannot be on the same valve.

How To Order

G3 Electronics



- 1. Refer to the selection table on the previous page to specify the control electronics and I/O configuration.
- 2. Each discrete I/O module is listed in sequential order from RIGHT to LEFT as shown.
- 3. A maximum of 16 I/O modules are supported by a single communication node. Analog I/O & digital I/O (NPN & PNP)

Example Order - 2005 Shown

Assembly Kit	AK3EP00003LMUF
Station 1	052BB4Z2ML00061
Station 2	052BB4Z2ML00061
Station 3	052BB4Z2ML00061
Station 4	052BB4Z2ML00061
Station 5	052BB4Z2ML00061
Station 6	052BB4Z2ML00061
Station 7	052BB4Z2ML00061
Station 8	052BB4Z2ML00061
Station 9	052BB4R2ML00061
Station 10	052BB4Z2ML00061
Station 11	052BB4Z2ML00061
Station 12	052BB4Z2ML00061
Station 13	052BB4Z2ML00061
Station 14	052BB4Z2ML00061
Station 15	052BB4Z2ML00061
Station 16	052BB4Z2ML00061
Electronics	G3DN116R0E40
Station 1	240-205
Station 2	240-205
•	
:	
Station 15	240-205
Station 16	240-205

Example Order - I/O Assembly w/ Sub-bus In and Sub-bus Out Modules Shown

Electronics G3DS316D0STD Station 1 240-205 Station 2 240-205

Station 15 240-205 Station 16 240-205

501 Series - Directional Control Valve Platform

Featuring Higher Flow in a Compact Valve Package

Features

- · Solenoid air pilot actuated
- Low wattage 0.8 Watt for DC application
- DC solenoids Polarity insensitive with surge suppression
- · Plug together circuit boards eliminate internal wiring
- Integral recessed gaskets
- IN Fittings to accommodate various tube sizes
- Simple conversion from internal to external pilot
- IP65 Certified

Sandwich and Manifold Accessories

- Pressure Regulators for supply pressure control at individual valve
- Speed control to control exhaust flow allows for control of actuator extend or retract speed
- Shut off block for individual valve to be isolated from pressure supply during operation and repair
- Mid Station Supply Manifold block allows for multiple pressure zones (with blocking discs) or additional air supply to a manifold

Fieldbus Electronics Compatible

- G3 Fieldbus Electronics
 - Graphic Display for easy commissioning, visual status & diagnostics
 - 128 valve solenoids per manifold
 - Easy distribution of additional manifolds through Sub-bus communication
 - One Node supports up to 16 I/O modules
 - Available with Auto Recovery Module (ARM) which allows configuration information to be saved and reloaded to replacement module automatically
- 580 Fieldbus Electronics
 - Graphic Display for easy commissioning, visual status & diagnostics
 - 128 valve solenoids per manifold











Performance Data

Function Type	Function Code	ISO Symbol Pilot (14)	Interface	at 90	Flow PSI V (ANR))	Response Time (ms)	Pilot Pr at 73°I PSI (F/23°C	Operat Pressi Port PSI (bar)/inl	ıre 1	
		Return (12)		1 → 2 1 → 4	2 → 3 4 → 5	Energize/ De-Energize	min.	max	min.	max	Part Number
			Rubber	Packed To	echnology	, with Manua	al Overrio	de	1		
	B1	14 2 12 12 12 13 18 18 12 12 12 12 12 12 12 12 12 12 12 12 12		0.460 (460)	0.465 (465)	14/29	29 (2)	115 (8)	28 (-0.95)	115 (8)	R501A2B10MA00F1
5/2	BN	Differential Air Return		0.460 (460)	0.465 (465)	25/21	29 (2)	115 (8)	28 (-0.95)	115 (8)	R501A2BN0MA00F1
	B4	Solenoid Air Return		0.460 (460)	0.465 (465)	11/11	29 (2)	115 (8)	28 (-0.95)	115 (8)	R501A2B40MA00F1
	B5	Center Open to Exhaust	Proprietary	0.420 (420)	0.470 (470)	27/12	29 (2)	115 (8)	28 (-0.95)	115 (8)	R501A2B50MA00F1
5/3	B6	Center Closed	riopriotary	0.460 (460)	0.465 (465)	13/12	29 (2)	115 (8)	28 (-0.95)	115 (8)	R501A2B60MA00F1
	B7	Center Open to Pressure		0.460 (460)	0.411 (411)	17/38	36 (2.5)	115 (8)	28 (-0.95)	115 (8)	R501A2B70MA00F1
2 x 3/2 NO	ВА	Normally Open		0.450 (450)	0.450 (450)	18/18	0.3 x Operating Pressure + 13 PSI	115 (8)	30 (2)	115 (8)	R501A2BA0MA00F1
2 x 3/2 NC	BD	Normally Closed		0.460 (460)	0.470 (470)	18/18	0.09 x Operating Pressure + 33.5 PSI	115 (8)	30 (2)	115 (8)	R501A2BD0MA00F1

Construction


Materials in Contact w/Fluid								
Body	Aluminum, E-Coating treatment							
Spool	Aluminum or Stainless Steel							
Piston	POM							
Spring	Steel							
Spool Seals	NBR + PUR							
Other Seals	NBR + FKM							
Other materials	PAM (Polyarylamide) 50% Glass Fiber Reinforced							
Valve to Subbase Gasket	NBR							
Subbases	Aluminum, E-Coating treatment							

Operating Data

All Solenoids Are Continuous Duty Rated	d 24 VDC
Power (Watts)	0.8
Holding Current (Amps)	0.025
Ambient Temperature Range Min/Max °F (°C)	-14° F (-10° C)/122° F (50° C)




How to Order: Valve



How to Order: Regulator

Dual 3-Way, 14 Normally Open – 12 Normally Closed
 Dual 3-Way, 14 Normally Closed – 12 Normally Closed
 2 Position 4-Way (5/2), Differential Air Return w/o Spring



^{*} Regulator gauges must be offset with 18V option on alternating stations to prevent interference.



502 Series - Directional Control Valve Platform

Featuring Higher Flow in a Compact Valve Package

Features

- Solenoid air pilot actuated
- Low wattage 1.3 Watt for DC application
- DC solenoids Polarity insensitive with surge suppression
- Plug together circuit boards eliminate internal wiring
- Integral recessed gaskets
- IN Fittings to accommodate various tube sizes
- Simple conversion from internal to external pilot
- IP65 Certified

Sandwich and Manifold Accessories

- Pressure Regulators for supply pressure control at individual valve
- Speed control to control exhaust flow allows for control of actuator extend or retract speed
- Shut off block for individual valve to be isolated from pressure supply during operation and repair
- Mid Station Supply Manifold block allows for multiple pressure zones (with blocking discs) or additional air supply to a manifold

Fieldbus Electronics Compatible

- G3 Fieldbus Electronics
 - Graphic Display for easy commissioning, visual status & diagnostics
 - 80 valve solenoids per manifold
 - Easy distribution of additional manifolds through Sub-Bus communication
 - One Node supports up to 16 I/O modules
 - Available with Auto Recovery Module (ARM) which allows configuration information to be saved and reloaded to replacement module automatically
- 580 Fieldbus Electronics
 - Graphic Display for easy commissioning, visual status & diagnostics
 - 80 valve solenoids per manifold





Performance Data

	Function Code	ISO Symbol Pilot (14) Return (12)	Interface	Rated Flow at 90 PSI Cv (I/min (ANR))		Response Time (ms)	e at 73°F/23°C		Operating Pressure Port 1 PSI (bar)/inHg (-bar)		
				1 → 2 1 → 4	2 → 3 4 → 5	Energize/ De-Energize	min.	max	min.	max	Part Number
Rubber Packed Technology, with Manual Override											
2 x 3/2 NC	BD	Normally Closed	Proprietary	0.650 (650)	0.600 (600)	36/15	58 (4.0)	115 (8)	36* (2)	115 (8)	R502A2BD0MA00F1
			ISO	0.500 (500)	0.440 (440)						
Spool and Sleeve Technology, with Manual Override											
5/2	B1	Spring Return	Proprietary	0.470 (470)	0.530 (530)	16/49	29 (2)	115 (8)	28 (-0.95)	115 (8)	R502A1B10MA00F1
			ISO	0.410 (410)	0.390 (390)						
	BN	Differential Air Return	Proprietary	0.470 (470)	0.530 (530)	11/26	22 (1.5)	115 (8)	28 (-0.95)	115 (8)	R502A1BN0MA00F1
			ISO	0.410 (410)	0.390 (390)						
	В4	Solenoid Air Return	Proprietary	0.470 (470)	0.530 (530)	12/15	29 (2)	115 (8)	28 (-0.95)	115 (8)	R502A1B40MA00F1
			ISO	0.410 (410)	0.390 (390)						
5/3	B5		Proprietary	0.380 (380)	0.500 (500)	23/13	22 (1.5)	115 (8)	28 (-0.95)	115 (8)	R502A1B50MA00F1
		Center Open to Exhaust	ISO	0.340 (340)	0.350 (350)						
	В6	Center Closed	Proprietary	0.420 (420)	0.440 (440)	12/12	22 (1.5)	115 (8)	28 (-0.95)	115 (8)	R502A1B60MA00F1
			ISO	0.360 (360)	0.350 (350)						
	В7	Center Open to Pressure	Proprietary	0.420 (420)	0.430 (430)	- 13/23	22 (1.5)	115 (8)	28 (-0.95)	115 (8)	R502A1B70MA00F1
			ISO	0.370 (370)	0.350 (350)						

^{*} Minimum pressure with external piloting


Construction

Materials in Contact w/Fluid						
Body	Aluminum, E-Coating treatment					
Spool	Aluminum or Stainless Steel					
Piston	POM					
Spring	Steel					
Spool Seals	NBR + PUR					
Other Seals	NBR + FKM					
Other materials	PAM (Polyarylamide) 50% Glass Fiber Reinforced					
Valve to Subbase Gasket	NBR					
Subbases	Aluminum, E-Coating treatment					


Operating Data

All Solenoids Are Continuous Duty Rated	24 VDC				
Power (Watts)	1.3				
Holding Current (Amps)	0.054				
Ambient Temperature Range Min/Max °F (°C)	-14 °F (-10 °C)/122 °F (50 °C)				

How to Order: Valve



Regulator





= with 1/8" NPTF adaptor for external gauge

= with 1/8" G tap adaptor for external gauge

= 10 - 130 PSIG (0.7 - 9 bar)

= 5 - 60 PSIG (0.3 - 4.1 bar)

= 3 - 30 PSIG (0.2 - 2 bar)

2

8

^{*} Regulator gauges must be offset with 61Y option on alternating stations to prevent interference.

503 Series - Directional Control Valve Platform

Featuring Higher Flow in a Compact Valve Package

Features

- 5 Ported, 2 and 3 position, 4-way, Spool & Sleeve and Rubber Seal, Cv: 1.2 1.4
- · Solenoid air pilot actuated
- Low wattage 1.7 Watt for DC application
- DC solenoids Polarity insensitive with surge suppression
- Plug together circuit boards eliminate internal wiring
- · Integral recessed gaskets
- IN Fittings to accommodate various tube sizes
- Simple conversion from internal to external pilot
- G3 Fieldbus Electronics
- IP65 Certified

Sandwich and Manifold Accessories

- Pressure Regulators for supply pressure control at individual valve
- Speed control to control exhaust flow allows for control of actuator extend or retract speed
- Shut off block for individual valve to be isolated from pressure supply during operation and repair
- Mid Station Supply Manifold block allows for multiple pressure zones (with blocking discs) or additional air supply to a manifold

Fieldbus Electronics Compatible

- G3 Fieldbus Electronics
 - Graphic Display for easy commissioning, visual status & diagnostics
 - 80 valve solenoids per manifold
 - Easy distribution of additional manifolds through Sub-Bus communication
 - One Node supports up to 16 I/O modules
 - Available with Auto Recovery Module (ARM) which allows configuration information to be saved and reloaded to replacement module automatically
- 580 Fieldbus Electronics
 - Graphic Display for easy commissioning, visual status & diagnostics
 - 80 valve solenoids per manifold

Construction

Materials in Contact w/Fluid			
Body	Aluminum, E-Coating treatment		
Spool	Aluminum or Stainless Steel		
Piston	POM		
Spring	Steel		
Spool Seals	NBR + PUR		
Other Seals	NBR + FKM		
Other materials	PAM (Polyarylamide) 50% Glass Fiber Reinforced		
Valve to Subbase Gasket	NBR		
Subbases	Aluminum, E-Coating treatment		











Operating Data

All Solenoids Are Continuous Duty Rated	24 VDC
Power (Watts)	1.7
Holding Current (Amps)	0.071
Ambient Temperature Range Min/Max °F (°C)	-14° F (-10° C)/122° F (50° C)


Performance Data

Function Type	Function Code	ISO Symbol Pilot (14)	Interface	at 9	d Flow 0 PSI Cv (ANR))	Response Time (ms)	at 73°	ressure F/23°C (bar)	Operat Pressi Port PSI (bar)/inl	ure 1			
		Return (12)		1 → 2 1 → 4	2 → 3 4 → 5	Energize/ De-Energize	min.	max	min.	max	Part Number		
			Rubber	r	echnology	, with Manua	al Overri	de					
	B1	4 2 12 14 5 1 3 83	Proprietary	1.422 (1400)	1.321 (1300)	20/60	29 (2)	115 (8)	28 (-0.95)	115 (8)	R503A2B10MA00F1		
		Spring Return	ISO	1.220 (1200)	1.118 (1100)		(2)	(6)	(0.33)	(0)			
5/2	BN	4 2	Proprietary	1.422 (1400)	1.321 (1300)	28/40	44 (3)	115	28 (-0.95)	115	R503A2BN0MA00F1		
		Differential Air Return	ISO	1.220 (1200)	1.118 (1100)		(3)	(8)	(-0.95)	(8)			
	B4	4 2	Proprietary	1.422 (1400)	1.321 (1300)	20/20	29 (2)	115	28 (-0.95)	115	R503A2B40MA00F1		
		Solenoid Air Return	ISO	1.220 (1200)	1.118 (1100)		(2)	(8)	(-0.95)	(8)			
	B5		Proprietary	0.610 (600)	1.321 (1300)	18/45	44	115	28 (-0.95)	115	R503A2B50MA00F1		
		Center Open to Exhaust	ISO	0.610 (600)	1.118 (1100)	10/10	(3)	(8)	(-0.95)	(8)	110007 12200117 1001 1		
5/3	B6	4 2 7	Proprietary	1.422 (1400)	1.321 (1300)	15/20	58	115	28	115	R503A2B60MA00F1		
0,0		Center Closed	ISO	1.220 (1200)	1.118 (1100)	10,20	(4)	(8)	(-0.95)	(8)	11000/1200111/1001		
	B7	4 2 3	Proprietary	1.321 (1300)	0.610 (600)	18/45	8/45 44	44 115	28 (-0.95)	115	R503A2B70MA00F1		
		Center Open to Pressure	ISO	1.118 (1100)	0.610 (600)		(3)	(8)	(-0.95)	(8)			
2 x 3/2	BA	Term W Term	Proprietary	0.965 (950)	0.965 (950)	15/20	51	115	51*	115	R503A2BA0MA00F1		
NO		Normally Open	ISO	0.915 (900)	0.915 (900)	10,20	(3.5)	(8)	(3.5)	(8)			
2 x 3/2	BD		Proprietary	1.016 (1000)	0.813 (800)	15/20	51	51 115	51 115	51 115 5	51*	115	R503A2BD0MA00F1
NC	3 23	Normally Closed	ISO	0.915 (900)	0.813 (800)		(3.5)	(8)	(3.5)	(8)			
	Spool and Sleeve Technology, with Manual Override												
	B1	4 2 12 14 5 1 3 83	Proprietary	1.220 (1200)	1.220 (1200)	20/60	29 (2)	115	28	115 (8)	R503A1B10MA00F1		
5/2		Spring Return	ISO	1.118 (1100)	1.016 (1000)		(2)	2) (8)	(8) (-0.95)	(8)			
	B4	14 2 3 83	Proprietary	1.220 (1200)	1.220 (1200)	15/15	29	29 115 (2) (8)		115 (8)	R503A1B40MA00F1		
		Solenoid Air Return	ISO	1.118 (1100)	1.016 (1000)		(2) (8)			(6)			
	B5		Proprietary	1.016 (1000)	1.016 (1000)	20/60	20/60 29 (2)	29 115 (2) (8)		115 28	115 (8)	R503A1B50MA00F1	
		Center Open to Exhaust	ISO	0.813 (800)	0.813 (800)				(8) (-0.	(-0.95)	(0)	(0)	
E /0	_ /a B7	14 4 2 W	Proprietary	1.016 (1000)	1.016 (1000)	20/60	29 (2)	115 (8)	28 (-0.95)	115 (8)	R503A1B70MA00F1		
5/3		Center Open to Pressure	ISO	0.813 (800)	0.813 (800)		(2)	(0)	(-0.93)	(0)			
	DT.	14 2 2 3 3 3 5 1 3	Proprietary	1.016 (1000)	1.016 (1000)	Spring: 20/60	29	29 115 (2) (8)	28	115 (8)	DECOMARDAMACOFA		
	BT	Open Center, Spring and Detent	ISO	0.813 (800)	0.813 (800)	Detent: 15/NA	(2)		(-0.95)		R503A1BT0MA00F1		


 $^{^{\}star}$ 51 PSI for a pressure supply (P1) \leq 109 PSI (if > 109 PSI, Pmin. = P1-58 PSI)



How to Order: Valve



Regulator





= with 1/8" G tap adaptor for external gauge

G


SERIES 2002


2002 R2 & 02 SERIES

2002-R2 & 02 Series Functions




double solenoid air pilot 3 position 4-way open center






double solenoid air pilot 3 position 4-way closed center




2002-R2 Series Only Functions

double solenoid air pilot dual 3-way "12(B)" & "14(A)" NO




double solenoid air pilot dual 3-way "12(B)" & "14(A)" NC



double solenoid air pilot 2 position dual 3

2 position dual 3-way "12(B)" NO, "14(A)" NC



5 Ported, 2 and 3 position, 4-way and dual 3-way, Packed Spool

Cv: 0.25 (4-way)

0.25 (Dual 3-way) R2 Series Spool and Sleeve

Cv: 0.20 (4-way) 02 Series

- Solenoid air pilot actuated
- · Low wattage coil
- Elimination of internal wiring
- Buna-N seals provide leakproof sealing
- Pusher piston-high spool shifting force
- Adjustable port sizes utilizing interchangeable cartridge fittings



Technical Data

Valve Data	Eng	lish	Met	ric
valve Data	R2 Series	02 Series	R2 Series	02 Series
Cv	0.25	0.2	0.25	0.2
Flow Capacity	11.5 SCFM @ 80 PSIG upstream pressure to atmosphere	9.2 SCFM @ 80 PSIG upstream pressure to atmosphere	246 NI/m @ 6 bar upstream pressure to 5 bar downstream	197 NI/m @ 6 bar upstream pressure to 5 bar downstream
Operating Pressure Range	28" Hg to 100 PSIG	28" Hg to 150 PSIG	Vacuum to 7 bar	Vacuum to 10 bar
Pilot Pressure Range	35 to 100 PSIG	35 to 100 PSIG	2.5 to 7 bar	2.5 to 7 bar
Temperature Range (Ambient)	-10 °F to 115 °F	-10 °F to 115 °F	-23 °C to 50 °C	-23 °C to 50 °C


Operating Data

All Solenoids are Continuous Duty Rated	24 VDC
Power (Watts)	0.5
Holding Current (Amps)	0.02

Response Time	Ener	rgize	De-Energize	
in Seconds	R2 Series	02 Series	R2 Series	02 Series
2-Position, Single, Spring Return	0.017	0.014	0.013	0.20
2-Position, Double, Detented	0.010	0.010	N/A	N/A
3-Position, Spring Centered	0.009	0.009	0.022	0.057
Dual 3-way	0.018	N/A	0.010	N/A



How To Order: Valves



Z4 =

Manifold Block, Side Ports

Only, Double Solenoid Output

3 Position 4-Way, Open Center, Dual Pressure 5


6 = 3 Position 4-Way, Closed Center

= Dual 3-way, A Normally Open - B Normally Open Α = Dual 3-Way, A Normally Closed - B Normally Open С = Dual 3-way, A Normally Closed - B Normally Closed D


Blank Station Plate

2005 SERIES


single solenoid air pilot 2 position 4-way



double solenoid air pilot 3 position 4-way open center




double solenoid air pilot 3 position 4-way pressure center




double solenoid 2 position dual 3-way "14(A)" & "12(B)" NC


double solenoid 2 position dual 3-way "14(A)" NC, "12(B)" NO double solenoid air pilot 2 position 4-way




double solenoid air pilot 3 position 4-way closed center









(B) (B) (A) (A 12 2 4 4 14 3 1 5 (EB) (P) (EA) 5 Ported, 2 and 3 position, 4-way, Spool & Sleeve Cv: 0.56

Dual 3-Way Pack Spool Cv: 0.56

- · Solenoid air pilot actuated
- · Low wattage coil
- DC solenoids polarity insensitive with spike suppression
- Plug together circuit boards eliminate internal wiring
- Integral recessed gaskets
- Interchangeable Push-In fittings to accommodate various tube sizes
- Simple conversion from internal to external pilot supply
- NEMA 4/IP65





Technical Data


Valve Data	English	Metric
Cv	0.56	0.56
Flow Capacity	26 SCFM @ 80 PSIG upstream pressure to atmosphere	552 NI/m @ 6 bar upstream to 5 bar downstream
Operating Pressure Range	28" Hg Vacuum to 150 PSIG	Vacuum to 10 bar
Operating Pressure Range – 3 Way	22" Hg Vacuum to 100 PSIG	Vacuum to 7 bar
Pilot Pressure Range	26 to 120 PSIG	1.8 to 8.2 bar
Pilot Pressure Range – 3 Way	26 to 100 PSIG	1.8 to 7 bar
Pilot Pressure Vacuum	50 to 100 PSIG	3.5 to 7 bar
Temperature Range (Ambient)	-10 °F to 115 °F	-23 °C to 50 °C

Operating Data

All Solenoids are Continuous Duty Rated	24 VDC
Power (Watts)	1.35
Holding Current (Amps)	0.056

Response Time in Seconds	Energize	De-Energize
2-Position, Single, Spring Return	0.014	0.016
2-Position, Double, Detented	0.013	N/A
3-Position, Spring Centered	0.014	0.016
Dual 3-way	0.014	0.016

SERIES 2005



Port Type

Wiring Option

Push-In

NPTF (1/8 Only)

G Tap (1/8 Only)

Plug-In Receptacle Assembly

Κ

Ρ

Ω

Dual Pressure to Ports 4 (4) & 2 (B)

2 Pressure Selector

* For Metric Gauge replace R with E in 4th digit

Pressure Range

10 - 130 PSIG (0.7 - 9 bar)

3 - 30 PSIG (0.2 - 2 bar) 3

4 5 - 60 PSIG (0.5 - 4 bar)

Mounting

Manifold Block w/ Side and Bottom Ports, Transfer board, used w/ RE Regulators Z0

Manifold Block w/ Side and Bottom Ports, Single Solenoid Internal Circuit Board Z1

72 Manifold Block w/ Side and Bottom Ports, Double Solenoid Internal Circuit Board

75 Z1 w/ Speed Control 76

Z2 w/ Speed Control =

Z1 w/ Ribbon Cable Connector R1 Z2 w/ Ribbon Cable Connector R2

Z5 w/ Ribbon Cable Connector

Z6 w/ Ribbon Cable Connector R6

NOTE: Regulator Gauges must be offset on alternating stations to prevent interference (see photo)


Odd numbered stations will use either standard (no option) or top facing ("16W" option) gauges Even numbered stations will use either extended standard ("61Y" option) or extended top facing ("63D" option) gauges




2012

2012 SERIES


single solenoid air pilot 2 position 4-way




double solenoid air pilot 2 position 4-way




double solenoid air pilot 3 position 4-way open center



double solenoid air pilot 3 position 4-way pressure center double solenoid air pilot 3 position 4-way closed center





5 Ported, 2 and 3 position, 4-way, Spool & Sleeve Cv: 1.2

- · Solenoid air pilot actuated
- · Low wattage coil
- DC solenoids polarity insensitive with spike suppression
- Plug together circuit boards eliminate internal wiring
- Integral recessed gaskets
- Interchangeable Push-In fittings to accommodate various tube sizes
- Simple conversion from internal to external pilot
- NEMA 4/IP65





Technical Data


Valve Data	English	Metric
Cv	1.20	1.20
Flow Capacity	56 SCFM @ 80 PSIG upstream pressure to atmosphere	1180 NI/m @ 6 bar upstream to 5 bar downstream
Operating Pressure Range	28" Hg Vacuum to 150 PSIG	Vacuum to 10 bar
Pilot Pressure Range	26 to 120 PSIG	1.8 to 8.2 bar
Temperature Range (Ambient)	-10 °F to 115 °F	-23 °C to 50 °C


Operating Data

All Solenoids are Continuous Duty Rated	24 VDC
Power (Watts)	2.5
Holding Current (Amps)	0.10

Response Time in Seconds	Energize	De-Energize
2-Position, Single, Spring Return	0.010	0.020
2-Position, Double, Detented	0.010	N/A
3-Position, Spring Centered	0.010	0.020


How to Order





2035 SERIES

single solenoid air pilot 2 position 4-way




315 (EB)(P)(EA)


double solenoid air pilot

2 position 4-way

double solenoid air pilot 3 position 4-way open center



double solenoid air pilot 3 position 4-way closed center



5 Ported, 2 and 3 position, 4-way, Spool & Sleeve Cv: 3.5

- Solenoid air pilot actuated
- · Low wattage coil
- DC solenoids polarity insensitive with spike suppression
- Plug together circuit boards eliminate internal wiring
- Integral recessed gaskets
- Simple conversion from internal to external pilot supply
- Designed to meet NEMA 4/IP65
- Manifold connection allows disassembly at any station





Technical Data

Valve Data	English	Metric
Cv	3.5*	3.5*
Flow Capacity	161 SCFM @ 80 PSIG upstream pressure to atmosphere	3500 NI/m @ 6 bar upstream pressure to 5 bar atmosphere
Operating Pressure Range	28" Hg Vacuum to 145 PSIG	Vacuum to 10 bar
Pilot Pressure Range	26.1 to 120 PSIG	1.8 to 8.2 bar
Temperature Range (Ambient)	-10 °F to 115 °F	-23 °C to 50 °C

^{*} Valve on 1/2 NPTF Sub-Plate


Operating Data


All Solenoids are Continuous Duty Rated	24 VDC
Power (Watts)	2.5
Holding Current (Amps)	0.10

Response Time in Seconds**	Energize	De-Energize
2-Position, Single, Spring Return	0.021	0.067
2-Position, Double, Detented	0.017	N/A
3-Position, Spring Centered	0.021	0.072

^{**} Per ISO 12238 Standard

How to Order: Valves





Transfer board, used w/ RE Regulators Z1 Manifold Block w/ Side and Bottom Ports,

Single Solenoid Internal Circuit Board Manifold Block w/ Side and Bottom Ports, **Z**2 Double Solenoid Internal Circuit Board

Z5 Z1 w/ Speed Control Z2 w/ Speed Control Z6

R1 Z1 w/ Ribbon Cable Connector Z2 w/ Ribbon Cable Connector Z5 w/ Rib on Cable Connector R5 R6 Z6 w /Ribbon Cable Connector




ISO 15407-2 18mm SERIES

ISO 15407


single solenoid air pilot 2 position 4-way



double solenoid air pilot 2 position 4-way



double solenoid air pilot 3 position 4-way open center



double solenoid air pilot 3 position 4-way closed center



5 Ported, 2 and 3 position, 4-way, Spool & Sleeve Cv: 0.56

- Solenoid air pilot actuated
- · Low wattage coil
- DC solenoids polarity insensitive with spike suppression
- Plug together circuit boards eliminate internal wiring
- Integral recessed gaskets
- Interchangeable Push-In fittings to accommodate various tube sizes
- Simple conversion from internal to external pilot
- NEMA 4/IP65



Technical Data - 18mm

Valve Data	English	Metric
Cv	0.56	0.56
Flow Capacity	26 SCFM @ 80 PSIG upstream pressure to atmosphere	552 NI/m @ 6 bar upstream to 5 bar downstream
Operating Pressure Range	28" Hg Vacuum to 150 PSIG	Vacuum to 10 bar
Pilot Pressure Range	26 to 120 PSIG	1.8 to 8.2 bar
Temperature Range (Ambient)	-10 °F to 115 °F	-23 °C to 50 °C


Operating Data

All Solenoids are Continuous Duty Rated	24 VDC
Power (Watts)	1.35
Holding Current (Amps)	0.056

Response Time in Seconds	Energize	De-Energize
2-Position, Single, Spring Return	0.014	0.016
2-Position, Double, Detented	0.013	N/A
3-Position, Spring Centered	0.014	0.016

SERIES ISO 15407

How to Order 15407-2 18mm: Valves




Z6

R1

Z2 w/ Speed Control Z1 w/ Ribbon Cable Connector

Z2 w/ Ribbon Cable Connector Z5 w/ Ribbon Cable Connector



Mounting

Z1 = Manifold Block w/ Side and Bottom Ports, Single Solenoid Internal Circuit Board
Z2 = Manifold Block w/ Side and Bottom Ports, Double Solenoid Internal Circuit Board

Z5 = Z1 w/ Speed Control

Z6 = Z2 w/ Speed Control

R1 = Z1 w/ Ribbon Cable Connector R2 = Z2 w/ Ribbon Cable Connector R5 = Z5 w/ Ribbon Cable Connector

R6 = Z6 w/ Ribbon Cable Connector

NOTE: Regulator Gauges must be offset on alternating stations to prevent interference (see photo)

Odd numbered stations will use either standard (no option) or top facing ("16W" option) gauges

Even numbered stations will use either extended standard ("61Y" opton) or extended top facing ("63D" option) gauges




ISO 15407-2 26mm SERIES

ISO 15407


single solenoid air pilot 2 position 4-way




double solenoid air pilot 2 position 4-way



double solenoid air pilot 3 position 4-way open center



double solenoid air pilot 3 position 4-way closed center



5 Ported, 2 and 3 position, 4-way, Spool & Sleeve Cv: 1.2

- Solenoid air pilot actuated
- · Low wattage coil
- DC solenoids polarity insensitive with spike suppression
- · Plug together circuit boards eliminate internal wiring
- Integral recessed gaskets
- Interchangeable Push-In fittings to accommodate various tube sizes
- Simple conversion from internal to external pilot
- Modular plug-together Fieldbus electronics
- NEMA 4/IP65



Technical Data - 26mm

Valve Data	English	Metric
Cv	1.20	1.20
Flow Capacity	56 SCFM @ 80 PSIG upstream pressure to atmosphere	1180 NI/m @ 6 bar upstream to 5 bar downstream
Operating Pressure Range	28" Hg Vacuum to 150 PSIG	Vacuum to 10 bar
Pilot Pressure Range	26 to 120 PSIG	1.8 to 8.2 bar
Temperature Range (Ambient)	-10 °F to 115 °F	-23 °C to 50 °C


Operating Data

All Solenoids are Continuous Duty Rated	24 VDC
Power (Watts)	2.5
Holding Current (Amps)	0.10

Response Time in Seconds	Energize	De-Energize
2-Position, Single, Spring Return	0.010	0.020
2-Position, Double, Detented	0.010	N/A
3-Position, Spring Centered	0.010	0.020

SERIES ISO 15407

How to Order 15407-2 26mm: Valves




R5


R6

Z5 w/ Ribbon Cable Connector

Z6 w/ Ribbon Cable Connector




Direct Solenoid Actuated



5 Ported, 4-way, 2 and 3 position, Spool & Sleeve, Cv: 1.2 to 5.3

- Direct and Solenoid Pilot Actuated
- Complies with ISO Standard 5599/2- Sizes 1, 2 & 3
- NEMA 4/IP65

Solenoid Pilot Actuated



Technical Data

Valve Data		Direct	Acting	Solenoid Pilot Actuated		
valve Data		English	Metric	English	Metric	
Cv	Size 1 Size 2 Size 3	1.2 2 NA	1.2 2 NA	1.3 2.9 5.3	1.3 2.9 5.3	
Flow Capacity	Size 1 Size 2 Size 3	55.5 SCFM 101.7 SCFM NA	1181 NI/m 2168 NI/m NA	60.1 SCFM 134.0 SCFM 245.0 SCFM	1280 NI/m 2857 NI/m 5222 NI/m	
Main valve operating pressure range - All sizes		80 PSIG upstream pressure to atmosphere	6 bar upstream to 5 bar downstream	80 PSIG upstream pressure to atmosphere	6 bar upstream to 5 bar downstream	
Pilot pressure range - All sizes		28" Hg to 232 PSIG	Vacuum to 16 bar	15 to 125 PSIG	1 to 8.6 bar	
Temperature Range (Ambient) - All sizes		-10 °F to 115 °F	-23 °C to 50 °C	-10 °F to 115 °F	-23 °C to 50 °C	

Operating Data - All solenoids continuous duty rated

All Solenoids are	24 VDC Di	rect Acting	24 VDC Solenoid Pilot		
Continuous Duty Rated	Sizes 1 & 2	Size 3	Size 1 & 2	Size 3	
Power (Watts) - All Sizes	6.0	NA	4.0	4.0	
Holding Current (Amps)	.25	NA	0.016	0.016	
In-Rush Current (Amps) - All Sizes	NA	NA	NA	NA	

Response Time in Seconds		Direct /	Acting		Solenoid Pilot Actuated					
	Energize	Sec) De-Energize (Sec)		Energize (Sec)		De-Energize (Sec)				
	Sizes 1 & 2	Size 3	Sizes 1 & 2	Size 3	Size 1	Size 2	Size 3	Size 1	Size 2	Size 3
2-Position, Single, Spring Return	0.038	NA	0.012	NA	0.013	0.013	0.020	0.036	0.060	0.066
2-Position, Double, Detented	0.012	NA	NA	NA	0.013	0.013	0.020	NA	NA	NA
3-Position, Spring Centered	0.038	NA	NA	NA	0.013	0.013	0.020	0.036	0.060	0.066


SERIES ISO 5599

R5

Z5 w/ Ribbon Cable Connector

Z6 w/ Ribbon Cable Connector

How to Order: Valves



* Not available in Direct Operated SA and SS Series

NOTE: Standard for all ISO 5599/2 Solenoid Pilot Valve Series is internal pilot supply from Port 1

R6

Regulators P 124 RS **Z**1 000 00 Valve Series & Port Size **Options** 112 ISO 5599/2 Size 1 1/4" 16N = ISO 5599/2 Size 1 3/8" Jumper on 14 (A) End 16P Jumper on 12 (B) End ISO 5599/2 Size 2 3/8" 123 = ISO 5599/2 Size 2 1/2" 000 = No Option 124 ISO 5599/2 Size 3 1/2" 134 **Port Type** ISO 5599/2 Size 3 3/4" NPTF Regulator Type G Tap Single Pressure to Port 1 (P) Dual Pressure to Ports 3 (EB) & 5 (EA) Wiring Option * RD = Plug-In Receptacle Assembly * RC Dual Pressure w/ Non-Relieving Checks Air Return (Sizes 2 & 3 Only) \cap Non-Plug-In (Type RE Only) RQ* Dual Pressure w/ Relieving Checks Mounting RE Dual Pressure, External Outlet Z0 Manifold Block w/ Side and Bottom Ports, Transfer board, used w/ RE Regulators Pressure Range Z1 Manifold Block w/ Side and Bottom Ports, 10 - 130 PSIG (0.7 - 9 bar) Single Solenoid Internal Circuit Board 3 3 - 30 PSIG (0.2 - 2 bar) Manifold Block w/ Side and Bottom Ports, Z2 4 5 - 60 PSIG (0.5 - 4 bar) Double Solenoid Internal Circuit Board 20 - 250 PSIG (1.4 - 17 bar) 6 75 Z1 w/ Speed Control Z2 w/ Speed Control Z6 Z1 w/ Ribbon Cable Connector R1 * Solenoid Pilot Valves used with RC, RD & RQ Regulators must R2 Z2 w/ Ribbon Cable Connector have the pilot supply from other than internally from Port 1 (P) R5 Z5 w/ Ribbon Cable Connector

Z6 w/ Ribbon Cable Connector

G3 POWER CABLES & CONNECTORS

7/8" MINI Cables

4 Pin Cables for DeviceNet™, DeviceLogix™, EtherNet/IP™ DLR, Modbus® TCP/IP, CANopen®, and Sub-bus



7/8" MINI Straight 4 Pin Female Single Ended Cable, Euro Color Code

MC0405MAC0000000 - 5 Meter

MC0410MAC0000000 - 10 Meter



7/8" MINI 90° 4 Pin Female Single Ended Cable, Euro Color Code

MD0405MAC0000000 - 5 Meter

MD0410MAC0000000 - 10 Meter



5 Pin Cables for PROFIBUS™ DP, PROFINET™, POWERLINK®, EtherCAT®, and CC-Link IE Field™

7/8" MINI Straight 5 Pin Female Single Ended Cable, Euro Color Code

MC0505MAG0000000 - 5 Meter

MC0510MAG0000000 - 10 Meter



7/8" MINI 90° 5 Pin Female Single Ended Cable, Euro Color Code

MD0505MAG0000000 - 5 Meter

MD0510MAG0000000 - 10 Meter



7/8" MINI Field Wireable Connectors

4 Pin Connectors for DeviceNet™, DeviceLogix™, EtherNet/IP™ DLR, Modbus® TCP/IP, CANopen®, and Sub-bus



7/8" MINI Straight 4 Pin Female Field Wireable Connector

MC04F9000000000 - Cable Gland - One size fits all



7/8" MINI 90° 4 Pin Female Field Wireable Connector

MD04F20000000000 - PG 9 Cable Gland



5 Pin Connectors for PROFIBUS™ DP, PROFINET™, POWERLINK®, EtherCAT®, and CC-Link IE Field™

7/8" MINI Straight 5 Pin Female Field Wireable Connector

MC05F9000000000 - Cable Gland - One size fits all



7/8" MINI 90° 5 Pin Female Field Wireable Connector

MD05F20000000000 - PG 9 Cable Gland



M12 to 7/8" MINI Cable

4 Pin Cable for Sub-bus Power



M12 Straight 4 Pin Male to 7/8" MINI 4 Pin Female Extension

TA0401MA0MC0471T - 1 Meter

TA0405MA0MC0471T - 5 Meter

TA0410MA0MC0471T - 10 Meter

M12 Cables



4 Pin Cables for Sub-bus Power

M12 Straight 4 Pin Female Single Ended Cable, Euro Color Code

TC0405MAE0000000 - 5 Meter

TC0410MAE0000000 - 10 Meter



M12 90° 4 Pin Female Single Ended Cable, Euro Color Code

TD0405MAE0000000 - 5 Meter

TD0410MAE0000000 - 10 Meter



M12 Straight 4 Pin Male to Female Cable Extension

TC0401MAETA04000 - 1 Meter

TC0405MAETA04000 - 5 Meter

TC0410MAETA04000 - 10 Meter

M12 Field Wireable Connectors

4 Pin Connectors for Sub-bus Power



M12 Straight 4 Pin Female Field Wireable Connector

TC04F10000000000 - PG 7 Cable Gland

TC04F20000000000 - PG 9 Cable Gland



M12 90° 4 Pin Female Field Wireable Connector

TD04F10000000000 - PG 7 Cable Gland


TD04F20000000000 - PG 9 Cable Gland

Pin Out and Technical Data

M12 Cable - Pin Out/Euro Color Code

(Male View)







7/8" MINI Cable - Pin Out/Euro Color Code

(Male View)









Technical Data	M12	7/8" MINI
Molded Body/Insert	Cable = PVC Field Wireable = Polyamide	Cable = PVC Field Wireable = Polyamide or PBT
Coupling Nut	Nickel Copper Alloy	Black Anodized Aluminum/Die Cast Zinc
Cable Jacket Material	PVC	PVC
Cable O.D.	7.4mm	7.4mm (4 Pin & 5 Pin)
Voltage Rating (Nominal)	250 V Max. @ 105 °C (221 °F)	250 V Max. @ 105 °C (221 °F)
Current Rating	Cables = 4.0 Amps Field Wireable = 4.0 Amps	Cables = 5.5 Amps Field Wireable = 8.0 Amps
Degree of Protection	IP67 (mated)	IP67 (mated)
Operating Temperature	-25 °C to 85 °C (-13 °F to 185 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	Cable = 18 AWG	Cable = 18 AWG
Bend Radius	Cable = 74mm	Cable = 74mm (4 Pin & 5 Pin)
Maximum Wire AWG	Field Wireable = 18 AWG	Field Wireable = 16 AWG
Wire Connection	Field Wireable = Screw Terminal	Field Wireable = Screw Terminal
PG 7 Range	4 – 6mm	N/A
PG 9 Range	6 – 8mm	5 – 13mm -One size fits all
PG 13.5 Range	N/A	5 – 13mm - One size fits all

G3 CANOPEN® AND DEVICENET™ CABLES & CONNECTORS













M12 Cable -Pin Out/Color Code (Male View)

(Male View)



7/8" MINI Drop Cables

7/8" MINI Straight 5 Pin Female Single Ended Cable - Shielded MC0505MGD0000000 - 5 Meter MC0510MGD0000000 - 10 Meter

M12 Drop Cables

M12 Straight 5 Pin Female Single Ended Cable - Shielded TC0505MGD0000000 - 5 Meter TC0510MGD0000000 - 10 Meter

7/8" MINI 3 Way "T"


3 Way 7/8" MINI "T" MC0500000MT05000

Terminating Resistors "TR"

7/8" MINI & M12 Straight 5 Pin Male Terminators TA05TR0000000000 - M12 Male MA05TR0000000000 - MINI Male

7/8" MINI Field Wireable Connectors

7/8" MINI Straight 5 Pin Field Wireable Connectors MC05F9000000000 - Female - Cable Gland - One size fits all MA05F9000000000 - Male - Cable Gland - One size fits all



Technical Data	Cable	T & TR	Field Wireable
Molded Body/Insert	PVC	PVC	Body = Glass Filled Polyamide
Coupling Nut	Nickel Plated Brass or Anodized Aluminum	Clear Anodized Aluminum	Black Anodized Aluminum
Cable Jacket Material	PVC	N/A	N/A
Cable O.D.	MINI = 8mm	N/A	5 – 13mm - One size fits all
Voltage Rating (Nominal)	150 Volts	T = 300 Volts	600 Volts
Current Rating	MINI = 4.0 Amps MR = 3.0 Amps	T = 8.0 Amps TR = NA	8.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP65 (mated)
Operating Temperature	-40 °C to 80 °C (-40 °F to 176 °F)	-40 °C to 105 °C (-40 °F to 221 °F)	-40 °C to 90 °C (-40 °F to 194 °F)
Conductor Gauge	22 AWG Power 24 AWG Signal	N/A	16 – 22 AWG
Bend Radius Minimum	Cable = 72mm	N/A	N/A
Wire Connection	NA	N/A	Screw Terminal

G3 CC-LINK IE FIELD™ CABLES & CONNECTORS


















(Male View)



M12 Straight 8 Pin Male Single Ended Cable - Shielded		
XA0905MR0000071P - 5 Meter		
XA0910MR0000071P - 10 Meter		

M12 Straight 8 Pin Male Double Ended Cable - Shielded		
XA0905MR0EA0971P - 5 Meter		
XA0910MR0EA0971P - 10 Meter		

M12 Straight 8 Pin Male to Male RJ45 Cable - Shielded			
XA0905MR0VA0971P - 5 Meter			
XA0910MR0VA0971P - 10 Meter			


M12 X-Coded Field Wireable Connector

M12 Straight 8 Pin Male Field Wireable Connector w/ IDC
XA09F2000000081E - PG 9 Cable Gland

RJ45 Field Wireable Connector

RJ45 Field Wireable Connector w/ IDC

VA09F2000000071N - PG 9 Cable Gland



Technical Data	Cable	M12 Field Wireable	RJ45 Field Wireable
Molded Body/Insert	TPU/PE	Nickel Plated Zinc/PP	Housing = PA Carrier = PC
Coupling Nut	Nickel Plated Zinc	Nickel Plated Zinc	NA
Cable Jacket Material	PUR	NA	NA
Cable O.D.	6.4mm	Accepts 4.0 to 8.0mm	Accepts 4.5 to 8.0mm
Voltage Rating (Nominal)	48 Volts	48 Volts	50 Volts
Current Rating	0.5 Amps	0.5 Amps	1.75 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP 65 (mated)
Operating Temperature	-20 °C to 80 °C (-4 °F to 176 °F)	-40 °C to 85 °C (-40 °F to 185 °F)	-40 °C to 70 °C (-40 °F to 158 °F)
Conductor Gauge	26 AWG	26 AWG	26 – 24 AWG
Bend Radius	51.2mm	NA	NA
Wire Connection	NA	IDC	IDC

G3 ETHERCAT® CABLES & CONNECTORS













M12 D-Coded Cable - Pin Out/Color Code

M12 D-Coded Cables

M12 Straight 4 Pin Male D-Coded Single Ended Cable

QA0405MT00000000 - 5 Meter

QA0410MT00000000 - 10 Meter

M12 Straight 4 Pin Male D-Coded Double Ended Cable

QA0405MT0QA04000 - 5 Meter

QA0410MT0QA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable

QA0405MT0VA04000 - 5 Meter

QA0410MT0VA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor

QA04D2MK0VC04000 - 0.2 Meter

M12 D-Coded Field Attachable Connectors

M12 Straight 4 Pin Male D-Coded Field Wireable Connector

QA04F2000000000 - PG 9 Cable Gland - Screw Terminal

M12 Straight 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QA04F200R000071N - PG 9 Cable Gland - IDC


RJ45 Field Attachable Connector

RJ45 Field Wireable Connector w/ IDC

VA08F200R000071N - PG 9 Cable Gland (1658435)







Technical Data	Cable	RJ45 Field Wireable	M12 Field Attachable
Molded Body/Insert	TPU/PE	Housing = PA Carrier = PC	Nickel Plated Zinc/PA 66
Coupling Nut	Nickel Plated Zinc	NA	Nickel Plated Brass
Cable Jacket Material	PVC	NA	NA
Cable O.D.	6.5mm	Accepts 4.5 to 8.0mm	Accepts 4.0 to 8mm
Voltage Rating (Nominal)	250 Volts	NA	60 Volts
Current Rating	4.0 Amps	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated), RJ45 – IP20	IP20	IP 65 (mated)
Operating Temperature	-40 °C to 70 °C (-40 °F to 158 °F)	-10 °C to 60 °C (14 °F to 140 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	22 & 24 AWG	22 AWG Solid/Stranded	Screw 24 - 18 AWG IDC 26 - 22 AWG
Bend Radius Minimum	19.5mm (fixed) 45.5mm (Flexible)	NA	NA
Wire Connection	NA	IDC	Screw Terminal, IDC

G3 ETHERNET/IP™ DLR AND MODBUS® TCP/IP CABLES & CONNECTORS











M12 D-Coded Cable - Pin Out/Color Code

M12 D-Coded Cables

M12 Straight 4 Pin Male D-Coded Single Ended Cable

QA0405MK00000000 - 5 Meter

QA0410MK00000000 - 10 Meter

M12 Straight 4 Pin Male D-Coded Double Ended Cable

QA0405MK0QA04000 - 5 Meter

QA0410MK0QA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable

QA0405MK0VA04000 - 5 Meter

QA0410MK0VA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor

QA04D2MK0VC04000 - 0.2 Meter

M12 D-Coded Field Wireable Connectors

M12 Straight 4 Pin Male D-Coded Field Wireable Connector

QA04F2000000000 - PG 9 Cable Gland - Screw Terminal

M12 Straight 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QA04F2000000071N - PG 9 Cable Gland - Screw Terminal


RJ45 Field Wireable Connector

RJ45 Field Wireable Connector w/ IDC

VA08F2000000071N - PG 9 Cable Gland

oded Cable - (Male View)





Technical Data	Cable	RJ45 Field Wireable	M12 Field Attachable
Molded Body/Insert	TPU, PA, PA66	Housing = PA Carrier = PC	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc or Brass	NA	Nickel Plated Brass
Cable Jacket Material	PUR or PVC	NA	NA
Cable O.D.	0.67 to 8.0mm	4.5 to 8.0mm	6.0 to 8.0mm
Voltage Rating (Nominal)	42 Volts	NA	60 Volts
Current Rating	1.5 Amps	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated)	IP20	IP 65 (mated)
Operating Temperature	-20 °C to 60 °C (-4 °F to 140 °F)	-20 °C to 70 °C (-4 °F to 158 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	26 & 24 AWG	26 – 22 AWG Solid/Stranded	Screw 24 - 18 AWG IDC 26 - 22 AWG
Bend Radius	40mm	NA	NA
Wire Connection	NA	IDC	IDC, Screw Terminal

G3 ETHERNET POWERLINK® CABLES & CONNECTORS




















QA0405MS0QA04000 - 5 Meter

M12 D-Coded Cables

M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable

M12 Straight 4 Pin Male D-Coded Double Ended Cable

QA0405MS0VA04000 - 5 Meter

QA0410MS0VA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Converter

QA04D2MK0VC04000 - 0.2 Meter

M12 D-Coded Field Attachable Connectors

M12 Straight 4 Pin Male D-Coded Field Wireable Connector

QA04F20000000000 - PG 9 Cable Gland - Screw Terminal

M12 Straight 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QA04F200R000071N - PG 9 Cable Gland - IDC

RJ45 Field Attachable Connectors


RJ45 Field Wireable Connector w/ IDC


VA08F200R000071N - PG 9 Cable Gland



(Male View)







Technical Data	Cable	RJ45 Field Attachable	M12 Field Attachable
Molded Body/Insert	N/A	Housing = PA Carrier = PC	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc or Brass	N/A	Nickel Plated Brass
Cable Jacket Material	PUR	N/A	N/A
Cable O.D.	6.5mm	Accepts 4.5 to 8.0mm	Accepts 6.0 to 8mm
Voltage Rating (Nominal)	N/A	N/A	60 Volts
Current Rating	N/A	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated), RJ45 – IP20	IP20	IP 65 (mated)
Operating Temperature	-25 °C to 60 °C (-13 °F to 140 °F)	-10 °C to 60 °C (14 °F to 140 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	22 AWG	22 AWG Solid/Stranded	Screw 24 - 18 AWG IDC 26-22 AWG
Bend Radius Minimum	45.5mm	N/A	N/A
Wire Connection	N/A	IDC	Screw Terminal, IDC

G3 PROFIBUS™ DP CABLES & CONNECTORS











M12 Reverse Key B-Coded Cables

M12 Straight 5 Pin Male Reverse Key Single Ended Cable - Shielded

RA0505MHP0000000 - 5 Meter

RA0510MHP0000000 - 10 Meter

M12 Straight 5 Pin Female Reverse Key Single Ended Cable - Shielded

RC0505MHP0000000 - 5 Meter

RC0510MHP0000000 - 10 Meter

M12 Straight 5 Pin MALE TO FEMALE Reverse Key EXTENSION CABLE

RC0505MHPRC05000 - 5 Meter

RC0510MHPRC05000 - 10 Meter

M12 Reverse Key B-Coded Field Wireable Connectors

M12 Straight 5 Pin Male Reverse Key Field Wireable Connector

RA05F200P0000000 - PG 9 Cable Gland

M12 Straight 5 Pin Female Reverse Key Field Wireable Connector

RC05F200P0000000 - PG 9 Cable Gland

M12 Reverse Key B-Coded Terminating Resistor


M12 Straight 5 Pin Male Reverse Key Terminating Resistor

RA05TR0000000000 - Male

M12 Reverse Key B-Coded Cable - Pin Out/Color Code

(Male View)





Technical Data	Cable	RJ45 Field Attachable	M12 Field Attachable
Molded Body/Insert	TPU	TR = TPU	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc	Nickel Plated Zinc or Brass	Nickel Plated Brass
Cable Jacket Material	PUR	N/A	N/A
Cable O.D.	7.4 mm	N/A	8.5 mm Max.
Voltage Rating (Nominal)	250 Volts	60 Volts	60 Volts
Current Rating	4.0 Amps	4.0 Amps	4.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP 65 (mated)
Operating Temperature	-20 °C to 80 °C (-4 °F to 176 °F)	-10 °C to 60 °C (14 °F to 140 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	24 AWG	N/A	18 AWG Maximum
Bend Radius	Cable = 78mm	N/A	N/A
Wire Connection	N/A	N/A	Screw Terminal

G3 PROFINET™ CABLES & CONNECTORS















M12 D-Coded Cable -Pin Out/Color Code

(Male View)







M12 Straight 4 Pin Male D-Coded Single Ended Cable

QA0405MR00000000 - 5 Meter

M12 D-Coded Cables

QA0410MR00000000 - 10 Meter

M12 Straight 4 Pin Male D-Coded Double Ended Cable

QA0405MR0QA04000 - 5 Meter

QA0410MR0QA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable

QA0405MR0VA04000 - 5 Meter

QA0410MR0VA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor

QA04D2MK0VC04000 - 0.2 Meter

M12 D-Coded Field Attachable Connectors

M12 Straight 4 Pin Male D-Coded Field Wireable Connector

QA04F2000000000 - PG 9 Cable Gland - Screw Terminal


M12 Straight 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QA04F200R000071N - PG 9 Cable Gland - IDC

RJ45 Field Attachable Connectors

RJ45 Field Wireable Connector w/ IDC

VA08F200R000071N - PG 9 Cable Gland



Technical Data	Cable	RJ45 Field Attachable	M12 Field Attachable
Molded Body/Insert	TPU	Housing = PA Carrier = PC	Body = Nickel Plated Zinc Insert = PA 66
Coupling Nut	Nickel Plated Zinc	N/A	Nickel Plated Brass
Cable Jacket Material	PVC	N/A	N/A
Cable O.D.	6.5 to 7.4mm	Accepts 4.5 to 8.0mm	Accepts 6.0 to 8mm
Voltage Rating (Nominal)	250 Volts	N/A	60 Volts
Current Rating	4.0 Amps	1.75 Amps	Screw 4.0 Amps IDC 1.75 Amps
Degree of Protection	IP65 (mated), RJ45 – IP20	IP20	IP 65 (mated)
Operating Temperature	-25 °C to 60 °C (-13 °F to 140 °F)	-10 °C to 60 °C (14 °F to 140 °F)	-40 °C to 85 °C (-40 °F to 185 °F)
Conductor Gauge	22 & 24 AWG	22 AWG Solid/Stranded	Screw 24-18 AWG IDC 26-22 AWG
Bend Radius Minimum	19.5mm (fixed) 45.5mm (Flexible)	N/A	N/A
Wire Connection	N/A	IDC	Screw Terminal, IDC

G3 I/O CABLES & CONNECTORS

I/O Cables with SPEEDCON® Connector Technology

















TA04E5MIE000071P – 1.5 Meter

TA0403MIE000071P - 3 Meter

TA0405MIE000071P - 5 Meter

M12 90° 4 Pin Male Single Ended Cable, Euro Color Code

TB04E5MIE000071P - 1.5 Meter

TB0403MIE000071P - 3 Meter

TB0405MIE000071P - 5 Meter

M12 Straight 4 Pin Male to Female Cable Extension

TC04E5MIETA0471P - 1.5 Meter

TC0403MIETA0471P - 3 Meter

M12 Straight 3 Pin Male to M8 3 Pin Straight Female Extension

TC03E5MIEPA0371P - 1.5 Meter

TC0303MIEPA0371P - 3 Meter

M8 3 Pin Straight Male to M8 3 Pin Straight Female Extension

PC03E5MIEPA0371P - 1.5 Meter

PC0303MIEPA0371P - 3 Meterr

I/O Connectors

M12 Straight 4 Pin Male Field Wireable Connector, IDC Connection

TA04F2000000081E - PG 9 Cable Gland w/ SPEEDCON® connector technology

M12 Straight 4 Pin Male Field Wireable Connector, Screw Terminal

TA04F10000000000 - PG 7 Cable Gland

TA04F20000000000 - PG 9 Cable Gland

M12 90° 4 Pin Male Field Wireable Connector, Screw Terminal

TB04F10000000000 - PG 7 Cable Gland

TB04F20000000000 - PG 9 Cable Gland

I/O Splitters

M12 to M12 "Y" Splitter, 21mm Spacing

TA0500000JC05000

M12 to M8 "Y" Splitter

TA0400000KC03000







TA04D3MIEJC04000 - 0.3 Meter

TA04E5MIEJC04000 - 1.5 Meter

TA0403MIEJC04000 - 3.0 Meter



M12 Cable Splitter, 2 Straight M8 Female Connectors

TA04D3MIEKC03000 - 0.3 Meter

TA04E5MIEKC03000 - 1.5 Meter

TA0403MIEKC03000 - 3.0 Meter



Wire Stripper Tool

140-1097

I/O Cable Connector Pin Out Diagrams

M12 Cable - Pin Out/Color Code

TA04XXMIE0000000. TB04XXMIE0000000

(Male View)

M12 Cable - Pin Out/Color Code

TC03XXMIEPA0371P

(Male to Female View)

M12 Cable - Pin Out/Color Code

TC03XXMIEPA0371P

(Male to Female View)








M12 to M12 "Y" Splitter - Pin Out

TA0500000JC05000


(Male to Female View)



M12 to M8 "Y" Splitter - Pin Out

TA0400000KC03000

(Male to Female View)



M12 Field Wireable (IDC) - Pin Out

TA04F2000000081E (SPEEDCON®)


(Male View)



M12 to M12 Cable Splitter - Pin Out M12 to M8 Cable Splitter - Pin Out


TA04XXMIEJC04000

(Male to Female View)



TA04XXMIEKC03000

(Male to Female View)



M8 Cable - Pin Out/Color Code

PC03XXMIEPA0371P

(Male to Female View)



NOTE:

XX denotes allowable length. See pages 101 & 102.

Cable and Connector Technical Data

Technical Data	M12 Cables	M12/M8 Cables	M12 Connectors
Molded Body/Insert	TPU	TPU	Polyamide (or) PA 66
Coupling Nut	Nickel Plated Zinc	Nickel Plated Zinc	Nickel Plated Zinc
Cable Jacket Material	PUR	PUR	NA
Cable O.D.	4.70mm	4.70mm	PG7 4.0 to 6.0mm PG9 4.0 to 8.0mm
Voltage Rating	250 Volts	60 Volts	50 Volts
Current Rating (Cond.)	4.0 Amps	3.0 Amps	4.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP67 (mated)
Operating Temperature	-25 °C to 80 °C (-13 °F to 176 °F) (fixed instl.)	-25 °C to 80 °C (-13 °F to 176 °F) (fixed instl.)	-25 °C to 80 °C (-13 °F to 176 °F)
Conductor Gauge	22 AWG	22 AWG	22 AWG Min. 18 AWG Max.
Bend Radius	47mm	47mm	NA

Technical Data	I/O "Y" Splitter	I/O Cable Splitter	M8 Cables
Molded Body/Insert	TPU	TPU	TPU
Coupling Nut	Nickel Plated Zinc	Nickel Plated Zinc	Nickel Plated Zinc
Cable Jacket Material	NA	PUR	PUR
Cable O.D.	NA	4.40mm	1.17mm
Voltage Rating	60 Volts	60 Volts	60 Volts
Current Rating (Cond.)	3.0 Amps	3.0 Amps	4.0 Amps
Degree of Protection	IP67 (mated)	IP67 (mated)	IP67 (mated)
Operating Temperature	-25 °C to 90 °C (-13 °F to 194 °F)	-25 °C to 80 °C (-13 °F to 176 °F)	-25°C to 90°C (-13 °F to 194°F)
Conductor Gauge	NA	22 AWG or 24 AWG	24 AWG
Bend Radius	NA	44mm	44mm

Technical Data	Wire Stripper	
Use with	PVC Insulation	
Stripping Range	28 AWG to 10 AWG	
Cutting Range (Flexible)	10 AWG	
Cutting Range (Rigid)	12 AWG	

M23 19 PIN CABLES & CONNECTORS



M23 19 Pin Cables

M23 19 Pin Female Single Ended Cable

CC1905MI00000000 - 5 Meter

CC1910MI00000000 - 10 Meter

M23 19 Pin Male Single Ended Cable

CE1905MI00000000 - 5 Meter

CE1910MI00000000 - 10 Meter

M23 19 Pin Female to Male Double Ended Cable

CC1902MI0CE19000 - 2 Meter

CC1905MI0CE19000 - 5 Meter

CC1910MI0CE19000 - 10 Meter

M23 19 Pin Connectors

M23 19 Pin Female Field Wireable Connector, Solder Cup

CC19000000000000 - PG 13.5 Cable Gland

M23 19 Pin Cable -Pin Out/Color Code

(Male View)



(Female View)



Conductor	Cable
Pin 1	White
Pin 2	Brown
Pin 3	Green
Pin 4	Yellow
Pin 5	Gray
Pin 6	Pink
Pin 7	Blue
Pin 8	Red
Pin 9	Black
Pin 10	Purple

Conductor	Cable
Pin 11	Gray/Pink
Pin 12	Green/Yellow
Pin 13	White/Green
Pin 14	Brown/Green
Pin 15	White/Yellow
Pin 16	Yellow/Brown
Pin 17	White/Gray
Pin 18	Gray/Brown
Pin 19	Red/Blue

Technical Data	Cable	Connector
Molded Body/Insert	PA66	PBT
Coupling Nut	Gadolinium-Zinc Plated Brass	Gadolinium-Zinc Plated Brass/ Nickel Plated Brass
Cable Jacket Material	PUR/PVC	N/A
Cable O.D.	10.5mm	Accepts 10.0 to 12.0mm
Voltage Rating (Nominal)	150 Volts	150 Volts
Current Rating	8.0 Amps	8.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)
Operating Temperature	-40 °C to 80 °C (-40 °F to 176 °F)	-20 °C to 80 °C (-4 °F to 176 °F)
Conductor Gauge	18 & 20 AWG	18 AWG
Bend Radius Minimum	78.75mm	N/A
Wire Connection	N/A	Solder Cup

SUB-BUS CABLES & CONNECTORS

Sub-bus Cables



M12 Straight 5 Pin Male to Female Sub-bus Cable - Shielded

TA0501MGDTC0571P - 1 Meter

TA0505MGDTC0571P - 5 Meter

TA0510MGDTC0571P - 10 Meter



M12 Straight 5 Pin Female Field Wireable Connector, Spring Cage

TC05F2000000071V - PG9 Cable Gland



M12 Straight 5 Pin Male Field Wireable Connector, Spring Cage

TA05F2000000071V - PG9 Cable Gland



M12 90° 5 Pin Female Field Wireable Connector, Spring Cage

TD05F2000000071V - PG9 Cable Gland



M12 90° 5 Pin Male Field Wireable Connector, Spring Cage

TB05F2000000071V - PG9 Cable Gland



Bulk Sub-bus Cable*

 $000550 MGD0005000-50\ Meter\ Length$

0005A0MGD0005000 - 100 Meter Length


Technical Data

Technical Data	Cable	Connectors	Bulk Cable
Molded Body / Insert	TPU	Zinc - Nickel Plated	N/A
Coupling Nut	Zinc - Nickel Plated	Brass - Nickel Plated	N/A
Cable Jacket Material	PUR	N/A	Gray RAL 7001
Cable O.D.	6.70mm	N/A	6.70mm
Voltage Rating (Nominal)	60 Volts	60 Volts	60 Volts
Current Rating	4.0 Amps	4.0 Amps	4.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP65 (terminated)
Operating Temperature	-40 °C to 80 °C (-40 °F to 176 °F)	-40 °C to 80 °C (-40 °F to 176 °F)	-20 °C to 75 °C (-4 °F to 167 °F)
Conductor Gauge	24 AWG Signal 22 AWG Power	26 – 20 AWG	24 AWG Signal 22 AWG Power
Bend Radius	67mm	N/A	67mm
No. of Bending Cycles	5 Million	N/A	5 Million

^{*} NOTE: Length of field wired cables should not exceed the maximum length of 30 meters for total Sub-bus communications link. See appropriate technical manual for Sub-bus length requirements. The cable assemblies and Bulk cable are the only approved cables for the G3 Sub-bus link. See technical document TDG3SBWD1-0EN for proper installation and wiring of field wireable connectors.



Example Sub-bus Layout and Cabling (DeviceNet™/CANopen® Network)



Cable	Description	Example Cable Part #	Page
	Power Cable	MC0405MAC0000000	97
	Alternate Sub-bus Power Option	TA0401MA0MC0471T	98
• • • • • • • • • • • • • • • • • • • •	DeviceNet™/CANopen [®] Communication Cable	MC0505MGD0000000	100
	I/O Field Wireable Connector	TA04F2000000081E	107
	I/O Connector with Molded Cable	TA0405MIE000071P	107
	Sub-bus Cable	TA0501MGDTC0571P	111

580 Fieldbus - Electronics Made Easy!

Innovative Graphic Display is used for easy commissioning, visual status & diagnostics.

Commissioning Capabilities

- Set network address (including IP & Subnet mask for Ethernet)
- · Set baud rate
- Set brightness
- · Set factory defaults

Visual Diagnostics

- Shorted and open load detection
- Shorted sensor/cable detection
- Low & missing power detection
- · Self-test activation
- Log of network errors

580 Fieldbus Communications Electronics

Why use AVENTICS Fieldbus communications electronics? Modular Reality...

- No internal wiring simplifies assembly
- Power connector allows output power to be removed while inputs and communications are left active
- IP65 protection
- Up to 128 valve solenoids per manifold
- Direct Connection to Emerson DeltaV[™] with Electronic Marshalling platform via the 580 CHARM Node
- 500 Series valve compatibility



Graphic Display for configuration & diagnostics

Supported Protocols

- CANopen®
- DeviceNetTM
- EtherCAT®
- EtherNet/IP™ DLR
- Ethernet POWERLINK®
- IO-Link®*
- PROFIBUS™ DP
- PROFINETTM

* IO-Link® is a communication network that requires an IO-Link® Master with a higher level fieldbus or Ethernet communication protocol.







EtherNet/IP and DeviceNet are trademarks of ODVA.

Ethernet POWERLINK is a registered trademark of Bernecker + Rainer Industrie – Elektronik Ges.m.b.H.

CANopen is a registered Community trademark of CAN in Automation e.V.

PROFIBUS and PROFINET are trademarks and IO-Link is a registered trademark of Profibus Nutzerorganisation e.V.

EtherCAT is a registered trademark of Beckhoff Automation GmbH.

CANopen®

CANopen® is an open protocol based on Controller Area Network (CAN). It was designed for motion-oriented machine control networks but has migrated to various industrial applications. CAN in Automation (CIA) is the international users' and manufacturers' organization that develops and supports CAN-based protocols.

AVENTICS' 580 nodes for CANopen® have an integrated graphic display.

More information about CANopen® and the CIA can be found at: www.can-cia.org.



Description	Replacement Part Number
CANopen® communications module (node)	P580AECO1010A00

Technical Data

Electrical Data	Voltage	Current	
Node Power	24 VDC +/- 10%	0.007 Amps	
Bus Power	11 – 25 VDC	0.05 Amps	
Valves	24 VDC +/- 10%	4 Amps Maximum	
Power Connector	A-Coded 4 Pin M12 (Male)	A-Coded 4 Pin M12 (Male)	
Communication Connector	A-Coded 5 Pin M12 (Male)	A-Coded 5 Pin M12 (Male)	
LEDs	Module Status and Network Status		

Operating Data		
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)	
Humidity	95% relative humidity, non-condensing	
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6	
Moisture Protection	IP65	

Configuration Data	
Graphic Display	Display used for setting Node Address, Baud Rate, Fault/Idle Actions, and all other system settings
Maximum Valve Solenoid Outputs	32

Network Data	
Supported Baud Rates	125K Baud, 250K Baud, 500K Baud, 1M Baud
Bus Connector	Single key 5 Pin M12 (male)
Diagnostics	Power, short, open load conditions are monitored
Special Features	Fail-safe device settings

	Weight
CANopen® Communications Module	320g/11.3 oz



DeviceNet™

DeviceNet™ is an open bus fieldbus communication system developed by Allen-Bradley based on Controller Area Network (CAN) technology. The governing body for DeviceNet™ is the Open DeviceNet™ Vendors Association (ODVA). The ODVA controls the DeviceNet™ specification and oversees product conformance testing.

AVENTICS' 580 nodes for DeviceNet[™] have an integrated graphic display.

They have been tested and approved for conformance by the ODVA.

More information about DeviceNet[™] and the ODVA can be obtained from the following website: www.odva.org



Description	Replacement Part Number
DeviceNet™ Communications Module (node)	P580AEDN1010A00

Electrical Data	Voltage	Current
Node Power	24 VDC +/- 10%	0.05 Amps
Bus Power	11 – 25 VDC	0.05 Amps
Valves	24 VDC +/- 10%	4 Amps Maximum
Power Connector	A-Coded 4 Pin M12 (Male)	
Communication Connector	A-Coded 5 Pin M12 (Male)	
LEDs	Module Status and Network Status	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65

Configuration Data	
Graphic Display	Display used for setting Node Address, Baud Rate, Fault/Idle Actions, and all other system settings
Maximum Valve-Solenoid Outputs	32

Network Data	
Supported Baud Rates	125K Baud, 250K Baud, 500K Baud, with Auto-Baud detection
Supported Connection Type	Polled, Cyclic, Change of State (COS) and combination Message Capability
Bus Connector	Single key 5 Pin M12 (male)
Diagnostics	Power, short, open load conditions are monitored
Special Features	Supports Auto-Device Replacement (ADR) and fail-safe device settings

Weight		
DeviceNet™ Communications Module	320g/11.3 oz	





EtherCAT®

EtherCAT® is an open ethernet based fieldbus protocol developed by Beckhoff. EtherCAT® sets new standards for real-time performance and topology flexibility with short data update/cycle times and low communication jitter.

AVENTICS' 580 EtherCAT® node has an integrated graphic display for simplified commissioning and diagnostics.

The 580 nodes for EtherCAT® have been designed and tested to conform with EtherCAT® specifications set forth by the ETG.

More information regarding EtherCAT® can be obtained from the following website: www.ethercat.org



Description	Replacement Part Number
EtherCAT [®] Communications Module (node)	P580AEEC1010A00

Electrical Data	Voltage	Current
Node Power	24 VDC +/- 10%	0.11 Amps
Valves	24 VDC +/- 10%	4 Amps Maximum
Power Connector	Single key 5 Pin M12 (male)	
Communication Connector	Two D-Coded 4 Pin M12 (female)	
LEDs	Error/Run	

Operating Data	
Temperature Range	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC 60068-2-6
Moisture	IP65

Configuration Data	
Graphic Display	Display used for Subnet Mask, Fault/Idle Actions, and all other system settings
Maximum Valve Solenoid Outputs	128 for 501 and 80 for 502/503

Network Data	
Supported Baud Rates	10 Mbit/100 Mbit
Bus Connector	Two D-Coded 4 Pin M12 (female)
Diagnostics	Power, short, open load conditions and module health and configuration are monitored
Special Features	Integrated web server, fail-safe device settings

Weight		
EtherCAT® Communications Module	332g/11.7 oz	



EtherNet/IP™ DLR

EtherNet/IPTM used throughout the world to network millions of PCs has now evolved into a viable industry network. EtherNet/IPTM is an open architecture high-level communication network that meets the demands of today's industrial applications requiring high-speed (10/100 Mbit/s), high-throughput and flexibility. Additionally, EtherNet/IPTM technology can integrate an on-board Web server, which can make the node readily accessible to any standard Web browser for configuration, testing and even retrieval of technical documentation.

AVENTICS' 580 EtherNet/IP™ DLR (Device Level Ring) node with integrated display, has an embedded switch which allows the unit to be used in simplified networks with linear topology configurations (daisy chain). This technology alleviates the need for an external Ethernet switch device in a single subnet configuration. Additionally, the DLR compatibility allows the node to be used in a fault tolerant "ring" network, when using appropriate EtherNet/IP™ DLR scanners. DLR configuration allows communication recovery from a single point failure on the network ring (e.g. failed network connection or cable).



Description	Replacement Part Number
EtherNet/IP™ DLR Communications Module (node)	P580AEED1010A00

The 580 EtherNet/IP $^{\text{TM}}$ nodes have been tested and approved for conformance by the ODVA.

More information about EtherNet/IP and the ODVA can be obtained from the following website: www.odva.org

Electrical Data	Voltage	Current
Node Power	24 VDC +/- 10%	0.09 Amps
Valves	24 VDC +/- 10%	4 Amps Maximum
Power Connector	A-Coded 4 Pin M12 (male)	
Communication Connector	Two D-Coded 4 Pin M12 (female)	
LEDs	Module Status, Network Status and Activity/Link	

Operating Data	
Temperature Range	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC 60068-2-6
Moisture	IP65

Configuration Data	
Graphic Display	Display used for setting IP address, Subnet Mask, Fault/Idle Actions, and all other system settings
Maximum Valve Solenoid Outputs	128 for 501 and 80 for 502/503

Network Data	
Supported Baud Rates	10 Mbit/100 Mbit
Bus Connector	Two D-Coded 4 Pin M12 (female)
Diagnostics	Power, short, open load conditions and module health and configuration are monitored
Special Features	Embedded two port switch, Device Level Ring (DLR) compatibility, Linear network topology, fail-safe device settings, integrated web server, HTTP, TFTP, UNICAST

Weight	
EtherNet/IP™ DLR Communications Module	337g/11.9 oz



Ethernet POWERLINK®

Ethernet POWERLINK® is an open fieldbus protocol designed by B&R for communication between automation control systems and the device level.

AVENTICS' 580 nodes for Ethernet POWERLINK® have an integrated graphic display.

The 580 Ethernet POWERLINK® nodes have been designed and tested to conform to the Ethernet POWERLINK® specifications available at EPSG group (Ethernet Powerlink Standardization Group). The certification process ensures interoperability for all Ethernet POWERLINK® devices and compatibility with B&R systems.

More information regarding Ethernet POWERLINK® can be obtained from the following website: www.ethernet-powerlink.org



Description	Replacement Part Number
POWERLINK [®] Communications Module (node)	P580AEPL1010A00

Electrical Data	Voltage	Current
Node Power	24 VDC +/- 10%	0.09 Amps
Valves	24 VDC +/- 10%	4 Amps Maximum
Power Connector	Single Key 5 Pin M12 (male)	
Communication Connector	Two D-Coded 4 Pin M12 (female)	
LEDs	Error, Status and Activity/Link	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture	IP65

Configuration Data	
Graphic Display	Display used for setting IP address, Subnet Mask, Fault/Idle Actions, and all other system settings
Maximum Valve Solenoid Outputs	128 for 501 and 80 for 502/503

Network Data	
Supported Baud Rates	10 Mbit/100 Mbit
Bus Connector	Two D-Coded 4 Pin M12 (female)
Diagnostics	Power, short, open load conditions and module health and configuration are monitored
Special Features	Integrated web server and fail-safe device settings

Weight	
POWERLINK® Communications Module	Class A: 328g/11.6 oz



IO-Link® (Class A & Class B)

IO-Link® is a globally standardized IO technology (IEC 61131-9) developed primarily for communication with smart sensors and actuators that can also be used with valves and other field devices. IO-Link® is used to individually link field devices and resides below the I/O level. An IO-Link® Master with a higher level fieldbus or Ethernet communication protocol is required. The IO-Link Consortium, which is a technical committee within PROFIBUS™ & PROFINET™ International (PI), oversees and manages IO-Link® specifications.

AVENTICS' IO-Link® communications node offers both event based as well as standard I/O mapped diagnostics, requires minimal commissioning, and is compatible with distributed modular I/O. Supports both Class A (4 Pin) and Class B (5 Pin with isolated ground) communication port types.

More information regarding IO-Link® can be obtained from the following website: www.io-link.com



Description	Replacement Part Number
IO-Link [®] Class A (4 Pin) Communications Module (node)	P580AELM1010A00
IO-Link [®] Class B (5 Pin) Communications Module (node)	P580AELM2010A00

Electrical Data	Voltage	Current
Node Power	24 VDC +/- 10%	0.020 Amps
Valves	24 VDC +/- 10%	4 Amps Maximum
Power and Communication Connector	Class A: A-Coded 4 Pin M12 (male)/Class B: A-Coded 5 Pin M12 with isolated ground (male)	
LEDs	Valve Power, Node Power and Communication	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% Relative Humidity, Non-condensing
Vibration/Shock	IEC 60068-2-27, IEC 60068-2-6
Moisture	IP65

Configuration Data	
Maximum Valve Solenoid Outputs	32

Network Data	
Supported Baud Rates	38.4K
Diagnostics	Power, short, open load conditions with both standard I/O mapped diagnostics and event based diagnostics
Special Features	Fail-safe device settings

Weight	
IO-Link® Communications Module	Class A: 298g/10.5 oz, Class B: 303g/10.7 oz



PROFIBUS™ DP

PROFIBUS™ DP is a vendor-independent, open fieldbus protocol designed for communication between automation control systems and distributed I/O at the device level.

AVENTICS' 580 nodes for PROFIBUS™ DP have an integrated graphic display.

The 580 nodes for PROFIBUS™ DP have been designed and tested to conform to the PROFIBUS™ standard EN50170. Certification has been done by the PROFIBUS™ Interface Center (PIC) according to the guidelines determined by the PROFIBUS™ Trade Organization (PTO). The certification process ensures interoperability for all PROFIBUS™ devices.

More information regarding PROFIBUS™ can be obtained from the following website: www.profibus.com



Description	Replacement Part Number
PROFIBUS™ DP Communications Module (node)	P580AEPT1010A00

Electrical Data	Voltage	Current
Node Power	24 VDC +/- 10%	0.08 Amps
Valves	24 VDC +/- 10%	4 Amps Maximum
Power Connector	A-Coded 5 Pin M12 (male)	
Communication Connector	Single reverse key (B-Coded) 5 Pin M12 (1 male and 1 female	e)
LEDs	Module Status and Network Status	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65

Configuration Data	
Graphic Display	Display used for setting Node Address, Fault/Idle Actions, and all other system settings
Maximum Valve-Solenoid Outputs	128 for 501 and 80 for 502/503

Network Data	
Supported Baud Rates	Auto-Baud (From 9.6k to 12m Baud)
Bus Connector	Single reverse key (B-Coded) 5 Pin M12 (1 male and 1 female)
Diagnostics	Power, short, open load conditions and module health are monitored

Weight	
PROFIBUS™ DP Communications Module	326g/11.5 oz



PROFINET™

PROFINET™ is the innovative open standard for Industrial Ethernet, development by Siemens and the Profibus™ User Organization (PNO). PROFINET™ complies to IEC 61158 and IEC 61784 standards. PROFINET™ products are certified by the PNO user organization, guaranteeing worldwide compatibility.

AVENTICS' 580 nodes for PROFINET™ IO (PROFINET™ RT) have an integrated graphic display.

PROFINET™ is based on Ethernet and uses TCP/IP and IT standards and complements them with specific protocols and mechanisms to achieve Real Time performance.

More information regarding PROFINET™ can be obtained from the following website: www.profibus.com



Description	Replacement Part Number
PROFINET™ Communications Module (node)	P580AEPN1010A00

Electrical Data	Voltage	Current
Node Power	24 VDC +/- 10%	0.11 Amps
Valves	24 VDC +/- 10%	4 Amps Maximum
Power Connector	A-Coded 5 Pin M12 (male)	
Communication Connector	Two D-Coded 4 Pin M12 (female)	
LEDs	System Fault, Bus Fault and Activity Link	

Operating Data	
Temperature Range (ambient)	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% relative humidity, non-condensing
Vibration/Shock	IEC 60068-2-27, IEC60068-2-6
Moisture Protection	IP65

Configuration Data	
Graphic Display	Display used for setting IP Address, Subnet Mask, Fault/Idle Actions, and all other system settings
Maximum Valve-Solenoid Outputs	128 for 501 and 80 for 502/503

Network Data	
Supported Baud Rates	10 Mbit/100 Mbit
Bus Connector	Two D-Coded 4 Pin M12 (Female)
Diagnostics	Power, short, open load conditions and module health and configuration are monitored
Special Features	Integrated web server, Integrated 2 port switch, fail-safe device settings

Weight	
PROFINET™ Communications Module	335g/11.8 oz

580 CHARM Node

The 580 CHARM node provides direct connectivity of pneumatic manifolds to DeltaV with Electronic Marshalling. The node connects directly to the CHARM I/O baseplate via 2 cables which attach to CHARM column extender. The cables provide redundant communication and power to the pneumatic manifold and allow the 580 CHARM node to be directly controlled by DeltaV Explorer. The 580 CHARM node configures the same as a DO CHARM.



Description	Replacement Part Number
580 CHARM Module (node)	P580AECH2010A00

Electrical Data	Voltage	Current
Bus Power	6.3 V	100 mA
Valve Power	24 V	1.07 Amps
Power and Bus Connector	A-Coded 5 Pin M12 Male	
LEDs	Module Status and Network Status	

Operating Data	
Temperature Range	-23 °C to 50 °C (-10 °F to 122 °F)
Humidity	95% Relative Humidity, Non-condensing
Vibration/Shock	IEC 60068-2-27, IEC 60068-2-6
Moisture	IP65


Configuration Data	
Graphic Display	Display used for setting CHARM address and other system settings
Maximum Valve Solenoid Outputs	96 for 501, 64 for 502 / 503


Network Data	
Power and Bus Connector	A-Coded 5 Pin M12 Male
Diagnostics	Power, short, open load conditions are monitored

Weight	
CHARM Communications Module	320g/11.3 oz

CHARM Communication & Power Connection

The front panel of the communication module is equipped with a 5 pin M12.






Both Cables provide 6.3 V for Comm. and 24 V for valve Power

Accessories for CHARM

Accessory	Description	Order Code
-	1.5 Meter Cable with M12 and Sub-D Connectors (Moulded version)	P599AF519387001
-	0.5 Meter Cable with M12 and Sub-D Connectors (Moulded version)	P599AF519387002
ASTO DAY, FRANCISCO	Valve Power Isolator M12-Y	P599AF516881001
-	Cable kit to connect 2 CHARM modules for 96 coils capability maximum	P599AF533776001


NOTE: Cables are not included with node and must be ordered separately.




Dimensions: mm (inches)

580 Fieldbus Manifold Assembly

503 Series Valve Manifold Assembly with 580 Electronics






Α	В	С	D	E	F	G	Н	J	K	L	М	N	Р	Q	R
77	7.5	38	147.1	180	39.1	75.8	7.5	113	101	194	49.4	68.1	53	54	55.1
(3.032)	(0.295)	(1.5)	(5.79)	(7.087)	(1.539)	(2.984)	(0.295)	(4.449)	(3.976)	(7.638)	(1.945)	(2.681)	(2.087)	(2.13)	(2.169)

^{*} For valve manifold dimensions refer to Valve Series product catalogs


How to Order: Manifold Assembly



How to Order

Electronics

- ³ With 502 11mm (501) valve available, with 503 18mm (502) valve available
- ⁴ 501 Port Sizes 1/8, 1/4, 5/16, 8mm, 502 and 530 Port Sizes 3/8, 1/2, 10 and 12mm







stations and with up to 80 valve solenoids

Ordering Valve Manifold Assemblies with 580 Electronics

For Valve Series





Shaded components are described by the manifold assembly number (see previous page). The communications module is described by the electronic interface model number designation (see previous page).

Each valve station is listed in sequential order from left to right when facing the port side of the manifold as shown.

NOTE:

Up to 128 solenoid outputs are available. Either 128 single solenoid valves or 64 double solenoid valves or any combination of singles and doubles not to exceed 128 outputs can be specified.

Example Order - 503 Shown

Assembly Kit	8503AV8H300VMUF
Valve Station #1	R503A2B40MA00F1
Valve Station #2	R503A2B40MA00F1
Mounting #1	8503AMM22MA0010
Valve Station #3	R503A2B40MA00F1
Valve Station #4	R503A2B40MA00F1
Mounting #2	8503AMM22MA0010
Valve Station #5	R503A2B40MA00F1
Valve Station #6	R503A2B40MA00F1
Mounting #3	8503AMM22MA0010
Valve Station #7	R503A2B40MA00F1
Valve Station #8	R503A2B40MA00F1
Mounting #4	8503AMM22MA0010
Electronics	P580AEDN1010A00
	Assembled

POWER CABLES & CONNECTORS

M12 A-Coded Cables



M12 Straight 4 Pin Female Single Ended Cable, Euro Color Code
TC0405MAE0000000 – 5 Meter
TC0410MAE0000000 – 10 Meter

M12 Straight 5 Pin Female Single Ended Cable, Euro Color Code

TC0505MAE0000000 – 5 Meter

TC0510MAE0000000 - 10 Meter



M12 90° 4 Pin Female Single Ended Cable, Euro Color Code

TD0405MAE0000000 - 5 Meter

TD0410MAE0000000 - 10 Meter

M12 90° 5 Pin Female	Single Ended Cable, Euro Color Code
TD0505MAE0000000 - 5 Meter	

TD0510MAE0000000 - 10 Meter

M12 A-Coded Field Wireable Connectors



M12 Straight 4 Pin Female Field Wireable Connector
TC04F1000000000 - PG 7 Cable Gland
TC04F2000000000 - PG 9 Cable Gland

M12 Straight 5 Pin Female Field Wireable Connector

TC05F10000000000 – PG 7 Cable Gland TC05F20000000000 – PG 9 Cable Gland



M12 90° 4 Pin Female Field Wireable Connector

TD04F10000000000 - PG 7 Cable Gland

TD04F20000000000 - PG 9 Cable Gland

M 12 90° 5 Pin Female Field Wireable Connector

TD05F10000000000 - PG 7 Cable Gland

TD05F20000000000 - PG 9 Cable Gland

Technical Data	Cable	Field Wireable	Pin Out/Color Code	
Molded Body/Insert	PVC/Polyamide	Polyamide		
Coupling Nut	Nickel C	Copper Alloy	Female View	
Cable Jacket Material	PVC	NA		
Cable O.D.	7.4mm	NA	3 4 1 BN	
Voltage Rating	125 V Ma	ax. @ 105° C	WH BU	
Current Rating	4.0) Amps	2 0 0 1 3 BB BK	
Degree of Protection	IP65	(mated)		
Operating Temperature	-25° (C to 85° C		
Conductor Gauge	18 AWG	NA	BN 1	
Bend Radius	74mm	NA	050 4 2 1 WH	
Maximum Wire AWG	NA	18 AWG	BK	
Wire Connection	NA	Screw Terminal	2 1 3 1 BU	
PG 7 Range	NA	4 – 6mm	5 [) GN/YE	
PG 9 Range	NA	6 – 8mm		

DEVICENET™ COMMUNICATION CABLES & CONNNECTORS

AVENTICSTM

M12 A-Coded Cables



M12 Straight 5 Pin Female Single Ended Cable - Shielded

TC0505MGD0000000 - 5 Meter

TC0510MGD0000000 - 10 Meter



M12 90° 5 Pin Female Single Ended Cable - Shielded

TD0505MGD0000000 - 5 Meter

TD0510MGD0000000 - 10 Meter



3 Way M12 "T"

TC0500000TT05000 - M12

M12 A-Coded Field Wireable Connectors



M12 90° 5 Pin Female Field Wireable Connector - Spring Cage

TD05F2000000071V - PG 9 Cable Gland



M12 Straight 5 Pin Female Field Wireable Connector - Spring Cage

TC05F2000000071V - PG 9 Cable Gland

Technical Data	Cable	M12 Field Wireable	"T"	Pin Out/Color Code
Molded Body/Insert	PVC/Polyamide	Nickel Plated Zinc/TPU	TPU/TPU GF	Female View
Coupling Nut	Nickel Plated Brass	Nickel Plated Brass	Nickel Plated Zinc	remaie view
Cable Jacket Material	PVC	NA	NA	3 Pin 1=Shield
Cable O.D.	7mm	4.0 – 8mm	NA	Pin 2= V+ Pin 3= V-
Voltage Rating	300 Volts	60 Volts	60 Volts	Pin 4= CAN_H Pin 5= CAN_L
Current Rating	4.0 Amps	4.0 Amps	4.0 Amps	
Degree of Protection	IP65 (mated)	IP 65 (mated)	IP 65 (mated)	
Operating Temperature	-40° C to 80° C	-40° C to 85° C	-25° C to 90° C	
Conductor Gauge	24 AWG (power & data)	26 – 20 AWG	NA	
Minimum Bend Radius	74mm	NA	NA	
Wire Connection	NA	Spring Cage	NA	'

ETHERCAT® COMMUNICATION CABLES & CONNNECTORS

M12 D-Coded Cables



M12 Straight 4 Pin Male D-Coded Single Ended Cable QA0405MT00000000 - 5 Meter

QA0410MT00000000 - 10 Meter



M12 90° 4 Pin Male D-Coded Single Ended Cable

QB0405MT00000000 - 5 Meter

QB0410MT00000000 - 10 Meter



M12 Straight 4 Pin Male D-Coded Double Ended Cable

QA0405MT0QA04000 - 5 Meter

QA0410MT0QA04000 - 10 Meter



M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable

QA0405MT0VA04000 - 5 Meter

QA0410MT0VA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor

QA04D2MK0VC04000 - 0.2 Meter

M12 D-Coded Field Wireable Connectors



M12 90° 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QB04F200R000071N - PG 9 Cable Gland - IDC



M12 Straight 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QA04F200R000071N - PG 9 Cable Gland - IDC

Technical Data	Cable	M12 Field Wireable	Pin Out/Color Code
Molded Body/Insert	PVC/PE	Nickel Plated Zinc/PA 66	
Coupling Nut	Nickel Plated Zinc	Nickel Plated Brass	Male View
Cable Jacket Material	PUR	NA	4 3
Cable O.D.	6.5mm	8.0mm	
Voltage Rating (Nominal)	300 Volts	60 Volts	
Current Rating	2.0 Amps	1.75 Amps	1 2
Degree of Protection	IP65 (mated)	IP65 (mated)	1[
Operating Temperature	-5° C to 50° C	-40° C to 85° C	YE 2 - WH
Conductor Gauge	22 AWG	26 – 22 AWG	3 — OG
Bend Radius	46mm	NA	4 BU
Wire Connection	NA	IDC	1

ETHERNET/IP™ COMMUNICATION CABLES & CONNECTORS

AVENTICSTM

M12 D-Coded Cables



M12 Straight 4 Pin Male D-Coded Single Ended C	able

QA0405MK00000000 – 5 Meter QA0410MK00000000 – 10 Meter

M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable

QA0405MK0VA04000 - 5 Meter

QA0410MK0VA04000 - 10 Meter

M12 90° 4 Pin Male D-Coded Single Ended Cable

QB0405MK00000000 - 5 Meter

QB0410MK00000000 - 10 Meter



M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor

QA04D2MK0VC04000 - 0.2 Meter

M12 D-Coded Field Wireable Connectors



M12 90° 4 Pin Male D-Coded Field Wireable Connector w/ IDC

 $\ensuremath{\mathsf{QB04F2000000071N}}\xspace - \ensuremath{\mathsf{PG}}\xspace \ensuremath{\mathsf{PG}}\xspace \ensuremath{\mathsf{9}}\xspace \ensuremath{\mathsf{Cable}}\xspace \ensuremath{\mathsf{G}}\xspace \ensuremath{\mathsf{and}}\xspace - \ensuremath{\mathsf{IDC}}\xspace$



M12 Straight 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QA04F2000000071N - PG 9 Cable Gland - IDC

Technical Data	Cable	M12 Field Wireable	Pin Out/Color Code
Molded Body/Insert	PUR/Polyamide	Nickel Plated Zinc/PA 66	
Coupling Nut	Nickel Plated Brass	Nickel Plated Brass	Male View
Cable Jacket Material	PUR	NA	4 3
Cable O.D.	5.6mm	4.0 – 8mm	
Voltage Rating (Nominal)	300 Volts	60 Volts	
Current Rating	2.0 Amps	1.75 Amps	1 2
Degree of Protection	IP65 (mated)	IP 65 (mated)	1
Operating Temperature	-40° C to 75° C	-40° C to 85° C	WH/OG OG
Conductor Gauge	24 AWG	IDC 26 – 22 AWG	3 WH/GN
Bend Radius	61mm	NA	4 GN
Wire Connection	NA	IDC	

IO-LINK® COMMUNICATION CLASS A & B CABLES & CONNNECTORS

580

M12 Class A & B Compatible Cables*



M12 Straight 5 Pin Female Single Ended Cable - Unshielded
TC0505MIE000071P - 5 Meter
TC0510MIE000071P - 10 Meter



M12 Straight 5 Pin Female to Male Double Ended Cable - Unshielded						
TC0505MIETA0571P - 5 Meter						
TC0510MIETA0571P – 10 Meter						



M12 90° 5 Pin Female Single Ended Cable - Unshielded					
TD0505MIE000071P – 5 Meter					
TD0510MIE000071P - 10 Meter					



M12 90° 5 Pin Female to Male Double Ended Cable - Unshielded

TD0505MIETA0571P - 5 Meter

TD0510MIETA0571P - 10 Meter

M12 Class A & B Compatible Field Wireable Connectors*



M12 Straight 5 Pin Male Field Wireable Connector - Screw Terminal

TA05F10000000000 - PG 7 Cable Gland



M12 90° 5 Pin Male Field Wireable Connector - Screw Terminal

TB05F10000000000 - PG 7 Cable Gland

^{*} See page 107 for M12 4 Pin field wireable connectors if the selected IO-Link® Master does not accept 5 Pin field wireable connectors. Maximum IO-Link® cable length is 20m.

Technical Data	Cable	M12 Field Wireable	Pin Out/Color Code
Molded Body/Insert	TPU	Polyamide	
Coupling Nut	Nickel Plated Zinc	Nickel Plated Zinc	Female View
Cable Jacket Material	PUR	NA	3 4
Cable O.D.	5mm	Accepts 3.0 – 6.5mm	0 5 0
Voltage Rating	60 Volts	125 Volts	
Current Rating	4.0 Amps	4.0 Amps	2 1
Degree of Protection	IP65 (mated)	IP65 (mated)	BN
Operating Temperature	-25° C to 90° C (-13° F to 194° F)	-20° C to 100° C (-4° F to 212° F)	2) WH
Conductor Gauge	22 AWG	18 – 24 AWG	вк з) ви
Minimum Bend Radius	50mm	NA	5 D GN/YE
Wire Connection	NA	Screw Terminal	

^{*} See page 107 for M12 4 Pin cables if the selected IO-Link® Master does not accept 5 Pin cables. Maximum IO-Link® cable length is 20m.

PROFIBUS™ DP COMMUNICATION CABLES & CONNECTORS

AVENTICSTM

M12 B-Coded (Reverse Key) Cables



M12 Straight 5 Pin Male & Female Single Ended Cables					
RA0505MHP0000000 - 5 Meter - MALE					
RA0510MHP0000000 - 10 Meter - MALE					
RC0505MHP0000000 - 5 Meter - FEMALE					
RC0510MHP0000000 - 10 Meter - FEMALE					



M12 Straight 5 Pin Male - to - Female Double Ended Cables

RC0505MHPRA05000 - 5 Meter

RC0510MHPRA05000 - 10 Meter

M12 90° 5 Pin Male & Female Single Ended Cable

RB0505MHP0000000 - 5 Meter - MALE

RB0510MHP0000000 - 10 Meter - MALE

RD0505MHP0000000 - 5 Meter - FEMALE

RD0510MHP0000000 - 10 Meter - FEMALE

M12 B-Coded (Reverse Key) Field Wireable Connectors





M12 90° 5 Pin Male & Female Field Wireable Connector w/ IDC

RB05F200P000071V - PG9 Cable Gland - IDC MALE

RD05F200P000071V - PG9 Cable Gland - IDC FEMALE





M12 Straight 5 Pin Male & Female Field Wireable Connector

RA05F200P0000000 - PG7 Cable Gland - MALE

RC05F200P0000000 - PG7 Cable Gland - FEMALE





RA05TR0000000000 - MALE

RA050000PRT05000



Technical Data	Cable	Field Wireable	"T"
Molded Body	PUR	Nickel Plated Zinc/Brass Aluminum	
Insert	Polyamide	TPU/PVC	Nylon
Coupling Nut	Nickel Plated Brass	Nickel Plated Brass/Stainless Steel	Nickel Plated Brass
Cable Jacket Material	PVC	NA	NA
Cable O.D.	8.5mm	4.0 – 8.0mm/3.0 – 6.5mm	NA
Voltage Rating	300 Volts	60 Volts	250 Volts
Current Rating	4.0 Amps	4.0 Amps	4.0 Amps
Degree of Protection	IP65 (mated)	IP65 (mated)	IP65 (mated)
Operating Temperature	-40° C to 80° C	-40° C to 85° C	-40° C to 80° C
Conductor Gauge	22 AWG	26 – 20 AWG/24 – 18 AWG	NA
Minimum Bend Radius	74mm	NA	NA
Wire Connection	NA	IDC/Screw Terminal	NA

PROFINET™ COMMUNICATION CABLES & CONNNECTORS

M12 D-Coded Cables



M12 Straight 4 Pin Male D-Coded Single Ended Cable

QA0405MR00000000 - 5 Meter

QA0410MR00000000 - 10 Meter



M12 90° 4 Pin Male D-Coded Single Ended Cable

QB0405MR00000000 - 5 Meter

QB0410MR00000000 - 10 Meter



M12 Straight 4 Pin Male D-Coded Double Ended Cable

QA0405MR0QA04000 - 5 Meter

QA0410MR0QA04000 - 10 Meter



M12 Straight 4 Pin Male D-Coded to Male RJ45 Cable

QA0405MR0VA04000 - 5 Meter

QA0410MR0VA04000 - 10 Meter

M12 Straight 4 Pin Male D-Coded to RJ45 Female Socket Convertor

QA04D2MK0VC04000 - 0.2 Meter

M12 D-Coded Field Wireable Connectors



M12 90° 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QB04F200R000071N - PG 9 Cable Gland - IDC



M12 Straight 4 Pin Male D-Coded Field Wireable Connector w/ IDC

QA04F200R000071N - PG 9 Cable Gland - IDC

Technical Data	Cable	M12 Field Wireable	Pin Out/Color Code
Molded Body/Insert	PUR/PUR or PE	Nickel Plated Zinc/PA 66	
Coupling Nut	Nickel Plated Zinc and Brass	Nickel Plated Brass	Male View
Cable Jacket Material	PVC	NA	4 3
Cable O.D.	6.5mm/74mm	4.0 – 8.0mm	
Voltage Rating (Nominal)	42 Volts	60 Volts	
Current Rating	1.5 Amps	1.75 Amps	1 2
Degree of Protection	IP65 (mated)	IP65 (mated)	1
Operating Temperature	-25° C to 60°	-40° C to 85° C	2 — WH
Conductor Gauge	24 & 22 AWG	26 – 22 AWG	3 - OG
Bend Radius	19.5mm	NA	4 BU
Wire Connection	NA	IDC	





Visit us: www.Emerson.com/aventics Your local contact: <u>Emerson.com/contactus</u>