Fisher[™] L2 Liquid Level Controller

Fisher L2 and L2 Snap level controllers are part of the rugged L2 series of liquid level controllers. They use a displacer type sensor to detect liquid level or the interface of two liquids of different specific gravities. These controllers are ideal for controlling level on gas separators and scrubbers. The reliability of the L2 design makes it well suited for liquid level applications in natural gas production, compression, and processing. The device delivers a pneumatic output signal to a control/dump valve. The sensor uses a threaded 2 NPT or an NPS 2 CL150 through 1500 slip-on flange connection to the vessel.

Features

- More Reliable Control—Two-stage proportional relay with integral action provides more dependable liquid level control.
- Snap-Acting or Throttling Control—One standard controller available as either throttling or snap-acting.
- Vibration Resistant Sensor Dynamics— O-ring friction and process pressure sensitivity are minimal. Performance stays constant with process pressure changes and controller remains vibration resistant.
- NACE Service Ready—Standard construction uses materials that comply with the requirements of NACE MR0175-2002.
- Field-Configurable Vertical or Horizontal Displacer—Displacer may be adjusted in the field for vertical or horizontal operation without additional parts.



- Field-Reversible Output—The controller can be adjusted in the field for direct or reverse action without additional parts. The controller also has adjustable gain sensitivity.
- CL1500 Pressure Rating—Sensor assembly is designed and specified for ASME B16.34 CL1500 service when using a Polyvinylchloride (PVC) displacer. For PED (97/23/EC) maximum pressure is limited to 200 bar (2900 psig).
- Vent-Away Case—The ability to pipe away exhaust permits using natural gas as the operating medium.
- Easy Maintenance—Both the controller and the sensor can be easily disassembled to inspect the process seals and for maintenance.





www.Fisher.com

Specifications

Available Configurations

Controllers: Snap-acting or throttling **Sensor:** Displacer-type liquid level sensor for mounting to side of tank. Displacer travel is transmitted to controller by pivotal movement of displacer rod

Input Signal

Type: Liquid level or liquid-to-liquid interface

Level Change Required for Full Change in Output Signal in a 1.0 Specific Gravity Liquid, with 1.4 bar (20 psig) Supply Pressure, Direct Action, and Standard 1-7/8 X 12-Inch (48 x 305 mm) Vertical Displacer with Standard Lever Arm Length:

Control Mode	Minimum Span Level Change, mm (Inches) ⁽¹⁾	Maximum Span Level Change, mm (Inches) ⁽¹⁾
Throttling	102 (4)	305 (12)
On-off	127 (5)	305 (12)
Snap-acting	13 (0.5)	20 (0.8)

Minimum Specific Gravity⁽²⁾

Minimum specific gravity, or specific gravity differential for interface applications Throttling Controllers: 0.4 On/Off Controllers: 0.45 Snap-Acting Controllers: 0.1

Output Signal

Pneumatic ■ on/off or ■ proportional pressure signal

Ranges:

Throttling: ■ 0.2 to 1.0 bar (3 to 15 psig) or ■ 0.4 to 2.0 bar (6 to 30 psig)

On/Off: 0 (off) or full supply pressure (on) **Action:** Field-reversible between direct (increasing level increases output signal) and reverse (increasing level decreases output signal)

Supply Pressure Requirements

Throttling and On/Off Controller: Throttling: 1.4 bar (20 psig) for 0.2 to 1.0 bar (3 to 15 psig) output signal and 2.4 bar (35 psig) for 0.4 to 2.0 bar (6 to 30 psig) output signal On/Off: Any desired pressure between 1.4 and 3.4 bar (20 and 50 psig) Snap-Acting Controller: Any desired pressure between 1.4 and 5.2 bar (20 and 50 psig) direct, and 1.4 and 2.4 bar (20 and 35 psig) reverse

Do not use supply pressure below 1.4 bar (20 psig)

Supply Pressure Medium

Air or Natural Gas

Steady-State Air Consumption⁽³⁾

Throttling Controller: ≤ 0.03 normal m³/hr (1.0 scfh) at 1.4 bar (20 psig) supply pressure Snap-Acting Controller: ≤ 0.03 normal m³/hr (1.0 scfh) at 1.4 bar (20 psig) supply pressure or ≤ 0.04 normal m³/hr (1.5 scfh) at 2.4 bar (35 psig) supply pressure in tripped condition; air consumption increases during trip

Sensor to Vessel Connection

■ 2 NPT threaded or ■ NPS 2 CL150 through 1500 slip-on flange connection⁽⁴⁾

Controller Connections

Supply: 1/4 NPT internal located on the bottom of the case

Output: 1/4 NPT internal located on the top of the case

Case Vent: 1/4 NPT internal with vent screen assembly located on the back of the case

Standard Displacer Size

48 x 305 mm, 541 cm³ (1-7/8 x 12 inches, 33 in³)

Maximum Displacer Insertion Length⁽⁵⁾

Standard lever arm length plus one 6-inch extension, horizontal or vertical

Displacer Material and Maximum Sensor Working Pressure⁽⁶⁾

PVC Displacer: Consistent with CL1500 pressure temperature ratings per ASME B16.34 up to maximum pressure of 258.5 bar (3750 psig) For PED (97/23/EC) maximum pressure limited to 200 bar (2900 psig)

S31603 SST Displacer: CL600 pressure temperature ratings per ASME B16.34 up to maximum pressure of 99.3 bar (1440 psig)

Note: For slip-on flange connection, maximum sensor working pressure must be consistent with the flange ratings

-continued-

L2 Controller D103034X012

Specifications (continued)

Displacer Material and Sensor Temperature Limits⁽⁶⁾

PVC Displacer: -18 to 71°C (0 to 160°F) S31603 SST Displacer: -40 to 204°C (-40 to 400°F)

Operative Ambient Temperature Limits⁽⁶⁾

Controller: -29 to 71°C (-20 to 160°F)

Standard Supply, and Output Pressure Gauge Indications

Triple scale gauges in 0 to 60 psig/0 to 0.4 MPa/ 0 to 4.0 bar

Construction Materials

Controller: Case and Cover: Marine grade aluminum Relay Body: Thermoplastic Relay Trim: Stainless steel, nitrile Span Levers: Stainless steel

Sensor: Sensor Body: LCC O-Rings: Fluorocarbon Pivot Assembly: Stainless steel Displacer: ■ Polyvinylchloride (PVC) or ■ S31603 SST Sensor Spring: Stainless steel

Dimensions

Refer to figure 1

Hazardous Area Classification

Complies with the requirements of ATEX Group II Category 2 Gas and Dust

EX h IIC Tx Gb $\langle \boldsymbol{\xi} \langle \boldsymbol{\xi} \boldsymbol{\chi} \rangle \mathbf{I} \mathbf{I} \mathbf{2} \mathbf{G} \mathbf{D}$ EX h IIIC Tx Db

Maximum surface temperature (Tx) depends on operating conditions

Gas: T6 Dust: T71

Meets Customs Union technical regulation TP TC 012/2011 for Groups II/III Category 2 equipment

II Gb c T*X Ex EHC III Db c T*X

NOTE: Specialized instrument terms are defined in ANSI/ISA Standard 51.1 - Process Instrument Terminology.

NOTE: Specialized instrument terms are defined in ANSI/ISA Standard 51.1 - Process Instrument Terminology.
Any deviation from the standard construction described in the input signal specification above requires special displacer sizing considerations. Contact your <u>Emerson sales office</u> for information.
Minimum specific gravity values apply to both horizontal and vertical displacers with standard lever arm length (see dimension in figure 1).
Normal m³/In-Normal cubic meters per hour (0°C and 1.01325 bar, absolute). Schr-Standard cubic feet per hour (60°F and 14.7 psia).
Converting from a threaded NPT connection to a flange connection is to be done by the end-user. Refer to Converting a Threaded NPT Connection to a Flange Connection instruction Manual Supplement (<u>D103277X012</u>), available at Fisher.com or from your Emerson sales office.
Standard lever arm length: See figure 1.
The pressure and temperature limits in this document and any applicable code limitations should not be exceeded.

Product Bulletin 34.2:L2 July 2021

Figure 1. Dimensions



Notes:

Dimensions include one standard 152 mm (6-inch) extension. Contact your Emerson sales office for optional extension lengths.

Dimensions valid with standard displacers only.

Neither Emerson, Emerson Automation Solutions, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher is a mark owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. Emerson Automation Solutions, Emerson, and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Automation Solutions Marshalltown, Iowa 50158 USA Sorocaba, 18087 Brazil Cernay, 68700 France Dubai, United Arab Emirates Singapore 128461 Singapore

www.Fisher.com

