

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NOVA SCOTIA PRINCE EDWARD ISLAND NEWFOUNDLAND AND LABRADOR
NUNAVUT YUKON NORTHWEST TERRITORIES

MANUFACTURERS NAME: Emerson Process Management, Regulator Technologies, Inc.
MANUFACTURERS ADDRESS: 310 East University Drive, McKinney, Texas 75069
PLANT LOCATIONS: See attached list of 5 included manufacturing sites
CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY
A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
B Flanges: all flanges
C Valves: all line valves
D Expansion joints, flexible connections, and hose assemblies; all types
E Strainers, filters, separators, and steam traps
F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
H Pressure retaining components that do not fall into one of the above categories
N Nuclear components: Class 1 [ ] Class 2 [ ] Class 3 [ ], (Meeting CNSC or ASME requirements)
TITLE OF THE STANDARD OF CONSTRUCTION
ASME B31.3, Section 326
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT
FISHER
TYPE OF CONSTRUCTION
FORGED [ ] WELDED [ ] WROUGHT [ ]
CAST [ ] OTHER [ ]
DESCRIBE OTHER:
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:
Product Types: Type T205 Series & Type T208 Series
Product Catalogue/Bulletin Numbers: 74.1: T205, 74.1: T205B, 74.2: T208, 71.3: T205VB, 71.3: T208VR
Supporting Documentation: Drawings, Calculations, Witnessed Hydrostatic Test Certificates and ISO 9001 Certificates for all manufacturing sites.

DECLARATION: Emerson Process Management
Keoki P. Kusano (see note 3) employed by Regulator Technologies, Inc. and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by Bureau Veritas, CQC or SAI as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: [Signature]
Declared before me at Emerson Process Mgmt.
This 11th day of July AD 2013
Commissioner of Oaths or Notary Public: (sign) Vanessa Lawson



This space for Regulatory Authority use
This registration must be revalidated after ten (10) years from the date of acceptance.
CRN: OC11538.2 Add.2
FID#: 2509
Notes:
1. All fittings shall be registered in the name of the Manufacturer.
2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.
Date: March 21/14
C.R.N. OC.11538.28ADD2
Dwg. as described
Signed Yvonne Perry
Part of Act & Regulations
Sect. 1.0 - Fittings Rev. 1 06/2003