

ROC800 ROC Keypad Display

The ROC Keypad Display provides access to the process and operational information contained in a ROC800-Series 1 or Series 2 Remote Operations Controller (ROC800). It allows you to view and change parameters in the ROC800.

Keypad

The keypad has twenty-five multi-function keys. You can browse through lists and screens, type text, and enter numeric values using the ROC Keypad Display. Changes take effect immediately in the ROC800.

Display

The ROC Keypad Display contains two, eight-line by twenty-one character liquid crystal displays (LCDs) with user-configurable backlighting. When powered-up, the ROC Keypad Display shows ROC800 values in real-time.

Connections to ROC800

The ROC800 communicates with the ROC Keypad Display through any EIA-232 (RS-232) port on the ROC800 unit. The ROC Keypad Display requires 10 to 30 Volts dc and can be powered by the ROC800's power module or an external power source.

Screens

Easy-to-navigate menus and screens allow access to the most commonly used parameters. You can add, delete, and modify screens using ROCLINK™ 800 configuration software.

Information is organized and displayed by the ROC Keypad Display on both LCDs. The main display shows default Point Type/Logical/ Parameter (TLP) items and their values and actions. The default screens provide the following:

- Input/Output (I/O) information.
- ROC system parameters.
- Proportion, Integral, and Derivative (PID) loop information.
- Event Log information.
- Alarm log information.
- Meter run and station information.
- Plate changes.
- Calibrations.

The ROC Keypad Display also displays user-defined point types which are used with User C programs.

Security is provided by the ROC Keypad Display to control user access to information. Users are placed in "groups" having an assigned access level. Within each group, individuals can be assigned an additional level of access that overrides the group access level. Screens can be customized to allow users to view and edit parameters, view parameters only, or have no display access based on their group or individual access level. Typically, group or individual access is assigned based on job function. Each user within a group assumes the group's access level. However, an individual user can be granted or denied access to a specific display screen based on their individual access level.

Screens and menu structures can be saved to a file (on a PC running ROCLINK 800 configuration software) for later use or review.

Mounting

The ROC Keypad Display has CSA Class I, Division 2 approval and can be mounted on a panel or in a Type 4 enclosure. The gasket on the back of the ROC Keypad Display unit provides a seal against an enclosure wall or door.


Option

The ROC Keypad Display may be installed with an optional visor for use in high glare applications.



ROC800 Keypad Display

ROC800 Keypad Display

Communications		
Type	EIA-232 (RS-232), maximum cable length of 15 m (50 ft)	
Power		
Input Power	1.2 W maximum, supplied by ROC or other power source	
Input Voltage	10 to 30 Vdc	
Physical		
Display	Two, 8-line by 21-character LCD display with user-configurable backlighting. Each display is 128 x 64 pixels.	
Keypad	25 touchpad keys	
LEDs	Two. One for Shift/Alt Function (Red, Blue, and Off) and one reserved for future use.	
Housing	PC/Acrylic alloy, UV stabilized	
Dimensions	235 mm H x 134 mm W x 42 mm D (9.25 in. H x 5.25 in. W x 1.64 in. D)	
Weight	0.84 kg (1.85 lb), without optional visor 0.95 kg (2.1 lb), with optional visor	
Mounting	Suitable for Panel or Enclosure mounting	
Environmental		
Operating Temperature	-20 to 70°C (-4 to 158°F)	
Storage Temperature	-30 to 85°C (-22 to 185°F)	
Operating Humidity	0 to 95% relative humidity, non-condensing	
Radiated/Conducted Transmissions	Meets the requirements of IEC 61326 Electrical equipment for use in industrial locations	
Radiated Emissions	Meets FCC Part 15, Class A.	
Approvals		
Product Markings for Hazardous Locations	CSA CUS	Class I, Division 2, Groups A, B, C, and D. Type 4 rating when installed on enclosure per included instructions sheet Form A6164.
	RoHS (China)	

For customer service and technical support, visit www.EmersonProcess.com/Remote/Support.

**Global Headquarters,
North America, and Latin America:**

Emerson Process Management
Remote Automation Solutions
6005 Rogerdale Road
Houston, TX 77072 U.S.A.
T +1 281 879 2699 | F +1 281 988 4445
www.EmersonProcess.com/Remote

Europe:

Emerson Process Management
Remote Automation Solutions
Unit 8, Waterfront Business Park
Dudley Road, Brierley Hill
Dudley UK DY5 1LX
T +44 1384 487200 | F +44 1384 487258

Middle East/Africa:

Emerson Process Management
Remote Automation Solutions
Emerson FZE
P.O. Box 17033
Jebel Ali Free Zone – South 2
Dubai U.A.E.
T +971 4 8118100 | F +971 4 8865465

Asia-Pacific:

Emerson Process Management
Remote Automation Solutions
1 Pandan Crescent
Singapore 128461
T +65 6777 8211 | F +65 6777 0947

© 2005–2016 Remote Automation Solutions, a business unit of Emerson Process Management. All rights reserved.

This publication is for informational purposes only. While every effort has been made to ensure accuracy, this publication shall not be read to include any warranty or guarantee, express or implied, including as regards the products or services described or their use or applicability. Remote Automation Solutions (RAS) reserves the right to modify or improve the designs or specifications of its products at any time without notice. All sales are governed by RAS terms and conditions which are available upon request. RAS accepts no responsibility for proper selection, use or maintenance of any product, which remains solely with the purchaser and/or end-user.