

# Injection Control Application for FloBoss™ 107 and ROC800-Series SmartProcess™ Oil & Gas Applications

The Injection Controller Application for the FloBoss 107 and the ROC800-Series provides simple, configurable management of multiple injection streams. Injection manifolds are used to deliver specific quantities of water or steam to one or more wells. The Injection Controller Application will attempt to meet flow rate targets while also limiting wellhead pressures to safe levels.

The Injection Control Application delivers three key benefits:

## Dramatically Lower Installed Cost

- Low power system does not require AC power to be available at the wellsite
- Replaces PLC and flow transmitter(s) with a single device
- Native HART support permits high I/O density reducing I/O module cost
- WirelessHART support allows monitoring of wellhead pressures without trenching
- Configurable – not programmable – system expedites commissioning

## Improved Control

- Configurable, dual objective control strategy provides simplified, yet effective control
- Valve ‘no flow pre-positioning’ simplifies injection system restarts following an upset
- Target flow rates can be by volume, mass, or heat flow
- Pressure control with rate override also supported
- Dual valve control schemes also supported

## Superior Visibility to Injection Configuration, Status, and History

- Interfaces easily with leading SCADA/HMI/PLC systems
- Serial and/or Ethernet physical media
- Supports multiple simultaneous hosts



- Minimum/maximum/average values of flow rates, pressures, and temperatures available on an hourly and daily basis
- Historical retention of any desired values

The Injection Control Application delivers these benefits through features including:

## Versatile Meter Interface

The application can be configured to compute flow rate using typical injection instrumentation:

- Coriolis
- Magnetic
- Orifice
- Turbine
- Vcone
- Vortex

## Flexible Control Strategy

The control algorithm employs a configurable “dual objective” strategy. For example, the system may be configured to maintain a target flow rate (primary objective) but not to exceed a specific wellhead pressure limit (override objective). Other combinations are possible. A conventional proportional-integral-differential (PID) algorithm drives the control valve as long as the override set point is not violated. If the override objective is violated, the control immediately begins bringing the process back into conformance.

## Water or Steam

The application is designed to calculate volume, mass, and heat flow rates for:

- Water
- Saturated Steam (single phase vapor)
- Saturated Steam (two phase)

Orifice calculations are performed per ISO 5167.

Steam calculations through orifice plate elements support a variety of wetness correction factors for 2-phase steam.

## Supports All Valve Actuators

The Injection Controller Application can be configured to interface with the following valve positioners:

- Analog
- Digital

## Extensive Data Logging

The application accumulates hourly, daily, and monthly values for all parameters on each flow stream:

- Volume flow (minimum, maximum, average, total accumulated)
- Mass flow (minimum, maximum, average, total accumulated)
- Heat flow (minimum, maximum, average, total accumulated)
- Pressure (minimum, maximum, average)

These values can be retained in the controller for up to 35 days of history.

## SCADA-Ready

- Natively communicates via modbus RTU or ROC protocol communications
- Modbus map can be customized
- Supported by leading OPC servers (including tag browsing)

## Multi-Stream Support

- Floboss supports up to 4 streams (ideal for wellsite injection skids)
- ROC supports up to 25 streams (ideal for injection manifolds)

## Valve ‘No Flow Pre-Positioning’

- Program detects injection system upsets and pre-positions control valve to simplify injection system restarting



**Global Headquarters**  
**North America and Latin America**  
Emerson Process Management  
Remote Automation Solutions  
6005 Rogerdale Road  
Houston, TX, USA 77072  
T +1 281 879 2699  
F +1 281 988 4445

[www.EmersonProcess.com/Remote](http://www.EmersonProcess.com/Remote)



**Europe**  
Emerson Process Management  
Remote Automation Solutions  
Unit 8, Waterfront Business Park  
Dudley Road, Brierley Hill  
Dudley, UK DY5 1LX  
T +44 1384 487200  
F +44 1384 487258



**Middle East and Africa**  
Emerson Process Management  
Remote Automation Solutions  
Emerson FZE  
PO Box 17033  
Jebel Ali Free Zone - South 2  
Dubai, UAE  
T +971 4 8118100  
F +1 281 988 4445



**Asia Pacific**  
Emerson Process Management  
Remote Automation Solutions  
1 Pandan Crescent  
Singapore 128461  
T +65 6777 8211  
F +65 6777 0947

© 2014 Remote Automation Solutions, a business unit of Emerson Process Management. All rights reserved.

Emerson Process Management Ltd, Remote Automation Solutions (UK), is a wholly owned subsidiary of Emerson Electric Co. doing business as Remote Automation Solutions, a business unit of Emerson Process Management. FloBoss, ROCLINK, ControlWave, Helicoid, and OpenEnterprise are trademarks of Remote Automation Solutions. AMS, PlantWeb, and the PlantWeb logo are marks owned by one of the companies in the Emerson Process Management business unit of Emerson Electric Co. Emerson Process Management, Emerson and the Emerson logo are trademarks and service marks of the Emerson Electric Co. All other marks are property of their respective owners.

The contents of this publication are presented for informational purposes only. While every effort has been made to ensure informational accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. Remote Automation Solutions reserves the right to modify or improve the designs or specifications of such products at any time without notice. All sales are governed by Remote Automation Solutions' terms and conditions which are available upon request. Remote Automation Solutions does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Remote Automation Solutions product remains solely with the purchaser and end-user.

### Find us in social media



RemoteAutomationSolutions



Remote Automation Solutions Community



Emerson\_RAS



Remote Automation Solutions