


Chances are, you will retire before it does.



The FISHER® R600 Series domestic service regulator. Proven technology backed by over 100 years of FISHER engineering and design experience.

- Built-in inlet and outlet pressure taps
- Best overpressure protection in the industry
- Superior lockup performance
- Corrosion resistant materials and coatings



www.emersonprocess.com/regulators/lp
1-800-558-5853

D450160T012 © December 2008 Emerson Process Management Regulator Technologies, Inc. All rights reserved. Fisher, Emerson Process Management, and the Emerson Process Management design are marks of one of the Emerson Process Management group of companies. All other marks are the property of their respective owners.

