

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

REVISIONS						
REV	ECN	DESCRIPTION OF CHANGE	DRAWN	CHKD	APVD	DATE


# Sensor Terminals

Sensor Types:


- CMF010
- CMF025
- CMF050
- CMF100
- CMF200
- CMF300 (excluding CMF300A)
- CMF400
- CNG050
- T025 F025 H025 R025-VALID ONLY WITH 1500
- T050 F050 H050 R050-VALID ONLY WITH 1500
- T075 F100 H100 R100-VALID ONLY WITH 1500
- T100 F200 H200 R200-VALID ONLY WITH 1500
- T150 F300 H300

# Transmitter:

1500D  
2500D



CUSTOMER SUPPLIED CABLE  
 MAXIMUM LENGTH:  
 1000 ft (300m) OF 18 AWG(0.8 mm<sup>2</sup>)  
 300 ft (100m) OF 22 AWG(0.35 mm<sup>2</sup>)



ITEM	DESCRIPTION	PART OR REF. NO.	MATL. OR MFR.	QTY.
			MICRO MOTION, INC. BOULDER, COLORADO	
	THIRD ANGLE PROJECTION		WIRING, CORE TO 1500D/2500D	
DRAWN	NAME	DATE	SIZE	DWG. NO.
CHKD.	JLA	6/3/03	D	EW-20001163
APVD.	JLA	6/3/03	SCALE NONE	DO NOT SCALE DRAWING SHEET 1 OF 1

COPYRIGHT 2005 MICRO MOTION, INC.  
ALL RIGHTS RESERVED

8

7

6

5

4

3

2

1