



**Technical
Safety Authority
of Saskatchewan**

330 - 1855 Victoria Avenue
Regina, SK S4P 3T2
Canada

306-787-1443
info@tsask.ca
www.tsask.ca

REGISTRATION APPROVAL

Wednesday, March 20, 2013

Emerson Process Management, Rosemount
Analytical
2400 Barranca Parkway
Irvine, CA
92606

ATTENTION : Dana Crowley

Our File : 9002 [0 F

With reference to your submission respecting the registration of the item below, for legal use in the province, please note we have surveyed, approved and registered this design as noted.

MANUFACTURER : Emerson Process Management, Rosemount Analytical	
CATALOG OR DRAWING : 1700749 Rev.B	
ITEM : PERpH-X SENSOR MODEL 3300, 3400 & 3500	CRN : OF1392.3

We wish to point out that every fitting must be constructed strictly in accordance with the registered design.

Fitting registrations are required to be resubmitted for validation after ten (10) years from the registration date in accordance with CSA B51, Clause 4.2.1. The date of expiry for this registration is **20 MAR 2023**

Sincerely,

Mohammad Rokanuzzaman

Codes and Standards Compliance

REMARKS:

1. The MAWP for Model 3300 & 3400 shall be 288 Psi at 311F
2. A valid quality management system must be maintained for the fitting registration to remain valid until the expiry date.