



NOTE 1

THE ANCHOR WEIGHT SHALL BE SO DESIGNED THAT IT CAN PASS THROUGH THE HOLE IN THE TANK ROOF. RECOMMENDED WEIGHT IS APPROX. 12 KG. THE DIAMETER OF THE WEIGHT SHOULD BE LESS THAN 150MM TO AVOID DISTURBING ECHOES TO THE RADAR SENSOR.

NOTE 2

THE CLAMP CAN BE REPLACED BY A HEAVY WEIGHT THAT STANDS STILL ON THE TANK BOTTOM. FOR MAX. DIMENSION SEE NOTE 1.

ISSUED BY	WEEK	PRODUCT CODE	FILE	INSTALLATION DRAWING TITLE
GKLE	8847	REX	ACAD	MECH. INSTALLATION
APPROVED BY	WEEK	ORIGINAL DWG NO.	SCALE	TEMPERATURE SENSOR
GKL	8847	9150 044-905	-	
ROSEMOUNT		1 ST ANGLE	DOC TYPE	DWG NO.
Tank Gauging			2	9150 044-905
				ISSUE SHEET
				4 1/1

THE USER/COMPANIES OF THIS DOCUMENT IS/ARE WILL REMAIN OURS. THE CONTENTS ARE NOT BE USED WITHOUT OUR AUTHORIZATION OR SUBJECT TO THE KNOWLEDGE OF A THIRD PARTY. COMMUNICATION WILL BE PROSECUTED. ROSEMOUNT TANK GAUGING AB, SWEDEN.