


Product Discontinued

Junction box

NOTE 7



SEE ELECTRICAL
INSTALLATION
DWG FOR RTG

NOTE 6

NOTE 1
CONNECT RTDS TO MULTIPLEXER CHANNELS FROM THE
BOTTOM UP. LEAVE UNUSED CHANNELS AT THE TOP.

NOTE 2
MAKE NO CONNECTIONS TO TERMINALS 1,2,3,4 OR 8 OF X20.

NOTE 6
MAX 50 M SHIELDED CABLE MIN AWG 20 OR 0.5 SQ MM.
Lmax = 0.6 mH; Cmax = 3 uF. (VALID FOR CENELEC (IEC)
(CUSTOMER SUPPLY)
FOR FURTHER INFORMATION, SEE ACTUAL CERTIFICATE.

NOTE 7
CUSTOMER SUPPLY. (OPTIONAL RTR SUPPLY)
JUNCTION BOX MAY BE EXCLUDED DEPENDING ON
LOCAL CONDITIONS

HAZARDOUS AREA

ISSUED BY	GKM	WEEK	9137	PRODUCT CODE	REX	TITLE	ACAD	INSTALLATION DRAWING TITLE	EL. INSTALLATION DRAWING	ISSUE	5	SHEET	1/1
APPROVED BY	GKT	WEEK	9138	ORIGINAL DWG NO.	9240	002-909	SCALE	1 ST ANGLE	DOC TYPE	2	DWG NO.	9240	002-909
<p>ROSEMOUNT</p> <p>Tank Gauging</p> <p>THE COMPANY/CONTRACTOR OF THIS DOCUMENT IS AND WILL REMAIN LIABLE FOR THE CORRECTNESS OF THE INFORMATION PROVIDED AND FOR THE ACCURACY OF THE DATA. THE COMPANY/CONTRACTOR WILL NOT BE RESPONSIBLE FOR THE USE OF THIS DOCUMENT BY ANY OTHER PARTY. THE COMPANY/CONTRACTOR WILL NOT BE RESPONSIBLE FOR THE USE OF THIS DOCUMENT BY ANY OTHER PARTY. THE COMPANY/CONTRACTOR WILL NOT BE RESPONSIBLE FOR THE USE OF THIS DOCUMENT BY ANY OTHER PARTY.</p>													

CASE IS TO BE EARTH CONNECTED