



Cu 90
Pt 100



BLACK WIRES, (WIRES TO BE TWISTED IN 3-GROUPS:
PINK, BLACK, BLACK; WHITE, BLACK, BLACK,....ETC.)

| | | | | |
|---------------------|--------------|-----------------------------|-------------------------|--|
| ISSUED BY GKT-AK | WEEK 9411 | PRODUCT CODE REX | TITLE ACAD | INSTALLATION DRAWING TITLE TEMPERATURE SENSOR |
| APPROVED BY GKT | WEEK 9240 | ORIGINAL DWG NO. 002-948 | SCALE 1:2 | NYLON |
| ROSEMOUNT | | DOC TYPE 2 | DWG NO. 9240 002-948 | ISSUE 4 |
| Tank Gauging | | TEMPERATURE SENSOR | | SHEET 1/1 |

THE ROSEMOUNT CORPORATION OF THIS DOCUMENT IS AND WILL REMAIN OPEN. THE ROSEMOUNT NAME NOT BE USED WITHOUT OUR AUTHORIZATION OR ENDORSE TO THE KNOWLEDGE OF A THIRD PARTY. COMMUNICATION WILL BE PROSECUTED. ROSEMOUNT TANK GAUGING AB, SWEDEN.