



Formula for calculating spot distance "A":

$$A = \frac{H}{N-1}$$

where N = total no of spots.

Example:  
For 5 spots and H=12 M,  
the distance A will be:  
 $\frac{12}{4} = 3$  M.

**NOTE 1**

TEMP. SENSOR POSITIONING ACCORDING TO API, Chapt 7, Sect 4.3.2.2  
THE DISTANCE "A" SHALL BE MAX 3 M (10')

**NOTE 2**

SEE ALSO RTR RSI-FORM FOR TEMP. SENSOR ORDERING

ISSUED BY	GSP-MH	WEEK	9851	PRODUCT CODE	REX	FILE	ACAD	INSTALLATION DRAWING TITLE	RECOMMENDED TEMP SENSOR POSITIONS
APPROVED BY	GU-AK	WEEK	9917	ORIGINAL DWG NO.	9240 003-942	SCALE	-		
<b>ROSEMOUNT</b>		1 ST ANGLE		DOC TYPE	2	DWG NO.	9240 003-942	ISSUE	3
Tank Gauging		THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.						SHEET 1/1	