



① FOR CLEAN PRODUCTS ONLY. MIN PIPE SIZE FOR HIGH VISCOSITY PRODUCTS IS 3" SCH 40-80. THE ROSEMOUNT 765 IS NOT RECOMMENDED TO BE INSTALLED IN STILL PIPE FOR WAXY CRUDE OILS.

ISSUED BY TP-AJ	WEEK 1047	PRODUCT CODE 2240	FILE ACAD	INSTALLATION DRAWING TITLE ROSEMOUNT 765 MECH INTALLATION DWG			
APPROVED BY EMe-MH	WEEK 1047	ORIGINAL DWG NO.	SCALE -	DOC TYPE 2	DWG NO. 9240041-932	ISSUE 01	SHEET 01/01
ROSEMOUNT Tank Gauging			1 ST ANGLE 	THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.			