



The manufacturer
may use the mark:



Valid until September 1, 2017
Revision 1.1 Aug 27, 2014



ANSI Accredited Program
PRODUCT CERTIFICATION
#1004

Certificate / Certificat Zertifikat / 合格証

ROS 1312032 C001

exida hereby confirms that the:

**5900 Radar Level Gauge and 2410 Tank Hub
(Rosemount Tank Gauging System)
SIL 3 2-in-1 (1oo2) Option**

**Rosemount Tank Gauging
Gothenburg, Sweden**

Has been assessed per the relevant requirements of:

IEC 61508 : 2010 Parts 1-7

and meets requirements providing a level of integrity to:

Systematic Capability: SC 3 (SIL 3 Capable)

Random Capability: Type B Element

SIL 3 @ HFT = 0; Route 1_H

**PFH / PFD_{AVG} and Architecture Constraints
must be verified for each application**

Safety Function:

The level transmitter will de-energize a safety critical output when exceeding any of the configured alarm limits within the stated accuracy and within the specified demand response time.

Application Restrictions:

The unit must be properly designed into a Safety Instrumented Function per the Safety Manual requirements.



John C Yozallinas
Evaluating Assessor

David G. Smith
Certifying Assessor

Certificate / Certificat / Zertifikat / 合格証

ROS 1312032 C001

Systematic Capability: SC 3 (SIL 3 Capable)

Random Capability: Type B Element

SIL 3 @ HFT = 0; Route 1_H

**PFH / PFD_{AVG} and Architecture Constraints
must be verified for each application**

5900 Radar Level
Gauge and 2410 Tank
Hub

SIL 3 2-in-1 (1oo2)
Option

Systematic Capability :

The product has met manufacturer design process requirements of Safety Integrity Level (SIL) 3. These are intended to achieve sufficient integrity against systematic errors of design by the manufacturer.

A Safety Instrumented Function (SIF) designed with this product must not be used at a SIL level higher than stated.

Random Capability:

The SIL limit imposed by the Architectural Constraints must be met for each element.

IEC 61508 Failure Rates in FIT*

	λ_S	λ_{DD}	λ_{DU}	SFF %
SIL 3, 2-in-1 (@ 40 C)	1921	00	17	99.0

* FIT = 1 failure / 10⁹ hours

SIL Verification:

The Safety Integrity Level (SIL) of an entire Safety Instrumented Function (SIF) must be verified via a calculation of PFH and PFD_{AVG} considering redundant architectures, proof test interval, proof test effectiveness, any automatic diagnostics, average repair time and the specific failure rates of all products included in the SIF. Each subsystem must be checked to assure compliance with minimum hardware fault tolerance (HFT) requirements.

The following documents are a mandatory part of certification:

Assessment Report: ROS 1312032 R001 V1R1

Safety Manual: #300540xx, Rev EA

Where "xx" = language code



64 N Main St
Sellersville, PA 18960

T-002, V3R3-3