



MODEL NO.

**TVL-R22GNEM161**

PRODUCT LINE

**Valvetop Discrete Valve Controller**

<b>Model</b>	Valvetop Model TVL, epoxy-coated A360 Aluminum enclosure
<b>Bus Sensor</b>	(2) SPDT reed switch (200mA@30VDC)
<b>Area Classification</b>	Class 1, Div. 2, Groups A,B,C&D; Class II, Div. 2 Groups F,G; Type 4,4x; Ex nA nC IIC T4 Gc Ex tc IIIC T115°C Dc, IP66/68
<b>Visual Display</b>	90° Green Open / Red Closed
<b>Shaft</b>	NAMUR, 304 Stainless Steel
<b>Conduit Entries</b>	(2) 3/4" NPT
<b>O-Rings</b>	Silicone
<b>Pilot</b>	(1) 24Vdc, fail open/closed
<b>Spool Valve</b>	316 Stainless Steel, 1.0Cv with 1/4" NPT Ports
<b>Valve Cv</b>	1.0 Cv (1/4" NPT ports)
<b>Manual Override</b>	None
<b>Temperature Rating</b>	-40 °C to 55 °C

Current as of Jun 12, 2013 - subject to change without notice.

**TOPWORX**

TopWorx, Inc. (502) 969-8000 ph.  
 3300 Fern Valley Rd. (502) 969-5911 fax  
 Louisville, KY 40213 www.topworx.com