

Instrumentation for the Water and Wastewater industry



Application Solutions

ROSEMOUNT®



EMERSON™
Process Management

Best in class instrumentation for waste water treatment

Today's instrument engineer doesn't have the time to study specifications and suppliers to find the solution to specific application requirements.

With Emerson, we have the complete product portfolio for water industry applications, along with the expertise of our instrument consultants who understand your process and the issues that you face.

Emerson has been providing reliable measurement and control products to the water and wastewater treatment industry for over 50 years. Our instrument consultants can help you with the selection process and provide the support, advice and fast response that you need.



INLET WORKS

Inlet pumping station

3100 Ultrasonic level, 9700 hydrostatic pressure transmitters with 3491 programmable pump controllers for automated control of up to 4 pumps
2051 Pressure transmitter for pumping main pressure

Inlet flow measurement

8700 Electromagnetic flowmeters for full pipes, 8714i Calibration Verification™ and diagnostics
3100 Ultrasonic transmitter and 3493 flow controller for open channel flow

Automatic screen control

3100 Ultrasonic level transmitters and 3492 differential level controllers for automatic control of screen rake system

PRIMARY TREATMENT

Sludge blanket monitoring

MSL600 Continuous sludge interface level measurement and/or 433 fixed sludge alarm level sensors for primary settling tanks

Automatic desludging

MSM400 Sludge density monitor for automatic desludge control

Sludge density measurement

MSM400 Sludge density measurement directly in tank or in-line pipe measurement

Sludge thickening

MSL600 Continuous sludge interface level measurement for sludge thickeners

Sludge holding tanks


5400 Non-contacting radar level
5300/3300 Guided wave radar for lime dosing level
3100 Ultrasonic level for open tanks
9700 Hydrostatic pressure transmitters
2051 Pressure transmitter with 1199 diaphragm seals for DP level measurement
3491 Controllers for level measurement and control

Sludge transfer

8700 Electromagnetic flowmeters for full pipes, 8714i Calibration Verification and diagnostics

Sludge digester

5400 Non-contacting radar level



BIOLOGICAL TREATMENT

Aeration flow monitoring

485 Annubar® averaging pitot tubes

405 Compact orifice plates

2051 Differential pressure transmitters for volume and mass flow of air to aeration lanes

SECONDARY TREATMENT

Final settlement blanket monitoring

MSL600 Continuous sludge interface level

433 Fixed sludge interface level for final and secondary settlement tanks

Dissolved air flotation (DAF)

2051 Pressure transmitters for air pressure measurement

TERTIARY TREATMENT

Level measurement

3100 Ultrasonic level transmitter

9700 Hydrostatic pressure transmitters

3491 Controllers for level measurement and control

Sand filter backwash control

2051 Differential pressure transmitters for head loss across filters

Backwash solids detection

433 Ultrasonic interface level sensors and controllers

Final effluent discharge monitoring

3100 Ultrasonic level transmitter and 3493 flow controller

8700 Electromagnetic flowmeters for full pipes, 8714i Calibration Verification diagnostic

2051 Pressure transmitter for pump discharge monitoring

Chemical treatment

3100 Ultrasonic level

5400 Non-contacting radar level

2051 Pressure transmitter with diaphragm seal for tank level

3491 Controllers for level measurement and control



MSL600 Sludge blanket level



5400 Sludge holding tank



3107 Open channel flow



3100 and 3300 on effluent sump




485 Annubar air flow to aeration



433S Sludge interface level

Best in class instrumentation for clean water treatment



ABSTRACTION AND BOREHOLE

Flow measurement: open channel and closed pipe

3100 Ultrasonic transmitter and 3493 open channel flow controller
8700 Electromagnetic flowmeters for full pipes, 8714i Calibration Verification diagnostic

INLET MONITORING and SCREENING

Level measurement

3100 Ultrasonic level
9700 Hydrostatic pressure transmitters
3491 Controllers for level measurement and control

Flow measurement

8700 Electromagnetic flowmeters for full pipes

FILTRATION

Level measurement

3100 Ultrasonic level transmitters
9700 Hydrostatic pressure transmitters
3491 Controllers for level measurement and control

Filter backwash control

2051 Differential pressure transmitters for measuring head loss across filters

Backwash solids detection

433 Ultrasonic interface level sensors and controllers

Flow to filters and backwash flow

8700 Electromagnetic flowmeters for full pipes

GAC PLANT

GAC interface level


MSL600 Continuous interface level
433 Fixed alarm interface level sensors

Level measurement

3100 Ultrasonic level transmitters
9700 Hydrostatic pressure transmitters
3491 Controllers for level measurement and control

Backwash solids detection

MSL600 Continuous interface level, and 433 fixed alarm interface level sensors



CHEMICAL TREATMENT

Level measurement

- 3100 Ultrasonic level transmitter
- 2051 Pressure transmitter with diaphragm seal
- 3491 Controllers for level measurement and control

CLARIFIER

Sludge blanket monitoring

- MSL600 Continuous sludge interface level, and 433 fixed alarm sludge interface level

Clarifier level

- 3100 Ultrasonic level transmitters
- 9700 Hydrostatic pressure transmitters
- 3491 Controllers for level measurement and control

SLUDGE TREATMENT (Waste)

Sludge blanket monitoring

- MSL600 Continuous sludge interface level, and 433 fixed sludge interface level

Automatic desludging

- MSM400 Sludge density monitor for initiation of automatic desludge control

Sludge density measurement

- MSM400 Sludge density measurement for in-tank or in-line pipe measurement

Sludge holding tanks

- 5400 Non-contacting radar level
- 5300/3300 Guided wave radar for lime dosing level
- 3100 Ultrasonic level transmitters
- 9700 Hydrostatic pressure transmitters
- 3491 Controllers for level measurement and control in closed and open tanks

DISTRIBUTION NETWORK

Network pressure


- 2051 Pressure transmitter for pump discharge and network pressure

Network flow

- 3051S Differential pressure for DP flow fiscal metering
- 8700 Electromagnetic flowmeters for full pipes, 8714i Calibration Verification diagnostic
- 485 Annubar averaging pitot tubes
- 405 Compact orifice plates



2051 Sludge pump pressure



3100 Contact tank level



3108 High accuracy flow over weir



3300 Reservoir level



3107 Pumping station level

Instrumentation for water industry applications



3100 Series Ultrasonic Level Transmitters

Transmitters for level measurement, wetwell, sump pump control and open channel flow measurement.

- Reference accuracy $\pm 0.25\%$, measuring range up to 40ft (12m)
- FM, CSA, ATEX, IECEX Hazardous area approval, HART® digital communication
- 2 Wire 24V dc loop powered
- Measures liquid height, distance to liquid, volume or flow in open channels
- Automatic temperature compensation



3490 Series Universal Controllers

Wall and panel mounting control units for any 4-20mA or HART compatible transmitter.

- Five fully field programmable relays
- Programme wizards to assist configuration and set-up for level, pump control and flow
- Pre-configured flow curves for weirs and flumes in accordance with ISO / BS standards
- 4-20 mA output, 5 x SPDT relay contacts on controllers
- FM, CSA, ATEX, IECEX Hazardous area approval, HART digital communication
- Data logging of up to 7000 events plus totalized flow



Rosemount Radar Level Transmitters

Direct level measurement, virtually unaffected by process conditions.

- Repeatability: $\pm 0.04"$ ($\pm 1\text{mm}$)
- 4-20mA output with digital HART communication
- IS or explosion proof FM, CSA, IECEX, ATEX

5400 Series Non-contacting radar

Pulsed, free propagating radar for level measurement in liquids

- Wide range of antennas and mounting connections.
- Measuring range up to 98ft (30m)
- Reference accuracy:

Model 5401: $\pm 0.4"$ ($\pm 10\text{mm}$) - Model 5402: $\pm 0.12"$ ($\pm 3\text{mm}$)

3300 and 5300 Series Guided wave radar

Top mounted, level and interface measurement for liquids or solids.

- Wide variety of probe styles and mounting connections
- Measuring range up to 164ft (50m)
- Reference accuracy:

3300: $\pm 0.2"$ ($\pm 5\text{mm}$), 5300: $\pm 0.12"$ ($\pm 3\text{mm}$)



2100 Series Vibrating Fork Level Switches

Level switches using vibrating fork technology for level alarm and control applications

- 4-20mA output with digital HART communications
- IS or explosion-proof FM, CSA, IECEX, ATEX
- WirelessHART™ options
- Extended length to 10ft (3m) available
- Stainless steel wetside with ECTFE/PFA coating option for corrosive applications
- 24-264V dc or ac powered with relay or solid state output



MSL600 Ultrasonic Continuous Sludge Blanket Level Measurement

For continuous monitoring of sludge blanket interface in primary and secondary settlement tanks and clarifiers and sludge thickeners.

- Graphical display of sludge blanket
- Self cleaning sonar transducer
- 23ft (7m) Measuring range (tank depth)
- 4-20 mA output, 2 x SPDT relay contacts
- On board data logging with user defined logging intervals



MSM400 Ultrasonic Sludge Density Measurement

Sludge density measurement for primary and secondary sludge and industrial slurries.


- Sludge density measuring ranges up to 20% solids
- 316SS Tank mounted sensors NEMA type 6P (IP68) rating
- Flanged pipe sections with in-line sensors: 4", 6", 8" (DN100, DN150, DN200) Other sizes on request
- Back lit LCD display on weatherproof wall mounting enclosure
- 4-20 mA output, 2 x SPDT relay output contacts
- Simple calibration using pre-programmed sludge types



433 Series Sludge Blanket Level Sensors

Sludge blanket level detection and density measurement for primary and secondary sludge and industrial slurries. Simple sludge level detection using the 433 sensor with either MCU200 or Electrosensor controllers

- 316 Stainless steel tank mounted sensors for blanket level, NEMA type 6P (IP68)
- Flanged pipeline sensors for in-line density, 4", 6" and 8". (100, 150, 200mm) Other sizes on request
- NEMA type 4 (IP65) wall mounting enclosure
- DPDT relay output contacts with adjustable time delays
- Simple configuration and calibration



9710 Hydrostatic Level Transmitters

Level measurement for arduous conditions.

- Flush mount ceramic sensor in tough 316SS body
- 2 Wire 24V dc loop powered, 4-20mA output
- Measuring range up to 650ft (200m)
- Low cost installation



Pressure Transmitters

All models available with flexible Coplanar™ design which helps reduce engineering and installed costs.

Pressure measurement:

- Reference accuracy $\pm 0.075\%$ Span (0.065% optional)
- Installed stability = 2 years (5 year optional)
- 100:1 Rangedown

Differential pressure flow measurement:

- Rosemount 3051S Ultra for flow enables up to 14:1 flow turndown with a single transmitter
- Annubar technology has $\pm 0.8\%$ of volumetric flow rate accuracy, ideal for large lines due to minimal pressure loss

Differential pressure level measurement:

- Rosemount Tuned Systems™ optimize performance and lower installed costs
- Multiple direct mount and capillary options to match vessel mounting requirements



Magnetic Flowmeters

Microprocessor-based SMART instruments using pulsed DC technology providing continuous automatic zeroing to compensate for variations in the process environment.

- All welded construction
- Simple design to enhance reliability
- Available in sizes 0.5 to 72" (12mm to 1.8m)
- Wide selection of wetted materials for compatibility with virtually all conductive fluids
- Advanced diagnostic capabilities, in HART or Fieldbus protocols, reducing commissioning and maintenance time
- NSF approved
- Rosemount 8714i Calibration Verification diagnostic. Allows users to verify calibration without additional equipment
- Verifies both transmitter and flowtube sensor calibration
- No need to remove the meter from the line



Other water industry products from Emerson include:-



Rosemount Pressure, Temperature, Flow and Level

The Rosemount product offering includes a complete line of pressure, temperature, flow, level, and safety measurement instrumentation. Throughout the process industries, Rosemount devices are specified more often than any other brand of process instrumentation.



Rosemount Analytical

Rosemount Analytical offers a comprehensive line of process gas and liquid analyzers, sensors and systems for efficiency, quality, and environmental analysis solutions. Rosemount Analytical instruments and systems will help you maximize performance, productivity and profitability.



Smart Wireless Networks

Emerson's Smart Wireless networks enable a cost effective solution for measurements that were unattainable previously. The self-organizing network ensures an interoperable, adaptive and flexible approach to wireless. It is secure, robust, infinitely configurable, with data reliability of greater than 99%.



Instrument and Valve Services

Offering an extensive network of service centers and field service technicians in North America, Emerson's Instrument and Valve Services help build reliability programs to help plants achieve maximum capacity and minimal risk of downtime.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount and the Rosemount logotype are registered trademarks of Rosemount Inc. PlantWeb is a registered trademark of the Emerson Process Management group of companies. All other marks are the property of their respective owners. We reserve the right to modify or improve the designs or specifications of product and services at any time without notice
©2010 Rosemount Inc. All rights reserved.

**Emerson Process Management
Rosemount Inc.**
8200 Market Boulevard
Chanhassen, MN 55317 USA
T (U.S.) 1-800-999-9307
T (International) (952) 906 8888
F (952) 949 7001

Emerson Process Management
Blegistrasse 23
P.O. Box 1046
CH 6341 Baar
Switzerland
Tel +41 (0) 41 768 6111
Fax +41 (0) 41 768 6300

Emerson Process Management Asia Pacific
Pte Ltd
1 Pandan Crescent
Singapore 128461
Tel +65 6777 8211
Fax +65 6777 0947
Service Support Hotline : +65 6770 8711

Emerson FZE
P.O. Box 17033
Jebel Ali Free Zone
Dubai, UAE
Tel +971 4 883 5235
Fax +971 4 883 5312

www.rosemount.com

