

## Wisconsin Paper Mill Profits from the NEW Rosemount Compact Annubar Technology Through Quick Delivery and Easy Installation

### RESULTS

- Provided a more accurate, stable, reliable, and repeatable flow measurement
- Quick delivery and installation kept the project on schedule
- Avoided costly pipe modifications during installation

### APPLICATION

Measuring flow in a condensate line

### APPLICATION CHARACTERISTICS

4" line

### CUSTOMER

Major paper mill in the U. S.

### CHALLENGE

A paper mill located in Wisconsin wanted to improve the performance of a measurement point on a condensate line during a brief process shutdown. They needed a measurement solution that would be installed easily with minimal installation costs. Additionally, a solution was needed quickly, so the mill could stay on schedule - a prolonged shutdown would affect profitability.

The mill was experiencing measurement reliability problems with a different manufacturer's vortex and magnetic flow meters they have tried on this application, and were looking for new alternative. The mill wanted to pursue a DP Flow measurement option that didn't require an expensive installation with additional pipe penetrations or time-consuming impulse piping. They needed a solution that was easy to install and could be delivered on short notice that wouldn't result in the lost production.



*The Rosemount 3051SFC Compact Annubar Flowmeter was quickly installed without any additional pipe modifications.*



*Figure 1: The Compact Annubar Flowmeter installed between two raised-face flanges.*

**ROSEMOUNT**<sup>®</sup>

For more information:  
[www.rosemount.com](http://www.rosemount.com)

  
**EMERSON**<sup>™</sup>  
Process Management

### SOLUTION

A Rosemount 3051SFC Compact Annubar flowmeter was ordered and delivered on time. The paper mill was able to install the Flowmeter between two standard raised face flanges on the process line with ease. The centering mechanism ensured proper alignment in the pipe and optimal accuracy. The integrated Flowmeter did not require impulse piping or extra welding which ensured that the installation could be completed during this short process shutdown.

This technology proved to be a more accurate, stable, reliable and repeatable flow measurement. The quick delivery of the Rosemount Compact Annubar Flowmeter prevented a costly production start-up delay. The flowmeter was quickly and easily installed, and it eliminated the additional labor costs associated with piping modifications or assembling impulse piping.

### RESOURCES

#### Emerson Process Management Pulp & Paper Industry

<http://www2.emersonprocess.com/en-US/plantweb/customerproven/Pages/PulpPaper.aspx>

#### Rosemount Annubar® Flowmeter Series

<http://www2.emersonprocess.com/en-US/brands/rosemount/Flow/DP-Flow-Products/Annubar-Flowmeters/Pages/index.aspx>

#### Rosemount 3051S® Transmitter Series

<http://www2.emersonprocess.com/en-US/brands/rosemount/Pressure/Pressure-Transmitters/MultiVariable-Transmitters/3051S-MultiVariable/Pages/index.aspx>



Figure 2: No new piping modifications or welding was required in this quick installation.



Figure 3: The Rosemount 3051SFC Compact Annubar Flowmeter.

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which can be found at [www.rosemount.com/terms\\_of\\_sale](http://www.rosemount.com/terms_of_sale). We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

The Emerson logo is a trade mark and service mark of Emerson Electric Co. Rosemount and the Rosemount logotype are registered trademarks of Rosemount Inc. PlantWeb is a registered trademark of one of the Emerson Process Management group of companies. All other marks are the property of their respective owners.

**Emerson Process Management**  
Rosemount Division  
8200 Market Boulevard  
Chanhausen, MN 55317 USA  
T (U.S.) 1-800-999-9307  
T (International) (952) 906-8888  
F (952) 906-8889  
[www.rosemount.com](http://www.rosemount.com)

**Emerson Process Management**  
Blegistrasse 23  
P.O. Box 1046  
CH 6341 Baar  
Switzerland  
Tel +41 (0) 41 768 6111  
Fax +41 (0) 41 768 6300

**Emerson FZE**  
P.O. Box 17033  
Jebel Ali Free Zone  
Dubai UAE  
Tel +971 4 811 8100  
Fax +971 4 886 5465

**Emerson Process Management**  
Emerson Process Management Asia Pacific  
Private Limited  
1 Pandan Crescent  
Singapore 128461  
T (65) 6777 8211  
F (65) 6777 0947  
Enquiries@AP.EmersonProcess.com

**ROSEMOUNT®**

For more information:  
[www.rosemount.com](http://www.rosemount.com)