



**Emerson Process Management**  
 Rosemount Analytical Inc.  
 6565P Davis Industrial Parkway  
 Solon, OH 44139-3922  
 USA  
 T +1 440 914 1261  
 F +1 440 914 1271

**MATERIAL CERTIFICATION**

**OXYMITTER OXYGEN TRANSMITTER  
 MODELS OXT4A, OXT4C, OXT4CDR, OXT4CNF, OXT4CDRNF, OXT5A,  
 OXT5C AND OXT5CNF**

Rosemount Analytical Inc. declares the Oxymitter Oxygen Transmitters referenced above are supplied with the following materials. This declaration meets the requirements of EN 10204:2004, Type 2.1.

Process Wetted Components:

- 316L Stainless Steel ..... Probe Tube, Measurement Cell, Calibration Gas Line, Diffuser Hubs
- 316 Stainless Steel ..... Flame Arrestor Housing Components (OXT4C, OXT4CDR & OXT5C only)
- Inconel 601 ..... Flame Arrestor Element (OXT4C, OXT4CDR & OXT5C only)
- Zirconia ..... Measurement Cell
- Platinum ..... Measurement Cell Electrode
- Alumina ..... Ceramic Diffuser Elements
- 300 Series Stainless Steel ..... Hardware

Non-Process Wetted Components:

- 316 or 316L Stainless Steel ..... Mounting Flange, Adapter Flanges
- 356-T6 Aluminum ..... Adapter Casting
- A360 Aluminum ..... Electronics Housing
- 300 Series Stainless Steel ..... Hardware, Gas Fittings
- Carbon Steel ..... Adapter Flange Studs & Hardware

Please contact the Customer Support Center (CSC) at 1.800.433.6076 (toll free, US only) or 1.440.914.1261 (toll, international) for assistance.

Stephen J. Miesiak  
 Manager Mechanical & Engineering Services

This drawing contains information proprietary to Rosemount Analytical Inc. and is to be used solely for the purpose for which it is furnished. This document shall not be used for engineering, design, procurement, or manufacturing in whole or in part without written consent of Rosemount Analytical Inc.				1	REVISIONS	By: S. Miesiak	<b>Rosemount Analytical Inc.</b> Solon, Ohio
				CMB10631 3-30-12 SM		Eng: S. Miesiak	<b>MATERIAL CERTIFICATION OXYMITTER OXYGEN TRANSMITTER</b>
						App: D. Crowley	
							<b>6R00147</b>