

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
YUKON

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: FROMEX, S.A. DE C. V. Fisher Controls International

MANUFACTURERS ADDRESS: Avenida Industrias #5025 Parque Industrial Finse Nuevo Laredo, Tamaulipas, Mexico 88273

PLANT LOCATIONS: Nuevo Laredo, Mexico

CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY

TITLE OF THE STANDARD OF CONSTRUCTION

- A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
- B Flanges: all flanges
- C Valves: all line valves
- D Expansion joints, flexible connections, and hose assemblies: all types
- E Strainers, filters, separators, and steam traps
- F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
- G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
- H Pressure retaining components that do not fall into one of the above categories
- N Nuclear components: Class 1 Class 2 Class 3 . (Meeting AECB or ASME requirements)

ASME Boiler and Pressure Vessel Code Section VIII

SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT

TYPE OF CONSTRUCTION

Fisher Controls

FORGED WELDED WROUGHT
 CAST OTHER
 DESCRIBE OTHER:
 Type 5112/8112 body machined from SST bar stock
 Type 282/832 body forged and machined from B1
 Types 722/822 & 732/832 body machined from S1 casting.

LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:

- Safety Relief Valves Models H722/822, H732/832, H282/882, H5112/8112
- National Board Production Capacity Certifications, NB-18 listing pages
- Assembly drawings, nameplate drawings, dimensional drawings, material lists
- Catalog page

DECLARATION:

I Roberto Leyva - Plant Manager employed by FROMEX, S.A. DE C. V. Fisher Controls International and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by ASME as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer:

Declared before me at

This _____ day of _____ AD _____

Commissioner of Oaths

Or Notary Public: (sign) _____

(Affix Official seal to the right)

This space for Regulatory Authority use
This registration must be revalidated after ten (10) years from the date of registration.

CRN: 0G10725.5

FID#: 2100

Notes:

1. All fittings shall be registered in the name of the Manufacturer.
2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.



C.R.N. 0G10725.58

Dwg. as described

Signed Lorraine Perry

