






**\*\* TERMINAL BLOCK \*\***

|    |    |
|----|----|
| 1  | 12 |
| 2  | 13 |
| 3  | 14 |
| 4  | 15 |
| 5  | 16 |
| 6  | 17 |
| 7  | 18 |
| 8  | 19 |
| 9  | 20 |
| 10 | 21 |
| 11 | 22 |

**USER REMOTE CONTROL**



**TERMINAL UNIT**

**SWITCH UNIT**

**\*\* NOTE \*\***

- AUTO : REMOTE mA CONTROL
- OLS : OPEN LIMIT SWITCH
- CLS : CLOSE LIMIT SWITCH
- OTS : OPEN TORQUE LIMIT SWICH
- CTS : CLOSE TORQUE LIMIT SWICH
- O/C : OPEN/CLOSE POWER RELAY(DC 24V)
- RL : RED LAMP FOR OPEN
- GL : GREEN LAMP FOR CLOSE
- YL : YELLOW LAMP FOR FAULT
- RY1 : REMOTE MONITOR RELAY
- RY3 : FAULT RELAY
- RY2/RY4 : RUNNING RELAY
- WL : WHITE LAMP FOR POWER
- BL : BLUE LAMP FOR REMOTE
- ⊙ : MARKS FOR TERMINAL

**\*\* LIMIT SWITCH CONTACT POSITIONS \*\***

| ROTOR       | CON-TACT | VALVE OPENING (%) |     |
|-------------|----------|-------------------|-----|
|             |          | 0                 | 100 |
| OPEN (OLS)  | 1-2      |                   |     |
|             | 1-3      |                   |     |
| CLOSE (CLS) | 1-2      |                   |     |
|             | 1-3      |                   |     |

— : CONTACT ON    - - - : CONTACT OFF