


REV	DATE	BY	ERO	CL
D	03/11/05			CL
C	02/25/05			CL
B	02/07/05			CL
A	01/10/05			CL

INCHES .XXX ± .005"  
 (MILLIMETERS) .XX ± .020"  
 X APPROX.



ENCLOSURE: IP65  
 TORQUE: 6Kg.m (520 in-lbs)  
 OPERATION TIME: 13sec  
 POSITION SWITCH: 4 SPDT SWITCH  
 CABLE ENTRY: 2 Plcs PG .531" (13.5)  
 (1/4" - 1/2" Wire Cable)  
 MOUNTING FLANGE: F03/F05/F07  
 acc to DIN/ISO5211

