

# Implementation of Lock-in-Last Strategy

## Supplement to Fisher™ FIELDVUE™ DVC6200 Digital Valve Controller Instruction Manuals

Many applications require a valve assembly to remain in the position it was prior to a specific control system failure (lock-in-last position). Functionality and safety can be designed into valve assemblies with FIELDVUE digital valve controllers by utilizing an array of accessories. The following paragraphs describe standard solutions for a number of generic lock-in-last applications with HART® Communicating DVC6200 digital valve controllers.

---

### Note

This instruction manual supplement also pertains to FIELDVUE DVC6000 digital valve controllers; refer to the appropriate DVC6200 or DVC6000 document below, available from your Emerson sales office, Local Business Partner, or at [Fisher.com](http://Fisher.com).

- DVC6200 Series Digital Valve Controller Quick Start Guide ([D103556X012](#))
  - DVC6200 HW2 Digital Valve Controller Instruction Manual ([D103605X012](#))
  - DVC6200 HW1 Digital Valve Controller Instruction Manual ([D103409X012](#))
  - DVC6000 Digital Valve Controllers Instruction Manual ([D102794X012](#))
- 

## Lock-in-Last on Loss of Supply Pressure

Once the supply pressure falls below a minimum value, the digital valve controller can no longer position a valve assembly; the valve will start to go to the actuator “at rest” position. The locking device senses this change and activates, preventing the remaining air from venting. The valve is “locked-in” this new position.

---

### Note


The locked-in valve position depends on the exhausting speed of the actuator.

---

## Assemblies with Single-Acting Actuators

A Fisher 167DA three-way switching valve should be used for locking a single-acting actuator in place on loss of supply pressure. Figure 1 is a schematic representing proper assembly layout. In normal operation, the digital valve controller output passes through the switching valve from port A to port B and on to the actuator.

Figure 1. Lock-in-Last on Loss of Supply Pressure for an Assembly with a Single-Acting Actuator




In a fail condition, the pressure at port D is below the switching valve's set point, causing the switching valve to trip. This closes port B, which locks the pressure in the actuator. Port C is plugged so the digital valve controller output will not exhaust to the atmosphere.

## Assemblies with Double-Acting Actuators

Similar to the locking strategy used with single-acting actuators, the locking strategy with double-acting actuators also uses a valve for locking supply pressure in the actuator. For assemblies with double-acting actuators, a Fisher 377L trip valve is used as the locking device. The 377L trip valve has two output ports for locking pressure on both sides of a double-acting actuator. Figure 2 is a schematic representing proper assembly layout.

Figure 2. Lock-in-Last on Loss of Supply Pressure for an Assembly with a Double-Acting Actuator



Connection of the digital valve controller output to a double-acting actuator determines the action of the actuator. Figure 2 shows the digital valve controller providing lower cylinder pressure through ports D and E, and upper cylinder pressure through ports A and B. When the supply pressure falls below the set point of the trip valve, the trip valve closes ports D and A and connects port B to C and port E to F. Because C and F are plugged, the control valve is locked in place by locking pressure on both sides of the actuator piston. The assembly returns to normal operation once supply pressure is restored at the trip valve INPUT port.

---

**Note**

Double-acting actuators with a 377L trip valve require a Fisher 67D or MR95H regulator. Regulators with smaller flow capacities may cause the trip valve to cycle (lock and unlock repeatedly) due to air flow demand as the assembly attempts to reset. Use a Fisher 252 or 262C pilot filter to filter supply air.

Both the 167DA switching valve and the 377L trip valve have a deadband that must be overcome. The switching valve must be calibrated to reset upon restoration of adequate supply pressure to the regulator. The 377L trip valve has only one spring selection. However, for minimal deadband, the lightest appropriate spring should be selected for the 167DA switching valve.

---

## Lock-in-Last Using Solenoid Valves

Solenoid valves are used with valve assemblies in many ways. Their electrical control can be utilized in combination with switches and controller logic to perform a number of functions.

---

**Note**

Solenoid valves placed between the output of a DVC6200 digital valve controller and the input to an actuator require a minimum  $C_v$  of 0.49. Greater restrictions can affect the response of the assembly. An example of an appropriate three-way solenoid valve for use with the digital valve controller is the ASCO™ 8327 Series solenoid valve from ASCO Valve, Inc.


---

## Assemblies with Single-Acting Actuators

A three-way universal solenoid valve can be placed between the digital valve controller output and the actuator input. Switching the valve assembly from an unlocked state to a locked state is controlled by switching power on and off to the solenoid valve. Figure 3 depicts proper assembly layout.

Under normal operating conditions the solenoid is energized and supply air flows from the digital valve controller output to the actuator input. In the fail state, power is removed from the solenoid causing the solenoid valve to close, locking air pressure in the actuator. Port 1 of the solenoid valve is plugged, preventing actuator air pressure from exhausting to the atmosphere.

Figure 3. Lock-in-Last Strategy for an Assembly with a Single-Acting Actuator Using a Solenoid Valve




NOTE:  
① A SOLENOID VALVE WITH A MINIMUM  $C_v$  OF 0.49, SUCH AS THE ASCO 8327 SERIES OR EQUIVALENT, IS REQUIRED FOR THIS ASSEMBLY

## Assemblies with Double-Acting Actuators

Assemblies with double-acting actuators require a 377L trip valve to lock pressures on both sides of the actuator piston. Figure 4 is a schematic of a double-acting actuator with lock-in-last capability shown in its normal operating mode. The solenoid valve is placed in series with the signal port of the trip valve. When tripped, the solenoid valve exhausts the signal pressure to the trip valve to atmosphere. This simulates a loss in supply pressure, causing the trip valve to lock pressure in the actuator.

Figure 4. Lock-in-Last for an Assembly with a Double-Acting Actuator Using a Solenoid Valve



NOTE:  
① THE ASCO 8320 SERIES SOLENOID VALVE OR EQUIVALENT IS APPROPRIATE FOR THIS ASSEMBLY.

The solenoid valve in this solution does not require a  $C_v$  greater than 0.49. Flow capacity of this valve can be much smaller. An example of a proper solenoid valve for this assembly is the 8320 Series three-way solenoid valve. As with all solenoid valves, ensure that the solenoid valve operating pressure differential rating is adequate for the supply pressure.

## Lock-in-Last on Loss of Supply Pressure and/or Loss of Loop Current

Most applications require a valve assembly to be in a lock-in-last fail state not only on loss of adequate supply pressure but also on loss of loop power. Lock-in-last on loss of supply pressure is quite straight forward. Lock-in-last on loss of loop power can be more complex.

Most control loops operate on a 4-20 mA control signal. A solenoid valve, adequately sized for the application, requires more than 4 mA to energize. Therefore, the control loop cannot be used to energize the solenoid. Instead the solenoid must be powered by a separate 24 volt power source. Thus an additional device is required to monitor the current to the digital valve controller and control the power to the solenoid.

A current threshold switch can be used to monitor the 4-20 mA signal to the digital valve controller. Upon loss of this signal, or when the signal falls below the threshold, the threshold switch will open an internal relay. This relay, if placed between a solenoid valve and its power supply, will essentially open and close the solenoid valve. The solenoid valve can be placed in line with the tubing to the actuator to provide the lock-in-last function.

To ensure adequate response time of a locking system to a loss of loop current, a threshold switch with a maximum deadtime of 0.025 seconds should be used. The locking system will be faster than the response of the positioning system to the failure.

One switch that meets the maximum deadtime requirements is the Phoenix Contact Dual Setpoint Module, Model MCR-2SP/UI.

---

### Note


The MCR-2SP/UI switch is not provided by Emerson. Order this switch from Phoenix Contact.

---

## Assemblies with Single-Acting Actuators

Assemblies with a single-acting actuator use a 167DA three-way switching valve in conjunction with a solenoid valve. Figure 5 is a schematic of a single-acting actuator assembly with lock-in-last capability on loss of supply pressure or loop current. Under normal operating conditions power is supplied to the solenoid valve and adequate supply pressure is available to the switching valve. Upon loss of supply pressure, the set point of the switching valve is exceeded and the switching valve trips.

Figure 5. Lock-in-Last on Loss of Loop Current and/or Supply Pressure for an Assembly with a Single-Acting Actuator



NOTE:  
THE ASCO 8320 SERIES SOLENOID VALVE OR EQUIVALENT IS APPROPRIATE FOR THIS ASSEMBLY.

Upon loss of loop current, the relay of the current threshold switch opens. This cuts power to the solenoid valve, causing the solenoid valve to trip. When the solenoid valve trips, the supply pressure that was holding the switching valve open is exhausted to atmosphere. This simulates a loss of supply pressure, causing the switching valve to trip.


**Note**

Use a single power source for both the analog output (AO) card providing loop current to the digital valve controller and the solenoid valve. This ensures power will be maintained to the solenoid valve so long as power is maintained to the AO card.

## Assemblies with Double-Acting Actuators

The same principle used for assemblies with single-acting actuators is used for assemblies with double-acting actuators. Figure 6 is a schematic of the double-acting assembly with lock-in-last capability shown under normal operating conditions.

Figure 6. Lock-in-Last on Loss of Loop Current and/or Supply Pressure for an Assembly with a Double-Acting Actuator



NOTE:  
 ① THE ASCO 8320 SERIES SOLENOID VALVE OR EQUIVALENT IS APPROPRIATE FOR THIS ASSEMBLY.

**Note**

DVC6200 digital valve controllers require approximately 0.5 seconds to initialize upon power up. During this time, the digital valve controller cannot provide control. In the case where control of a previously locked valve is restored to a digital valve controller prior to the completion of initialization, the valve will travel toward its fail-safe position. A relay with an engagement deadtime, such as the MCR-2SP/UI from Phoenix Contact, can be used to delay the release of the locking system until the digital valve controller has completely initialized. An engagement delay of 1.0 seconds will adequately minimize the dip in travel.

**Note**

While the valve is in a locked state, the set point from the digital valve controller may change in response to changes in process conditions. This change in set point may result in a process bump when control is restored to the digital valve controller.

Phoenix Threshold Switch Specifications<sup>(1)</sup>

<p><b>Switch Model Number</b> MCR-2SP/UI-DC</p> <p><b>Size</b> 44.5 X 76.2 X 108 mm (1-3/4 X 3 x 4-1/4 inches)</p> <p><b>Mounting</b> Mounts in control room (DIN rail mount)</p> <p><b>Wiring</b> Connect switch in series between control loop and field device Control Loop + to switch terminal 2 Control Loop - to switch terminal 1 24 VDC Power Supply to switch connections Power Supply + to switch terminal 8 Power Supply - to switch terminal 7</p>	<p>Connect switch in series between the solenoid valve and 24 VDC power supply Power Supply + to switch terminal 12 Power Supply - to switch terminal 13</p> <p><b>Configuration</b> <i>Set point 1: 15% (3 mA)</i> <i>Engagement Deadtime: 1 second</i></p> <p><b>Switch Settings</b></p> <table border="1"> <thead> <tr> <th>Switch</th> <th>Setting</th> <th>Description</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>On</td> <td>SP 1</td> </tr> <tr> <td>2</td> <td>On</td> <td>SP 2</td> </tr> <tr> <td>3</td> <td>Off</td> <td>In</td> </tr> <tr> <td>4</td> <td>On</td> <td>In</td> </tr> <tr> <td>5</td> <td>On</td> <td>Out 1</td> </tr> <tr> <td>6</td> <td>Off</td> <td>Out 2</td> </tr> <tr> <td>7</td> <td>Off</td> <td>Hys. 1</td> </tr> <tr> <td>8</td> <td>Off</td> <td>Hys. 2</td> </tr> </tbody> </table>	Switch	Setting	Description	1	On	SP 1	2	On	SP 2	3	Off	In	4	On	In	5	On	Out 1	6	Off	Out 2	7	Off	Hys. 1	8	Off	Hys. 2
Switch	Setting	Description																										
1	On	SP 1																										
2	On	SP 2																										
3	Off	In																										
4	On	In																										
5	On	Out 1																										
6	Off	Out 2																										
7	Off	Hys. 1																										
8	Off	Hys. 2																										

1. The Phoenix threshold switch is not supplied by Emerson. Order the switch from the manufacturer, Phoenix Contact ([www.phoenixcontact.com](http://www.phoenixcontact.com)). For complete installation details, see the instruction manual provided by the switch manufacturer.

Neither Emerson, Emerson Automation Solutions, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher and FIELDVUE are marks owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. Emerson Process Management, Emerson, and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Automation Solutions  
Marshalltown, Iowa 50158 USA  
Sorocaba, 18087 Brazil  
Cernay, 68700 France  
Dubai, United Arab Emirates  
Singapore 128461 Singapore

[www.Fisher.com](http://www.Fisher.com)

