


# M-series Mass Connection Solutions



- Fast, easy and error-free cabinet wiring
- Modular design, improves reliability
- Lowers overall termination footprint
- Significant labor and work reduction
- LED's and replaceable fuses for discrete signals
- Termination Fault Detection between discrete traditional I/O cards and Mass Connection board signals

## Introduction

The DeltaV™ M-series Mass Connection Solutions provide fast, easy and reliable connection from field devices to DeltaV simplex and redundant, high density discrete I/O Cards, while providing several wiring options.

The modular design of the Mass Connection Boards further helps to lower the overall termination footprint due to flexible mounting capabilities.

Ribbon cable connectors will be used to connect the Mass Connection Boards easily to the simplex or redundant, high density discrete I/O Cards, where loop and termination fault diagnostic information are available.

## Benefits

**Fast and easy way to connect terminals.** The DeltaV simplex and redundant high density discrete I/O Cards can be easily wired to the Mass Connection Boards within seconds.

No tools are necessary to connect the ribbon cables, so you can significantly reduce labor costs by eliminating additional cabinet wiring.

**Modular design, improved reliability.** The modular designed Mass Connection Boards are more reliable than other traditional solution, by splitting the Signals up, to a max of 16 Signals.

**Optimization of space.** The DeltaV M-series Mass Connection Solutions offer significant space advantages by integrating all needed cabinet wiring components on one board.

**Significant labor work reduction.** No need for cross wiring between I/O cards and Mass Connection Boards anymore, due to flexible 1:1 ribbon cable based connectivity.

**Significant cost reduction.** Due to the fact that off-the-shelf Ribbon cables can be used inside a Cabinet with a max. Length of 3m, significant cost reductions can be achieved.

In some cases, longer cables are needed for connections between two Cabinets. 6m long Standard Round Ribbon Cables can be ordered to be used with the Mass Connection Solutions.

**Loop Disconnect features for all signal types.** On the discrete Mass Connection boards, there is a loop disconnect feature realized using replaceable fuses. In this way, loop power to the field can be easily disconnected, during maintenance activities.

**Termination Fault Detection.** With the discrete Mass Connection boards, power or cable failures can now be detected by DeltaV Diagnostic when used with the new Plus Cards.

## Product Description

### DI Plus Mass Connection Board



The DI Plus Mass Connection Solution (set of two boards) connects to the **new simplex or redundant M-series Plus DI, 32 Channel, 24 VDC, Dry Contact cards** by using either two ribbon cables with 20-Pin connectors or two of the 20-Pin standard Round Ribbon Cable, which is required if the distance is longer than 3m.

Up to 16, 24 VDC based discrete input Signals can be connected to each of the DI Plus Mass Connection Boards by screw terminals. Dry Contact or 24 VDC Isolated Field Signals are supported by the 2- row screw architecture.

Yellow LED's are providing status indication for each channel, while the replaceable fuses can be used to disconnect loop power to the field, during maintenance activities.

A **Termination Fault Detection** feature is built into each of the DI Plus Mass Connection boards which allows the new **redundant M-series Plus DI, 32 Channel, 24 VDC, Dry Contact cards** to detect power or cable failures on the board. There is a **jumper on the board** to be able to turn this feature off, in case rewiring needs to be performed while the process is running.

The new M-series Plus DI, 32 Channel, 24 VDC, Dry Contact card does have **two new parameters in the Explorer view**, one for each cable connection. When these Parameters are turned on, DeltaV Diagnostics will mark the status of affected Signals accordingly.

Please refer to the Cross Reference List for your application.

### DO Plus Mass Connection Board



The DO Plus Mass Connection Solution (set of four boards) connects to the **new simplex or redundant M-series Plus DO, 32 Channel, 24 VDC, High-Side cards** by using either two ribbon cables with 20-Pin connectors or two of the 20-Pin standard Round Ribbon Cable, which is required if the distance is longer than 3m. Two DO Plus Mass Connection boards need to be daisy chained to get to 16 Channels, which can be connected back to the card. A short ribbon cable with 20-Pin connectors can be used for that purpose too.

Up to 8 Field devices can be connected to each of the DO Plus Mass Connection Boards by screw terminals. **Either +24 VDC high-side relay outputs or voltage free relay contacts can be used**, pending on the position of the fuse, which can be jumpered for this reason.

Yellow LED's are providing status Indication for each Channel, while the replaceable fuses can be used to disconnect loop power to the field, during maintenance activities.

A **Termination Fault Detection** feature is built into each of the DO Plus Mass Connection boards which allow the new **redundant M-series Plus DO, 32 Channel, High-Side cards** to detect power or cable failures on the board. There is a jumper on the board to be able to turn this feature off, in case rewiring needs to be performed while the process is running.

The new M-series Plus DO, 32 Channel, 24 VDC, High-Side card does have **two new parameters in the Explorer view**, one for each cable connection. When these Parameters are turned on, DeltaV Diagnostics will mark the status of affected Signals accordingly.

Please refer to the Cross Reference List for your application.

### 6m Round Ribbon Cable



The 6m long Standard Round Ribbon Cable is recommended **for distances longer than 3m.**

## Cross Reference List

Description	Ordering Information	VE40X1S2T2B7	VE40X1S2T2B8	Set consists of
DI Plus Mass Connection Solution	-	√	-	2 items
DO Mass Connection Solution	-	-	√	4 items
20-pin Round Ribbon Cable 6m	SE4000L6P20**	√	√	2 items
If the X gets replaced by a: 0 = your order will contain a simplex Card without a Mass Connection Solution* 3 = your order will contain a redundant Card set without a Mass Connection Solution* 5 = your order will contain a simplex Card with the correct Mass Connection Solution* 8 = your order will contain a redundant Card set with the correct Mass Connection Solution*				

\*If applicable

\*\* Round Ribbon Cables are not included in the bundles and needs to be ordered separately

## Hardware Specification

Common Environmental Specifications for Mass Connection Boards	
Category	Specifications
Operating temperature	-20 to +70°C
Storage temperature	-40 to 85°C
Relative humidity	5 to 95% Non-Condensing
Airborne Contaminates	ISA-S71.04-1985 Airborne Contaminants Class G3 Conformal coating
Protection rating	IP 20
Shock	10g, 1/2 sine wave for 11 milliseconds
Vibration	1mm Peak-to-Peak from 2 to 13.2 Hz, 0.7g from 13.2 to 150 Hz

\* See temperature derating on DO Plus Mass Connection Boards in specification below

Specifications for DI Plus Mass Connection Boards	
Category	Specifications
Channel Type	24 VDC Dry Contact, or 24 VDC Isolated
Number of Channels	16
Isolation	The field wiring connections are optically isolated from the DI Card circuits and factory tested to 1000 VDC for 2s. No Channel-to-Channel isolation.
Detection Level for ON	> 2 mA @ 24 VDC
Detection Level for OFF	< 0.25 mA @ 24 VDC
Source Impedance	5 K $\Omega$
Source Voltage	+24 VDC Input Power, recommend external fuse at power source
Field circuit power per board	+24VDC +/- 10% @ 75mA typical, 100mA maximum
Dimensions	Depth: 110.05 mm; Height: 44.1 mm; Width: 102.82mm

Specifications for DO Mass Connection Boards	
Category	Specifications
Channel Type	Isolated Relay Contact or 24 VDC High Side
Output Channel Options and Ratings	Isolated Relay Contacts - 250 VAC/24 VDC maximum@ 5 Amps maximum per channel +24 VDC High Side @ 5 Amps maximum per channel, 10 Amps maximum per board
Isolation	Isolated Relay Contacts – Isolated at 250 VAC and factory tested to 3600 VDC (channel-to-system and channel-to-channel)
	+24 VDC High Side – Isolated at 250 VAC and factory tested to 3600 VDC (channel-to-system). No channel-to-channel isolation
Relay Max. switching current	5A for 30 VDC; 5A for 250 VAC
Optional Power for +24 VDC High Side Outputs	+24VDC +/- 10% @ 10 Amps maximum
Dimensions	Depth: 109.75 mm; Height: 60.52 mm; Width: 133.3 mm

*\*De-rate to 3 A per channel when operating above 60°C ambient.*

Common Environmental / Specifications for Round Ribbon Cables	
Category	Specifications
Operating temperature	-20 to +70°C
Storage temperature	-20 to 70°C
Relative humidity	5 to 95% Non-Condensing
Airborne Contaminates	ISA-S71.04-1985 Airborne Contaminants Class G3 Conformal coating
Protection rating	IP 20
Available Cable lengths	6 m
Wires / Pairs per Cable	50/25 or 20/10
Wire Gauge	0.14 mm <sup>2</sup> / 26 AWG

## Certifications

The following certifications are available for M-series Mass Connection Solutions:

- **CE:**
  - EMC- EN 61326-1
  - LVD: Directive 2006/95/EC
- **FM:**
  - FM 3600
  - FM 3611
  - FM 3810
- **CSA:**
  - CAN/CSA-C22.2 No. 61010-1-04
- **ATEX:**
  - ATEX 94/9/EC
  - EN60079-0
  - EN60079-15
- **IEC-Ex:**
  - IEC60079-0
  - IEC60079-15

### Certifications



M-series Mass Connection Solutions will be submitted for the following certifications:

Marine Certifications IACS E10:



- ABS Certificate of Design Assessment
- DNV-GL Marine Certificate

## Hazardous Area/Location

M-series Mass Connection Solutions can be installed and used based on the following Standards:

- **FM (USA):**
  - Class I, Division 2, Groups A, B, C, D, T4
- **FM (Canada):**
  - Class I, Division 2, Groups A, B, C, D, T4
- **ATEX:**
  -  Ex nA IIC T4 Gc
  -  Ex nA nC IIC T4 Gc
- **IEC-Ex:**

Installation and Field Circuits:

-  Ex nA IIC T4 Gc
-  Ex nA nC IIC T4 Gc

Regarding the Installation instructions please refer to the following Documents:

<i>Class 1 Division 2 Installation Instructions DeltaV M-Series</i>	<i>12P1293</i>
<i>Zone 2 Installation Instructions DeltaV M-Series</i>	<i>12P2046</i>

## Ordering Information

Description	Model Number
DI Plus Mass Connection Solution (two boards as a set)	VE4051MC1
DO Mass Connection Solution (two boards as a set)	VE4052MC1
Round Ribbon Cable (6m, two as a set)	VE4050R1

*\*M-series Traditional I/O Cards and Mass Connection Solutions can only be ordered in a set right now, please refer to the PDS M-series Traditional I/O to find the correct ordering number for the set.*

## Spare part Ordering Information

Description	Model Number
DI Plus Mass Connection Board	KJ4007X1-BB1
DO Mass Connection Board	KJ4007X1-BC1
DI Mass Connection Board Fuse – Main 125 VAC/1 A, pack of 10 fuses	KJ4007X1-DB1
DI Mass Connection Board Fuse – Channel 125 VAC/160mA, pack of 10 fuses	KJ4007X1-DA1
DO Mass Connection Board Fuse – Main 125 VAC/10 A, pack of 10 fuses	KJ4007X1-DD1
DO Mass Connection Board Fuse – Channel 250 VAC/5 A, pack of 10 fuses	KJ4007X1-DC1



## Related 3rd Party Products

Description	Phoenix Contact Part Number	
	Part Number	Part Type
20-pin Round Ribbon Cable 0.5m	2296391	FLK 20/EZ-DR/ 50KONFEK
20-pin Round Ribbon Cable 1.0m	2296401	FLK 20/EZ-DR/ 100KONFEK
20-pin Round Ribbon Cable 1.5m	2296472	FLK 20/EZ-DR/ 150KONFEK
20-pin Round Ribbon Cable 2.0m	2296485	FLK 20/EZ-DR/ 200KONFEK
20-pin Round Ribbon Cable 3.0m	2296498	FLK 20/EZ-DR/ 300KONFEK
20-pin Round Ribbon Cable 4.0m	2296508	FLK 20/EZ-DR/ 400KONFEK
20-pin Round Ribbon Cable 8.0m	2296524	FLK 20/EZ-DR/ 800KONFEK
20-pin Round Ribbon Cable 10.0m	2296537	FLK 20/EZ-DR/1000KONFEK

### Emerson

#### North America, Latin America:

+1 800 833 8314 or

+1 512 832 3774

#### Asia Pacific:

+65 6777 8211

#### Europe, Middle East:

+41 41 768 6111

[www.emerson.com/deltav](http://www.emerson.com/deltav)

©2017, Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. The DeltaV logo is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.