



Cu 90

Pt 100



BLACK WIRES, (WIRES TO BE TWISTED IN 3-GROUPS: PINK, BLACK, BLACK; WHITE, BLACK, BLACK,....ETC.)

COLOUR CODED LEAD OUT WIRES  
SEE TABLE BELOW

1000-5000

ISSUED BY GKT-AK	WEEK 9411	PRODUCT CODE REX	TITLE ACAD	INSTALLATION DRAWING TITLE TEMPERATURE SENSOR STAINLESS STEEL Ø20MM
APPROVED BY GKT	WEEK 9240	ORIGINAL DWG NO. 002-949	SCALE 1:2	
ROSEMOUNT		1 <sup>ST</sup> ANGLE	DOC TYPE 2	DWG NO. 9240 002-949
Tank Gauging			ISSUE	SHEET
			5	1/1

THE COMPANY ASSUMES NO RESPONSIBILITY FOR THE ACCURACY OF THIS DOCUMENT. THE USER SHALL BE RESPONSIBLE FOR THE ACCURACY OF THE INFORMATION CONTAINED HEREIN. WITHOUT OUR AUTHORIZATION OR CONSENT TO THE KNOWLEDGE OF A THIRD PARTY, COMMUNICATION WILL BE PROSECUTED. ROSEMOUNT TANK GAUGING AB, SWEDEN.