



Cu 90

Pt 100



BLACK WIRES, (WIRES TO BE TWISTED IN 3-GROUPS:
PINK, BLACK, BLACK; WHITE, BLACK, BLACK,....ETC.)

COLOUR CODED LEAD OUT WIRES
SEE TABLE BELOW

ISSUED BY GKT-AK	WEEK 9411	PRODUCT CODE REX	FILE ACAD	INSTALLATION DRAWING TITLE TEMPERATURE SENSOR STAINLESS STEEL Ø29MM
APPROVED BY GKT	ORIGINAL DWG NO. 9240 002-947	SCALE 1:2	DOC TYPE 2	DWG NO. 9240 002-947
ROSEMOUNT Tank Gauging				ISSUE SHEET 4 1/1

THE DESIGN/CONSTRUCTION OF THIS DOCUMENT IS OURS. WE WILL BE RESPONSIBLE FOR THE QUALITY. THIS DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR SUBJECT TO THE KNOWLEDGE OF A THIRD PARTY. COMMUNICATION WILL BE PROSECUTED. ROSEMOUNT TANK GAUGING AB, SWEDEN.