



Data sheet


Sheet No.: 1.501.01 Rev. B
Date: January 2012

EL-O-MATIC ACTUATOR WITH ONE WAY LIMIT STOPS

L1/LF



Note: Do not adjust under pressure.



Dim. in mm.	ACTUATOR TYPE	
	P2500	P4000
A	580	708
B	795	1152
C	356	380
D	30	30

Description

Actuators with one way adjustable limit stops are used where the maximum opening (or closing) position of the valve needs to be reduced. For instance to adjust the maximum capacity of a remote operated valve. Also actuators with 180° rotation are available with these stops.

Operation

Stop screws are fitted to both endcaps and the screw length is such that adjustment is possible through the specified rotation of the actuator. The modified endcap is machined for -0.5° to +93° rotation for all P-Series models.

Identification

"L1" is added to the basic part number i.e. PD2500-L1

Specification



Pressure : Up to 8 bar
 Operating media : Air, dry or lubricated or non-corrosive gas
 Torque (90°) : Data sheet 1.104.01 - 1.104.04
 (180°) : Data sheet P-Series 1.204.01 and 1.204.02
 Other dimensions : Data sheet 1.103.XXX (90°)
 : Data sheet 1.203.011 (180°)
 Temperature: -20° to +80°C
 Adjustable range : 80°-93°(90°) or 160°-186° (180°)

Adjustable position (see data sheet 1.503 or 1.504):

Code	Position	Spring to:
A	Valve open	close
B	Valve open	close
C	Valve closed	open
D	Valve closed	open

Note:

- 1) Can be provided with extra long screws for full range adjustment (identification: PD2500-LF)
- 2) This option in combination of a manual override gearbox is redundant



EL-O-MATIC

www.El-O-matic.com

Copyright © Emerson Process Management. The information in this document is subject to change without notice.

Updated data sheets can be obtained from our website www.El-O-matic.com or from your nearest Valve Automation Center **USA:** +1 813 319 0266 **Europe:** +31 74 256 10 10 **Asia-Pacific:** +65 6501 4600



EMERSON
Process Management