Micro Motion[™] 1000 and 2000 Transmitters with MVD[™] Technology





Advanced architecture with flexible installation options

- Integral or remote mounting provides maximum flexibility
- Cost-effective 4-wire interface reduces installation costs
- Remote field mount models available with stainless steel housing for harsher environments
- DIN rail option reduces complexity and increases versatility

Wide variety of I/O and application capabilities to fit your needs

- High-speed DSP for accuracy under the toughest conditions—entrained gas, high noise, high turndown, and more
- Concentration and net flow measurement eliminate the need for additional instruments
- Approved for custody transfer and certified for SIL2 and SIL3, which provides measurement confidence and reliability
- WirelessHART® option allows you to gain access to additional diagnostics and process information without added wiring costs





Micro Motion 1000 and 2000 transmitters

1000 and 2000 transmitters allow for the precise fit and integration for your Micro Motion Coriolis Flow and Density meters. Powerful adaptability to your installation needs combined with ultimate flexibility in output connections provides the proper fit for your application.

MVD technology makes your meter work smarter

- Front-end signal processing gives faster response time and dramatically reduces signal noise
- Provides reduced wiring costs through use of standard 4-wire instrument cable
- Onboard signal processing results in the cleanest, most accurate signal delivered, even with tough measurement conditions such as entrained gas

Smart Meter Verification™: advanced diagnostics for your entire system

- A comprehensive test that can be run locally or from the control room to provide confidence in your meter functionality and performance
- Verifies that your meter performs as well as the day it was installed, giving you assurance in less than 90 seconds
- A basic version of Smart Meter Verification is included with new enhanced core processors that provides simple pass/fail results, and simple diagnostics that run without interrupting your processes
- A licensed version includes enhanced capabilities, such as viewing previous results and generating comprehensive reports

Mounting and installation flexibility to fit your exact needs

- Form factors include rugged field mounts with a full suite of hazardous area approvals or DIN rail packages for cost effective control room cabinets
- Local user interfaces provide detailed operator feedback and accessibility
- Connection to new or existing Micro Motion sensors easily achieved through flexible configurations

Connection and Interface adaptability for seamless integration

- Broad combinations of analog and frequency outputs allow for you to get signals where you need them
- Digital outputs bring a wealth of information to your control room, with offerings for Smart WirelessHART®, HART®, Modbus®, FOUNDATION™ Fieldbus, and PROFIBUS-PA
- Direct plug and play operation with the Micro Motion Ethernet/IP® Module for fast, efficient communications

Access information when you need it with asset tags

Newly shipped devices include a unique QR code asset tag that enables you to access serialized information directly from the device. With this capability, you can:

- Access device drawings, diagrams, technical documentation, and troubleshooting information in your MyEmerson account
- Improve mean time to repair and maintain efficiency
- Ensure confidence that you have located the correct device
- Eliminate the time-consuming process of locating and transcribing nameplates to view asset information

Overview

Feature	2700	2500	1700	1500
For applications requiring simultaneous monitoring of multiple flow variables: Selected combinations of outputs including milliamp, frequency, and discrete I/O	•	•		
 Modbus, HART, WirelessHART, FOUNDATION fieldbus, and PROFIBUS-PA digital communications 				
 Simultaneously outputs multiple variables, including: mass flow rate, volume flow rate, gas standard volume flow rate, density, temperature, and drive gain 				
For applications requiring only mass flow or volume flow measurement: Milliamp and a frequency/pulse output			•	•
 HART or Modbus digital communications 				
 Outputs one of: mass flow rate, volume flow rate, or gas standard volume flow rate 				
Compact, integral mounting to sensor with 360 degrees of rotation, or field mount option to a 4-wire or 9-wire Micro Motion sensor	•		•	
1700M/P and 2700M/P transmitters (with stainless steel housing) are available only as remote mount.				
Compact, small-footprint, remote-mount transmitter using 1.38 in (35 mm) DIN rail, with connection to either a 4-wire or 9-wire Micro Motion sensor		•		•
Class I, Division 1/Zone 1 local operator interface: Standard display supports English, French, Spanish, and German languages	•		•	
Chinese-language display supports English and Chinese languages This display is available for purchase in China only, on 1700 and 2700 transmitters with analog outputs. This display is certified for ATEX / NEPSI / IECEx Zone 1 use only. For detailed information regarding the approvals options available, see Hazardous area classifications.				
 View process variables, handle alarms, control totalizers, meter configuration, and more 				
 Interface functions can be customized and password protected 				
SIS certification:	•		•	
 Available on the mA Output on the 1700 with output option codes A or D, and on the 2700 with output option codes A, B, C, or D 				
 One meter can be used in SIL 2 applications, and SIL 3 levels can be achieved if redundant meters are used 				
Compatible with a Smart Wireless THUM [™] Adapter for WirelessHART capability For more information on the Smart Wireless THUM Adapter, see the <i>Emerson Wireless</i> THUM Adapter Product Data Sheet available at Emerson.com.	•	•	•	•
Available with Smart Meter Verification	•	•	•	•
Available with filling and dosing application for filling, dosing, and bottling processes				•
Fuel consumption application	•	•		
Production Volume Reconciliation (PVR)	•	•	•	•
Piecewise Linearization (PWL)	•	•	•	•
Transient Bubble Remediation (TBR)	•	•	•	•
Transient Mist Remediation (TMR)	•	•	•	•

Applications

Application are custom designed programs and software available to offer additional functionality and performance to transmitters. These applications are available through options in the transmitter model code, see the ordering information section for details.

Smart Meter Verification (SMV)

- Provides a quick, complete assessment of a Coriolis meter, determining whether the meter has been affected by erosion, corrosion, or other influences affecting meter calibration.
- No secondary references are required to perform this operation, and the meter can continue normal process measurement while the test is in progress.
- A basic version of Smart Meter Verification is included with new enhanced core processors that provides simple pass/fail results, and simple diagnostics that run without interrupting your processes.

Discrete batch control

- Simple batch control based on totalizer values
- For transmitters with analog or intrinsically safe outputs, the Frequency Output can be configured as a Discrete Output.
- For transmitters with configurable I/O, a channel can be configured as a Discrete Output.

Weights & Measures custody transfer

- Physical and software security
- Security-alarm posting
- Mass or volume totalizer that can be configured by the user
- Compliant with MID 2014/32/EU Annex MI-005
- Certified by NTEP and OIML

Concentration measurement

Provides concentration measurement based on either industry-specific or liquid-specific units and relationships. Standard measurement options include:

- Industry-specific:
 - Brix
 - °Plato
 - Balling
 - Baumé at SG60/60
 - Specific gravity
- Liquid-specific:
 - %HFCS
 - Concentration derived from reference density
 - Concentration derived from specific gravity

Additionally, the application can be customized for site-specific concentration measurement (such as %HNO₃, %NaOH).

Petroleum measurement

Adds the following calculations to the standard software:

- Calculates base density (corrected API Gravity) and Ctl (the correction for the effect of temperature on a liquid)
- Calculates gross volume at standard temperature
- Calculates flow-weighted average temperature and flow-weighted average observed gravity (flowing density)

Fuel consumption

- Automatically calculates the fluid consumption between two Coriolis flow sensors, typically for recirculating fuel consumption loops
- Eliminates the need to program an external calculation system and minimizes common inaccuracies related to time lag, sampling issues and cumulative errors
- Uses a proprietary algorithm that adapts to the unique calibration of each pair of Coriolis flow sensors

Production Volume Reconciliation (PVR)

- Provides oil and water volumes through density-based calculations for both line and reference conditions
- Detects bubble entrainment or flashing in the sensor and can correct volumes accordingly
- Best for undersized three-phase separators that frequently have intermittent gas or water contamination in the oil leg
- Offers a simple, low-cost solution for net oil and net water measurement for two-phase separators

Transient Bubble Remediation (TBR)

- Used with single-component liquid streams that may experience intermittent low levels of gas entrainment (gas carryunder)
- Enables accurate measurement of a single fluid during periods of entrained gas by providing a substitute density value based on the immediately preceding process density (standard configuration)
- Tracks total time of aerated flow to assist in diagnosing process issues that may cause aeration

Transient Mist Remediation (TMR)

- Used with gas streams that may experience intermittent low levels of liquid entrainment (liquid carry-over)
- Allows gas measurement to continue during periods of entrained liquid (mist) by providing a substitute flow rate value based on the immediately preceding process flow rate
- Returns to reporting the measured flow rate when the mist interval is over, increased or decreased by a maximum
 of 10 percent, until flow totals are appropriately adjusted for the unmeasured flow
- Provides an indication of the amount of time that liquid was present in the stream identifying process improvements to reduce gas stream contamination

Piecewise Linearization (PWL) for enhanced gas applications

- Provides gas calibration enhancement capability for industry-leading gas measurement performance
- Designed specifically for midstream natural gas fiscal metering applications

Note

Piecewise Linearization is not available with Micro Motion 5700 Transmitter FOUNDATION Fieldbus.

Third-party gas calibration services are not included.

Electrical connections

1500 and 2500 transmitters

Connection type	Description
Input/Output	■ Three pairs of wiring terminals for transmitter outputs
	One pair of terminals for digital communications (Modbus/RS-485)
Power	The transmitter has two pairs of terminals for the power connection: Either pair accepts DC power The remaining pair can be used for making a jumper connection to a second transmitter
Service port	One pair of terminals supports Modbus/RS-485 signal or service port mode. On device power-up, user has 10 seconds to connect in service port mode. After 10 seconds, the terminals default to Modbus/RS-485 mode.

Note

Each screw terminal connection accepts one or two solid conductors, 14 AWG (2.08 mm²) to 12 AWG (3.31 mm²) or one or two stranded conductors, 22 AWG (0.326 mm²) to 14 AWG (2.08 mm²). Each plug type connector accepts one stranded or solid conductor, 24 AWG (0.205 mm²) to 12 AWG (3.31 mm²).

Table 1: 1700 and 2700 transmitters

Connection type	1700	2700	
Input/Output	 Intrinsically safe version: Two pairs of wiring terminals for transmitter outputs 	Three pairs of wiring terminals for transmitter I/O and communications	
	Non-intrinsically safe analog outputs (output option A): Three pairs of wiring terminals for transmitter outputs		
Power	One pair of wiring terminals accepts AC or DC power		
	One internal ground lug for power-supply ground wiring		
Service port	Two clips for temporary connection to the service port		

Notes

- Each screw terminal connection accepts one or two solid conductors, 14 AWG (2.08 mm²) to 12 AWG (3.31 mm²) or one or two stranded conductors, 22 AWG (0.326 mm²) to 14 AWG (2.08 mm²). Each plug type connector accepts one stranded or solid conductor, 24 AWG (0.205 mm²) to 12 AWG (3.31 mm²).
- For 1700/2700 transmitters with an integral core processor (mounting code C), the 4-wire connection between the transmitter and core processor is not normally accessed.

Output summary

Model	Output code	Channel A	Channel B	Channel C	Channel D
1500	A	mA w/ Bell 202 HART	unused	FO/DO	RS-485 HART and Modbus

Model	Output code	Channel A	Channel B	Channel C	Channel D
	C ⁽¹⁾	mA	DO	DO/DI	RS-485Modbus
2500	В	mA w/ Bell 202 HART	configurable to mA, FO, or DO (default mA)	configurable to FO, DO, or DI (default FO)	RS-485 HART and Modbus
	С	mA w/ Bell 202 HART	configurable to mA, FO, or DO (custom)	configurable to FO, DO, or DI (custom)	RS-485 HART and Modbus
1700	А	mA w/ Bell 202 HART	FO/DO	RS485 HART and Modbus	N/A
	D	mA w/ Bell 202 HART	FO/DO	unused	N/A
2700	А	mA w/ Bell 202 HART	FO/DO	RS485 HART and Modbus	N/A
	В	mA w/ Bell 202 HART	configurable to mA, FO, or DO (default mA)	configurable to FO, DO, or DI (default FO)	N/A
	С	mA w/ Bell 202 HART	configurable to mA, FO, or DO (custom)	configurable to FO, DO, or DI (custom)	N/A
	D	mA w/ Bell 202 HART	FO/DO	mA	N/A
	E	FOUNDATION Fieldbus (FISCO)	unused	unused	N/A
	G	Profibus PA	unused	unused	N/A
	N	FOUNDATION Fieldbus (FNICO)	unused	unused	N/A
	2 ⁽²⁾	mA w/ Bell 202 HART	FO/DO	RS485 HART and Modbus	N/A
	3 ⁽²⁾	mA w/ Bell 202 HART	configurable to mA, FO, or DO (custom)	configurable to FO, DO, or DI (custom)	N/A
	4(2)	mA w/ Bell 202 HART	FO	mA	N/A

⁽¹⁾ Requires Filling & Dosing software package.

Legend

FO = Frequency/pulse Output, scalable to 10,000 Hz

DO = Discrete Output

DI = Discrete Input

Input/output signal detail

All codes

Inputs for all codes:

- With mounting codes R, M, and B: One 4-wire sensor signal input connection, intrinsically safe
- With mounting codes C and P (9-wire remote transmitter): One 9-wire sensor signal input connection, intrinsically safe

⁽²⁾ Output codes 2, 3, and 4 include a 2700 transmitter housing with extra conduit connection for 775 THUM mounting capability.

Output code A or 2

These codes are for non-intrinsically safe mA Output (with HART and Modbus) for 1500, 1700, and 2700 transmitters.

One active 4-20 mA Output

- Not intrinsically safe
- Isolated to ±50 VDC from all other outputs and earth ground
- Maximum load limit: 820 ohms
- 1500 and 1700 can report mass flow or volume flow
- 2700 can report mass flow, volume flow, density, temperature, or drive gain
- Output is linear with process from 3.8 to 20.5 mA, per NAMUR NE 43 (February 2003)

One active FO/pulse output

- Not intrinsically safe
- Can report mass flow or volume flow, which can be used to indicate flow rate or total
- For 1500 and 1700, Frequency Output reports the same flow variable as the mA Output
- For 2700, Frequency Output is independent of mA Output
- Scalable to 10,000 Hz
- For 1500 and 2500, output voltage is +15 VDC ±3% with a 2.2 kohm internal pull-up resistor
- For 1700 and 2700, output voltage is +24 VDC ±3% with a 2.2 kohm internal pull-up resistor
- Output is linear with flow rate to 12,500 Hz
- Configurable polarity: active high or active low
- 1700 Discrete Output: Can be configured as a Discrete Output to report flow direction and flow switch
- 2700 Discrete Output: Can be configured as a Discrete Output to report 5 discrete events, flow direction, flow switch, calibration in progress, or fault
- On 1700 and 2700 transmitters, this can also be configured as a Discrete Output

Output codes B, C, and 3

These codes are for non-intrinsically safe configurable output 2500 and 2700 transmitters. The transmitter has a total of 3 configurable inputs/outputs. Refer to the following data for the ways that these 3 inputs/outputs can be configured.

One or two active 4-20 mAO

- Not intrinsically safe
- Isolated to ±50 VDC from all other outputs and earth ground
- Maximum load limit of mA1: 820 ohms; of mA2: 420 ohms
- Can report mass flow, volume flow, density, temperature, or drive gain
- Output is linear with process from 3.8 to 20.5 mA, per NAMUR NE 43 (February 2003)

One or two active or passive FOs/pulse outputs

- Not intrinsically safe
- Can report mass flow or volume flow, which can be used to indicate flow rate or total

- If configured as a dual pulse output, the channels are electrically isolated but not independent (see custody transfer note below)
- Scalable to 10,000 Hz
- If active, output voltage is +15 VDC ±3% with a 2.2 kohm internal pull-up resistor
- If passive, output voltage is 30 VDC maximum, 24 VDC typical, sinking up to 500 mA at 30 VDC
- Output is linear with flow rate to 12,500 Hz

One or two active or passive DOs

- Not intrinsically safe
- Can report 5 discrete events, flow switch, forward/reverse flow, calibration in progress, or fault
- If active, output voltage is +15 VDC ±3% with a 2.2 kohm internal pull-up resistor
- If passive, output voltage is 30 VDC maximum, 24 VDC typical, sinking up to 500 mA at 30 VDC

One DI

- Can be configured for active or passive power
- Not intrinsically safe
- Active power +15 VDC, 7 mA maximum source current
- Passive power +3–30 VDC maximum
- Can start/stop totals and inventories, reset all totals, reset mass total, reset volume total, start sensor zero, or initiate multiple actions

For custody transfer using double-pulse Frequency Output, the transmitter can be configured for 2 Frequency Outputs. The second output can be phase-shifted –90, 0, 90, or 180 degrees from the first output, or the dual-pulse output can be set to quadrature mode.

Output codes E and G

These codes are for intrinsically safe FOUNDATION fieldbus and PROFIBUS-PA 2700 transmitters.

One FOUNDATION fieldbus H1 or PROFIBUS-PA output

- FOUNDATION fieldbus and PROFIBUS-PA wiring is intrinsically safe with an intrinsically safe power supply
- The transmitter fieldbus circuit is passive, and draws power from the fieldbus segment. Current draw from the fieldbus segment is 13 mA
- Manchester-encoded digital signal conforms to IEC 61158-2
- Entity parameters:
 - Ui = 30 VDC
 - Ii = 300 mA
 - Pi = 1,3 W
 - Ci = negligible
 - Li = negligible

Output code N

These codes are for non-incendive FOUNDATION fieldbus transmitters.

One Foundation fieldbus H1 output

- FOUNDATION fieldbus wiring is non-incendive
- The transmitter fieldbus circuit is passive, and draws power from the fieldbus segment. Current draw from the fieldbus segment is 13 mA
- Manchester-encoded digital signal conforms to IEC 61158-2
- Entity parameters:
 - Ui = 33 VDC
 - Ii = 380 mA
 - Pi = 5.32 W
 - Ci = negligible
 - Li = negligible

Output codes D and 4

These codes are for intrinsically safe 1700 and 2700 transmitters.


One intrinsically safe passive 4-20 mAO (2 with the 2700)

- Maximum input voltage: 30 VDC, 1 watt maximum
- Maximum load limit: see the following chart
- 1700 can report mass flow or volume flow; 2700 can report mass flow, volume flow, density, temperature, or drive gain
- Entity parameters:
 - Ui = 30 VDC
 - Ii = 300 mA
 - Pi = 1 W
 - $Ci = 0.0005 \mu F$
 - Li = Less than 0.05 mH
- Output is linear with process from 3.8 to 20.5 mA, per NAMUR NE 43 (February 2003)

mA Output Load Resistance Value

$$R_{\text{max}} = (V_{\text{supply}} - 12)/0.023 *$$

^{*} If communicating with HART, a minimum or 250 ohms and 17.75 V supply is needed.



- A. External resistor (ohms)
- B. Operating region
- C. Supply voltage (volts)

One intrinsically safe FO/pulse output, or configurable FO/pulse output/DO


- Maximum input voltage: 30 VDC, 0.75 watt maximum
- Maximum load limit: see the following chart
- Can report mass flow or volume flow, which can be used to indicate flow rate or total
- For 1700, Frequency Output reports the same flow variable as the mA Output
- For 2700, Frequency Output is independent of the mA Output
- Scalable to 10,000 Hz
- Entity parameters:
 - Ui = 30 VDC
 - Ii = 100 mA
 - Pi = 0.75 W
 - Ci = 0.0005 μ F
 - Li = Less than 0.05 mH
- Output is linear with flow rate to 12,500 Hz

Frequency Output Load Resistance Value

$$R_{\text{max}} = (V_{\text{supply}} - 4)/0.003$$

$$*R_{\min} = (V_{\text{supply}} - 25)/0.006$$

* Absolute minimum = 100 ohms for V_{supply} < 25.6 volts



- A. External resistor (ohms)
- B. Operating region
- C. Supply voltage (volts)

2000 transmitters with CIO functionality

The 2000 transmitter with configurable inputs and outputs is designed to increase transmitter flexibility and reduce the number of transmitter variations required in inventory. The following table shows the various configuration options that can be produced with the configurable I/O output option.

Channel assignments for 2000 transmitters with CIO (output option codes B, C, and 3)

- When output code B is selected, the transmitter ships with channels assigned to default values.
- When output codes C or 3 are selected, the transmitter is custom configured prior to shipment. Output code 3 is available only with 2700 transmitters.

Channel	Terminals		Configuration options	Default variable	Power
	2700	2500		assignment	
А	1 & 2	21 & 22	mA Output with Bell 202/ HART (only)	Mass flow	Active
В	3 & 4	23 & 24	mA Output (default)	Density	Active
			Frequency Output ⁽¹⁾	Mass flow	Active or passive ⁽²⁾
			Discrete Output	Fwd/rev flow	Active or passive
С	5 & 6	31 & 32	Discrete Output (default) ⁽¹⁾	Mass flow	Active or passive
			Frequency Output	Flow switch	Active or passive
			Discrete Input	None	Active or passive

⁽¹⁾ If channels B and C are both configured as a Frequency Output (dual pulse), both outputs are generated from the same signal. The outputs are electrically isolated but not independent.

Digital communications

Output type	Outputs and descriptions	
All	One service port can be used for temporary connection only	
	■ Uses RS-485 Modbus signal, 38.4 kilobaud, one stop bit, no parity	

⁽²⁾ The user must supply power when a channel is set to passive power.

Output type	Outputs and descriptions
HART/RS-485, Modbus/RS-485	 Models/output codes: — All models with output code A, except when ordered with display code 8
	 2500 with output codes B and C
	— 2700 with output code 2
	 One RS-485 output can be used for direct connection to a HART or Modbus host system; accepts data rates between 1200 baud and 38.4 kilobaud
	HART revision 7 as default, selectable to HART revision 5
HART/Bell 202	 Models/output codes: 1500 with output code A, 1700 and 2500 with output codes A, B, C, and D. 2700 with output codes A, B, C, D, 2, 3, and 4
	■ HART Bell 202 signal is superimposed on the primary milliamp output, and is available for host system interface. Frequency 1.2 and 2.2 kHz, Amplitude: to 1.0 mA, 1200 baud, Requires 250 to 600 ohms load resistance
	HART revision 7 as default, selectable to HART revision 5
FOUNDATION fieldbus	■ Models/output codes: — 2700 with output code E
	 2700 with output code N
	■ Transmitters are registered with the Fieldbus Foundation, and conform to the FOUNDATION fieldbus H1 protocol specification. Transmitters with output code E are FISCO certified. Transmitters with output code N are FNICO certified
	■ FISCO: — Field device in compliance with EN/IEC 60079-11:2012 Annex G
	— Ui = 30 V, Ii = 380 mA, Pi = 5.32 W, Ci = 0.0005 μF, Li = Less than 0.05 mH
	Non intrinsically safe FF output
PROFIBUS-PA	■ 2700 with output code G
	■ Transmitters are registered with the Profibus Organization, and fulfill the requirements of the PROFIBUS-PA Profile for Process Control Devices. Compatible for configuration with Siemens® Simatic® PDM
	■ FISCO:
	Field device in compliance with EN/IEC 60079-11:2012 Annex G
	— Ui = 30 V, Ii = 380 mA, Pi = 5.32 W, Ci = 0.0005 μ F, Li = Less than 0.05 mH

2700 transmitter with FOUNDATION fieldbus

Fieldbus software functionality

The 2700 Foundation fieldbus software is designed to permit remote testing and configuration of the transmitter using the $DeltaV^{\mathbb{M}}$ Fieldbus Configuration Tool, or other Foundation fieldbus compliant hosts. The Coriolis sensor signal is channeled through the flowmeter to the control room and the Foundation fieldbus configuration device.

Function block overview

Function block type	Quantity	Execution time (milliseconds)
Analog Input (AI)	4	18
Analog Output (AO)	2	18
Discrete Input (DI)	1	16
Discrete Output (DO)	1	16

Function block type	Quantity	Execution time (milliseconds)
Integration (INT)	1	18
Proportional, Integral, Derivative (PID)	1	20

Transducer blocks

Transducer blocks hold data from the Coriolis sensor, including process variables, configuration, calibration, and diagnostics.

The 2700 transmitter with FOUNDATION fieldbus provides up to seven transducer blocks:

- Measurement For process variables
- Calibration For calibration information
- Diagnostic For diagnosing problems and running diagnostic tests (including the Smart Meter Verification procedure, if the transmitter is paired with an enhanced core processor)
- Device Information For data such as sensor type
- Local Display For configuring the transmitter display
- API For petroleum measurement calculations using API MPMS Chapter 11.1
- Concentration measurement
- For complex density and concentration calculations (e.g.,%HFCS, SG60/60)

Resource block

The resource block contains physical device information, including available memory, manufacturer identification, type of device, and features.

Analog input function blocks

The Analog Input (AI) function block processes the measurement from the Coriolis sensor and makes it available to other function blocks. It also allows filtering, alarm handling, and engineering unit changes. Each of the 4 2700 AI blocks can be assigned to one of 19 available variables.

Analog output block

The AO function block assigns an output value to a field device through a specified channel. The block supports mode control, signal status calculation, and simulation. The AO block can report either pressure from an external pressure source or temperature from an external temperature source.

Discrete Input block

One permanent Discrete Input (DI) function block can be assigned to any of the discrete input variable channels in the transducer block. The DI block channels are: forward/reverse indication, zero in progress, fault condition indication, and meter verification failure.

Discrete Output block

One permanent Discrete Output (DO) function block can be assigned to any of the Discrete Output variable channels in the transducer block. The DO block channels are: start sensor zero, reset mass total, reset volume total, reset API reference (standard) volume total, reset all process totals, reset concentration measurement reference volume total, reset concentration measurement net wolume total, start/stop all totals, increment concentration measurement curve, reset gas standard volume total, and start meter verification in continuous measurement mode.

Proportional integral derivative block

The optional proportional integral derivative (PID) function block combines all the necessary logic to perform proportional/integral/derivative control. The block supports mode control, signal scaling and limiting, feed forward control, override tracking, alarm limit detection, and signal status propagation.

Integrator block

The integrator block provides functionality for the transmitter totalizers. Any process total can be selected and reset.

Diagnostics and service

2700 transmitters automatically perform continuous self diagnostics. Using the Diagnostic transducer block, the user can perform online testing of the transmitter and sensor. Diagnostics are event driven and do not require polling for access.

PlantWeb[™] Field Diagnostic is supported. The diagnostic information is based on NAMUR NE 107 standard.

Power supply

Model	Description
1700 and 2700	■ Self switching AC/DC input, automatically recognizes supply voltage
	Complies with low voltage directive 2014/35/EU per EN 61010-1 (IEC 61010-1) with amendment 2; Installation (Overvoltage) Category II, Pollution Degree 2
	AC power: 85 to 265 VAC, 50/60 Hz, 6 watts typical, 11 watts maximum
	■ DC power: — 18 to 100 VDC, 6 watts typical, 11 watts maximum
	— Minimum 22 VDC with 1,000 ft (305 m) of 18 AWG (0.823 mm²) power-supply cable
	 At startup, transmitter power source must provide a minimum of 1.5 amperes of short- term current at a minimum of 18 volts at the transmitter's power input terminals
	Fuse: IEC 127-1.25 non-serviceable fuse, slow blow
1500 and 2500	 Transmitter power supply meets Installation (Overvoltage) Category II, Pollution Degree 2 requirements
	■ DC power: — Minimum 19.2 to 28.8 VDC, 6.3 watts
	 At startup, transmitter power source must provide a minimum of 1.0 amperes of short- term current per transmitter
	 Length and conductor diameter of the power cable must be sized to provide 19.2 VDC minimum at the power terminals, at a load current of 330 mA
	Fuse: IEC 1.6A non-serviceable fuse, slow blow

Environmental limits

1500 and 2500

Туре	Value
Ambient temperature limits ⁽¹⁾	Operating: -40 °F (-40.0 °C) to 131 °F (55.0 °C)
	Storage: -40 °F (-40.0 °C) to 185 °F (85.0 °C)
Humidity limits	5 to 95% relative humidity, non-condensing at 140 °F (60.0 °C)

Туре	Value
Vibration limits	Meets IEC 60068.2.6, endurance sweep, 5 to 2000 Hz, 50 sweep cycles at 1.0 g
Housing rating	None

⁽¹⁾ If the temperature is above 131 °F (55.0 °C), and you are mounting multiple transmitters, the transmitters must be at least 0.33 in (8.4 mm) apart.

1700 and 2700

Туре	Value	
Ambient temperature limits ⁽¹⁾	Operating: -40 °F (-40.0 °C) to 140 °F (60.0 °C)	
	Storage: -40 °F (-40.0 °C) to 140 °F (60.0 °C)	
Humidity limits	5 to 95% relative humidity, non-condensing at 140 °F (60.0 °C)	
Vibration limits	Meets IEC 60068-2-6,endurance sweep, 5 to 2000 Hz up to 1.0 g	
Housing rating	NEMA 4X [IP66/67/69(K)] ⁽²⁾	

⁽¹⁾ Display responsiveness decreases, and display may become difficult to read below -4 °F (-20.0 °C). Above 131 °F (55.0 °C), some darkening of display might occur.

Environmental effects

EMI effects

- Complies with EMC directive 2014/30/EU per EN 61326 Industrial
- Complies with NAMUR NE-21 (May 2012). With the exception of voltage dip when powered by 24 VDC on 1700/2700 transmitters

Ambient temperature effect

On analog outputs: ±0.005% of span per °C change from temperature at which the outputs were trimmed

Hazardous area classifications

1700 and 2700

CSA, and CSA-US

- Ambient temperature is limited to -40 °F (-40.0 °C) to 140 °F (60.0 °C) for CSA compliance.
- Class I, Div. 1, Groups C and D. Class II, Div. 1, Groups E, F, and G explosion proof (when installed with approved conduit seals). Otherwise, Class I, Div. 2, Groups A, B, C, and D.
- Provides nonincendive sensor outputs for use in Class I, Div. 2, Groups A, B, C, and D; or intrinsically safe sensor outputs for use in Class I, Div. 1, Groups C and D or Class II, Div. 1, Groups E, F, and G.

IECEx

Certain models/options limit the ambient temperature range for IECEx compliance. Consult technical sales for model restrictions. Transmitters with output codes A, B, C, D, E, G, and N are rated for increased safety or flameproof with approved cable glands.

⁽²⁾ The protection is IP69K-based NEN-ISO 20653:2013 and IP69 when using standard IEC/EN 60529.

Output option	Code	Approval		
Analog outputs A	A	Flameproof Terminal	Ex db [ib] IIB+H2 T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	Standard display or Chinese- language display
		compartment	Ex db [ib] IIC T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	No display or IIC display
Configurable I/O	B or C	B or C Flameproof Terminal compartment	Ex db [ib] IIB+H2 T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	Standard display
			Ex db [ib] IIC T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	No display or IIC display
FOUNDATION fieldbus (non- intrinsically safe)	N	Flameproof Terminal	Ex db [ib] IIB+H2 T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	Standard display
		compartment	Ex db [ib] IIC T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	No display or IIC display
Intrinsically safe D	D	D Flameproof Terminal	Ex db [ia Ga] [ib] IIB+H2 T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	Standard display
		compartment	Ex db [ia Ga] [ib] IIC T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	No display or IIC display
FOUNDATION fieldbus (IS), or PROFIBUS-PA (1)	E or G	E or G Flameproof Terminal compartment	Ex db [ia Ga] [ib] IIB+H2 T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	Standard display
			Ex db [ia Ga] [ib] IIC T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	No display or IIC display
Intrinsically safe D	D	Increased Safety Terminal compartment	Ex db eb [ia Ga] [ib] IIB+H2 T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	Standard display
			Ex db eb [ia Ga] [ib] IIC T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	No display or IIC display
FOUNDATION fieldbus (IS), or PROFIBUS-PA	E or G	E or G Increased Safety Terminal compartment	Ex db eb [ia Ga] [ib] IIB+H2 T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	Standard display
			Ex db eb [ia Ga] [ib] IIC T5 Gb Ex tb IIIC T65 °C Db IP66/IP67	No display or IIC display
I.S. with <i>Wireless</i> HART	4	Increased safety ⁽²⁾ Terminal compartment	Ex db eb [ia Ga] [ib] IIB+H2 T4 Gb	Standard display
			Ex db eb [ia Ga] [ib] IIC T4 Gb	No display or IIC display
Non-I.S. with <i>Wireless</i> HART	т	non-Sparking Terminal	Ex nA db eb [ib Gb] IIB+H2 T4 Gc	Standard display
		compartment	Ex nA db eb [ib Gb] IIC T4 Gc	No display or IIC display
				1 17 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1

Output codes E and G are FISCO field devices in compliance with IEC 60079-11:2011.
 1700M, 1700P, 2700M, and 2700P (stainless steel housing) are limited to flameproof (Exd) rating.

ATEX

Certain models/options limit the ambient temperature range for IECEx compliance. Consult technical sales for model restrictions. Transmitters with output codes A, B, C, D, E, G, and N are rated for increased safety or flameproof with approved cable glands.

Output option	Code	Approval		
Analog outputs	A	C € 2460 (£x)	II 2G (Ex codes per below) II 2D Ex tb IIIC T65 °C Db IP66/IP67	
		Increased safety ⁽¹⁾ Terminal compartment	Ex db eb [ib] IIB+H2 T5 Gb	Standard display or Chinese- language display
			Ex db eb [ib] IIC T5 Gb	No display or IIC display
		Flameproof Terminal	Ex db [ib] IIB+H2 T5 Gb	Standard display or Chinese- language display
		compartment	Ex db [ib] IIC T5 Gb	No display or IIC display
Configurable I/O	B or C	C € 2460 ⟨£x⟩	II 2G (Ex codes per below) II 2D Ex tb IIIC T65 °C Db IP66/IP67	
		Increased safety ⁽²⁾	Ex db eb [ib] IIB+H2 T5 Gb	Standard display
		Terminal compartment	Ex db eb [ib] IIC T5 Gb	No display or IIC display
		Flameproof	Ex db [ib] IIB+H2 T5 Gb	Standard display
		Terminal compartment	Ex db [ib] IIC T5 Gb	No display or IIC display
FOUNDATION fieldbus (non- intrinsically safe)	N	C € 2460 ⟨£x⟩	II 2G (Ex codes per below) II (1)2G Ex tb IIIC T65 °C Db IP66/IP67	
		Increased safety ⁽²⁾ Terminal compartment	Ex db eb [ib] IIB+H2 T5 Gb	Standard display
			Ex db eb [ib] IIC T5 Gb	No display or IIC display
		Flameproof	Ex db [ib] IIB+H2 T5 Gb	Standard display
		Terminal compartment	Ex db [ib] IIC T5 Gb	No display or IIC display
Intrinsically safe	D	C € 2460 ⟨£x⟩	II (1)2G (Ex codes per below) II 2D Ex tb IIIC T65 °C Db IP66/IP67	
		Increased safety ⁽²⁾ Terminal compartment	Ex db eb [ia Ga] [ib] IIB+H2 T5 Gb	Standard display
			Ex db eb [ia Ga] [ib] IIC T5 Gb	No display or IIC display
		Flameproof Terminal compartment	Ex db [ia Ga] [ib] IIB+H2 T5 Gb	Standard display
			Ex db [ia Ga] [ib] IIC T5 Gb	No display or IIC display
FOUNDATION fieldbus (IS), or PROFIBUS-PA ⁽²⁾	E or G	C € 2460 ⟨£x⟩	II (1)2G (Ex codes per below) II 2D Ex tb IIIC T65 °C Db IP66/IP67	
		Increased safety ⁽²⁾	Ex db eb [ia Ga] [ib] IIB+H2 T5 Gb	Standard display
		compartment	Ex db eb [ia Ga] [ib] IIC T5 Gb	No display or IIC display
		Flameproof	Ex db [ia Ga] [ib] IIB+H2 T5 Gb	Standard display
		Terminal compartment	Ex db [ia Ga] [ib] IIC T5 Gb	No display or IIC display
I.S. with WirelessHART	4	C € 2460 ⟨E _X ⟩	II (1)2G (Ex codes per below)	

Output option	Code	Approval		
		Increased safety ⁽²⁾ Terminal compartment	Ex db eb [ia Ga] [ib] IIB+H2 T4 Gb	Standard display
			Ex db eb [ia Ga] [ib] IIC T4 Gb	No display or IIC display
Non-I.S. with WirelessHART	2 or 3 C € 2460 ⟨£x		II (2)3G (Ex codes per below)	
		non-Sparking Terminal compartment	Ex nA db eb [ib Gb] IIB+H2 T4 Gc	Standard display
			Ex nA db eb [ib Gb] IIC T4 Gc	No display or IIC display

^{(1) 1700}M, 1700P, 2700M, and 2700P transmitters with stainless steel housing are limited to flameproof (Exd) rating.

NEPSI

Output option	Code	Approval		
Analog outputs	А	Increased safety ⁽¹⁾	Ex de [ib] IIB+H2 T5 Gb	Standard display or Chinese- language display
			Ex de [ib] IIC T5 Gb	No display or IIC display
		Flameproof	Ex d [ib] IIB+H2 T5 Gb	Standard display or Chinese- language display
			Ex d [ib] IIC T5 Gb	No display or IIC display
Configurable I/O	B or C	Increased safety ⁽¹⁾	Ex de [ib] IIB+H2 T5 Gb	Standard display
			Ex de [ib] IIC T5 Gb	No display or IIC display
		Flameproof	Ex d [ib] IIB+H2 T5 Gb	Standard display
			Ex d [ib] IIC T5 Gb	No display or IIC display
Intrinsically safe	D	Increased safety ⁽¹⁾	Ex de [ia/ib] IIB+H2 T5 Gb	Standard display
			Ex de [ia/ib] IIC T5 Gb	No display or IIC display
		Flameproof	Ex d [ia/ib] IIB+H2 T5 Gb	Standard display
			Ex d [ia/ib] IIC T5 Gb	no display or IIC display
FOUNDATION	E or G	Increased safety ⁽¹⁾	Ex de [ia/ib] IIB+H2 T5 Gb	Standard display
fieldbus (IS), or PROFIBUS-PA ⁽¹⁾			Ex de [ia/ib] IIC T5 Gb	No display or IIC display
		Flameproof	Ex d [ia/ib] IIB+H2 T5 Gb	Standard display
			Ex d [ia/ib] IIC T5 Gb	No display or IIC display

⁽¹⁾ Output codes E and G are FISCO field devices in compliance with EN/IEC 60079-11:2012 Annex G.

1500 and 2500

CSA and CSA-US

- Transmitter (when installed in a suitable enclosure): Class I, Div. 2, Groups A, B, C, and D.
- Sensor, including wiring to sensor: Class I, Div. 1, Groups C and D or Class II, Div. 1, Groups E, F, and G.

ATEX

Ambient temperature	Limited to -40 °F (-40.0 °C) to 131 °F (55.0 °C) for ATEX compliance
---------------------	--

⁽²⁾ Output codes E and G are FISCO field devices in compliance with EN 60079-11:2012 Annex G.

Operating conditions: Environmental	C E (Ex)
	II (2) 3G [EEx ib] IIB/IIC

Marine approval classifications

Marine approval	Country
Det Norske Veritas- Germanischer Lloyd (1500 and 2500 only)	Norway-Germany
American Bureau of Shipping (all models)	USA

Physical specifications

1700 and 2700

Specification	Value			
Housing	Polyurethane-painted cast aluminum or CF3M stainless steel; NEMA 4X (IP66)			
Weight	Painted aluminum, 4-wire remote: — With display: 8 lb (4 kg)			
	— Without display: 7 lb (3 kg)			
	Painted aluminum, 9-wire remote:With display: 14 lb (6 kg)			
	— Without display: 13 lb (6	kg)		
	Stainless steel:— With display: 21 lb (10 kg)		
	— Without display: 20 lb (9	kg)		
	 Option with Smart Wireless 1 	THUM Adapter: Add 0.65 lb (0.295	kg) to transmitter weight	
		ited to a sensor, you may need to to the sensor product data sheet.	add the weight of the	
Terminal compartments	Output terminals are physical	ally separated from the power and	l service-port terminals.	
Cable gland entrances	■ 0.5 in–14 NPT or M20 × 1.5 fe	emale conduit ports for outputs ar	nd power supply	
	■ 0.75 in–14 NPT female conduit port for sensor/core processor cable			
	■ Painted aluminum transmitters with <i>Wireless</i> HART, and all stainless steel transmitters, have one additional 0.5 in–14 NPT conduit opening			
Mounting	■ Integral or remote mounting options (stainless steel versions are always remote-mounted.)			
	■ May be remotely connected to any 4-wire or 9-wire Micro Motion sensor			
	 Remote-mount transmitters: Painted aluminum versions include a 304L stainless steel mounting bracket; hardward installing the transmitter on the mounting bracket is included 			
	Stainless steel versions include a 316 stainless steel mounting bracket and hardware			
	— Transmitter can be rotated on the sensor or the mounting bracket, 360 degrees, in 90-degree increments.			
Maximum cable lengths	Cable type	Wire gauge	Maximum length	
between sensor and transmitter ⁽¹⁾	■ Micro Motion 9-wire	Not applicable	60 ft (18 m)	
	■ Micro Motion 4-wire	Not applicable	1,000 ft (305 m)	
	 User-supplied 4-wire power wires (VDC) 	22 AWG (0.326 mm²)	300 ft (91 m)	
		20 AWG (0.518 mm ²)	500 ft (152 m)	
		18 AWG (0.823 mm ²)	1,000 ft (305 m)	
	 User-supplied 4-wire signal wires (RS-485) 22 AWG (0.326 mm²) or larger 1,000 ft (305 m) 			

Specification	Value			
Standard interface/display	 Segmented 2-line display with LCD screen with optical controls and flowmeter-status LED is standard; suitable for hazardous area installation 			
	Available in both backlit and non-backlit versions			
	 Depending on purchase option, transmitter housing cover has non-glass or non-glare tempered glass lens 			
	■ To facilitate various mounting orientations, the display can be rotated on transmitter, 360 degrees, in 90-degree increments			
	■ LCD line 1 lists the process variable; LCD line 2 lists engineering unit of measure			
	Display supports English, French, German, and Spanish languages			
	Display controls feature optical switches that are operated through the glass with a red LED for visual feedback to confirm when a button is pressed			
Chinese-language interface/ display	 Six-line graphical display optimized for Chinese-language support. Has LCD screen with optical controls and flowmeter-status LED; suitable for hazardous area installation 			
Available only in China.	Available in both backlit and non-backlit versions			
	Transmitter housing cover has non-glare tempered-glass lens			
	■ To facilitate various mounting orientations, the display can be rotated on transmitter, 360 degrees, in 90-degree increments			
	Display shows the process variable name, value, and units of measure			
	■ Display supports English and Chinese languages			
	Display controls feature three optical switches that are operated through the lens with a red LED for visual feedback to confirm when a button is pressed.			
	 Pressing specific optical switch combinations can access the display menu, change the language display, lock/unlock display access, and return to the process variables view 			
Display functions Applies to all display options.	 Operational: View process variables; start, stop, and reset totalizers; view and acknowledge alarms. 			
	 Offline: Zero flowmeter, Smart Meter Verification, simulate outputs, change measurement units, configure outputs, and set RS-485 communications options. 			
	Status LED: Three-color LED status light on display panel indicates flowmeter condition at a glance.			

⁽¹⁾ Where 4-wire cable is required, use only Micro Motion 4-wire cable. Depending on the specific model number ordered, 10 ft (3.05 m) of cable (4-wire or 9-wire) may be included (see ordering information for details). For longer cable lengths, contact customer support.


1500 and 2500

Weight	0.52 lb (0.2 kg)	0.52 lb (0.2 kg)			
Mounting	■ Mounted on 1.4 in (36 mm) r	■ Mounted on 1.4 in (36 mm) rail			
	Rail must be grounded	Rail must be grounded			
	May be remotely connected	e remotely connected to any Micro Motion sensor			
	between the sensor and the sensor, the maximum length	Requires standard 4-wire twisted, shielded signal cable, up to 1,000 ft (305 m) in length, between the sensor and the transmitter - if the core processor is remotely mounted from the sensor, the maximum length of the 9-wire signal cable between the sensor and the remote core processor is 60 ft (18 m).			
Maximum cable lengths	Cable type	Wire gauge	Maximum length		
between sensor and transmitter ⁽¹⁾	■ Micro Motion 9-wire	Not applicable	60 ft (18 m)		
	■ Micro Motion 4-wire	Not applicable	1,000 ft (305 m)		
	■ User-supplied 4-wire power	22 AWG (0.326 mm²)	300 ft (91 m)		
	wires (VDC)	20 AWG (0.518 mm ²)	500 ft (152 m)		
		18 AWG (0.823 mm²)	1,000 ft (305 m)		
	User-supplied 4-wire signal wires (RS-485)	22 AWG (0.326 mm²) or larger	1,000 ft (305 m)		
Status LED		Three-color status LED on face of transmitter indicates flowmeter condition at a glance, using a solid green, yellow, or red light. Zero in progress is indicated by a flashing yellow light.			
Zero button	A zero button on the face of the	A zero button on the face of the transmitter can be used to start the transmitter zero procedure.			

⁽¹⁾ Where 4-wire cable is required, use only Micro Motion 4-wire cable.

1700 and 2700 4-wire remote-mount with display

This drawing is for a 1700 and 2700 4-wire remote-mount transmitter with a display that is made with painted aluminum housing.




- A. 3 x 1/2 in -14 NPT or M20 x 1.5
- B. Wall mount
- C. To center line of 2 in (51 mm) pipe (pipe mount)
- D. To conduit opening

Note

Dimensions are in inches (mm).

1700 and 2700 4-wire remote-mount transmitter without display

This drawing is for a 1700 and 2700 4-wire remote-mount transmitter without a display that is made with painted aluminum housing.




- A. To center line of 2 in (51 mm) pipe (pipe mount)
- B. Wall mount
- C. To conduit opening

Note

- Dimensions are in inches (mm).
- For integrally-mounted transmitter and sensor dimensions, see the sensor product data sheet.

1700 and 2700 9-wire remote-mount transmitter and CP assembly with display

This drawing is for a 1700 and 2700 9-wire remote-mount transmitter and core processor with a display that is made from painted aluminum housing.




- A. 2 x 1/2 in 14 NPT or M20 x 1.5
- B. To center line of 2 in (51 mm) pipe (pipe mount)

Note

- Dimensions are in inches (mm).
- For integrally-mounted transmitter and sensor dimensions, refer to the sensor product data sheet.

1700 and 2700 9-wire remote-mount transmitter and CP assembly without display

This drawing is for a 1700 and 2700 9-wire remote-mount transmitter and core processor without a display that is made from painted aluminum housing.




- A. To center line of 2 in (51 mm) pipe (pipe mount)
- B. Wall mount

Note

- Dimensions are in inches (mm).
- For integrally-mounted transmitter and sensor dimensions, refer to the sensor product data sheet.


1700 and 2700 4-wire and 9-wire remote mount transmitter – stainless steel housing

This drawing shows a 1700 and 2700 4-wire and 9-wire remote-mount transmitter with stainless steel housing.



Note Dimensions are in inches (mm).

Remote (standard) core processor




- A. 5.5 in (140 mm) pipe mount: To center line of 2 in (51 mm) pipe
- B. 4.57 in (116 mm) wall mount
- C. 1/2 in -14 NPT or M20 x 1.5

Note

Dimensions are in inches (mm).

Remote enhanced core processor



- A. To center line of 2 in (51 mm) pipe
- B. 5.5 in (140 mm) pipe mount
- C. 4.57 in (116 mm) wall mount
- D. 1/2 in 14 NPT or M20 x 1.5


Note


Dimensions are in inches (mm).


2700 with Smart Wireless THUM Adapter

Output options 2 and 3 (all approval codes) and output option 4 (approval codes E and Z only)

The 2700 transmitter with the WirelessHART option provides an additional conduit opening at the top of the transmitter to install the Smart Wireless THUM Adapter. The THUM Adapter comes integrally mounted to the transmitter for output options 2 and 3 (all approval codes) and output option 4 (approval codes E and Z).








- A. Remote-mount transmitter with integral-mount THUM Adapter
- B. Remote-mount transmitter/core processor assembly with integral-mount THUM Adapter

Note

Dimensions are in inches (mm).

2700 transmitter with Smart Wireless THUM Adapter Output option 4 (approval code A)

The 2700 transmitter with WirelessHART output option 4 (approval code A) requires using poured conduit seals or a stopping box between the transmitter and Smart Wireless THUM Adapter. The THUM Adapter is not pre-installed for approval code A.





- A. Smart Wireless THUM Adapter
- B. ½ in -14 NPT male
- C. Remote-mount transmitter with additional conduit opening for installation of the THUM Adapter
- D. Remote-mount transmitter/core processor assembly with additional conduit opening for installation of the THUM Adapter


Note


Dimensions are in inches (mm).

1500 and 2500











A. For mounting on a 1.39 in (35 mm) rail

Note

Dimensions are in inches (mm).

Ordering information

1500

Base model

Model	Product description
1500	Micro Motion Coriolis MVD 1500 single variable flow transmitter

Mounting

Code	Mounting options for 1500
D	4-wire remote 1.39 in (35 mm) DIN rail transmitter
Е	4-wire remote 1.39 in (35 mm) DIN rail transmitter with 9-wire remote enhanced core processor; includes 10 ft (3 m) each 9-wire shielded FEP and 4-wire shielded PVC cable Available with approval codes M, C, A, B or P only
В	4-wire remote 1.39 in (35 mm) DIN rail transmitter with 9-wire remote core processor; includes 10 ft (3 m) 9-wire shielded FEP cable

Power

Code	Power options for 1500
3	19.2 to 28.8 VDC

Conduit connection

Code	Conduit connection options for 1500 — with mounting code D
Α	None

Code	Conduit connection options for 1500 — with mounting code B or E
В	½ in NPT remote core processor – no gland
E	M20 remote core processor – no gland
F	Remote core processor – brass/nickel cable gland Not available with approval code S, T, or J
G	Remote core processor – stainless steel cable gland Not available with approval code S, T, or J
К	JIS B0202 1/2G – no gland Only available with approval code M, T, or S
L	Japan - brass nickel cable gland Only available with approval code M, T, or S
М	Japan - stainless cable gland Only available with approval code M, T, or S

Output

Code	Output options for 1500
	One mA, one frequency, RS-485 Not available with software option 1 code B
С	One mA, two DO, RS-485 Only available with software 1 code B

Terminal

Code	Terminal options for 1500
В	Screw terminals

Approval

Code	Approval options for 1500
М	Micro Motion Standard (no approval, with CE/EAC mark)
С	CSA (Canada only)
А	CSA (US and Canada)
В	ATEX - Safe area with IS sensor outputs
Р	NEPSI – Safe area Only available with language code M (Chinese)
Т	TIIS - IIC sensor (not available for quotes outside of Japan) Available for quote only.
S	TIIS - IIB sensor (not available for quotes outside of Japan) Available for quote only.
J	Hardware ready for TIIS approval (EPM Japan only) Approval Code J is only available with Conduit Connections Option E; Available for order only
G	Country Specific Approval - Requires a selection from the Approvals section of Add on options

Language

Code	Language options for 1500
Α	Danish CE requirements document; English installation and configuration manuals
D	Dutch CE requirements document; English installation and configuration manuals
Е	English installation manual; English configuration manual
F	French installation manual; English configuration manual
G	German installation manual; English configuration manual
Н	Finnish CE requirements document; English installation and configuration manuals
I	Italian installation manual; English configuration manual
J	Japanese installation manual; English configuration manual
М	Chinese installation manual; English configuration manual
N	Norwegian CE requirements document; English installation and configuration manuals
Р	Portuguese installation manual; English configuration manual
S	Spanish installation manual; English configuration manual

Code	Language options for 1500
W	Swedish CE requirements document; English installation and configuration manuals
C ⁽¹⁾	Czech CE requirements document; English installation and configuration manuals
B ⁽¹⁾	Hungarian CE requirements document; English installation and configuration manuals
K ⁽¹⁾	Slovak CE requirements document; English installation and configuration manuals
T ⁽¹⁾	Estonian CE requirements document; English installation and configuration manuals
U ⁽¹⁾	Greek CE requirements document; English installation and configuration manuals
L ⁽¹⁾	Latvian CE requirements document; English installation and configuration manuals
V ⁽¹⁾	Lithuanian CE requirements document; English installation and configuration manuals
Y ⁽¹⁾	Slovenian CE requirements document; English installation and configuration manuals

⁽¹⁾ Not available with approval code J, T, or S.

Software 1

Code	Software options 1 for 1500
Z	Flow variable (standard)
В	Filling & Dosing application Not available with Output code A
J	Production Volume Reconciliation Available with software option 2 codes Z and C only
К	Transient Mist Remediation Available with software option 2 codes Z and C only
L	Transient Bubble Remediation Available with software option 2 codes Z and C only
R	Piece-wise linearization for gas Available with software option 2 codes Z and C only
Х	ETO software option 1 Requires "X" Factory option code

Software 2

Code	Software options 2 for 1500
Z	No software options 2
С	Smart Meter Verification Not available with Mounting Option B; Smart Meter Verification is not available with all sensors.
X	ETO software option 2 Requires "X" Factory option code

Factory

Code	Factory options for 1500
Z	Standard product
X	ETO product

Add on options

Country specific approval (select one from the following if approval code G is selected):

Code	Add on options for 1500
R4	EAC Safe Area Only with IS Sensor Outputs - Hazardous Area Approval
B4	INMETRO Safe Area Only with IS Sensor Outputs - Hazardous Area Approval

1700

Base model

Model	Product description
1700	Micro Motion Coriolis MVD 1700 single variable flow transmitter

Mounting

Code	Mounting options for 1700
R	4-wire remote mount transmitter (polyurethane-painted aluminum housing) includes10 ft (3 m) 4-wire shielded PVC cable)
I	Integral mount transmitter (polyurethane-painted aluminum housing)
Е	4-wire remote mount transmitter with 9-wire remote enhanced core processor; includes 10 ft (3 m) each of 4-wire shielded PVC cable and 9-wire shielded FEP cable
	Not available with conduit connection code C or D; Not available with approval option codes S or T with conduit connections L or M
В	4-wire remote mount transmitter with 9-wire remote core processor; includes 10 ft (3 m) each of 4-wire shielded PVC cable and 9-wire shielded FEP cable
	Not available with conduit connection code C or D
С	9-wire remote transmitter with integral core processor (polyurethane-painted aluminum housing) includes 10 ft (3 m) CFEPS cable
М	4-wire remote mount transmitter with stainless steel housing; includes 10 ft (3 m) 4-wire shielded PVC cable;
	Not available with Approval codes U, Z, P, K, T, S, J or G with country-specific approval codes R1 or B1
Р	9-wire remote mount transmitter with stainless steel housing and integral core processor; includes 10 ft (3 m) CFEPS cable
	Not available with Approval codes U, Z, P, K, T, S, J or G with country-specific approval codes R1 or B1

Power

Code	Power options for 1700
1	18 to 100 VDC or 85 to 265 VAC; self switching

Display

Code	Display options for 1700
1	Dual line display for CSA and IIB + H2 ATEX, IECEx and NEPSI ratings Not available with mounting code M or P
2	Backlit dual line display for CSA and IIB + H2 ATEX, IECEx and NEPSI ratings
3	No display Not available with approval codes J, T, or S

Code	Display options for 1700
5	Backlit dual line display for IIC ATEX, IECEx, and NEPSI rating Only available with approval codes Z, F, P, K, I or G with country specific approval R1, B1, R2, B2
7	Non-glass backlit dual line display for General Purpose (no approvals) Only available with approval code M; Not available with either mounting code M or P
8	Display optimized for Chinese-language support; China only Available with Mounting Option codes R, I, C, or B; Output code A; Conduit Connections codes B, C, D, E, F or G; Approval codes M, Z, F, P, K, I or G with country specific approval codes R1, B1, R2, or B2; Language codes E or M; Software 2 Options Z or C; Factory Option Z

Output

Code	Output options for 1700
Α	Analog outputs: one mA; one frequency; RS-485
D	Intrinsically safe analog outputs: one mA, one frequency Not available with approval code T, S, or J

Conduit connection

Code	Conduit connection options for 1700
В	1/2 in NPT – no gland Not available with approval code T, S, or J
С	1/2 in NPT with brass nickel cable gland (not approved for Class 1 Division 1 installations) Not available with approval code T, S, or J; Not available with mounting codes B, E, M, or P
D	1/2 in NPT with stainless-steel cable gland (not approved for Class 1 Division 1 installations) Not available with approval code T, S, or J; Not available with mounting code B or E
E	M20 – no gland Not available with approval code T or S
F	M20 with brass nickel cable gland (not approved for Class 1 Division 1 installations) Not available with mounting code M or P
G	M20 with stainless steel cable gland (not approved for Class 1 Division 1 installations)
К	JIS B0202 1/2G – no gland; Only available with approval code M; Not available with mounting code M or P
L	Japan - brass nickel cable gland; Only available with approval code M, T, or S; Not available with mounting code M or P
М	Japan - stainless-steel cable gland; Only available with approval code M, T, or S; Not available with mounting code M or P

Approval

Code	Approval options for 1700
М	Micro Motion Standard (no approval, with CE/EAC mark)
С	CSA (Canada only)
Α	CSA (US and Canada)
Z	ATEX – Equipment Category 2 (Zone 1 – Increased safety terminal compartment)
F	ATEX – Equipment Category 2 (Zone 1 – Flameproof terminal compartment)

Code	Approval options for 1700
Р	NEPSI – Equipment Category 2 (Zone 1– Flameproof terminal compartment) Only available with language code M (Chinese)
К	NEPSI – Equipment Category 2 (Zone 1 – Increased safety terminal compartment) Only available with language code M (Chinese)
I	IECEx Equipment Category 2 (Zone 1 – Flameproof terminal compartment)
Т	TIIS - IIC sensor (not available for quotes outside of Japan) Available for quote only
S	TIIS - IIB sensor (not available for quotes outside of Japan) Available for quote only
J	Hardware ready for TIIS approval (EPM Japan only) Approval code J is only available with Conduit Connections Option E; Available for order only
G	Country Specific Approval - Requires a selection from the Approvals section of Add on options

Language

Code	Language options for 1700
А	Danish CE requirements document; English installation and configuration manuals
D	Dutch CE requirements document; English installation and configuration manuals
E	English installation manual; English configuration manual
F	French installation manual; English configuration manual
G	German installation manual; English configuration manual
Н	Finnish CE requirements document; English installation and configuration manuals
I	Italian installation manual; English configuration manual
J	Japanese installation manual; English configuration manual
М	Chinese installation manual; English configuration manual
N	Norwegian CE requirements document; English installation and configuration manuals
Р	Portuguese installation manual; English configuration manual
S	Spanish installation manual; English configuration manual
W	Swedish CE requirements document; English installation and configuration manuals
С	Czech CE requirements: English installation and configuration manuals
В	Hungarian CE requirements document; English installation and configuration manuals
К	Slovak CE requirements document; English installation and configuration manuals
Т	Estonian CE requirements document; English installation and configuration manuals
U	Greek CE requirements document; English installation and configuration manuals
L	Latvian CE requirements document; English installation and configuration manuals
V	Lithuanian CE requirements document; English installation and configuration manuals
Υ	Slovenian CE requirements document; English installation and configuration manuals

Software 1

Code	Software options 1 for 1700
Z	Flow variable (standard)

Code	Software options 1 for 1700
J	Production volume reconciliation Available with software option 2 Z and C only
К	Transient mist remediation Available with software option 2 Z and C only
L	Transient bubble remediation Available with software option 2 Z and C only
R	Piece-wise linearization for gas Available with software option 2 Z and C only

Software 2

Code	Software options 2 for 1700
Z	No software options 2
С	Smart Meter Verification Not available with Mounting Option B, C, or P; Smart Meter Verification is not available with all sensors.
S	Safety certification of 4–20 mA Output per IEC 61508 Only available with output code A or D
V	Safety Certification per IEC 61508 with Smart Meter Verification Not available with Mounting Option B, C, or P; Smart Meter Verification is not available with all sensors. Only available with output code A or D

Factory

Code	Factory options for 1700
Z	Standard product
Х	ETO product

Add on options

Code	Add on options for 1700
CL	Hardware for cover lockout Hardware only; does not include Weights & Measures software
PK	2 in (51 mm) pipe mount U-bolt kit for electronics Not available with Mounting Option I
	Country specific approval (select one from the following if approval code G is selected)
R1	EAC Zone 2 - Hazardous Area Approval - Increased safety terminal compartment (Exe)
R2	EAC Zone 1 - Hazardous Area Approval - Flameproof terminal compartment
B1	INMETRO Zone 1 - Hazardous Area Approval - Increased safety terminal compartment
B2	INMETRO Zone 1 - Hazardous Area Approval - Flameproof terminal compartment

2500

Base model

Model	Product description
2500	Micro Motion Coriolis MVD 2500 MultiVariable flow and density transmitter

Mounting

Code	Mounting options for 2500
D	4-wire remote 1.4 in (36 mm) DIN rail transmitter
Е	4-wire 1.4 in (36 mm) DIN rail transmitter with 9-wire remote enhanced core processor; includes 10 ft (3 m) each 9-wire shielded FEP and 4-wire shielded PVC cable Available with approval options M, C, A, B or P only
В	4-wire remote 1.4 in (36 mm) DIN rail transmitter with 9-wire remote core processor; includes 10 ft (3 m) 9-wire shielded FEP cable

Power

Code	Power options for 2500
3	19.2 to 28.8 VDC

Conduit connection

Code	Conduit connection options for 2500 — with mounting code D
Α	None

Code	Conduit connection options for 2500 — with mounting code B or E
В	½ in NPT remote core processor – no gland
E	M20 remote core processor – no gland
F	Remote core processor – brass/nickel cable gland Not available with approval code S, T, or J
G	Remote core processor – stainless steel cable gland Not available with approval code S, T, or J
К	JIS B0202 1/2G – no gland; Only available with approval code M, T, or S
L	Japan - brass nickel cable gland; Only available with approval code M, T, or S
М	Japan - stainless cable gland; Only available with approval code M, T, or S

Output

Code	Output options for 2500
В	One mA, two configurable I/O channels, RS-485 – default configuration of two mA, one FO
С	One mA, two configurable I/O channels, RS-485 – custom configuration

Terminal

Code	Terminal options for 2500
В	Screw terminals

Approval

Code	Approval options for 2500
М	Micro Motion Standard (no approval, with CE/EAC mark)
С	CSA (Canada only)
Α	CSA (US and Canada)
В	ATEX - Safe area with IS sensor outputs
Р	NEPSI – Safe area Available only with language code M (Chinese)
Т	TIIS - IIC sensor (not available for quotes outside of Japan) Available for quote only
S	TIIS - IIB sensor (not available for quotes outside of Japan) Available for quote only
J	Hardware ready for TIIS approval (EPM Japan only) Approval code J is only available with Conduit Connections Option E; Available for order only
G	Country Specific Approval - Requires a selection from the Approvals section of Add on options

Language

Code	Language options for 2500					
Α	Danish CE requirements document; English installation and configuration manuals					
D	Dutch CE requirements document; English installation and configuration manuals					
Е	English installation manual; English configuration manual					
F	French installation manual; English configuration manual					
G	German installation manual; English configuration manual					
Н	Finnish CE requirements document; English installation and configuration manuals					
I	Italian installation manual; English configuration manual					
J	Japanese installation manual; English configuration manual					
М	Chinese installation manual; English configuration manual					
N	Norwegian CE requirements document; English installation and configuration manuals					
Р	Portuguese installation manual; English configuration manual					
S	Spanish installation manual; English configuration manual					
W	Swedish CE requirements document; English installation and configuration manuals					
B ⁽¹⁾	Hungarian CE requirements document; English installation and configuration manuals					
K ⁽¹⁾	Slovak CE requirements document; English installation and configuration manuals					
T ⁽¹⁾	Estonian CE requirements document; English installation and configuration manuals					
U ⁽¹⁾	Greek CE requirements document; English installation and configuration manuals					
L ⁽¹⁾	Latvian CE requirements document; English installation and configuration manuals					
V ⁽¹⁾	Lithuanian CE requirements document; English installation and configuration manuals					

Code	Language options for 2500
Y ⁽¹⁾	Slovenian CE requirements document; English installation and configuration manuals

(1) Not available with Approval T.

Software 1

Code	Software options 1 for 2500
Z	Flow and density variables (standard)
G	Concentration measurement Not available with approval code S, T or J
А	Petroleum measurement
J	Production Volume Reconciliation Available with Software Option 2 Z and C only
К	Transient Mist Remediation Available with Software Option 2 Z and C only
L	Transient Bubble Remediation Available with Software Option 2 Z and C only
М	Fuel consumption Available with Software Option 2 Z and C only
Q	Transient Bubble Remediation and petroleum measurement Available with Software Option 2 Z and C only
R	Piece-wise linearization for gas Available with Software Option 2 Z and C only
Х	ETO software option 1 Requires factory code X

Software 2

Code	Software options 2 for 2500					
Z	No software options 2					
С	Smart Meter Verification Not available with Mounting Option B; Smart Meter Verification is not available with all sensors.					
w	Weights & Measures custody transfer (requires user-provided external sealing for approval)					
D	Weights & Measures custody transfer & Smart Meter Verification (requires user-provided external sealing) Not available with Mounting Option B; Smart Meter Verification is not available with all sensors.					
Х	ETO software option 2 Requires factory code X					

Factory

Code	Factory options for 2500
Z	Standard product
X	ETO product

Add on options

Country specific approval (select one from the following if approval code G is selected):

Code	Add on options for 2500				
R4	AC Safe Area Only with IS Sensor Outputs - Hazardous Area Approval				
B4	INMETRO Safe Area Only with IS Sensor Outputs - Hazardous Area Approval				

2700

Base model

Model	Product description
2700	Micro Motion Coriolis MVD 2700 MultiVariable flow and density transmitter

Mounting

Code	Mounting options for 2700						
R	4-wire remote mount transmitter (polyurethane-painted aluminum housing) includes 10 ft (3 m) 4-wire shielded PVC cable						
I	Integral mount transmitter (polyurethane-painted aluminum housing)						
E	4-wire remote mount transmitter with 9-wire remote enhanced core processor; includes 10 ft (3 m) each of 4-wire shielded PVC cable and 9-wire shielded FEP cable;						
	Mounting code B, E not available with conduit connection code C or D; Available with approval options M, C, A, F, Z, P or I only; Not available with approval option codes S or T or with Conduit Connections L or M.						
В	4-wire remote mount transmitter with 9-wire remote core processor (polyurethane-painted aluminum housing) includes 10 ft (3 m) each 9 wire shielded FEP and 4 wire shielded PVC cable						
	Mounting code B, E not available with conduit connection code C or D						
С	9-wire remote transmitter with integral core processor (polyurethane-painted aluminum housing) includes 10 ft (3 m) CFEPS cable						
	Mounting codes M and P are not available with approval codes U, Z, P, K, T, S, J, E or G with country-specific approval codes R1 and B1.						
М	4-wire remote mount transmitter with stainless steel housing; includes 10 ft (3 m) 4-wire shielded PVC cable;						
	Mounting codes M and P are not available with approval codes U, Z, P, K, T, S, J, E or G, with country-specific approval R1or B1; Mounting codes M and P are not available with Output codes 2 and 3 because the SS housing is not Zone 1 increased safety (Ex e) approved.						
Р	9-wire remote mount transmitter with stainless steel housing and integral core processor; includes 10 ft (3 m) CFEPS cable						
	Mounting codes M and P are not available with approval codes U, Z, P, K, T, S, J, E or G, with country-specific approval R1or B1; Mounting codes M and P are not available with Output codes 2 and 3 because the SS housing is not Zone 1 increased safety (Ex e) approved.						
Н	4-wire remote mount transmitter (polyurethane-painted aluminum housing) for connecting to CDM/FDM/FVM meters [power and communications] includes 10 ft (3 m) 4-wire shielded PVC cable Not available with approval codes J, T or S						
	Not available with approval codes J, 1 of 3						

Power

Code	Power options for 2700
1	18 to 100 VDC or 85 to 265 VAC; self switching

Display

Code	Display options for 2700					
1	Dual line display for CSA and IIB + H2 ATEX, IECEx and NEPSI ratings; Not available with mounting codes M, P; or H					
2	Backlit dual line display for CSA and IIB + H2 ATEX, IECEx and NEPSI ratings					
3	No display Not available with approval codes J, T, or S					
5	Backlit dual line display for IIC ATEX, IECEx, and NEPSI rating Only available with approval codes Z, F, P, K, I, E, L, or 3					
7	Backlit dual line display for process variables and totalizer reset, non-glass lens Only available with approval code M; not available with mounting codes M, H, or P					
8	Display optimized for Chinese-language support; China only Only available with mounting code R, I, C, or B, output code A, conduit connection code B, C, D, E, F or G, and approval code M, Z, F, P, K, I, or G code with country specific approval R1, R2, B1, B2					

Output

Code	Output options for 2700						
A	Analog outputs: one mA; one frequency; RS-485 Not available with mounting code H						
В	One mA; two configurable IO channels - default configuration of two mA, 1 FO Not available with mounting code H						
С	One mA; two configurable IO channels - custom configuration Not available with mounting code H						
D	Intrinsically safe analog outputs: two mA, one frequency; Not available with mounting code H; Output code D and E are not available with approval codes T, S, and J.						
Е	Foundation fieldbus intrinsically safe H1 with standard function blocks (4 x AI, 1 x AO, 1 x integrator, 1 x DI, 1 x DO) Output code D and E are not available with approval codes T, S, and J; Output code E is not available with approval code U, 2, L, 3 or G with country specific approval codes R3 or B3.						
G	PROFIBUS-PA; not available with approval codes U, 2, L and 3 Output code G not available with approval codes U, 2, L, 3 or G with country-specific approval option R3, B3; not available with mounting code H.						
N	FOUNDATION fieldbus H1 with standard function blocks ($4 \times AI$, $1 \times AO$, $1 \times Integrator$, $1 \times DI$, $1 \times DO$); Output code N is not available with approval codes U, C, A, E, 2, L, 3 or G with country-specific approval R3, B3						
2	One mA; one frequency; RS485; Wireless HART ready; order 775 with ½ in NPT mounting option Not available with mounting code H; output codes 2 and 3 are only available with approval codes M, 2, L, 3, G with country-specific approval R3, B3.						
3	One mA; two configurable IO channels - custom configuration; Wireless HART ready; order 775 with 0.5 in NPT mounting option Not available with approvals J, T or S; not available with mounting code H; output codes 2 and 3 are only available with approval codes M, 2, L, 3, G with country-specific approval R3, B3.						
4	Intrinsically safe outputs; two mA; one frequency; Wireless HART ready; order 775 with ½ in NPT mounting option Not available with mounting code H; output code 4 is only available with approval codes E, Z, A, or G with country-specific approval R1, B1 when using stopping box.						

Conduit connection

Code	Conduit connection options for 2700								
Available with mounting codes:		R	I	В	E	С	М	Р	Н
В	1/2 in NPT – no gland; Not available with approval code T, S, or J	•	•	•	•	•	•	•	•
Only avail	able with mounting code R, I, B, E, C, M, or P.								
С	1/2 in NPT with brass nickel cable gland (not approved in Class 1 Division 1 installations) Not available with approval code T, S, or J; mounting code B, E not available with Conduit Connection C or D; not available with mounting code M, or P	•	•			•			
D	1/2 in NPT with stainless steel cable gland (not approved in Class 1 Division 1 installations) Not available with approval codes J, T, or S; mounting codes B or E not available with Conduit Connection codes C or D	•	•			•	•	•	
Е	M20 – no gland Not available with approvals T or S	•	•	•	•	•	•	•	
F	M20 with brass nickel cable gland (not approved in Class 1 Division 1 installations) Not available with mounting code M or P	•	•	•	•	•			
G	M20 with stainless steel cable gland (not approved in Class 1 Division 1 installations)	•	•	•	•	•	•	•	
К	JIS B0202 1/2G – no gland Only available with approval code M; not available with mounting code M or P	•	•	•	•	•			
L	Japan - brass nickel cable gland Only available with approval codes M, T, or S; not available with mounting code M or P	•	•	•	•	•			
М	Japan - stainless cable gland Only available with approval codes M, T, or S; not available with mounting code M or P	•	•	•	•	•			

Approval

Code	Approval options for 2700
М	Micro Motion Standard (no approval, with CE/EAC mark)
С	CSA (Canada only)
Α	CSA C-US (US and Canada)
Z	ATEX - Equipment Category 2 (Zone 1 - Increased safety terminal compartment)
F	ATEX - Equipment Category 2 (Zone 1 - Flameproof terminal compartment)
Р	NEPSI – Equipment Category 2 (Zone 1– Flameproof terminal compartment) Available with Chinese (M) language option only
К	NEPSI – Equipment Category 2 (Zone 1 – Increased safety terminal compartment) Available with Chinese (M) language option only
I	IECEx Equipment Category 2 (Zone 1 – Flameproof terminal compartment)
Т	TIIS - IIC sensor (not available for quotes outside of Japan) Available for quote only

Code	Approval options for 2700
S	TIIS - IIB sensor (not available for quotes outside of Japan) Available for quote only
J	Hardware ready for TIIS approval (EPM Japan only) Approval code J is only available with Conduit Connections Option E; Available for order only
E	IECEx (Zone 1 - Increased safety terminal compartment) Only available with output code 4
2	CSA Class 1 Div. 2 (US and Canada) Sensor connections will be intrinsically Safe without additional barrier
L	ATEX - Equipment Category 3 (Zone 2) Sensor connections will be intrinsically Safe without additional barrier; Approval code L is only available with output options 2 and 3.
3	IECEx (Zone 2) Sensor connections will be intrinsically Safe without additional barrier
G	Country Specific Approval - Requires a selection from the Approvals section of Add on options

Language

Code	Language options for 2700
А	Danish CE requirements document; English installation and configuration manuals
D	Dutch CE requirements document; English installation and configuration manuals
E	English installation manual; English configuration manual
F	French installation manual; English configuration manual
G	German installation manual; English configuration manual
Н	Finnish CE requirements document; English installation and configuration manuals
I	Italian installation manual; English configuration manual
J	Japanese installation manual; English configuration manual
М	Chinese installation manual; English configuration manual
N	Norwegian CE requirements document; English installation and configuration manuals
Р	Portuguese installation manual; English configuration manual
S	Spanish installation manual; English configuration manual
W	Swedish CE requirements document; English installation and configuration manuals
С	Czech CE requirements document; English installation and configuration manuals
В	Hungarian CE requirements document; English installation and configuration manuals
К	Slovak CE requirements document; English installation and configuration manuals
Т	Estonian CE requirements document; English installation and configuration manuals
U	Greek CE requirements document; English installation and configuration manuals
L	Latvian CE requirements document; English installation and configuration manuals
V	Lithuanian CE requirements document; English installation and configuration manuals
Υ	Slovenian CE requirements document; English installation and configuration manuals

Software 1

Code	Software options 1 Available only with mounting codes R, I, B, E, C, M, and P
Z	Flow and density variables (standard)
G	Concentration measurement
Α	Petroleum measurement
J	Production Volume Reconciliation Approval code J is only available with conduit connections option E.
К	Transient Mist Remediation Approval code J is only available with conduit connections option E.
L	Transient Bubble Remediation Approval code J is only available with conduit connections option E.
М	Fuel consumption Approval code J is only available with conduit connections option E.
Q	Transient Bubble Remediation and petroleum measurement Approval code J is only available with conduit connections option E.
R	Piece-wise linearization for gas Approval code J is only available with conduit connections option E.
X	ETO software option 1 Requires factory code X

Code	Software options 1 Available only with mounting code H (1)
В	CDM density meter connection - IIC ATEX & IECEx rating Not available with display code 2
С	FDM density meter connection - IIC ATEX & IECEx rating Not available with display code 2
D	FVM viscosity meter connection - IIC ATEX & IECEx rating Not available with display code 2
Е	CDM density meter connection - CSA C1D1 & C1D2 and Zone 2 or 3 ATEX, IECEx ratings Not available with display code 5
F	FDM density meter connection - CSA C1D1 & C1D2 and Zone 2 or 3 ATEX, IECEx ratings Not available with display code 5
Н	FVM viscosity meter connection - CSA C1D1 & C1D2 and Zone 2 or 3 ATEX, IECEx ratings Not available with display code 5

⁽¹⁾ All concentration measurement or petroleum measurement options are automatically programmed by the CDM / FDM.

Software 2

Code	Software options 2 for 2700 Available with all mounting codes
Z	No software options 2
W	Weights & Measures custody transfer Only available with output codes A, B, C, 2 or 3; Not available with Software Options 1 codes C or D
Х	ETO software option 2; requires factory code X

Code	Software options 2 for 2700
	Available only with mounting codes R, I, B, E, C, or M and P
С	Smart Meter Verification Not available with Mounting Option I, B, C, or P; Smart Meter Verification is not available with all sensors.
D	Weights & Measures custody transfer and Smart Meter Verification Not available with Mounting Option I, B, C, or P; Smart Meter Verification is not available with all sensors.
А	Regulatory Control Suite: Standard function blocks plus 1 PID block Available with output codes E and N only
F	Regulatory Control Suite: Standard function blocks plus 1 PID block and Smart Meter Verification Available with output codes E and N only; Available with sensor electronic interface codes 2 through 5 only; Not available with mounting option I, B, E, C, or P
S	Safety Certification of 4-20 mA output per IEC 61508 Available with Output codes A, B, C, and D only
V	Safety Certification per IEC 61508 with Smart Meter Verification Available with output codes E and N only; Available with sensor electronic interface codes 2 through 5 only; Not available with mounting option I, B, E, C, or P; Not available with approval options S or T with conduit connections L or M

Factory

Code	Factory options for 2700
Z	Standard product
Х	ETO product

Add on options

Code	Add on options for 2700 Available only for output code 2, 3, or 4
NI	Smart Wireless 775 THUM Ready – 775 ordered separately and installation and wiring completed in the field. Not available with approvals J, T, or S

	Add on options for 2700 For mounting code R, B, E, H, M, P, or C
PK	2 in (51 mm) pipe mount U-bolt kit for electronics

Code	Add on options for 2700 Country-specific approval (select one from the following if approval code G is selected)
R1	EAC Zone 2 - Hazardous Area Approval - Increased safety terminal compartment (Exe)
R2	EAC Zone 1 - Hazardous Area Approval - Flameproof terminal compartment
R3	EAC Zone 2 - Hazardous Area Approval - Energy limited device (ExnA) Sensor connections will be intrinsically safe without additional barrier
B1	INMETRO Zone 1 - Hazardous Area Approval - Increased safety terminal compartment N/C
B2	INMETRO Zone 1 - Hazardous Area Approval - Flameproof terminal compartment
B3	INMETRO Zone 2 - Hazardous Area Approval Sensor connections will be intrinsically safe without additional barrier

For more information: **Emerson.com/global**

 $^{\hbox{\scriptsize @}}$ 2024 Micro Motion, Inc. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Micro Motion, ELITE, ProLink, MVD and MVD Direct Connect marks are marks of one of the Emerson Automation Solutions family of companies. All other marks are property of their respective owners.



