



# Certificate / Certificat Zertifikat / 合格証

ROS 1312032 C001

exida hereby confirms that the:

**5900 Radar Level Gauge and 2410 Tank Hub**  
(Rosemount Tank Gauging System)

**SIL 3 2-in-1 (1oo2) Option**

**Rosemount Tank Radar**

(an Emerson company)

**Sweden**

Have been assessed per the relevant requirements of:

**IEC 61508 : 2010 Parts 1-7**

and meets requirements providing a level of integrity to:

**Systematic Capability: SC 3 (SIL 3 Capable)**

**Random Capability: Type B Element**

**SIL 3 @ HFT=0; Route 1<sub>H</sub>**

**PFH / PFD<sub>AVG</sub> and Architecture Constraints  
must be verified for each application**

### Safety Function:

The level transmitter will de-energize a safety critical output when exceeding any of the configured alarm limits within the stated accuracy and within the specified demand response time.

### Application Restrictions:

The unit must be properly designed into a Safety Instrumented Function per the Safety Manual requirements.

The manufacturer may use the mark:



Revision 1.2 August 31, 2017

Surveillance Audit Due  
September 1, 2020



ANSI Accredited Program  
ISO/IEC 17065  
PRODUCT CERTIFICATION BODY  
#1004



*John C. Yozallinas*  
Evaluating Assessor

*[Signature]*  
Certifying Assessor

ROS 1312032 C001

**Systematic Capability: SC 3 (SIL 3 Capable)**

**Random Capability: Type B Element**

**SIL 3 @ HFT=0; Route 1<sub>H</sub>**

**PFH / PFD<sub>AVG</sub> and Architecture Constraints  
must be verified for each application**

5900 Radar Level  
Gauge and 2410 Tank  
Hub

SIL 3 2-in-1 (1oo2)  
Option

**Systematic Capability:**

The products have met manufacturer design process requirements of Safety Integrity Level (SIL) 3. These are intended to achieve sufficient integrity against systematic errors of design by the manufacturer.

A Safety Instrumented Function (SIF) designed with this product must not be used at a SIL level higher than stated.

**Random Capability:**

The SIL limit imposed by the Architectural Constraints must be met for each element.

**IEC 61508 Failure Rates in FIT\***

	$\lambda_S$	$\lambda_{DD}$	$\lambda_{DU}$	SFF %
SIL 3, 2-in-1	629	1175	16	99.0

\* FIT = 1 failure / 10<sup>9</sup> hours

**SIL Verification:**

The Safety Integrity Level (SIL) of an entire Safety Instrumented Function (SIF) must be verified via a calculation of PFH and PFD<sub>AVG</sub> considering redundant architectures, proof test interval, proof test effectiveness, any automatic diagnostics, average repair time and the specific failure rates of all products included in the SIF. Each subsystem must be checked to assure compliance with minimum hardware fault tolerance (HFT) requirements.

The following documents are a mandatory part of certification:

**Assessment Report:** ROS 1312032 R001 V3R1

**Safety Manual:** #00809-0200-5100 Rev GB



80 N Main St  
Sellersville, PA 18960