

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

D



D

### Sensor Terminals:


Sensor Models:

DH025	DL025	DS150
DH038	DL050	DS300
DH100	DL065	
DH150	DL100	
DH300	DL200	

- |   |        |
|---|--------|
| 1 | BROWN  |
| 2 | RED    |
| 3 | ORANGE |
| 4 | YELLOW |
| 5 | GREEN  |
| 6 | BLUE   |
| 7 | VIOLET |
| 8 | GRAY   |
| 9 | WHITE  |



NOTE: PREPARE CABLE PER THE INSTRUCTIONS PROVIDED WITH THE CABLE.



### 3500 IS CONNECTOR

	c	a	
	2	2	
YELLOW	4	4	BLACK (DRAINS)
VIOLET	6	6	ORANGE
GREEN	8	8	WHITE
BLUE	10	10	GRAY
BROWN	12	12	RED
	14	14	
	16	16	
	18	18	
	20	20	
	22	22	
	24	24	
	26	26	
	28	28	
	30	30	
	32	32	

C

C

B

B

A

A

8

7

6



5

4

3

2

1

		 <b>MICRO MOTION, INC.</b> BOULDER, COLORADO	
 THIRD ANGLE PROJECTION		WIRING, 3500 TO DH/DL/DS	
NAME	DATE	SIZE	DWG. NO.
DRAWN DLS	11/13/97	D	EW-3300524
CHKD. RBG	12/30/97		C
APVD. RBG	12/30/97	SCALE NONE	DO NOT SCALE DRAWING SHEET 1 OF 1

COPYRIGHT 2005 MICRO MOTION, INC. ALL RIGHTS RESERVED