

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

D

D

Sensor Terminals

Sensor Types:

- CMF 010
- CMF 025
- CMF 050
- CMF 100
- CMF 200
- CMF 300
- CMF 400

C

C


Transmitter:

1500D
2500D

B


B

1 2 3 4





VDC+
VDC-
COMA
COMB

CUSTOMER SUPPLIED CABLE
 MAXIMUM LENGTH:
 1000 ft (300m) OF 18 AWG(0.8 mm²)
 300 ft (100m) OF 22 AWG(0.35 mm²)



A

A

		 MICRO MOTION, INC. BOULDER, COLORADO	
 THIRD ANGLE PROJECTION		WIRING ENHANCED CORE TO 1500/2500D	
DRAWN	NAME	DATE	SIZE
WJB		4/27/06	D
CHKD.	SAD	5/19/06	DWG. NO.
APVD.	ER	5/19/06	20006808
SCALE		DO NOT SCALE DRAWING	
NONE		SHEET 1 OF 1	

8

7

6

5

4

3

2

1