

RIDGID

WD1270 12 Gallon High Performance Wet/Dry Vac



This RIDGID® 12 Gallon High Performance Wet/Dry Vac is designed for Pros and DIY'ers who want a traditionally styled, medium sized vac that delivers the powerful performance and rugged durability required for job site clean-up. Its 5.0 peak horsepower motor delivers the suction power necessary to handle tough clean-up chores. This vacuum's 12 gallon drum size results in a more compact design that requires less storage space on a service truck, in the shop, or in the garage. However, it still offers the capacity to handle large messes.

FEATURES	BENEFITS
• 5.0 Peak HP Motor	Delivers the powerful suction needed for efficient clean up of large messes.
• Sound Reduction Technology	Scroll Noise Reduction® is a patented feature that provides quiet operation by precisely controlling the flow of air through the vac.
• 12 Gallon Drum	Provides capacity for clean-up of large spills & messes at job-sites and busy shops.
• 4 Swivel Casters	Provide easy 360° mobility.
• On-Board Accessory Storage	Five unique built-in accessory storage pockets – 1 on each caster foot, plus hose storage on top. No more searching or fumbling to find accessories.
• Lower Center of Gravity	Design lowers the center of gravity to help prevent tipping. Compact design stores more easily.
• 1-Layer Standard Filter	Pleated paper filter captures common everyday dirt.
• Blowing Capability	Insert hose in exhaust port and use air-stream to blow saw dust from tools and debris from garages, decks & sidewalks.
• Dual-Flex® Locking Hose	Resists collapsing and adds 180° flexibility at both hose ends. Hose locks onto vac.
• Large Built-In Drain	Drain located to lowest point of drum for complete emptying of water.
• Included Accessories	2-1/2" x 7' Dual-Flex® Locking Hose, 2 Extension Wands, Utility Nozzle, Car Nozzle, Wet Nozzle, & 1-Layer Paper Pleated Filter



SPECIFICATIONS

Drum Size	12 gal.
Motor	
- Peak Horsepower	5.0
- Air Watts	227
- Voltage	120
- Amps	10.0
Cord Length	15'
Construction	High Impact Polypropylene
U.L. Listed	Yes
Filter Surface Area	1,600 sq. in.
Replacement Filters	VF4000 VF5000 VF6000
Optional Wet Filter	VF7000
Optional Filter Bag	VF3502
Accessory Size	2-1/2"
Shipping Weight	22.5 lbs.
Net Weight	16.5 lbs.



Dual-Flex® Locking Hose



Large Drain for Emptying Water



Vac with Accessories & Filter



Dry Pick-up - Workshop, Garage etc.