

AGA Report Applications Software

The AGA Report Applications Software adds AGA report generation capability to ROCLINK™ 800 Configuration Software for the FloBoss™ 500-Series Flow Managers. The AGA Report software creates fixed-format reports of the operational characteristics of measured meter runs. It also makes the reports available for display and saves them as disk files that can be viewed or printed at a later date.

The report software is used in conjunction with the AGA Flow Applications Software contained in the FloBoss 500-Series units (see Specification Sheet 3.1:FW2).

The AGA Report software consists of a utility that is part of ROCLINK 800 Configuration Software.

Specifications

GENERAL PARAMETERS

Report period, selected AGA number, meter run ID, tag ID, station name, customer name, operator, contract hour, report date, report file, time downloaded, firmware revision.

SYSTEM PARAMETERS

ROC address, ROC group, active AGAs, maximum AGAs, contract hour, MPU loading.

FLOW PARAMETERS

Latitude, elevation, calculation method, AGA configuration, specific gravity, heating value, gravitational acceleration, scan period, alarm code, low alarm, high alarm, viscosity, specific heat ratio, base pressure, base temperature, AGA8 characterization method, gravitational correction factor, atmospheric pressure, heating value.

AGA3 only: Pipe diameter, orifice diameter, measured temperature, orifice material, low flow cutoff, pipe reference temperature, pipe material.

GAS COMPOSITION

Nitrogen, carbon dioxide, hydrogen sulfide, water, helium, methane, ethane, propane, n-butane, i-butane, n-pentane, i-pentane, n-hexane, n-heptane, n-octane, n-nonane, n-decane, oxygen, carbon monoxide, hydrogen.

INPUT POINT ASSIGNMENT PARAMETERS

Meter input, static pressure input, temperature input, entered meter value, entered pressure value, entered temperature value.

AGA3: Stacked differential pressure enable, low differential pressure input, low differential pressure setpoint, high differential pressure setpoint.

CALCULATED FACTORS

AGA3: Instantaneous flow, instantaneous energy, flow today, energy today, flow yesterday, energy yesterday, pressure extension, orifice flow constant, Y, Fn, Ftf, Fpv, Fgr, Cd, Fpb, Ftb.

AGA7: Instantaneous flow, instantaneous energy, flow today, uncorrected flow, energy today, flow yesterday, energy yesterday, Fpm, Fpb, Ftm, Ftb, S, correction factor (BMV).

STATIC PRESSURE INPUT POINT DEFINITION

Parameters appropriate to the assigned static pressure input: analog input, DVS input, HART input, or manual input. Only the analog input parameters are listed here: point number, point tag ID, units, scan period, filter, adjusted A/D 0%, adjusted A/D 100%, low reading EU, high reading EU, low alarm EU, high alarm EU, low low alarm EU, high high alarm EU, rate alarm EU, alarm deadband, filtered EUs, mode, alarm code, raw A/D input, actual scan time.

Specifications (Cont'd)

METER INPUT POINT DEFINITION

AGA3 Analog Input Parameters: Point number, point tag ID, units, scan period, filter, adjusted A/D 0%, adjusted A/D 100%, low reading EU, high reading EU, low alarm EU, high alarm EU, low low alarm EU, high high alarm EU, rate alarm EU, alarm deadband, filtered EUs, mode, alarm code, raw A/D input, actual scan time.

AGA7 Pulse Input Parameters: Point number, point tag ID, units, rate flag, rate period, scan period, conversion, low alarm EU, high alarm EU, low low alarm EU, high high alarm EU, rate alarm EU, alarm deadband, value in EUs, mode, alarm code, accumulated value, current rate, today's total, yesterday's total.

TEMPERATURE INPUT POINT DEFINITION

Point number, point tag ID, units, scan period, filter, adjusted A/D 0%, adjusted A/D 100%, low reading EU, high reading EU, low alarm EU, high alarm EU, low low alarm EU, high high alarm EU, rate alarm EU, alarm deadband, filtered EUs, mode, alarm code, raw A/D input, actual scan time.

HOURLY/DAILY VOLUME REPORT

AGA3 (Orifice): Date, time, flow minutes, volume, energy, flow averages (hw, Pf, Tf, orifice flow constant, pressure extension).

AGA7 (Turbine): Date, time, flow minutes, uncorrected flow volume, volume, raw pulses, energy, flow averages (Pf, Tf), correction factor.

ALARM REPORT

Date, time, tag, set/clear, value, description.

EVENT REPORT

Date, time, type, ID, old value, new value, description.

Bristol, Inc., Bristol Babcock Ltd, Bristol Canada, BBI SA de CV and the Flow Computer Division, are wholly owned subsidiaries of Emerson Electric Co. doing business as Remote Automation Solutions ("RAS"), a division of Emerson Process Management. FloBoss, ROCLINK, Bristol, Bristol Babcock, ControlWave, TeleFlow and Helicoid are trademarks of RAS. AMS, PlantWeb and the PlantWeb logo are marks of Emerson Electric Co. The Emerson logo is a trademark and service mark of the Emerson Electric Co. All other marks are property of their respective owners.

The contents of this publication are presented for informational purposes only. While every effort has been made to ensure informational accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. RAS reserves the right to modify or improve the designs or specifications of such products at any time without notice. All sales are governed by RAS' terms and conditions which are available upon request. RAS does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any RAS product remains solely with the purchaser and end-user.

Emerson Process Management**Remote Automation Solutions**

Marshalltown, IA 50158 U.S.A.

Houston, TX 77041 U.S.A

Pickering, North Yorkshire UK Y018 7JA

