

Lime Kiln Throughput Improves with Smart Wireless Solution

RESULTS

- 5% throughput improvement in lime kiln
- Minute-by-minute mid-zone temperature trending
- Self-powered transmitters were sending temperature updates within 24 hours of delivery
- Communication of devices on opposite sides of a rotating kiln to one Gateway



APPLICATION

Lime Kiln Mid-Zone Temperature

APPLICATION CHARACTERISTIC

Rotating kiln, high temperature, radiant heat, dusty ambient environment

CUSTOMER

Pulp and Paper Mill in North America


CHALLENGE

A Pulp and Paper Mill in North America struggled to properly control calcining in the lime kiln. In fact, the kiln was operating so poorly that it had become a choke point. The mill bought a new burner system and adjusted the flame profile to improve heat transfer at the mid-zone, where calcining of the lime mud takes place. The burner system is fired at the hot end (2000 °F [1093 °C]) of this long, cylindrical, rotating kiln and a draft is induced at the feed end (400 - 500 °F [204 - 260°C]). The flame is adjusted through the draft to provide the optimum shape and achieve the right mid-zone temperature. For this mill, however, the mid-zone temperatures could not be measured reliably and were inferred through the firing and feed end temperatures.

Unfortunately, the new burner system did not solve the problem. The mill suspected a new chain system was needed on the inside of the kiln to break up the lime mud and promote heat transfer. The Pulp Mill Leader did not want to invest the money, however, until the mid-zone temperatures for the center of the kiln (the air temperature) and the inside wall (where lime mud tumbled around chains) could be measured and actual heat transfer could be confirmed. The temperature measurement that had accompanied the purchase of the kiln, which relied on a brush system, had never worked and had not been maintained. A wired solution could not handle the rotating equipment, so the customer approached their instrument partner - Emerson Process Management - for a solution.

“... four days after the order was placed, we could see minute-by-minute mid-zone temperatures trending on the control system.”

Pulp Mill E&I Leader



Lime Kiln Application

ROSEMOUNT

For more information:
www.rosemount.com


EMERSON
 Process Management

SOLUTION

Emerson Process Management's new Smart Wireless solution was proposed, and the customer asked for shipment as soon as possible. Two Rosemount 648 Wireless Temperature Transmitters with thermocouples and a 1420 Gateway arrived at the plant three days later. The sensors were installed on opposite sides of the kiln's mid-zone, 180° apart, without thermowells to provide the fastest possible response time. One was positioned toward the center of the kiln to pick up the air temperature, and the other was positioned at the outer extremity to pick up radiant heat from the brick, indicating lime mud temperature. The self-powered transmitters were mounted on a pipe that extends away from the kiln and were sending temperature updates to the control room through the 1420 Gateway within 24 hours of delivery. "We had a Modbus® address available, so it was easy to add the Gateway as a slave to the control system," said E&I Leader for the Pulp Mill and Lime Kiln. "In fact, four days after the order was placed, we could see minute-by-minute mid-zone temperatures trending on the control system."

Immediately the mill recognized the inferred temperatures were off by 350 °F (177 °C), and confirmed that a new chain system was required to break up the lime mud. "Since the wireless system has been installed, we can tell if there's build-up of lime in the mid-zone area," said the Pulp Mill Team Leader, "You can see fluctuation in the temperature, which is an indication of build-up. Overall, we have improved operation of the lime kiln, and increased throughput by 5%." The Pulp Mill Team Leader concluded by saying, "I think it's a pretty good achievement to have two different devices communicating with one Gateway, when they are on opposite sides of a rotating kiln."

RESOURCES

<http://www.emersonprocess.com/smartwireless>

"Since the wireless system has been installed, we can tell if there's a build-up of lime in the mid-zone area. . . . Overall, we have improved operation of the lime kiln, and increased throughput by 5%."

Pulp Mill Team Leader

Rosemount and the Rosemount logotype are registered trademarks of Rosemount Inc. All other marks are the property of their respective owners.

Standard Terms and Conditions of Sale can be found at www.rosemount.com/terms_of_sale

Emerson Process Management

Rosemount Division
8200 Market Boulevard
Chanhassen, MN 55317 USA
T (U.S.) 1-800-999-9307
T (International) (952) 906-8888
F (952) 949-7001

www.rosemount.com

Emerson Process Management

Heath Place
Bognor Regis
West Sussex PO22 9SH,
England
T 44 1243 863121
F 44 1243 867554

Emerson Process Management

Emerson Process Management Asia Pacific
Private Limited
1 Pandan Crescent
Singapore 128461
T (65) 6777 8211
F (65) 6777 0947
Enquiries@AP.EmersonProcess.com

ROSEMOUNT®

For more information:
www.rosemount.com

00830-0300-4180, Rev AA


EMERSON™
Process Management