

## KC4011X1-BT1 Simplex 32-Channel DO Plus Terminal Block

### Hazardous Atmosphere



II 3G Ex ec IIC Gc  
FM19ATEX0173U  
IECEX FMG 19.0019U  
FM21UKEX0017U



CL. I Div. 2 GP. A,B,C,D  
CL. I Zone 2 AEx/Ex ec IIC Gc  
FM17CA0145U  
FM17US0286U

### Power Specifications

Field Circuit Rating      24 VDC at 200 mA/Ch

### Environmental Specifications

Ambient Temperature	-40 °C to +70 °C
Shock	10 g half-sine wave for 11 ms
Vibration	1 mm peak to peak from 2 to 13.2 Hz; 0.7 g from 13.2 to 150 Hz
Airborne Contaminants	ISA-S71.04 –1985 Airborne Contaminants Class G3
Relative Humidity	5 to 95% non-condensing
Key position	B4

**Note:** Refer to the product label for serial number and location and date of manufacture.

**Warning:** This product has specific instructions for installation, removal and operation in hazardous areas. Refer to document 12P2046 "*DeltaV™ Scalable Process System Zone 2 Installation Instructions*". Other installation instructions are

available in the "*DeltaV™ S-series and CHARMs Hardware Installation*" manual.

### Removal and Insertion

Terminals Block can be added or removed with System Power applied only when no I/O Card is installed, and no field wiring is connected to the terminal.

A rotary keying system ensures compatibility between I/O cards and terminal blocks after installation is complete. The terminal block must have the keys set for the I/O card with which it is to be used.

### Maintenance and Adjustment

This unit contains no user-serviceable parts and should not be disassembled for any reason. Calibration is not required.

### Other Safety Approvals

