

ATEX Instruction Sheet

Part Number: ATEX15

Publish date: October, 2008

DO 8-Channel 24 VDC Isolated

KJ3208X1-BA1 DO 8-Channel 24 VDC Isolated

Hazardous Atmosphere



II 3G Ex nA IIC Gc
FM12ATEX0090U
IECEX FMG 12.0035U

Power Specifications

Local Bus Power	12 VDC at 150 mA
Field Circuit	60 VDC at 1 A/Channel

Environmental Specifications

Ambient Temperature	-40°C to +70°C
Shock	10g ½ Sinewave for 11msec
Vibration	1mm Peak to Peak from 2 to 13.2Hz; 0.7g from 13.2 to 150Hz
Airborne Contaminants	ISA-S71.04 –1985 Airborne Contaminants Class G3
Relative Humidity	5 to 95% Non-Condensing IP 20 Rating
Terminal Block key Position	B5

Note: Refer to the product label for serial number and location and date of manufacture.

Warning: This product has specific instructions for installation, removal and operation in hazardous areas. Refer to document 12P2046 "*DeltaV™ Scalable Process System Zone 2 Installation Instructions*". Other installation instructions are available in the "*DeltaV™ M-Series Hardware Installation and Reference*" manual.

Removal and Insertion

This unit cannot be removed or inserted with system power energized unless the area is known to be non-hazardous and only one unit at a time may be removed or inserted.

Non-sparking field circuits **MUST** be de-energized before removing and inserting including the fused terminal block.

A rotary keying system ensures compatibility between I/O cards and terminal blocks after installation is complete. The terminal block must have the keys set for the I/O card with which it is used.

Maintenance and Adjustment

This unit contains no user serviceable parts and should not be disassembled for any reason. Calibration is not required.

Other Safety Approvals



CL. 1 Div. 2
GP. A,B,C,D
HAZ. LOC.
TEMP. Rating T4

