Power Company Accurately Measures Air Flow in Large Ducts and Increases Generation Efficiency

RESULTS

- Reduced fuel cost
- Reduced heat rate
- Reduced project cost
- Reduced utility cost
- Increased megawatt generation

APPLICATION

Airflow profile in large rectangular ducts

APPLICATION CHARACTERISTICS

Large diameter rectangular duct with irregular flow profile and short straight run

CUSTOMER

Large power plant in the USA

CHALLENGE

The customer needed a way to accurately measure airflow in order to improve combustion efficiency and reduce emissions. In the past, the power plant was inferring secondary airflow from fan curves. These inferred measurements were only 25 percent accurate at times.

The rectangular duct measured 4-ft. by 5-ft. making traditional measurement technologies, such as nozzles, very expensive. In addition, the large duct cross section and short straight duct runs created high variability in the flow profile across the duct.

Lack of accurate airflow measurement resulted in excess combustion air being used to limit emissions. This lead to excess fuel consumption to heat the excess air. It also reduced combustion temperatures leading to a higher heat rate. In addition, higher airflow rates lead to higher utility costs to run the fans.

SOLUTION

The Rosemount Annubar primary element was introduced as a cost effective way to achieve accurate flow measurement in this difficult application. Because the ducting was large and rectangular, it was recommended that two primary elements be placed parallel to each other across the shorter span of the duct. This would allow a larger section of the flow profile to be sampled.

The flow consultant also recommended that a pitot traverse be performed to determine the true nature of the flow. In certain



The Rosemount[™] Annubar[™] primary element was introduced as a cost effective way to increase megawatt generation and reduce fuel cost.



applications where the duct is irregular or there is a disturbance upstream of the flow element, it is good practice to perform an inline calibration to understand the flow profile and calculate a correct K factor. This involves sampling the flow at multiple points and under varying flow rates using a single point pitot tube. Using this technique, the true nature of the flow profile can be determined.

Using a single point pitot, the field service personnel were able to verify a flow coefficient for the annubar and offer the customer an accuracy of ± 5 percent.


The customer achieved many positive business results, the first of which was a 10 percent reduction in fuel consumption. By reducing excess combustion air, the heat rate was also reduced. Finally, by lowering the demand on the fans, utility costs were reduced and the utility was able to increase megawatt generation to the grid.

RESOURCES

Emerson[™] Power Generation Emerson.com/Industries/Power-Generation **Rosemount Annubar Flowmeter Series** Emerson.com/Rosemount/Rosemount-485-Annubar



Primary elements and the traverse test points in the duct



Emerson Terms and Conditions of Sale are available upon request.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners. © 2018 Emerson. All rights reserved.

- Linkedin.com/company/Emerson-Automation-Solutions in
- 7 Twitter.com/Rosemount_News
- Facebook.com/Rosemount f
- Youtube.com/user/RosemountMeasurement Yas .
- Google.com/+RosemountMeasurement

Middle East and Africa Region Emerson Automation Solutions

Emerson FZE P.O. Box 17033, lebel Ali Free Zone - South 2 Dubai, United Arab Emirates

- +97148118100
- C
 - RFQ.RMTMEA@Emerson.com

Asia Pacific Region Emerson Automation Solutions

1 Pandan Crescent Singapore 128461

+65 6777 8211

- +65 6777 0947
- Enquiries@AP.Emerson.com




Global Headquarters Emerson Automation Solutions


- 6021 Innovation Blvd.
- Shakopee, MN 55379, USA +1 800 999 9307 or +1 952 906 8888
- +1 952 949 7001
- RFQ.RMD-RCC@Emerson.com

00830-0500-4809, Rev DA

Europe Region Emerson Automation Solutions Europe GmbH

Neuhofstrasse 19a P.O. Box 1046





- +41 (0) 41 768 6300
- RFQ.RMD-RCC@Emerson.com

ROSEMOUNT