University Solves Short Piping Problem with Rosemount[™] Compact Orifice Mass Flow Meter

RESULTS

- Reduced welding and installation
- Improved flexibility, accuracy, and reliability
- Improved productivity and bottom line results

APPLICATION

Steam supply for various university campus facilities

CUSTOMER

A major Northeastern U.S. university

CHALLENGE

Operating as a separate business unit, the university's physical plant is responsible not only for supplying steam to various campus facilities, but also for generating operating revenue by billing the facilities for steam consumption.

An assessment of the performance, efficiency, and steam consumption of the university's boiler system revealed inadequate straight runs of piping, which made it difficult to develop necessary flow profiles for an accurate flow measurement.

Originally, the university tried V-cone technology for applications where the required straight piping was not available. However, it failed to provide adequate results and had difficulty dealing with the varying swings of seasonal loads, only adding to the complexity of each measurement point.

The existing piping configuration consisting of two pipe diameters downstream from two out-of-plane 90-degree elbows was giving previous results of +5 percent or worse, making it difficult to get an accurate flow measurement.

SOLUTION

Emerson recommended the new Rosemount Compact Conditioning Orifice Mass Flow Meter. This technology allows installation within two diameters of upstream flow disturbances.



Emerson[™] recommended the new Rosemount Compact Conditioning Orifice Mass Flow Meter. This technology allows installation within two diameters of upstream flow disturbances.



Rosemount Conditioning Orifice Mass Flow Meter installed two pipe diameters after two out-of-plane 90degree elbows.



The Rosemount Compact Orifice Mass Flow Meter combines the Rosemount Compact Orifice with the Rosemount MultiVariable[™] Transmitter into an integrated DP Flow Meter. This fully integrated flow meter eliminated the need for fittings, tubing, adapters, manifolds, and mounting brackets, thereby reducing welding and installation. The Rosemount MultiVariable Compact Flow Meter offered the advantage of mass flow measurement for this steam application and provided true compensated mass flow measurement. The advanced electronics of the Rosemount MultiVariable transmitter dynamically compensates for any density changes due to pressure and temperature variations.

The Compact Orifice is a wafer-style primary that is machined from a single-cast part, integrating the primary element, impulse lines, and manifold to facilitate direct mounting of the Rosemount transmitter. Coupling these two components provides a flexible, accurate, and reliable process measurement solution, while also improving productivity and the bottom line.

To verify that the Rosemount Compact Orifice Flow Meter was reading accurately, it was compared to a compensated orifice plate located 60 diameters downstream. The results showed the Rosemount MultiVariable Transmitter tracked within one percent of the orifice meter, thus illustrating excellent accuracy and repeatability in this difficult piping configuration.

In addition to being extremely satisfied, the University is looking to standardize on the Rosemount Compact Orifice Mass Flow Meter in applications where short piping configuration is involved. They now realize that Emerson is capable of meeting almost any measurement need due to its wide offering of Rosemount DP primaries and DP flow solutions.

RESOURCES

Emerson Power Generation Industry

Emerson.com/Industries/Power-Generation

Rosemount Compact Orifice Flow Meter Series

Emerson.com/Rosemount/Rosemount-405-Conditioning-Orifice-Plate-Primary-Element



Rosemount Orifice Plate (check meter) installed downstream of the Rosemount Compact Orifice Mass Flow Meter.

- in Linkedin.com/company/Emerson-Automation-Solutions
- Twitter.com/Rosemount_News
- Facebook.com/Rosemount
- Youtube.com/user/RosemountMeasurement
- **B** Google.com/+RosemountMeasurement

Middle East and Africa Region Emerson Automation Solutions

Emerson FZE P.O. Box 17033, Jebel Ali Free Zone - South 2 Dubai, United Arab Emirates

- +97148118100
- +971 4 8865465
 - RFQ.RMTMEA@Emerson.com

Asia Pacific Region Emerson Automation Solutions

1 Pandan Crescent Singapore 128461

+65 6777 8211

- +65 6777 0947
- Enquiries@AP.Emerson.com



Emerson Terms and Conditions of Sale are available upon request. The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners. © 2018 Emerson. All rights reserved.

Global Headquarters Emerson Automation Solutions

6021 Innovation Blvd.

- Shakopee, MN 55379, USA
- +1 800 999 9307 or +1 952 906 8888
- +1 952 949 7001
- C RFQ.RMD-RCC@Emerson.com

00830-0100-4810, Rev CA

Europe Region Emerson Automation Solutions Europe GmbH

Neuhofstrasse 19a P.O. Box 1046



- +41 (0) 41 768 6111
- +41 (0) 41 768 6300
- RFQ.RMD-RCC@Emerson.com

ROSEMOUNT