

# **High-Shock Manual Reset Valves**

Brass and Stainless Steel Bodies 3/8" NPT

#### **Features**

- Once the solenoid is de-energized, it requires power to be restored to the solenoid then the valve to be manually reset. Ideal for controlling critical processes
- Designed to meet vibration and/or shock per ISA specification S71.03C2
- Handles aggressive atmosphere per salt resistance testing (ASTM B117)
- Most hardware is stainless steel, and all aluminum components are hard anodized and Nituff® coated
- Manual reset housing is sealed with closed-cell CR sponge rubber and equipped with sintered bronze breather to prevent accumulation of condensation
- Last chance filter installed in auxiliary air port of the pilot valve

Nituff is a registered trademark of Nimet Industries, Inc.

#### Construction

Valve Parts in Contact with Fluids											
Main Valve											
Body	Brass / Stainless Steel										
Disc	303 Stainless Steel										
Seats	Phosphor Bronze										
Springs	17-7 PH Stainess Steel										
Seals	Buna-N / FKM										
Air Operator Diaphragm	FMQ										
Bearing Screw 430 Stainless Steel											
Lever	302 Stainless Steel										
Pilot Valve	AC 10.1 W	DC 1.4 W									
Body	Brass / 303 Stainless Steel	Brass / 303 Stainless Steel									
Shading Coil	Silver / Coper	Not Applicable									
Seals	NBR	Buna-N/PTFE									
Core Tube	305 Stainess Steel	305 Stainess Steel									
Core and Plugnut	430F Stainless Steel	430F Stainless Steel									
Core Guide	CA CA										
Core Springs	302 & 17-7PH Stainess Steel	302 Stainess Steel									

#### **Electrical**

Standard	W		ig and Pov umption	wer	Spare Coil Part Number					
Coil and			AC		General	Purpose	Explosi	onproof		
Class of	DC		VA	VA						
Insulation	Watts	Watts	Holding	Inrush	AC	DC	AC	DC		
F	-	10.1	25	76	238610	-	238614	-		
F	1.4	-	-	-	-	-	274714-	902-D*		

Standard Voltages: 24, 120, 240, 480 volts AC, 60 Hz. 12, 24 volts DC. Must be specified when ordering. \* 24 VDC. For other voltages contact factory.


#### Solenoid Enclosures


Standard: Explosionproof and Watertight, Types 3, 3S, 4, 4X, 6, 6D, 7, and 9.

### **Approvals**

CSA certified and UL listed General Purpose Valve (pilot).

ATEX/IECEx certified with prefix "EV" as listed. Refer to Optional Features Electrical Section for details.





### **Options**

Position indicator switch (suffix SP); Redundant pilot valves.

Contact factory for ordering information.

### **Operation Alternatives**

Electrically Tripped - With the pilot valve solenoid deenergized, the handle is raised manually and latches the operator in the "up" (latched) position. Upon energizing the pilot valve solenoid, the latch is tripped returning the operator to the "down" (unlatched) position.

No Voltage Release – With the pilot valve solenoid energized, the handle is raised manually and latches the operator in the "up" (latched) position. Upon loss of voltage, the latch is tripped returning the operator to the "down" (unlatched) position.

Once tripped, the lever may be cycled causing the valve discs to open and close.



# **Specifications (English units)**

Pipe Size	Orifice Size	Cv Flow		Operating Pressure Differential (psi)		Fluid Max. Temp. °F Ambien		Max. Ambient	Catalog	Const.			Watt Rating/ Class of Coil Insulation per Solenoid	
(in)	(in)	Factor	Pilot Min.	Pilot Max.	Main Max.	Min.	Max.	Temp. °F	Number	Ref.	Body Material	Pilot Construction	AC	DC
3/2 High-Shock Manual Reset Valves														
3/8	1/4	0.45	25	125	125	-40	140	140	EV8308G385 ①	1	Brass	No Voltage Release (NVR)	-	1.4/F
3/8	1/4	0.45	25	125	125	-40	140	140	EV8310G385 ①	1	Brass	Electrically Tripped (TSO)	-	1.4/F
3/8	1/4	0.45	25	125	125	-4	200	125	EV8308G085 ①	1	Brass	No Voltage Release (NVR)	10.1/F	-
3/8	1/4	0.45	25	125	125	-4	200	125	EV8310G085 ①	1	Brass	Electrically Tripped (TSO)	10.1/F	-
3/8	1/4	0.45	25	125	125	-40	140	140	EV8308G386 ①	2	Stainless Steel	No Voltage Release (NVR)	-	1.4/F
3/8	1/4	0.45	25	125	125	-40	140	140	EV8310G386 ①	2	Stainless Steel	Electrically Tripped (TSO)	-	1.4/F
3/8	1/4	0.45	25	125	125	-4	200	125	EV8308G086 ①	2	Stainless Steel	No Voltage Release (NVR)	10.1/F	-
3/8	1/4	0.45	25	125	125	-4	200	125	EV8310G086 ①	2	Stainless Steel	Electrically Tripped (TSO)	10.1/F	-


① ATEX/IECEx certified with prefix "EV".

# **Specifications (Metric units)**

Pipe Size	Orifice Size	Kv Flow Factor		erating Pres ifferential (b		Fluid Max. Temp. °C Ambient		Catalog	Const.			Watt Rating/ Class of Coil Insulation per Solenoid		
(in)	(in)	$(m^3/h)$	Pilot Min.	Pilot Max.	Main Max.	Min.	Max.	Temp. °F	Number	Ref.	Body Material	Pilot Construction	AC	DC
3/2 Hig	3/2 High-Shock Manual Reset Valves													
3/8	1/4	0.39	1.7	9	9	-40	60	60	EV8308G385 ①	1	Brass	No Voltage Release (NVR)	-	1.4/F
3/8	1/4	0.39	1.7	9	9	-40	60	60	EV8310G385 ①	1	Brass	Electrically Tripped (TSO)	-	1.4/F
3/8	1/4	0.39	1.7	9	9	-20	93	52	EV8308G085 ①	1	Brass	No Voltage Release (NVR)	10.1/F	-
3/8	1/4	0.39	1.7	9	9	-20	93	52	EV8310G085 ①	1	Brass	Electrically Tripped (TSO)	10.1/F	-
3/8	1/4	0.39	1.7	9	9	-40	60	60	EV8308G386 ①	2	Stainless Steel	No Voltage Release (NVR)	-	1.4/F
3/8	1/4	0.39	1.7	9	9	-40	60	60	EV8310G386 ①	2	Stainless Steel	Electrically Tripped (TSO)	-	1.4/F
3/8	1/4	0.39	1.7	9	9	-20	93	52	EV8308G086 ①	2	Stainless Steel	No Voltage Release (NVR)	10.1/F	-
3/8	1/4	0.39	1.7	9	9	-20	93	52	EV8310G086 ①	2	Stainless Steel	Electrically Tripped (TSO)	10.1/F	-

① ATEX/IECEx certified with prefix "EV".

# Flow Diagrams





### **Dimensions inches (mm)**

