

ACCESSORIES

side mounting brackets	top mounting bracket		assembly kit	G1/4 exhaust silencer		key locking device
O'6 (70)	Bracket Ring		C.	bronze	Plastic	
34307017	34307016	34307015	34307005	34600002	34600407	34303050

dia. 50 mm pressure gauge - G1/8			mounting on pipe		mounting with brackets	
			set of 2 connecting flanges		set of 2 connecting flanges + 2 adapters	
1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1						
0-4 bar	0-12 bar	0-16 bar	G 1 1/4	G 1 1/2	G 1 1/4	G 1 1/2
34200061	34200062	34200997	34307014	34307018	34307065	34307066

■ SIDE MOUNTING BRACKETS


Side mounting brackets are for surface mounting of any of the air treatment components, i.e. isolation valve, filter, regulator, filter/regulator, lubricator, shut-off valve and soft-start unit, and 0,01 µm filter systems.

For G 1 1/4 and G 1 1/2 versions, use the set of flanges 34307065 - 34307066 (see following page for flange assembly).

CONSTRUCTION

Brackets : steel Retaining screws : steel

Weight of brackets: 0,365 kg



■ TOP MOUNTING BRACKET


The top mounting ring and bracket fit the filter/regulator and regulator. These accessories enable surface mounting of the components. The mounting ring can be used separately for panel mounting of a regulator.


CONSTRUCTION

Bracket : steel

Ring : aluminium alloy

Weight: 0,4 kg






■ TWO-PART ASSEMBLY KIT

This kit enables assembly of two components of the same range.

COMPOSITION

- 2 assembly yoke
- 1 intercomponent seal

Weight: 0,02 kg



rights reserved.




■ KEY LOCK

This accessory is used to lock the adjustment knob to prevent inadvertent adjustment of operating pressure. It can be fitted to regulators, filters/regulators, and shut-off valve and soft-start units.

CONSTRUCTION

Plastic lock body rotatable through 360° Supplied with two 2 Euro Locks no. 801 keys

Weight: 0,017 kg




■ PRESSURE GAUGE


G1/8 rear centre connection Fits all versions of regulators and filters/regulators

OVERALL SPECIFICATION

PORTS : G 1/8 tapered DIAMETER : 50 mm GRADUATIONS : bar and psi

Weight: 0,07 kg





Manuel installation recommended. Make sure other unused ports are sealed off on installation.

■ CONNECTING FLANGE FOR G1 1/4 AND G1 1/2 VERSIONS

The G 1 $\frac{1}{2}$ and G 1 $\frac{1}{2}$ versions are each supplied with 2 connecting flanges, one for each end of the Modulair unit. To assembly several components together, select G 1 components and provide for 1 set of G 1 $\frac{1}{2}$ or G 1 $\frac{1}{2}$ flanges. The components are directly mounted to the pipe with or without the brackets. The overall dimensions are those of the G 1 version plus the dimensions of the two flanges.

Weight of flanges: 0,55 kg

