

The manufacturer may use the mark:



Revision 3.0 September 30, 2022 Surveillance Audit Due June 1, 2025



# Certificate / Certificat Zertifikat / **合格証**

ASC 1301001 C003

exida hereby confirms that the:

Series 8320 Solenoid Valves

ASCO, L.P. Florham Park, NJ - USA

Has been assessed per the relevant requirements of:

IEC 61508 : 2010 Parts 1-2 and meets requirements providing a level of integrity to:

## Systematic Capability: SC 3 (SIL 3 Capable)

## Random Capability: Type A, Route 2<sub>H</sub> Device

PFH/PFD<sub>avg</sub> and Architecture Constraints must be verified for each application

### Safety Function:

The Valve will move to the designed safe position when deenergized / energized within the specified safety time.

### **Application Restrictions:**

The unit must be properly designed into a Safety Instrumented Function per the Safety Manual requirements.



Evaluating Assessor

1KA-7

Certifying Assessor

Page 1 of 2

# Certificate / Certificat / Zertifikat / 合格証 ASC 1301001 C003

# Systematic Capability: SC 3 (SIL 3 Capable)

Random Capability: Type A, Route 2<sub>H</sub> Device

PFH/PFD<sub>avg</sub> and Architecture Constraints must be verified for each application

#### Systematic Capability :

These products have met manufacturer design process requirements of Safety Integrity Level (SIL) 3. These are intended to achieve sufficient integrity against systematic errors of design by the manufacturer.

A Safety Instrumented Function (SIF) designed with these products must not be used at a SIL level higher than stated.

#### Random Capability:

The SIL limit imposed by the Architectural Constraints must be met for each element. This device meets *exida* criteria for Route  $2_{H}$ .

#### Versions:

Valve Types	Description and Application
8320, FT/HT Coil, NC, DTT	8320, FT/HT Coil (6.1-16 Watts), NC (Normally Closed), De-
	energize To Trip (DTT)
8320, FT/HT Coil, NC, ETT	8320, FT/HT Coil (6.1-16 Watts), NC (Normally Closed),
	Energize To Trip (ETT)
8320 Other Coil Options, DTT	Adder for 16-30 Watts Class H Coils, DTT Application
8320 Other Coil Options, ETT	Adder for 16-30 Watts Coils, ETT Application
8320 Manual Operator, DTT	Adder for Manual Operator Option, DTT Application
8320 Manual Operator, ETT	Adder for Manual Operator Option, ETT Application

#### IEC 61508 Failure Rates in FIT<sup>1</sup>

Device / Configuration	$\lambda_{SD}$	λ <sub>su</sub>	$\lambda_{DD}$	λ <sub>DU</sub>
8320, FT/HT Coil (<16 Watts), NC, DTT	0	411	0	88
8320, FT/HT Coil (<16 Watts), NC, ETT	0	33	0	213
Adder for HB Coils <sup>2</sup> 16-30 Watts, DTT	0	430	0	0
Adder for FB/HB Coils 16-30 Watts, ETT	0	0	0	93
Adder for MO or MS Option, DTT	0	42	0	3
Adder for MO or MS Option, ETT	0	3	0	42

<sup>1</sup> FIT = 1 failure /  $10^9$  hours

<sup>2</sup> Failure Rate Adders for other Coil Options available from ASCO

#### **SIL Verification:**

The Safety Integrity Level (SIL) of an entire Safety Instrumented Function (SIF) must be verified via a calculation of PFH/PFD<sub>avg</sub> considering redundant architectures, proof test interval, proof test effectiveness, any automatic diagnostics, average repair time and the specific failure rates of all products included in the SIF. Each element must be checked to assure compliance with minimum hardware fault tolerance (HFT) requirements.

The following documents are a mandatory part of certification:

Assessment Report: ASC 13-01-001 R001 V4 R1 (or later)

Safety Manual: V9629 Rev JC (or later)



80 N Main St Sellersville, PA 18960

T-061, V5R2

## Series 8320 Solenoid Valves