



PENBERTHY SUBMERSIBLE AUTOMATIC SUMP DRAINERS

Reliable, fail-safe units that create a powerful pumping action by using either water or saturated steam as the operating medium, without electricity



FEATURES

- Durable construction for long life.
- Simple, virtually maintenance-free design.
- No need for electricity.
- No moving parts in jet pump to wear out.
- Low initial cost.
- Easy installation.

GENERAL APPLICATION

Applications for these models include sump evacuation, steam service and boiler room operations, general manufacturing installations, in-plant services and manufacturing processes of many types.

TECHNICAL DATA

Materials:	Bronze, copper, brass and stainless steel
Pipe connections	
Inlet:	3/4" (DN 20)
Outlet:	1 1/4" (DN 32)
Pressures:	to 200 psig (13.79 barg)
Temperatures:	-20 to 400°F (-29 to 204°C)

PENBERTHY SUBMERSIBLE AUTOMATIC SUMP DRAINERS

PRODUCT OVERVIEW

Penberthy submersible automatic sump drainers provide practical solutions in environments with limited access and no electrical service (such as maintenance pits for underground cable, wiring or piping). They function effectively in either primary pumping operations or on standby to operate when electrical failure occurs. The units cannot be flooded, require minimal upkeep and are unaffected by power outages.

Capitalizing on a time-proven design, these units are available in either a space-saving non-loop design or an efficient loop configuration. There are four models:

- Model 2R-W is non-loop and operates with a liquid motive.
- Model 2R-WL is a loop design that operates with a liquid motive.
- Model 2R-S is non-loop and uses a steam motive.
- Model 2R-SL is a loop design that operates with a steam motive.

Their operation is simple. A copper float, rising with the water level, slides on a center tube to activate a low-friction valve automatically which 'turns the pump on'.


TABLE 1 - MODEL SPECIFICATIONS: 2R-W, 2R-WL - inches (mm)

Model	Pipe connect		High water	Drainer diam.	Drainer height	Max. pump down range
	Outlet	Inlet				
2R-W	1¼" (31.8)	¾" (19.1)	13½" (343)	12⅞" (327)	20" (508)	5" (127)
2R-WL	1¼" (31.8)	¾" (19.1)	13½" (343)	14¾" (375)	20" (508)	5" (127)

TABLE 2 - MODEL SPECIFICATIONS: 2R-S, 2R-SL - inches (mm)

Model	Pipe connect		High water	Drainer diam.	Drainer height	Max. pump down range
	Outlet	Inlet				
2R-S	1¼" (31.8)	¾" (19.1)	13½" (343)	12⅞" (327)	20" (508)	5" (127)
2R-SL	1¼" (31.8)	¾" (19.1)	13½" (343)	14¾" (375)	20" (508)	5" (127)

MODEL SHOWN - 2R - SL



PENBERTHY SUBMERSIBLE AUTOMATIC SUMP DRAINERS

PERFORMANCE

TABLE 3 - 2R-W/2R-WL CAPACITIES: gph (lph) OF SUCTION FLOW

Model	Discharge head in feet (meters)	Operating water pressure psig (kPag)									
		10 (69)	15 (103)	20 (138)	30 (207)	40 (276)	60 (414)	80 (552)	100 (689)	120 (827)	150 (1034)
2R-W	5 (1.5)	216 (817)	308 (1165)	417 (1578)	547 (2070)	668 (2529)	837 (3168)	1071 (4053)	1008 (3815)	999 (3781)	984 (3724)
	6 (1.8)		302 (1143)	401 (1517)	514 (1945)	740 (2600)	938 (3551)	1060 (4012)	1008 (3815)	999 (3781)	984 (3724)
	9 (2.7)				403 (1525)	559 (2115)	803 (3034)	1048 (3466)	1008 (3815)	999 (3781)	984 (3724)
	12 (3.7)					452 (1710)	702 (2657)	820 (3103)	1008 (3815)	999 (3781)	984 (3724)
	15 (4.6)						629 (2360)	817 (3092)	966 (3656)	999 (3781)	984 (3724)
	18 (5.5)							709 (2684)	914 (3449)	999 (3781)	984 (3724)
2R-WL	5 (1.5)	240 (908)	342 (1294)	463 (1752)	608 (2301)	742 (2808)	930 (3520)	1190 (4504)	1120 (4239)	1110 (4201)	1093 (4137)
	6 (1.8)		335 (1267)	446 (1688)	571 (2161)	822 (3112)	1042 (3943)	1178 (4498)	1120 (4239)	1110 (4201)	1093 (4137)
	9 (2.7)			273 (1033)	448 (1695)	621 (2350)	892 (3376)	1164 (4405)	1120 (4239)	1110 (4201)	1093 (4137)
	12 (3.7)				321 (1214)	502 (1400)	780 (2952)	1022 (3868)	1120 (4239)	1110 (4201)	1093 (4137)
	15 (4.6)					344 (1302)	684 (2588)	908 (3436)	1073 (4061)	1110 (4201)	1093 (4137)
	18 (5.5)					207 (783)	542 (2051)	788 (2982)	1015 (3841)	1107 (4149)	1093 (4137)

TABLE 4 - WATER CONSUMPTION - gph (lph)

Model	Operating water pressure, psig (kPag)									
	10 (69)	15 (103)	20 (138)	30 (207)	40 (276)	60 (414)	80 (552)	100 (689)	120 (827)	150 (1034)
2R-W	135 (510)	165 (624)	180 (681)	225 (851)	255 (965)	300 (1135)	345 (1305)	390 (1476)	420 (1599)	471 (1782)
2R-WL	135 (510)	165 (624)	180 (681)	225 (851)	255 (965)	300 (1135)	345 (1305)	390 (1476)	420 (1599)	471 (1782)

TABLE 5 - 2R-S/2R-SL CAPACITIES: gph (lph) OF SUCTION FLOW

Model	Discharge head in feet (meters)	Operating steam pressure psig (kPag)									
		10 (69)	15 (103)	20 (138)	30 (207)	40 (276)	60 (414)	80 (552)	100 (689)	120 (827)	150 (1034)
2R-S	5 (1.5)	249 (942)	409 (1548)	524 (1983)	696 (2635)	940 (3557)	1044 (3951)	1035 (3917)	990 (3747)	963 (3644)	904 (3421)
	6 (1.8)		383 (1449)	476 (1801)	644 (2437)	862 (3262)	1040 (3936)	1035 (3917)	944 (3573)	963 (3614)	904 (3421)
	9 (2.7)				562 (2127)	721 (2728)	1026 (3883)	1040 (3936)	998 (3777)	963 (3614)	904 (3421)
	12 (3.7)					557 (2108)	880 (3330)	1042 (3943)	990 (3747)	945 (3576)	904 (3421)
	15 (4.6)						703 (2660)	1038 (3928)	990 (3747)	945 (3576)	904 (3421)
	18 (5.5)							873 (3304)	988 (3739)	864 (3270)	904 (3421)
2R-SL	5 (1.5)	328 (1241)	454 (1748)	582 (2202)	773 (2925)	1044 (3951)	1160 (4390)	1150 (4352)	1100 (4163)	1070 (4049)	1005 (3803)
	6 (1.8)		437 (1654)	529 (2002)	715 (2706)	958 (3626)	1158 (4383)	1140 (4314)	1104 (4178)	1070 (4049)	1005 (3803)
	9 (2.7)				625 (2365)	801 (3031)	1140 (4314)	1155 (4371)	1109 (4197)	1070 (4049)	1005 (3803)
	12 (3.7)					619 (2342)	978 (3701)	1158 (4383)	1100 (4163)	1050 (3974)	1005 (3803)
	15 (4.6)						781 (2956)	1154 (4367)	1100 (4163)	1050 (3974)	1005 (3803)
	18 (5.5)							970 (3671)	1098 (4195)	1050 (3974)	1005 (3803)

TABLE 6 - STEAM CONSUMPTION - lbs./min. (kg/min.)

Model	Operating steam pressure psig (kPag)									
	10 (69)	15 (103)	20 (138)	30 (207)	40 (276)	60 (414)	80 (552)	100 (689)	120 (827)	150 (1034)
2R-S	0.47 (0.21)	0.59 (0.27)	0.69 (0.31)	0.89 (0.4)	1.1 (0.5)	1.46 (0.66)	1.84 (0.83)	2.21 (1.0)	2.59 (1.2)	3.14 (1.4)
2R-SL	0.54 (0.24)	0.66 (0.30)	0.77 (3.50)	0.99 (0.45)	1.2 (0.54)	1.62 (0.73)	2.04 (0.93)	2.46 (1.1)	2.88 (1.3)	3.5 (1.6)

NOTE

** All suction flow rates are based on water at 70°F (21°C)

PENBERTHY SUBMERSIBLE AUTOMATIC SUMP DRAINERS

SELECTION GUIDE

To determine the correct submersible automatic sump drainer, make note of the required specification data listed below. Use the capacity and consumption tables to determine the optimum submersible automatic sump drainer for your application.

Motive

- Water or steam
- Pressure (available)
- Flow rate (available volume)

Suction

- Required pumping capacity

Discharge

- Pressure or discharge head (that unit must overcome)

SELECTION GUIDE

Example:	2R	- W	L	- 01
Model				
2R	2R submersible automatic sump drainer			
Operating medium				
W	Water			
S	Steam			
Loop				
-	Without loop			
L	With loop			
Variation				
01	Catalog standard			

Neither Emerson, Emerson Automation Solutions, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Penberthy is a mark owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. Emerson Automation Solutions, Emerson and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson.com/FinalControl