

ALUMINIUM TANK SYSTEM 8" (Ø200)

NC



FEATURES

- Tank system using aluminium profile and end covers with CE approval according to Pressure Equipment Directive 2014/68/EU, modules B1+D
- For use in dust collector applications requiring high flow capacity and accurate
- Full immersed valve system with polychloroprene (CR) diaphragm design offers highest peak pressure and best flow performance
- The high quality polychloroprene (CR) diaphragm guarantees a long operating life and a large temperature range
- Possibility to apply different combinations of pitch distances and up to 18 valves
- Easy to connect to other tank systems. Service connections for different accessories such as: filter regulator, pressure gauge, safety valve and automatic/manual drain valve
- Several blow pipe connections available, such as: Quick Mount, push-in, hose or male or female threaded
- Tanks are available in a direct control valve version with a selection of coil systems and voltages or as a remote control, single or double diaphragm version for external pilot valves or pilot boxes
- The integral operators are provided with epoxy moulded F-class coils. Various optional explosionproof solenoids for use in potentially explosive atmospheres according to Directive ATEX 2014/34/EU, Zones 21+22 can be mounted



Pressure inlet connection ISO 228/1, G 1 1/2" female Air operating pressure min. 1,0 max. 8,0 bar

Safety pressure 12.2 bar

Flow rate Kv 43,3 = 724 l/min -20°C to +85°C Ambient temperature range

Tank System

0,314 dm3 / cm volume

recommended min. tank volume 15 dm³

min. pitch distance end cap 110 mm for bracket 120 mm;

between valve 160 mm

maximum length 3000 mm

The tank system can be mounted in any position without affecting operation

fluids	temperature range (TS)	diaphragm		
air	-20 to +100 °C	CR (polychloroprene)		

CONSTRUCTION

Anodised aluminium profile EN AW-6060 T66 Tank Die-cast aluminium GD-ALSi12 to EN 1706 Valve, outlet adapter **End caps** Die-cast aluminium GD-ALSi12 to EN 1706

Stainless steel Spring Plugs PA (polyamide) NBR (nitrile) Sealings & disc Screws Steel 8.8

CR (optionally FPM or TPE) Diaphragm Mounting brackets stainless steel AISI 304 (1.4301)

Shading coil Copper

ELECTRICAL CHARACTERISTICS Coil insulation class

Connector Spade plug (cable Ø 6-10 mm)

Connector specification 3 x DIN 46244 **Electrical safety** IEC 335 Standard voltages DC (=): 24V

(Other voltages and 60 Hz on request) AC (~): 24V - 120V - 230V / 50 Hz

Γ	coil type	nominal power ratings				operator		replacement coil	
		inrush ~		ding	hot/cold =	temperature range (TS)	protection	~	=
İ		(VA)	(VA)	(W)	(W)	(°C)		230 V/50 Hz	24 V DC
ſ	RHII-MXX-FT	55	23	10,1	-	-20 to +85	moulded IP65	238613-159	-
ì [RHII-MXX-FB	-	-	-	15 / 22,6			-	238713-106






ALUMINIUM TANK SYSTEM

0000

F1

HOW TO ORDER



Voltage - class

F1 = 24 DC - Class F = 24/50 - Class F = 230/50-60 - Class F FΗ

= 120/60 - Class F F2 = All remote valves no voltage required

Dimensions and option code

Consult our Dynamic Product Modeling Tool on: www.asconumatics.eu Mounting brackets (2 or 3) depending on total weight

Silencer for double stage valves

Pitch/dimensions

Dimension code for distance between valves, end caps and mounting brackets is determined by ASCO

Actuation

- 1 = Remote single stage prepared for pilot box, incl. brackets; push in fittings; plastic tube
- = Remote double stage prepared for pilot box, incl. brackets; push in fittings; plastic tube
- 3 = Remote control single stage
- = Remote control double stage
- = Remote single stage prepared for pilot box ATEX II G/D
- = Remote double stage prepared for pilot box ATEX II G/D
- = Remote control single stage ATEX II G/D
- = Remote control double stage ATEX II G/D
- = Solenoid operators SC IP65 ISO 4400
- = Solenoid operators SG ATEX 3D
- = Solenoid operators NF ATEX 2G/D N
- = Solenoid operators EM ATEX 2G/D
- = Solenoid operators PV ATEX 2G/D
- = Solenoid operators EF NEMA 7+9 ICS-6 ANSI

For more technical information see catalogue page "OPERATORS"

Number of valve stations

W = Push-in without clamps

U = Male hose connection

M = Male thread connection

F = Female thread connection

1 = 1

= 10

В = 11

С = 12

D = 13


Ε = 14 F


= 15 G = 16


Н = 17


= 18


OUTLET CONNECTION TYPES











SPARE PARTS KITS

designation	spare parts kit no.				
Double remote operated valve	C113826				
Solenoid operated valve	C113827				
Spare parts for valve sealings	M200336A00 M200337A00				
Spare parts kit for pilot box mounting brackets					
Fastening kit	P355BA433942001				



ORDERING INFORMATION

DIMENSIONS (mm), WEIGHT (kg), VOLUME (I)




Solenoid operated valve system

including spade plug connector ISO 4400, IP65, IEC 335

Fig. 1 (front view)

Fig. 2 (side view)



Example I: Dimension code for a 5 solenoid operated valve 24 DC tank system with push-in outlet:

Start distance A = 125 mm

Standard pitch P = 1+2+3+4 = 175 mm

End distance B = 125 mm**Total dimension** 950 mm Weight 27 kg Volume 26 I

Order number G355B8W5S0015F1

For assistance please consult our website: www.asconumatics.eu



ORDERING INFORMATION


DIMENSIONS (mm), **WEIGHT** (kg), **VOLUME** (l)



Remote double staged operated valve system prepared for pilot box

including pilot box mounting brackets, push-in fittings and tubes for G 1/8" pilot box series 110

Fig. 1 (front view) Fig. 2 (side view)



Example II: Dimension code for a 6 double remote operated valve tank system prepared for pilot box with clamp outlet:

Start distance $A = 137 \, \text{mm}$

Standard pitch P = 1+2+4+5 = 190 mm

Deviating pitch P = 3 = between valve 3 and 4 = 260 mm

End distance $B = 137 \, mm$ **Total dimension** 1294 mm Weight 34 kg Volume 37 I

Order number G355B8K62001600

For technical information on ASCO pilot boxes see catalogue series 110

For assistance please consult our website: www.asconumatics.eu

OPTIONS

- Special customised executions
- Valve can be supplied with FPM (fluoroelastomer) and TPE (thermoplastic polyester elastomer) diaphragms.
- Waterproof enclosures with embedded screw terminal coil according to protection class IP67, CEE 10
- Explosion proof solenoids for hazardous locations according to "ATEX" and national standards
- Explosion proof and watertight solenoids according to "NEMA" standards
- Separate Quick Mount clamps for outlet connection; kit number: C117-290

INSTALLATION

- The tank system can be mounted in any position using the standard brackets (M8 bolts recommended) without affecting
- Pipe connection identifier is: G = according to ISO 228/1 and ISO 7/1, or Ø for other outlet connections
- For Quick Mount types tightness is achieved by the O-ring sealing on the pipe (1 1/2" = Ø47,8 to 48,8) according to ISO 4200.
- When connecting piping or tubing to the G 1/8" or G 1/4" connection in the valve bonnet, the remote ASCO pilot valve should be mounted as close as possible to the main pulse valve. Connection tubing lengths of 3 meters or less have little effect on the pulse response. Installations with over 3 meters of tubing must be tested under actual operating conditions. Tubing with Ø6 or Ø8 mm O.D. is recommended for all installations.
- Installation/maintenance instructions and declaration of conformity are included with each tank system.
- Spare parts kits and coils are available.